

CENTRAL Transistors



SMALL SIGNAL TRANSISTORS - LEADED

Transistors
Central

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Central Part No.	Package	h _{FE}		f _T (MHz)	Price Each				
			Min.	Max.		1	25	100	250	
NPN Small Signal Transistors										
610-2N3866	2N3866	TO-39	10	200	500	1.82	1.77	1.69	1.63	
610-2N4427	2N4427	TO-39	10	200	500	2.21	2.14	2.06	1.98	
610-2N918	2N918	TO-72	20	---	600	1.04	1.01	.97	.93	
610-2N1480	2N1480	TO-39	20	60	1.5	2.32	2.25	2.16	2.07	
610-2N1700	2N1700	TO-39	20	80	---	1.96	1.81	1.67	1.53	
610-2N5785	2N5785	TO-39	20	100	1	1.85	1.64	1.48	1.39	
610-2N2925	2N2925	TO-92	25	235	160	.33	.20	.14	.13	
610-2N5179	2N5179	TO-72	25	250	900	1.10	1.07	1.02	.98	
610-2N708	2N708	TO-18	30	120	400	.71	.59	.53	.48	
610-2N2845	2N2845	TO-18	30	120	250	1.24	1.10	.99	.94	
610-2N2857	2N2857	TO-72	30	150	1000	1.89	1.80	1.72	1.65	
610-2N3014	2N3014	TO-18	30	120	350	.80	.74	.68	.62	
610-2N3114	2N3114	TO-39	30	120	40	2.58	2.51	2.41	2.31	
610-2N3706	2N3706	TO-92	30	600	100	.23	.21	.19	.17	
610-2N3839	2N3839	TO-72	30	150	1000	1.19	1.09	.99	.89	
610-2N4237	2N4237	TO-39	30	150	2	1.98	1.82	1.65	1.49	
610-2N4238	2N4238	TO-39	30	150	2	2.81	2.73	2.62	2.51	
610-2N5109	2N5109	TO-39	30	90	60	1.87	1.81	1.74	1.67	
610-2N5225	2N5225	TO-92	30	600	50	.29	.26	.24	.22	
610-2N5772	2N5772	TO-92	30	120	350	.23	.21	.20	.18	
610-2N1481	2N1481	TO-39	35	100	1.5	1.78	1.64	1.51	1.39	
610-2N697A	2N697A	TO-39	40	120	50	1.28	1.19	1.04	.90	
610-2N718A	2N718A	TO-18	40	120	60	.72	.67	.63	.58	
610-2N1613	2N1613	TO-39	40	120	60	.79	.76	.73	.70	
610-2N2218A	2N2218A	TO-39	40	120	250	.98	.95	.91	.87	
610-2N3020	2N3020	TO-39	40	120	250	.61	.54	.49	.42	
610-2N3420	2N3420	TO-39	40	120	40	2.96	2.87	2.76	2.65	
610-2N3421	2N3421	TO-39	40	120	40	2.64	2.42	2.20	1.98	
610-2N4895	2N4895	TO-39	40	120	50	5.07	4.97	4.82	4.67	
610-MPSA20	MPSA20	TO-92	40	400	125	.22	.20	.18	.16	
610-MPSA42	MPSA42	TO-92	40	---	50	.25	.15	.14	.13	
610-PN2369A	PN2369A	TO-92	40	120	500	.27	.21	.17	.12	
610-PN3567	PN3567	TO-92	40	120	60	.22	.20	.18	.16	
610-2N3708	2N3708	TO-92	45	660	---	.30	.27	.23	.19	
610-2N2270	2N2270	TO-39	50	200	100	1.31	1.27	1.22	1.17	
610-2N3053	2N3053	TO-39	50	250	100	.76	.74	.71	.68	
610-2N3705	2N3705	TO-92	50	150	100	.23	.21	.19	.17	
610-2N3903	2N3903	TO-92	50	150	250	.18	.12	.10	.09	
610-2N5770	2N5770	TO-92	50	200	800	.35	.32	.28	.25	
610-2N2405	2N2405	TO-39	60	200	50	.77	.74	.71	.69	
610-2N3725A	2N3725A	TO-39	60	150	300	1.60	1.55	1.49	1.43	
610-2N4013	2N4013	TO-18	60	150	300	1.09	.96	.87	.79	
610-2N4410	2N4410	TO-92	60	400	60	.18	.17	.15	.14	
610-2N5550	2N5550	TO-92	60	250	100	.22	.20	.11	.08	
610-MPSH10	MPSH10	TO-92	60	---	650	.35	.32	.28	.26	
610-2N5154	2N5154	TO-39	70	200	70	2.34	2.15	1.95	1.76	
610-2N3416	2N3416	TO-92	75	225	---	.18	.17	.15	.14	
610-2N5551	2N5551	TO-92	80	250	100	.20	.18	.16	.14	
610-2N2923	2N2923	TO-92	90	180	160	.38	.34	.30	.28	
610-2N3393	2N3393	TO-92	90	180	120	.29	.26	.24	.22	
610-MPS6531	MPS6531	TO-92	90	270	---	.29	.17	.12	.11	
610-2N930B	2N930B	TO-18	100	300	45	.55	.46	.41	.38	
610-2N2222A	2N2222A	TO-18	100	300	250	.43	.42	.40	.38	
610-2N2484	2N2484	TO-18	100	500	60	.65	.63	.61	.58	
610-2N3107	2N3107	TO-39	100	300	70	1.15	1.06	.96	.86	
610-2N3501	2N3501	TO-39	100	300	150	2.20	2.13	2.05	1.97	
610-2N3704	2N3704	TO-92	100	300	100	.34	.27	.22	.17	
610-2N3707	2N3707	TO-92	100	400	---	.38	.36	.34	.31	
610-2N3904	2N3904	TO-92	100	300	300	.10	.08	.06	.05	
610-2N4401	2N4401	TO-92	100	300	250	.16	.14	.13	.11	
610-2N5172	2N5172	TO-92	100	500	200	.28	.17	.12	.11	
610-2N5209	2N5209	TO-92	100	300	30	.43	.38	.34	.30	
610-MPS3704	MPS3704	TO-92	100	300	100	.37	.30	.24	.19	
610-MPS3706	MPS3706	TO-92	100	300	100	.34	.32	.29	.27	
610-PN2222A	PN2222A	TO-92	100	300	300	.18	.16	.14	.12	
610-PN3569	PN3569	TO-92	100	300	60	.17	.16	.15	.13	
610-PN3643	PN3643	TO-92	100	300	250	.23	.21	.19	.17	
610-2N2924	2N2924	TO-92	150	300	160	.28	.25	.22	.19	
610-2N3392	2N3392	TO-92	150	300	120	.30	.28	.25	.23	
610-2N3860	2N3860	TO-92	150	300	90	.29	.26	.24	.22	
610-2N5818	2N5818	TO-92	150	300	135	.38	.35	.32	.29	
610-MPS3392	MPS3392	TO-92	150	300	---	.23	.21	.19	.17	
610-PN3565	PN3565	TO-92	150	600	40	.17	.15	.14	.12	
610-PN3566	PN3566	TO-92	150	600	40	.18	.17	.15	.14	
610-2N5961	2N5961	TO-92	170	700	100	.18	.17	.15	.14	
610-2N3415	2N3415	TO-92	180	540	---	.18	.14	.12	.10	

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Central Part No.	Package	h _{FE}		f _T (MHz)	Price Each				
			Min.	Max.		1	25	100	250	
NPN Small Signal Transistors (cont.)										
610-2N3417	2N3417	TO-92	180	540	---	.18	.14	.12	.10	
610-2N3711	2N3711	TO-92	180	660	---	.30	.28	.25	.23	
610-2N4424	2N4424	TO-92	180	540	---	.22	.18	.16	.14	
610-2N5210	2N5210	TO-92	200	600	30	.28	.17	.12	.11	
610-MPS6520	MPS6520	TO-92	200	400	---	.29	.27	.25	.23	
610-2N3117	2N3117	TO-18	250	500	60	1.36	1.16	.99	.84	
610-2N3391A	2N3391A	TO-92	250	500	120	.32	.29	.26	.24	
610-2N5232A	2N5232A	TO-92	250	500	---	.33	.20	.14	.13	
610-MPS6515	MPS6515	TO-92	250	500	---	.27	.22	.17	.14	
610-MPS8097	MPS8097	TO-92	250	5	---	.30	.25	.20	.16	
610-2N5088	2N5088	TO-92	300	900	50	.26	.21	.17	.13	
610-MPS6521	MPS6521	TO-92	300	600	---	.22	.20	.18	.16	
610-2N5089	2N5089	TO-92	400	1200	50	.26	.21	.17	.13	
610-MPSA18	MPSA18	TO-92	500	1500	100	.43	.40	.36	.32	
610-2N5962	2N5962	TO-92	600	1400	100	.24	.22	.20	.18	
610-2N5306	2N5306	TO-92	7000	70000	60	.23	.18	.16	.15	
610-2N5308	2N5308	TO-92	7000	70000	60	.33	.20	.14	.13	
610-MPS5306	MPS5306	TO-92	7000	70000	60	.26	.22	.16	.14	
610-MPSA13	MPSA13	TO-92	10000	---	125	.23	.20	.18	.16	
610-MPSA26	MPSA26	TO-92	10000	---	---	.24	.22	.20	.18	
610-MPSA28	MPSA28	TO-92	10000	---	125	.30	.27	.25	.22	
610-MPSA29	MPSA29	TO-92	10000	---	125	.36	.30	.23	.19	
610-2N6427	2N6427	TO-92	14000	140000	130	.33	.20	.14	.12	
610-2N6426	2N6426	TO-92	20000	200000	---	.36	.22	.18	.15	
610-MPSA14	MPSA14	TO-92	20000	---	125	.25	.15	.14	.13	
610-2N706A	2N706A	TO-18	---	---	---	.62	.57	.53	.49	
PNP Small Signal Transistors										
610-MPSA92	MPSA92	TO-92	25	---	50	.25	.15	.14	.13	
610-2N4208	2N4208	TO-18	30	120	700	1.85	1.79	1.72	1.65	
610-2N4234	2N4234	TO-39	30	150	3	1.65	1.49	1.32	1.22	
610-2N3703	2N3703	TO-92	30	150	100	.23	.21	.19	.17	