

# Supplier Index

## 3

<b>3M™</b>	
Breadboards	2158
Bumpers	1826
Cable Assemblies	1071, 1223, 1231, 2106
Cable Ties	1009
Cleaners	2150-2151
Connectors	1035, 1223, 1231-1234, 1318-1319, 1357-1366, 1409, 1479, 1490-1491, 2106, 2120
Electronics Vacuum	2150
Heat Shrinkable Tubing	1035
IDC Flat Cable	1036-1038, 1409
Kits	1035, 1233, 1490, 2146-2147, 2149-2151, 2158
Sockets	1233-1234, 1318-1319, 1358-1359, 1361-1363, 1365-1366, 1409, 1478-1479, 2158
Static Control	2147-2151
Tape	60, 1009, 1490-1491, 2120, 2146-2147, 2151
Terminals	1490-1491, 2120, 2158
Test & Measurement	1479, 2106, 2149
Tools	1233-1234, 1490, 2106, 2120, 2150
Wire Identification	1009
<b>3M Touch Systems</b>	60

## A

<b>Aavid Thermalloy</b>	1933-1936
<b>Abracon</b>	880, 884-889
<b>Actel</b>	259-261
<b>Adam Tech</b>	1198, 1367
<b>Adda</b>	1918-1920
<b>Advanced Linear Devices (ALD)</b>	291, 350, 509
<b>AEM Inc.</b>	593
<b>AIM</b>	2139
<b>AIM/Cambridge</b>	1076, 1170-1171
<b>Alcoswitch/Tyco Electronics</b>	1561, 1582-1583, 1612-1614, 1646, 1658, 1819
<b>All Sensors</b>	1864-1865
<b>Alpha</b>	
Encoders	1578
Potentiometers	672-677
Switches	1595, 1652, 1664-1665
<b>Alpha Wire</b>	
Coaxial Cable	1042
Communication & Control Cable	1043-1047, 1050-1051
Hook-up Wire & Bus Bar Wire	1052-1053
IDC Flat Cable & Modular Cable	1041
Lacing Cord	1041
Local Area Network (LAN)	1042
Test Lead	1041
Tubing	1025-1030
XTRA-Guard Control Cable	1048-1051
<b>ALPS</b>	
Connectors	1320-1321
Encoders	1577-1579
Multi-Control Devices	1562, 1578
Potentiometers	678-679, 1848
Sensors	1848
Switches	1562-1564, 1575-1579, 1584, 1647
<b>Altech</b>	
Circuit Breakers	1793-1795
Enclosures	1898
Liquid Tight Strain Reliefs	1827
<b>AMP/Tyco Electronics</b>	
Advanced Mezzanine Card	1228
Advanced TCA	1228
AMP-Latch Connectors	1374, 1376-1377
AMPLIMITE	1235-1242
AMPMODU™ Connectors & Headers	1370-1374, 1378-1382
Cable Assemblies	1072, 1225, 1227
CAT 5e Assemblies	1185, 1204, 1225
CHAMP®	1243
Circular Connectors	1204-1205, 1270-1277, 1304
CT	1368-1369
D-Sub Connectors	1235-1243
DIN 41612	1323
Free Height	1228, 1398
Fiber Optic	1226-1227
Hard Metric	1228, 1325-1326
HPI	1368
I/O	1072, 1215-1216, 1228, 1243, 1324-1326, 1374
Industrial Ethernet	1204-1205
Lighting Connectors	1400
Mate-N-Lok	1389-1394, 1400, 2117
Micro-Match	1375
Micro TCA	1228
Mictor	1322
Mini-DIN	1304
Miniature Rectangular Connectors	1396
Modular Connectors	1183-1185
MTA Connectors	1383-1388, 2117
PC/104 and PC/104-Plus	1324

PCI & PCI Express	1322, 1326
Pin & Socket Connectors	1324, 1389-1397, 1399, 2117
Power Connectors	1228, 1271, 1273, 1326, 1344-1346, 1399, 1423
RF Connectors	1144-1152
Sockets	1482
Terminals	937, 1492-1494
Terminal Blocks	1507-1510
Tools	1147-1148, 1185, 1227, 1239, 1241, 1270-1271, 1273-1274, 1345, 1369-1371, 1379-1381, 1386, 1390-1391, 1393-1397, 1399, 1482, 1492-1493, 2117
USB Connectors	1072, 1225
Val-U-Lok	1399
Z-Pack	1325-1326
<b>Amphenol</b>	
44 Series Connectors	1293
97 Series Connectors	1278-1282
Amph-PPM Push/Pull	1290
Between Series Adapters	1153-1154, 1159
C091A/D Series Connectors	1292
Cable	1039-1040
Circular DIN Connectors	1291-1292
Circular Industrial Connectors	1278-1293
D-Sub Connectors	1199, 1244-1245
EcoMate	1291
Fiber Optics	1073-1074
I/O Connectors	1199, 1202-1203, 1213, 1327-1328
Industrial Ethernet, USB, & IEEE	1199-1203
MIL-C-26482 Type Connectors	1284-1287
MIL-C-5015 Type Connectors	1278-1280, 1283
Modular Jacks	1186, 1199
PT Series Connectors	1284-1286
RADSOK®	1288-1289
Rectangular Power	1347
RF Connectors/Tools	1153-1166
Smart Card Connectors	1327-1328
<b>Amprobe</b>	2082-2083
<b>AMSECO</b>	1654, 1948
<b>Amulet Technologies</b>	64
<b>Analogic Technologies</b>	377
<b>Antenova</b>	9
<b>APC</b>	2047
<b>API Delevan</b>	947-949
<b>APEM</b>	1572, 1585-1586, 1614, 1631, 1672
<b>APM Hexseal</b>	1677
<b>Applied Motion</b>	1785-1787
<b>Arcol</b>	645-646
<b>Arcotronics</b>	820
<b>Aries</b>	907, 1480-1481
<b>Artesyn Technologies/Emerson Network Power</b>	
AC Adapters	2034
DC-DC Converters	1964-1966
Power Supplies	1964-1966, 2000, 2034
<b>Astec/Emerson Network Power</b>	
AC Adapters	2027, 2034
Power Supplies	2001, 2027, 2034
<b>Atmel</b>	176-180, 198, 240-241
<b>Ault/SL Power</b>	2028-2029
<b>Autotrol</b>	1787-1788
<b>Avago Technologies</b>	80, 88, 94-96, 152-155, 351, 430, 1730
<b>Avery Dennison</b>	1010-1011
<b>AVX</b>	
Capacitors	
Ceramic	747, 754-765, 804-806
Feed Through	754-755
Film	821-823
Niobium Oxide	847
Supercapacitors	727
Tantalum	847-852, 867, 873
Ceramic Resonators	890
Circuit Protection	548-549, 567
Connectors	
DIN	1329
I/O	1407
IDC	1406-1407
Kits	567, 762, 765, 823
MOVs	567
Oscillators	891
TVS	548-549
<b>Axicom/Tyco Electronics</b>	1696-1697
<b>AXSEM</b>	16

## B

<b>BC Components</b>	(See Vishay)
<b>B&amp;K Precision</b>	
Programmers	237
Test Equipment	2060, 2084-2088
<b>BEI Duncan</b>	1849
<b>Belden</b>	1054-1070, 1075, 1119, 1168
<b>Bellin</b>	2160
<b>BI Technologies</b>	701
<b>Bi-Sonic</b>	1789, 1921

<b>Bivar</b>	90, 142-143
<b>Bomar Interconnect</b>	1119, 1167-1169
<b>Bourns</b>	
Circuit Protection	538-539, 576-577, 587, 594
Dials	666
Diodes	431
Encoders	576-577
Gas Discharge Tubes	1580
Inductors	950-956
Modular Contacts	2067
Power Resistors	635, 647
Resettable Fuses	587
Resistor Networks and Arrays	612-614
Resistors	612-614, 635, 647
Switches	431, 1580, 1672
Trimmers/Pots	665-666, 680-682, 688-693, 702-704
<b>BPS</b>	1906, 2161
<b>Buchanan/Tyco Electronics</b>	1508-1510
<b>Bud</b>	1877-1879, 1884-1887, 1899-1903
<b>Bulgin</b>	
AC Power Inlets/Outlets	1096-1097
Battery Holders	2068
Bluetooth	1210
CAT 5e	1211
Circular	1294-1297
Firewire	1211
Switches	1587
USB	1210
Water Proof Connectors	1210-1211, 1294-1297

## C

<b>C&amp;D Technologies</b>	(See Murata Power)
<b>C&amp;K</b>	
Coded Rotary Switches	1672
DIP/SIP Switches	1659, 1672
Pushbutton Switches	1588-1589
Pushwheel/Thumbwheel Switches	1675
Rocker/Paddle Switches	1634
Rotary Switches	1666, 1672
Slide Switches	1648-1649
Toggle Switches	1615-1616
<b>Caddock</b>	648-649
<b>CalAmp</b>	28
<b>California Eastern Laboratories (CEL)</b>	
Optoelectronics	156-158
RF and Microwave	16, 19, 352-354
Transistors	478-479
<b>Carling Technologies</b>	
Circuit Breakers	1796-1797
Switches	1617, 1631-1633
<b>Catalyst</b>	
DC-DC Analog Converters	293
Digital Pots	292
LED Drivers	84
Memory	242-245
<b>CCS, Inc.</b>	181
<b>Central Semiconductor</b>	432-433, 480-481
<b>Cherry Electrical</b>	
Sensors	1852
Switches	1547-1551, 1572, 1635, 1675
<b>Chicago Miniature (CML)</b>	87-88, 97-104
<b>CI (Continental Industries International)</b>	1728-1729
<b>Cinch</b>	1246-1247, 1348, 1408, 1511
<b>Cincon</b>	
AC Adapters	2030-2031
DC-DC Converters	1958-1963
Power Supplies	1991-1992, 2030-2031
<b>Circuit Works</b>	2145
<b>Cirrus Logic</b>	294-296
<b>Citizen</b>	881, 892-895
<b>Clare</b>	1731
<b>CMD (California Micro Devices)</b>	550-552
<b>Coiltronics</b>	957-964
<b>Condor/SL Power</b>	1993-1999
<b>CONEC</b>	1248-1251
<b>Congatec</b>	52
<b>Connect One</b>	29
<b>Conxall/Switchcraft</b>	1298-1299
<b>Cooper Tools</b>	2120-2121, 2123
<b>Cooper/Bussmann</b>	595-599
<b>Corcom/Tyco Electronics</b>	
Power Entry Modules	1100-1101, 2042
RFI/EMI Filters	1100-1101, 2042-2044
<b>Cornell Dubilier</b>	
Aluminum Electrolytics	707, 718-723, 726
Ceramic Capacitors	812
Film Capacitors	824-827
Mica Capacitors	843-845
Snubber Capacitors	826
Supercapacitors	726
<b>COTO</b>	
Magnetic/Reed/Tilt Switches	1655
Reed Relays	1722-1724
<b>Crouzet</b>	1732-1733

<b>Crydom</b>	1734-1740
<b>Crystek Corporation</b>	896-902
<b>CSB</b>	2055, 2059
<b>CTS</b>	615, 903-904, 1660, 1937
<b>CW Industries</b>	1636, 1650
<b>Cyan</b>	182
<b>Cypress</b>	183-187

## D

<b>Dale</b>	(See Vishay)
<b>Dantona</b>	2057-2058
<b>Datel/Murata Power</b>	
DC-DC Converters	1982-1986
Panel Meters	2074-2076
<b>Davies Molding</b>	1820
<b>Deltron</b>	
Banana Plugs & Jacks	1140
Die Cast Aluminum Boxes	1897
Din Connectors	1130-1131
Punches	2126
<b>Desco</b>	2152-2154
<b>Dialight</b>	87, 105-112
<b>Dielectric Laboratories</b>	766
<b>Digi International</b>	16-19, 30-34
<b>Digital View</b>	61
<b>Diodes Inc.</b>	
Analog ICs	303
Diodes and Rectifiers	297-298, 434-439, 510-511
Power Management	378-379
Transistors	482-486
Voltage Regulators	379
<b>Displaytech</b>	65
<b>DLP Design</b>	13, 35-38
<b>Duracell</b>	2055-2056

## E

<b>E-Switch</b>	
Tactile Switches	1566-1567
Pushbutton Switches	1590-1591
Toggle Switches	1618
Rocker/Paddle Switches	1637
Slide Switches	1650
<b>Eagle-Picher</b>	2066
<b>Eagle Plastic Devices</b>	
Battery Holders	2069-2071
Battery Snaps	2071-2072
Cable Mounting Hardware	1012-1016, 2168
Cable Ties	1012-1013, 1016, 2120
Cases	1895-1897
Copper Clad Boards	1896
Fuse Holders	600-601
Hardware	1012-1016, 1821-1824, 1828-1834, 2168
Hole Plugs	1830
Installation Tool	1012
Kits	600, 1012, 1016, 1833, 2121, 2168
Knobs	1821-1824
Mounting Hardware	1012-1016, 2168
Spacers	1829, 1833, 2168
Tools	601, 1012, 1188, 2120-2121, 2138, 2168
<b>ebm-papst</b>	1922-1927
<b>ECS</b>	905-909
<b>Ecliptek</b>	882
<b>EDAC</b>	1196, 1330-1331
<b>EETools</b>	238
<b>Electronic Assembly</b>	66-67
<b>Electronic Modules/Tyco Electronics</b>	66-67
<b>Electroswitch</b>	1581, 1591, 1618, 1667-1669
<b>Elna</b>	727
<b>Elpac</b>	2032-2033
<b>Emerson Network Power</b>	
Artesyn Technologies	(See Artesyn Technologies)
Astec	(See Astec)
<b>Energizer</b>	2055-2057, 2064-2065
<b>EnerSys</b>	2060
<b>Enpirion</b>	380
<b>EPCOS</b>	568-569, 580-581, 708-710, 729, 828-831, 910, 965-967
<b>Epson</b>	58
<b>Erem</b>	2122
<b>Ericsson</b>	1967-1968
<b>Esico-Triton</b>	2136
<b>ETA-USA</b>	1969, 2002
<b>ETI Systems</b>	667-670
<b>Etec</b>	440
<b>Everlight</b>	113-117, 159
<b>Evox Rifa</b>	730, 832
<b>Extech</b>	2089-2090
<b>EZURIO</b>	8

## F

<b>Fair-Rite</b>	917-918
------------------	---------