

EAGLE PLASTIC DEVICES Nylon Wire Handling Hardware



NYLON CABLE CLAMPS

* Nylon 6/6 For quantities of 2000 and up, call for quote. RoHS Compliant

MOUSER STOCK NO.	Fig.	Dimensions: in.				Price Each		
		D	W	H	E	1	100	1000
Miniature								
561-16A0062	A	.063	.156	.096	.187	.08	.06	.05
561-16A0093	A	.094	.156	.096	.203	.08	.06	.04
561-16A0125	A	.125	.156	.096	.217	.07	.05	.04
561-16A0156	A	.156	.156	.096	.233	.08	.06	.05
561-16A0187	A	.188	.156	.096	.250	.09	.06	.05
561-E0250	A	.250	.281	.128	.337	.13	.09	.08
561-E0375	A	.375	.281	.128	.400	.08	.06	.04
Standard								
561-37B0125	A	.125	.375	.140	.329	.08	.05	.04
561-37B0187	A	.188	.375	.140	.430	.07	.04	.03
561-37B0187E	A	.188	.375	.140	.430	.07	.04	.03
561-37B0250	A	.250	.375	.140	.410	.09	.07	.05
561-37B0312	A	.313	.375	.140	.495	.07	.05	.04
561-37B0375	A	.375	.375	.140	.595	.08	.05	.04
561-37B0437	A	.438	.375	.140	.574	.08	.05	.04
561-37B0500	A	.500	.375	.140	.605	.08	.05	.04
561-37C0187E	A	.188	.375	.167	.378	.07	.04	.03
561-37C0437	A	.438	.375	.167	.574	.08	.05	.04
561-37D0125	A	.125	.375	.203	.329	.07	.04	.03
561-37D0187	A	.188	.375	.203	.400	.07	.04	.03
561-37D0187E	A	.188	.375	.203	.430	.08	.06	.04
561-37D0250	A	.250	.375	.203	.410	.08	.06	.04
561-37D0312	A	.313	.375	.203	.495	.07	.05	.04
561-37D0375	A	.375	.375	.203	.595	.08	.05	.04
561-37D0437	A	.438	.375	.203	.574	.08	.05	.04
561-37D0500	A	.500	.375	.203	.605	.09	.06	.05
561-37D0562	A	.563	.375	.203	.606	.08	.06	.04
561-37D0625	A	.625	.375	.203	.678	.09	.06	.04
Heavy Duty								
561-50C0125	A	.125	.500	.167	.315	.09	.06	.05
561-50C0187	A	.188	.500	.167	.425	.09	.06	.05
561-50C0250	A	.250	.500	.167	.410	.10	.06	.05
561-50C0312	A	.313	.500	.167	.500	.10	.07	.05
561-50C0375	A	.375	.500	.167	.530	.11	.07	.05
561-50C0437	A	.438	.500	.167	.560	.11	.07	.06
561-50C0500	A	.500	.500	.167	.595	.11	.07	.06
561-50C0562	A	.563	.500	.167	.606	.12	.08	.06
561-50C0625	A	.625	.500	.167	.655	.13	.09	.07
561-50C0687	A	.688	.500	.167	.755	.14	.09	.07
561-50C0750	A	.750	.500	.167	.780	.15	.10	.07
561-50C0812	A	.813	.500	.167	.815	.15	.10	.08
561-50C0875	A	.875	.500	.167	.845	.16	.11	.08
561-50D0687	A	.688	.500	.203	.755	.14	.09	.07
561-50D0812	A	.813	.500	.167	.845	.15	.10	.08
561-50D0875	A	.875	.500	.203	.845	.16	.11	.08
561-50D1125	A	1.125	.500	.203	.970	.26	.17	.13
561-50D1187	A	1.188	.500	.203	1.00	.27	.18	.14
561-50D1375	A	1.375	.500	.203	1.06	.29	.19	.15
561-50G0375	A	.375	.500	.250	.585	.11	.07	.05
Extra Heavy								
561-87D1003	A	0.750	.875	.387	1.00	.56	.37	.28
561-87F0750	A	1.031	.875	.203	1.125	.49	.33	.25
561-87F1003	A	1.031	.875	.387	1.125	.56	.37	.28

FIN CLIP PUSH MOUNTS

The special head configuration allows use w/ beaded ties, as well as conventional cable ties. RoHS Compliant

MOUSER STOCK NO.	Fig.	Description	Price Each		
			1	100	1000
561-PM18765	B	3/16" Push Mount	.19	.12	.09
561-PM25095	C	1/4" Push Mount	.27	.18	.14

CABLE TIE MOUNTS

For use when both sides of the panel are accessible. RoHS Compliant

MOUSER STOCK NO.	D	Cable Tie Mount	.09	.07	.05
561-TA250125					

CABLE TIE HOLDERS

* Color: Natural Screw mount tie holder offers 2-way entry and is secured w/ mounting screw. RoHS Compliant

MOUSER STOCK NO.	Fig.	Dimensions: in.		Screw Size	Price Each			
		A	B		1	100	1000	5000
561-TA00600	E	.37	.26	1/4-20	.20	.14	.10	.09
561-TA00700	E	.37	.20	10-32	.20	.14	.10	.09

CLIP MOUNTS

* Color: Natural For quantities of 200 and up, call for quote. RoHS Compliant

MOUSER STOCK NO.	Fig.	Dimensions: in.					Price Each	
		A	B	C	D	E	1	100
561-TA00090	F	.32	.22	.05	.35	.150	.14	.09
561-N3600	F	.38	.22	.07	.40	.190	.20	.17
561-N3805	F	.38	.22	.07	.40	.190	.21	.18
561-TA40170	G	.171	#8 Mntng Screw 3/8" x 3/4"			.09	.05	
561-TA40200	G	.201	#10 Mntng Screw 3/8" x 3/4"			.07	.04	

© Copyright 2009 Mouser Electronics

CONTINUOUS FLEXIBLE GROMMETING

Protect wires, cables, tubing and other objects from sharp panel edges. Can be used for round, square, and irregular shaped panels. RoHS Compliant

- In Natural (N) or Black (B)
- Material: Polyethylene
- Attaches quickly and easily using no special tools.

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Dimensions: in.				Price Per Foot		
		A	B	C	Gap	1	100	1000
Serrated								
561-FGSP0100B	H	.045	.120	.220	.095	.56	.40	.32
561-FGSP0100N	H	.045	.120	.220	.095	.56	.40	.32
561-FGSP0125B	H	.040	.125	.220	.112	.59	.43	.35
561-FGSP0125N	H	.040	.125	.220	.112	.59	.43	.35
561-FGSP0187B	H	.050	.187	.275	.180	.61	.45	.37
561-FGSP0187N	H	.050	.187	.275	.180	.61	.45	.37
561-FGSP0400B	H	.028	.072	.190	.035	.49	.37	.31
561-FGSP0400N	H	.028	.072	.190	.035	.48	.35	.29
561-FGSP0520B	H	.028	.072	.190	.040	.52	.39	.33
561-FGSP0520N	H	.028	.072	.190	.040	.53	.40	.34
561-FGSP0620B	H	.040	.080	.200	.050	.50	.37	.31
561-FGSP0620N	H	.040	.080	.200	.050	.51	.39	.32
561-FGSP0850B	H	.040	.085	.190	.075	.52	.39	.33
561-FGSP0850N	H	.040	.085	.190	.075	.50	.37	.31
Uncut								
561-FGUP0100B	H	.045	.120	.220	.095	.47	.34	.28
561-FGUP0100N	H	.045	.120	.220	.095	.47	.34	.28
561-FGUP0125B	H	.040	.125	.220	.112	.48	.35	.29
561-FGUP0125N	H	.040	.125	.220	.112	.48	.35	.29
561-FGUP0187B	H	.050	.187	.275	.180	.50	.37	.31
561-FGUP0187N	H	.050	.187	.275	.180	.50	.37	.31
561-FGUP0400B	H	.028	.072	.190	.035	.40	.30	.21
561-FGUP0400N	H	.028	.072	.190	.035	.40	.30	.21
561-FGUP0520B	H	.028	.072	.190	.040	.45	.32	.26
561-FGUP0520N	H	.028	.072	.190	.040	.45	.32	.26
561-FGUP0620B	H	.040	.080	.200	.050	.42	.32	.23
561-FGUP0620N	H	.040	.080	.200	.050	.40	.30	.21
561-FGUP0850B	H	.040	.085	.190	.075	.45	.32	.26
561-FGUP0850N	H	.040	.085	.190	.075	.45	.32	.26

SPIRAL WRAP

Spiral wrap is a specifically designed polyethylene covering for bundling tubing, wires, and other types of conductors. RoHS Compliant

- Easy to apply and remove
- Reusable and flexible

For quantities of greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	OD: in. (mm)	Bundle Range	Wall Thickness	Price Per Coil (100')
Black - UV Resistant					
561-W100BK/C		1.00 (25.4)	1" - 7"	.070	120.54
561-W11BK/C		1.00 (25.4)	1" - 7"	.095	138.91
561-W12BK/C		.125 (3.175)	1/16" - 1/4"	.032	15.80
561-W24BK/C		.25 (6.35)	1/16" - 2"	.035	26.10
561-W25BK/C		.25 (6.35)	3/16" - 2"	.040	26.46
561-W36BK/C		.375 (9.53)	5/16" - 3"	.040	38.33
561-W37BK/C		.375 (9.53)	5/16" - 3"	.052	42.70
561-W38BK/C		.375 (9.53)	5/16" - 3"	.066	43.96
561-W48BK/C		.50 (12.70)	3/8" - 3"	.030	41.40
561-W49BK/C		.50 (12.70)	3/8" - 4"	.040	42.78
561-W50BK/C		.50 (12.70)	3/8" - 4"	.062	56.84
561-W51BK/C		.50 (12.70)	3/8" - 4"	.072	58.55
561-W62BK/C		.625 (15.88)	5/8" - 4 1/2"	.062	72.94
561-W75BK/C		.75 (19.05)	3/4" - 5"	.065	102.48
Natural					
561-W10NA/C		1.00 (25.4)	1" - 7"	.070	99.40
561-W11NA/C		1.00 (25.4)	1" - 7"	.095	112.28
561-W12NA/C		.125 (3.175)	1/16" - 1/4"	.032	14.00
561-W24NA/C		.25 (6.35)	1/16" - 2"	.035	25.40
561-W25NA/C		.25 (6.35)	3/16" - 2"	.040	26.15
561-W36NA/C		.375 (9.53)	5/16" - 3"	.040	37.25
561-W37NA/C		.375 (9.53)	5/16" - 3"	.052	41.61
561-W38NA/C		.375 (9.53)	5/16" - 3"	.066	42.84
561-W48NA/C		.50 (12.70)	3/8" - 3"	.030	39.09
561-W49NA/C		.50 (12.70)	3/8" - 4"	.040	41.13
561-W50NA/C		.50 (12.70)	3/8" - 4"	.062	53.31
561-W51NA/C		.50 (12.70)	3/8" - 4"	.072	54.91
561-W62NA/C		.625 (15.88)	5/8" - 4 1/2"	.062	71.00
561-W75NA/C		.75 (19.05)	3/4" - 5"	.065	86.69

HARDWARE ASSORTMENT KITS

RoHS Compliant For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Description	Price Each	
		1	5
561-M2001	150 Cable Clips in 12 Popular Sizes	31.48	29.98
561-M2007	32 PCB Card Guides, 7 Sizes	31.48	29.98
561-M2011	Wire/Cable Ties Assorted Sizes	31.48	29.98



Eagle Plastic Devices Wire & Cable Mgmt.

DIMENSIONS: in.

A Dimensions: D, E, W, H

B Dimensions: .350, .210, .125, .065, .260, .490 Ref, .150 Ref, .320, .200

C Dimensions: .320, .285, .480, .125, .065, .500, .750, .180, .270

D Dimensions: .425 ±.010, .080, .325 ±.015, .200

E Dimensions: 7/8, .080, 5/8, A, 3/8, oB

F Dimensions: E, A, B, C, D

G Dimensions: 3/8, .195 ±.015, 3/4, D, .069, .204

H Dimensions: Gap, C, B, A

I Dimensions: (Spiral wrap)

© Copyright 2009 Mouser Electronics