


PANDUIT Cable Ties



RoHS Compliant



PANDUIT PAN-TY® NYLON CABLE TIES

General Purpose Locking Cable Ties

Features:

- Engineered with quality features designed to increase productivity and reduce your total installed cost
- Low threading force
- No sharp edges
- Finger grip tip
- Bent tip
- Consistent quality assured by tests conducted by military and independent testing labs
- One-piece constructions - up to 250lbs. minimum loop tensile strength

- Materials and colors to suit the application and environment
- Applicable sizes meet all appropriate Military Specifications and are U.L. Recognized

Nylon 6.6 (Natural)

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
					1	100	500	1000
Subminiature - Minimum Loop Tensile Strength: 12lbs.								
644-PLT.6SM-M	PLT.6SM-M	2.80	0.60	0.098	.07	.06	.05	.04
Miniature - Minimum Loop Tensile Strength: 18lbs.								
644-PLT.7M-M	PLT.7M-M	3.10	0.68	0.098	.07	.06	.05	.04
644-PLT1M-M	PLT1M-M	3.90	0.87	0.098	.07	.06	.05	.04
644-PLT1.5M-M	PLT1.5M-M	5.60	1.25	0.098	.10	.09	.07	.06
644-PLT2M-M	PLT2M-M	8.00	2.00	0.098	.10	.09	.07	.06
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-PLT1.5I-M	PLT1.5I-M	5.60	1.38	0.142	.08	.07	.06	.05
644-PLT2I-M	PLT2I-M	8.00	2.00	0.142	.10	.08	.07	.06
644-PLT2.5I-M	PLT2.5I-M	9.70	2.50	0.145	.14	.13	.12	.11
644-PLT3I-M	PLT3I-M	11.40	3.00	0.145	.15	.14	.13	.12
644-PLT4I-M	PLT4I-M	14.60	4.00	0.145	.24	.22	.19	.18
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-PLT1S-M	PLT1S-M	4.80	1.00	0.190	.30	.11	.10	.08
644-PLT1.5S-M	PLT1.5S-M	6.20	1.50	0.190	.24	.12	.10	.08
644-PLT2S-M	PLT2S-M	7.40	1.88	0.190	.24	.15	.12	.07
644-PLT2.5S-M	PLT2.5S-M	9.80	2.50	0.190	.32	.18	.17	.16
644-PLT3S-M	PLT3S-M	11.50	3.00	0.190	.82	.20	.19	.18
644-PLT4S-M	PLT4S-M	14.50	4.00	0.190	.54	.24	.21	.19
Heavy - Minimum Loop Tensile Strength: 120lbs.								
644-PLT4H-L	PLT4H-L	14.50	4.00	0.300	.70	.62	.57	.50
644-PLT5H-L	PLT5H-L	17.70	5.00	0.350	1.21	.75	.72	.71

Weather (UV) Resistant Nylon 6.6 (Black)

• UL94V-2 rating For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
					1	100	500	1000
Subminiature - Minimum Loop Tensile Strength: 12lbs.								
644-PLT.6SM-MO	PLT.6SM-MO	2.80	0.60	0.098	.11	.08	.07	.06
Miniature - Minimum Loop Tensile Strength: 18lbs.								
644-PLT.7M-MO	PLT.7M-MO	3.10	0.68	0.098	.07	.06	.05	.04
644-PLT1M-MO	PLT1M-MO	3.90	0.87	0.098	.10	.08	.07	.06
644-PLT1.5M-MO	PLT1.5M-MO	5.60	1.25	0.098	.11	.10	.09	.07
644-PLT2M-MO	PLT2M-MO	8.00	2.00	0.098	.11	.10	.09	.07
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-PLT1.5I-MO	PLT1.5I-MO	5.60	1.38	0.142	.11	.10	.08	.07
644-PLT2I-MO	PLT2I-MO	8.00	2.00	0.142	.12	.11	.10	.09
644-PLT2.5I-MO	PLT2.5I-MO	9.70	2.50	0.145	.17	.15	.14	.13
644-PLT4I-MO	PLT4I-MO	14.60	4.00	0.145	.33	.29	.28	.25
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-PLT1S-MO	PLT1S-MO	4.80	1.00	0.190	.33	.12	.11	.10
644-PLT1.5S-MO	PLT1.5S-MO	6.20	1.50	0.190	.24	.10	.08	.07
644-PLT2S-MO	PLT2S-MO	7.40	1.88	0.190	.24	.18	.12	.07
644-PLT2.5S-MO	PLT2.5S-MO	9.80	2.50	0.190	.39	.20	.19	.18
644-PLT3S-MO	PLT3S-MO	11.50	3.00	0.190	.52	.27	.24	.21
644-PLT4S-MO	PLT4S-MO	14.50	4.00	0.190	.58	.30	.26	.24
Heavy - Minimum Loop Tensile Strength: 120lbs.								
644-PLT6H-L0	PLT6H-L0	20.90	6.00	0.350	1.76	1.38	1.10	1.01
Light - Heavy - Minimum Loop Tensile Strength: 120lbs.								
644-PLT6LH-L0	PLT6LH-L0	21.90	6.00	0.300	1.52	1.18	.96	.86
644-PLT7LH-L0	PLT7LH-L0	24.70	7.00	0.300	1.54	1.20	1.08	.99
644-PLT9LH-L0	PLT9LH-L0	30.50	9.00	0.300	1.83	1.43	1.14	1.09

Releaseable Locking Cable Ties

The extended tab end of releasable cable ties permits easy release and reuse even after tie has been pulled up snug by hand. Releasable ties are particularly useful in harnessing where changes are anticipated during development, production or servicing in the field.

Features:

- Tensile Strength: 50lbs.
- Curved tip




Nylon 6.6 (Natural)

RoHS Compliant

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
					1	100	500	1000
644-PR2S-M	PRT2S-M	7.40	1.88	0.190	.43	.14	.12	.11
644-PR3S-M	PRT3S-M	11.50	3.00	0.190	.91	.42	.369	.345
644-PR4S-M	PRT4S-M	14.50	4.00	0.190	1.10	.50	.452	.392



Weather (UV) Resistant Nylon 6.6 (Black)

• UL94V-2 rating For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
					1	100	500	1000
644-PR2S-MO	PRT2S-MO	7.40	1.88	0.190	.52	.18	.16	.13
644-PR3S-MO	PRT3S-MO	11.50	3.00	0.190	.88	.40	.37	.32
644-PR4S-MO	PRT4S-MO	14.50	4.00	0.190	.98	.43	.39	.35

PANDUIT DOME-TOP® BARB TY CABLE TIES

Features:

- Stainless steel barb provides consistent performance and reliability
- Tensile strength exceeds Aerospace Standard SAE (AS23190) standards
- Low threading force and high strength
- Curved tip
- Round, smooth edges




RoHS Compliant

Nylon 6.6 (Natural)

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
					1	100	500	1000
Miniature - Minimum Loop Tensile Strength: 18lbs.								
644-BT1M-M	BT1M-M	4.00	0.90	0.095	.07	.06	.05	.04
644-BT1.5M-M	BT1.5M-M	6.10	1.50	0.095	.08	.07	.06	.05
644-BT2M-M	BT2M-M	8.00	2.00	0.095	.10	.08	.07	.06
644-BT4M-M	BT4M-M	14.00	4.00	0.095	.39	.15	.14	.11
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-BT1.5I-M	BT1.5I-M	6.10	1.50	0.141	.10	.08	.07	.06
644-BT2I-M	BT2I-M	8.00	2.00	0.141	.11	.10	.08	.07
644-BT3I-M	BT3I-M	11.10	3.00	0.141	.15	.14	.13	.12
644-BT4I-M	BT4I-M	14.30	4.00	0.141	.23	.21	.20	.19
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-BT2S-M	BT2S-M	8.00	2.00	0.185	.11	.10	.08	.07
644-BT3S-M	BT3S-M	11.20	3.00	0.185	.32	.30	.27	.25
644-BT4S-M	BT4S-M	14.40	4.00	0.185	.26	.23	.19	.17
Light-Heavy - Minimum Loop Tensile Strength: 120lbs.								
644-BT5LH-C	BT5LH-C	18.100	5.000	0.275	.64	.58	.51	.46



Weather (UV) Resistant Nylon 6.6 (Black)

• UL94V-2 rating For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
					1	100	500	1000
Miniature - Minimum Loop Tensile Strength: 18lbs.								
644-BT1M-MO	BT1M-MO	4.00	0.90	0.095	.23	.08	.07	.06
644-BT1.5M-MO	BT1.5M-MO	6.10	1.50	0.095	.12	.11	.10	.08
644-BT2M-MO	BT2M-MO	8.00	2.00	0.095	.12	.11	.10	.08
644-BT4M-MO	BT4M-MO	14.00	4.00	0.095	.53	.20	.18	.16
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-BT1.5I-MO	BT1.5I-MO	6.10	1.50	0.141	.30	.11	.10	.08
644-BT2I-MO	BT2I-MO	8.00	2.00	0.141	.39	.15	.14	.12
644-BT3I-MO	BT3I-MO	11.10	3.00	0.141	.19	.18	.17	.15
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-BT2S-MO	BT2S-MO	8.00	2.00	0.185	.32	.13	.12	.10
644-BT3S-MO	BT3S-MO	11.20	3.00	0.185	.26	.24	.21	.19
644-BT4S-MO	BT4S-MO	14.40	4.00	0.185	.56	.37	.33	.29
Light-Heavy - Minimum Loop Tensile Strength: 120lbs.								
644-BT5LH-CO	BT5LH-CO	18.10	5.00	0.275	.79	.72	.63	.56
644-BT6LH-CO	BT6LH-CO	21.20	6.00	0.275	.93	.85	.74	.67


PANDUIT SUPER-GRIP™ CABLE TIES

Features:

- Thin, wide strap body provides flexibility enabling it to conform to bundle while maintaining tensile strength
- High strength allows the tie to withstand rough installation practices that occur in MRO and Construction environments
- Resists lateral movement on the bundle - tie is designed to grip the bundle when tightly applied
- Curved tip is easy to pick up from flat surfaces, allows faster initial threading, and speeds installation
- Flared neck and strong locking wedge



RoHS Compliant



Nylon 6.6 (Natural)

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
					1	100	500	1000
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-SG200S-M	SG200S-M	8.300	2.000	0.225	.17	.13	.119	.083
644-SG250S-C	SG250S-C	10.400	2.600	0.225	.72	.55	.43	.38
644-SG300S-M	SG300S-M	12.400	3.200	0.225	.42	.31	.25	.21

Weather (UV) Resistant Nylon 6.6 (Black)

• UL94V-2 rating For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
					1	100	500	1000
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-SG200S-MO	SG200S-MO	8.300	2.000	0.225	.20	.14	.118	.095
644-SG250S-CO	SG250S-CO	10.400	2.600	0.225	.80	.61	.48	.43
644-SG300S-MO	SG300S-MO	12.400	3.200	0.225	.58	.42	.357	.297



Wire & Cable Mgmt. Panduit