

BOMAR Between Series Adapters and RF Connectors



Between series adapters solve a variety of connection problems where connectors of different types could ordinarily not be mated together. Each adapter has a different type coupling at each end allowing for a wide variety of interconnections to fit almost all interconnection situations. All adapters are constructed of machined brass and are nickel plated.

BETWEEN SERIES ADAPTERS CONT.

- RoHS Compliant per Bomar documentation



RoHS Compliant

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Bomar Part No.	Fig.	Description	Price Each			
				1	10	25	50
Type UHF Adapters							
678-7311505	7311505	A	UHF Plug to N Jack	15.48	14.07	13.58	11.91
678-7313505	7313505	B	UHF Plug to BNC Jack	9.08	8.25	7.96	6.98
678-7316505	7316505	C	UHF Plug to Mini-UHF Jack	12.80	11.64	11.23	9.85
678-7309505	7309505	D	UHF Plug to SMA Plug	6.48	5.89	5.68	4.98
678-7319505	7319505	E	UHF Jack to SMA Plug	29.12	26.47	25.54	22.40
678-6317505	6317505	F	UHF Jack to Mini-UHF Plug	10.00	9.09	8.77	7.69
Type GSK Adapter							
678-83119505	83119505	G	GSK Jack to F Plug	6.66	6.05	5.84	5.12
Type RCA Adapters							
678-R0842	R0842	H	RCA Plug to BNC Plug	4.42	4.02	3.88	3.40
678-R0844	R0844	I	RCA Plug to BNC Jack	3.98	3.62	3.49	3.06
678-R0847	R0847	J	RCA Plug to F Plug	5.30	4.82	4.65	4.08
678-R0849	R0849	K	RCA Plug to F Jack	2.40	2.18	2.11	1.89
678-R0822	R0822	L	RCA Plug to UHF Jack	6.56	5.96	5.75	5.05
678-R0811	R0811	M	RCA Jack to UHF Plug	3.60	3.27	3.16	2.77
678-R0843	R0843	N	RCA Jack to BNC Plug	2.60	2.36	2.28	2.05
678-R0851	R0851	O	RCA Jack to F Plug	2.60	2.36	2.28	2.05

RF ADAPTER KITS

- RoHS Compliant per Bomar documentation



RoHS Compliant

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Bomar Part No.	Description	Price Each	
			1	5
Commercial Grade Kit-30 pcs				
678-ADPT1	ADPT1	2 Male and Female of each: BNC, TNC, N, Mini-UHF, UHF, SMA, and 6 Universal adapters	155.15	140.07
Broadcast Grade Kit-40 pcs				
678-ADPT2	ADPT2	2 Male and Female of each: BNC, TNC, N, Mini-UHF, UHF, SMA, F, RCA, and 8 Universal adapters	249.71	225.43
7/16 Kit-8 pc				
678-ADPT3PA	ADPT3PA	1 Male and Female of each: 7/16 to N, N to N, and 7/16 to 7/16	310.57	280.38
Antenna Kit-42 pcs				
678-ADPT4RP	ADPT4RP	2 Male and Female of each: N, BNC, UHF, TNC, TNC-RT, TNC-RP, SMA, SMA-RP, and 8 Universal adapters	295.38	266.67

MCX AND MMCX CABLE CONNECTORS

- Brass body parts
- Plating: Gold over Nickel
- RoHS Compliant per Bomar documentation



RoHS Compliant

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Bomar Part No.	Fig.	Imp. Ω	Description	RG Cable Type	Price Each			
						1	10	25	100
678-1210A204M	1210A204M	P	50	Straight Cable Plug	174/U	3.56	3.24	3.12	2.95
678-1213A204M	1213A204M	Q	50	Right Angle Plug	174/U	3.56	3.24	3.12	2.95
678-1310A204M	1310A204M	R	50	Straight Cable Plug	174/U	6.16	5.60	5.40	5.29

BNC COAXIAL CRIMP PLUGS

- High quality machined construction
- Semi-captive contacts that "click" into place assuring perfect installation
- RoHS Compliant per Bomar documentation



RoHS Compliant

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Bomar Part No.	Fig.	Imp. Ω	Description	RG Cable Type	Price Each			
						1	10	25	100
678-310A205F	310A205F	S	50	3 piece, dual crimp	58/U, 58C/U, 141	2.78	2.53	2.44	2.32
678-310A205G	310A205G	S	50	3 piece, dual crimp	59, 62, 210	2.48	2.25	2.18	2.00
678-310A205MV	310A205MV	S	50	3 piece, dual crimp	174, 179, 196	2.90	2.64	2.47	2.32
678-310A205P	310A205P	S	50	3 piece, dual crimp	223	2.74	2.49	2.32	2.18
678-310B205MV	310B205MV	S	75	3 piece, dual crimp	174, 178, 196	3.54	3.22	3.11	2.95
678-332A705	332A705	T	75	Inline Splice Adapter	-----	3.08	2.80	2.70	2.60
678-332A505	332A505	T	50	Inline Splice Adapter	-----	3.92	3.56	3.44	3.16

