

AIM/CAMBRIDGE RF Connectors and Adapters

RoHS Compliant This page of product is compliant.

UHF CONNECTORS

For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	AIM/Cambridge Part No.	Fig.	Description/Cable Type	Price Each			
				1	10	25	100
601-25-7307	25-7307	A	Crimp Contact, Plug for RG58	2.34	2.21	1.97	1.81
601-25-7300	25-7300	B	Straight Solder Type Plug for RG11	2.77	2.51	2.16	2.04
601-25-7350	25-7350	C	Flange Mount Jack	1.33	1.21	1.06	1.01

Tooling

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	AIM/Cambridge Part No.	Fig.	Description/Cable Type	Price Each	
				1	5
530-24-9960P	24-9960P	D	Crimp Tool for RG58, RG59, RG6, Belden 8281	65.00	60.00
530-24-7712P	24-7712P	D	Crimp Tool for RG6, RG11, UHF8	37.84	32.81

MINI UHF CONNECTORS

For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	AIM/Cambridge Part No.	Fig.	Description/Cable Type	Price Each			
				1	10	25	100
601-29-4010	29-4010	E	Straight Crimp Type Plug for RG58	1.24	1.14	1.06	1.00
601-29-4033	29-4033	E	Straight Crimp Type Plug for RG8X (MINI 8)	1.69	1.51	1.37	1.31

Tooling

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	AIM/Cambridge Part No.	Fig.	Description/Cable Type	Price Each	
				1	5
530-24-8860P	24-8860P	D	Crimp Tool for RG58, RG59, RG62	46.34	40.70

F CONNECTORS

For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	AIM/Cambridge Part No.	Fig.	Description/Cable Type	Price Each			
				1	10	25	100
601-25-7010	25-7010	F	F-59 Crimp Plug W/Separate 1/4 Ring for RG-59	.28	.26	.22	.20
601-25-7020	25-7020	G	F-59 Crimp Plug W/Separate 1/2 Ring for RG-59	.39	.36	.29	.23
601-25-7030	25-7030	H	F-59 Standard Straight Crimp Plug for RG-59	.39	.36	.29	.23
601-25-7032	25-7032	H	F-56 Standard Straight Crimp-On Plug for RG-6	.32	.30	.28	.27
601-25-7033	25-7033	H	F56ALX Crimp-On Plug RG6 Tri-Shield and Quad Plenum	.37	.34	.30	.28
601-25-7034	25-7034	H	F56ALX Crimp-On Plug Quad Shield for RG-6	.40	.35	.33	.30
601-25-7035	25-7035	-	F-59 Crimp-On Plug for Thin Cable for RG-59 & 62 Teflon	.46	.42	.37	.35
601-25-7047	25-7047	I	F-56 Crimp-On Plug for RG6 Teflon/Plenum	.60	.54	.47	.43
601-25-7050	25-7050	-	F-59A Crimp-On Plug W/Attached 1/8 Ring	.28	.25	.22	.20
601-25-7056	25-7056	H	F-56ALM Weatherproof Crimp Plug W/Interior Gasket for RG-6	.48	.44	.39	.36
601-25-7066	25-7066	-	Weatherproof Crimp Plug W/O-Ring, Gel Filled RG-6	.54	.49	.43	.41
601-25-7120	25-7120	J	F-59TW Standard Twist-On Plug for RG-59	.34	.32	.30	.28
601-25-7150	25-7150	K	F-56 Crimp-On Plug W/Separate 1/4 Ring for RG-6	.32	.29	.25	.23
601-25-7160	25-7160	-	F-56A Crimp-On Plug W/Attached 1/4 Ring for RG-6	.27	.25	.22	.20
601-25-7180	25-7180	L	F-56 Standard Twist-On Plug for RG-6	.35	.32	.28	.26
601-25-7191	25-7191	M	F-11 Standard Crimp-On Plug for RG-11	1.90	1.71	1.40	1.16
601-25-7630	25-7630	N	F Side Edge Mount, PCB Jack	.92	.84	.68	.57
601-25-7650	25-7650	O	F-61PC Straight Mount, PCB Jack	.48	.43	.40	.38
601-25-7651	25-7651	-	F Right Angle PCB Mount Jack	1.50	1.25	1.15	.95

Adapters and Accessories

601-25-7200	25-7200	O	3/4 In-Line Splice Jack to Jack	.34	.30	.24	.22
601-25-7200L	25-7200L	O	1" In-Line Splice Jack to Jack	.73	.66	.54	.45
601-25-7210	25-7210	P	3/4 Splice Jack to Jack with Hardware	.34	.29	.27	.25
601-25-7640	25-7640	Q	Double Male Splice Plug to Plug	.96	.92	.87	.81

Weatherproof Compression Connectors (Male - 7/16" Hex)

601-25-2502-10PB	25-2502-10PB	R	RG - 59 Dual/Tri/Quad, Nickel	.93	.78	.70	.60
601-25-2601-10PB	25-2601-10PB	R	RG - 6 Dual/Tri/Quad, Nickel	.93	.78	.70	.60
601-25-2502G-10PB	25-2502G-10PB	R	RG - 59 Dual/Tri/Quad, Gold	1.06	.96	.90	.82
601-25-2601G-10PB	25-2601G-10PB	R	RG- 6 Dual/Tri/Quad, Gold	1.06	.96	.90	.82

Tooling

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	AIM/Cambridge Part No.	Fig.	Description/Cable Type	Price Each	
				1	5
601-24-7710	24-7710	D	Crimp Tool for RG6, RG59	22.40	18.13
601-24-7714P	24-7714P	S	Adjustable 3-Way Ratchet Crimp Tool for Compression BNC, F, and RCA Connectors	70.09	53.33
601-24-7732P	24-7732P	-	2-Step Self Adjusting Coax Stripper Tool	18.66	17.23
601-24-7733P	24-7733P	-	3-Step Self-Adjusting Coax Stripper Tool	18.66	17.23
601-24-328P	24-328P	-	Crimp RG58, 178 Ratchet Professional	41.96	37.76

BETWEEN SERIES ADAPTERS

For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	AIM/Cambridge Part No.	Fig.	Description	Price Each			
				1	10	25	100
601-25-7500	25-7500	T	BNC Plug to F Jack Adapter	1.91	1.72	1.62	1.53
601-27-8110	27-8110	U	BNC Jack to RCA Plug Adapter	1.71	1.31	1.25	1.11
530-CP-AD517	CP-AD517	V	BNC 75Ω Plug to RCA Jack	4.16	3.74	3.12	2.55
601-25-7510	25-7510	V	BNC 50Ω Plug to RCA Jack	.93	.83	.78	.72
601-29-3840	29-3840	W	N Plug to SMA Jack	5.22	4.75	4.11	3.87

