

MOUNTAIN SWITCH Toggle Switches

Mountain Switch SUB-MINIATURE TOGGLE SWITCHES



Specifications:

- Rating: 1A/250VAC; 3A/120VAC or 28VDC
- Contact Resistance: 20mΩ max.
- Insulation Resistance: 1000MΩ min.

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Width (W) (in.)	Type	Circuit	Price Each				
					1	50	100	500	1000
108-0041-EVX	A	0.20	SPST	Off-On	1.97	1.81	1.74	1.67	1.26
108-0042-EVX	A	0.20	SPDT	On-On	1.97	1.81	1.74	1.67	1.26
108-0044-EVX	A	0.20	SPDT	On-Off-On	1.97	1.81	1.74	1.67	1.26
108-0043-EVX	A	0.36	DPDT	On-On	2.81	2.56	2.40	2.28	2.05
108-0046-EVX	A	0.36	DPDT	On-Off-On	4.20	3.46	2.92	2.42	2.30
108-0047-EVX	B	0.20	SPST	Off-On	2.98	2.66	2.24	1.80	1.59
108-0048-EVX	B	0.20	SPDT	On-On	2.98	2.66	2.24	1.80	1.59
108-0049-EVX	B	0.36	DPDT	On-On	2.81	2.56	2.40	2.28	2.05
108-0050-EVX	C	0.20	SPST	On-Off	2.98	2.66	2.24	1.80	1.59
108-0051-EVX	C	0.20	SPDT	On-On	1.97	1.81	1.74	1.67	1.26
108-0052-EVX	C	0.36	DPDT	On-On	2.74	2.49	2.33	2.21	1.99

Mountain Switch MINIATURE TOGGLE SWITCHES



Specifications:

- Rating: 2A/250VAC; 5A/120VAC or 28VDC
- Contact Resistance: 10mΩ max.
- Insulation Resistance: 1000MΩ min.

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Width (W) (in.)	Type	Circuit	Price Each				
					1	50	100	500	1000
108-0001-EVX	D	0.27	SPST	Off-On	1.70	1.64	1.58	1.51	1.26
108-0002-EVX	D	0.27	SPDT	On-Off-(On)	2.81	2.56	2.40	2.28	2.05
108-0053-EVX	D	0.27	SPDT	(On)-Off-(On)	2.81	2.56	2.40	2.28	2.05
108-0004-EVX	D	0.45	DPDT	On-Off-(On)	3.22	2.98	2.81	2.69	2.49
108-0005-EVX	D	0.45	DPDT	(On)-Off-(On)	3.62	3.06	2.87	2.71	2.44
108-0010-EVX	D	0.45	DPDT	On-On	2.74	2.49	2.33	2.21	1.99
108-0008-EVX	E	0.27	SPST	Off-On	2.04	1.47	1.38	1.28	1.07
108-0009-EVX	E	0.27	SPDT	On-On	2.04	1.47	1.38	1.28	1.07
108-0006-EVX	F	0.50	3PDT	On-Off-On	5.18	4.83	4.69	4.38	4.00
108-0007-EVX	F	0.50	4PDT	On-Off-On	8.99	7.80	7.09	6.45	5.94
108-0038-EVX	G	0.27	SPST	Off-On	2.83	2.58	2.42	2.30	2.07
108-0040-EVX	G	0.27	SPST	Off-On	2.83	2.58	2.42	2.30	2.07
108-0027-EVX	H	0.27	SPST	Off-On	1.97	1.81	1.74	1.67	1.26
108-0028-EVX	H	0.27	SPDT	(On)-Off-(On)	2.81	2.56	2.40	2.28	2.05
108-0029-EVX	H	0.45	DPDT	On-On	3.62	3.06	2.87	2.71	2.44
108-0031-EVX	H	0.45	DPDT	On-Off-On	3.62	3.06	2.87	2.71	2.44
108-0011-EVX	I	0.27	SPDT	On-On	1.97	1.81	1.74	1.67	1.26
108-0012-EVX	I	0.27	SPDT	On-Off-On	2.74	2.49	2.33	2.21	1.99
108-0014-EVX	I	0.27	SPDT	On-(On)	2.98	2.66	2.24	1.80	1.59
108-0015-EVX	I	0.27	SPDT	On-Off-(On)	3.62	3.06	2.87	2.71	2.44
108-0016-EVX	I	0.27	SPDT	(On)-Off-(On)	2.83	2.58	2.42	2.30	2.07
108-0017-EVX	J	0.45	DPDT	On-On	3.62	3.06	2.87	2.71	2.44
108-0018-EVX	J	0.45	DPDT	On-Off-On	3.62	3.06	2.87	2.71	2.44
108-0019-EVX	J	0.45	DPDT	On-(On)	3.62	3.06	2.87	2.71	2.44
108-0020-EVX	K	0.27	SPDT	On-On	2.98	2.66	2.24	1.80	1.59
108-0021-EVX	K	0.27	SPDT	On-Off-On	2.74	2.49	2.33	2.21	1.99
108-0022-EVX	K	0.27	SPDT	On-(On)	2.68	2.43	2.27	2.15	2.05
108-0023-EVX	K	0.27	SPDT	(On)-Off-(On)	2.83	2.58	2.42	2.30	2.07
108-0024-EVX	K	0.45	DPDT	On-On	3.62	3.06	2.87	2.71	2.44
108-0025-EVX	K	0.45	DPDT	On-Off-On	3.62	3.06	2.87	2.71	2.44

Mountain Switch TOGGLE SWITCH CAPS



Specifications:

- Threaded bushing

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Color	Price Each				
			1	50	100	500	1000
108-0032-EV	L	Red	.17	.15	.13	.12	.11
108-0033-EV	L	Black	.17	.15	.13	.12	.11
108-0034-EV	L	White	.17	.15	.13	.12	.11
108-0035-EV	L	Blue	.17	.15	.13	.12	.11
108-0036-EV	L	Yellow	.17	.15	.13	.12	.11
108-0037-EV	L	Green	.17	.15	.13	.12	.11

