

C&K Slide Switches



C&K AYZ SERIES MINIATURE SLIDE SWITCHES

Specifications:

- Dielectric Strength: 0.1 kV @ 50 Hz/1 min.
- Max Switching Power: 1.2 VA
- Max Switching Voltage: 12 VDC
- Max. Switching Current: 100 mA
- PC thru-hole termination
- Silver plated contacts



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Price Each			
					1	25	50	100
611-AYZ0102AGRL	AYZ0102AGRL	A	SPDT	On-On	.77	.74	.702	.672
611-AYZ0102AGRLC	AYZ0102AGRLC	A	SPDT	On-On	.90	.81	.74	.66
611-AYZ0202AGRL	AYZ0202AGRL	B	DPDT	On-On	1.08	1.03	.98	.93
611-AYZ0202AGRLC	AYZ0202AGRLC	B	DPDT	On-On	1.34	1.21	1.10	.98
611-AYZ0103AGRL	AYZ0103AGRL	C	SP3T	On-On-On	.78	.75	.71	.68

C&K ES SERIES SEALED TINY SLIDE SWITCHES

Specifications:

- Actuator Height: .121"
- Contact Rating: 0.4 VA max. @ 20 VAC or DC max.
- Lead free
- Mechanical and Electrical Life: 40,000 make-and-break cycles at full load
- Dielectric Strength: 500 Vrms min.



LEAD-FREE

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Price Each			
					1	25	50	100
PC Thru-Hole								
611-ES21MCBE	ES21MCBE	D	DPDT	On-None-On	5.73	5.42	4.95	4.80
Right-Angle PC Thru-Hole								
611-ES22MABE	ES22MABE	E	DPST	Off-None-On	6.74	6.37	5.83	5.65
611-ES01MAVBE	ES01MAVBE	F	SPDT	On-None-On	5.17	4.89	4.47	4.33
Right-Angle Surface Mount								
611-ES03MSABE	ES03MSABE	G	SPDT	On-Off-On	5.71	5.40	4.94	4.78

C&K OS SERIES MINIATURE SLIDE SWITCHES

Specifications:

- Dielectric Strength: 500 VAC for 1 minute
- Contact Rating: 0.2 A @ 30 VDC
- PC and panel mounting
- Mechanical and Electrical Life: 10,000 cycles
- Shorting or Non-shorting contacts
- Variety of actuators and terminations



RoHS Compliant

* Non-Shorting ** Shorting

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Price Each			
					1	25	50	100
Vertical Termination								
** 611-OS102011MS2QN1	OS102011MS2QN1	H	SPDT	On-On	.36	.32	.28	.26
** 611-OS102011MS2QS1	OS102011MS2QS1	H	SPDT	On-On	.41	.33	.31	.28
611-OS103011MS8QP1	OS103011MS8QP1	I	SP3T	On-On-On	.41	.38	.36	.34
611-OS103012MU1QP1	OS103012MU1QP1	J	SP3T	On-On-On	.57	.54	.51	.461
611-OS103012MU2QP1	OS103012MU2QP1	K	SP3T	On-On-On	.56	.54	.51	.48
* 611-OS202011MS2QN1	OS202011MS2QN1	L	DPDT	On-On	.46	.41	.33	.30
** 611-OS202011MS2QS1	OS202011MS2QS1	L	DPDT	On-On	.46	.44	.38	.33
* 611-OS202011MV4QN1	OS202011MV4QN1	M	DPDT	On-On	.52	.50	.47	.423
* 611-OS202013MT5QN1	OS202013MT5QN1	N	DPDT	On-On	.53	.45	.38	.33
* 611-OS202013MT8QN1	OS202013MT8QN1	O	DPDT	On-On	.56	.54	.51	.457
611-OS203011MS1QP1	OS203011MS1QP1	P	DP3T	On-On-On	.58	.56	.53	.476
* 611-OS203013MT6QN1	OS203013MT6QN1	Q	DP3T	On-On-On	.46	.44	.38	.33
Right-Angle Termination								
611-OS102011MA1QN1	OS102011MA1QN1	R	SPDT	On-On	.29	.28	.26	.24
** 611-OS102011MA1QS1	OS102011MA1QS1	R	SPDT	On-On	.36	.32	.28	.26
611-OS103011MA7QP1	OS103011MA7QP1	S	SP3T	On-On-On	.42	.36	.31	.27
* 611-OS202011MA0QN1	OS202011MA0QN1	T	DPDT	On-On	.46	.36	.29	.22
** 611-OS202011MA0QS1	OS202011MA0QS1	T	DPDT	On-On	.46	.39	.37	.33
611-OS203011MA2QP1	OS203011MA2QP1	U	DP3T	On-On-On	.50	.48	.45	.406

C&K LP SERIES: MINIATURE SNAP-IN SLIDE SWITCHES

Specifications:

- Dielectric Strength: 1000 Vrms min. @ sea level
- Contact Rating: 6A @ 125 VAC
- Easy Assembly - Snap-In Mounting
- Contamination resistant - extended actuator



RoHS Compliant

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Price Each			
					1	25	50	100
611-LP02C21T203DQ	LP02C21T203DQ	V	SPDT	On-Off	2.59	2.45	2.24	2.07
611-LP02C31T203DQ	LP02C31T203DQ	V	SPDT	On-Off	2.78	2.63	2.41	2.33
611-LP22C31T203DQ	LP22C31T203DQ	V	DPDT	On-Off	3.55	3.36	3.07	2.82

© Copyright 2009 Mouser Electronics

© Copyright 2009 Mouser Electronics

DIMENSIONS: in.

C&K Slide Switches