

# AVAGO Optocouplers

RoHS Compliant This product is RoHS compliant.

NEW FROM SUPPLIER

# AVAGO

TECHNOLOGIES

For quantities of 500 and up, call for quote.

## AVAGO OPTOCOUPERS

MOUSER STOCK NO.	Avago Part No.	Number of Channels	Package	Forward on Current (mA)	Total Power Dissipation (mW)	Isolation Voltage (VRMS)	Price Each			
							1	10	50	100
630-4N25-000E	4N25-000E	-	DIP-6	80	250	2500	.28	.23	.20	.17
630-4N25-W00E	4N25-W00E	-	DIP-6	80	250	2500	.31	.256	.222	.189
630-4N35-000E	4N35-000E	-	DIP-6	60	350	3550	.28	.23	.20	.17
630-4N46-000E	4N46-000E	-	DIP-6	20	100	3750	2.31	1.94	1.75	1.60
630-6N135-000E	6N135-000E	1	DIP-8	8	100	3750	.95	.83	.74	.675
630-6N136-000E	6N136-000E	1	DIP-8	8	100	3750	.95	.83	.74	.68
630-6N136-300E	6N136-300E	1	SO-8	8	100	3750	1.01	.87	.776	.71
630-6N137-000E	6N137-000E	1	DIP-8	15	85	3750	1.07	.925	.825	.75
630-6N138-000E	6N138-000E	1	DIP-8	135	135	3750	.96	.83	.74	.68
630-6N139-000E	6N139-000E	1	DIP-8	20	135	3750	.96	.83	.74	.68
630-6N140A	6N140A	4	DIP-16	40	200	-	66.50	59.50	57.75	46.55
630-ACPL-071L-000E	ACPL-071L-000E	1	SO-8	9	-	3750	2.67	2.31	2.06	1.88
630-ACPL-072L-000E	ACPL-072L-000E	1	SO-8	10	150	3750	3.41	2.96	2.64	2.40
630-ACPL-074L-060E	ACPL-074L-060E	2	SO-8	9	-	3750	6.80	5.59	4.98	4.53
630-ACPL-312T-000E	ACPL-312T-000E	1	DIP-8	7	400	3750	4.26	3.94	3.73	3.51
630-ACPL-782T-000E	ACPL-782T-000E	1	DIP-8	16	600	3750	13.48	11.76	10.78	9.80
630-ACPL-C780-000E	ACPL-C780-000E	1	Stretched SO-8	11	600	5000	8.87	7.27	6.48	5.90
630-ACPL-C784-000E	ACPL-C784-000E	1	Stretched SO-8	11	600	5000	6.54	5.37	4.78	4.35
630-ACPL-C78A-000E	ACPL-C78A-000E	1	Stretched SO-8	11	600	5000	12.50	10.26	9.13	8.31
630-ACPL-W70L-000E	ACPL-W70L-000E	1	Stretched SO-6	10	600	5000	2.93	2.41	2.14	1.95
630-ACPL-K73L-000E	ACPL-K73L-000E	2	Stretched SO-8	10	600	5000	5.40	4.44	3.95	3.60
630-ACPL-M46T-000E	ACPL-M46T-000E	1	SO-5	10	130	3750	4.14	3.83	3.62	3.42
630-ACPL-M61T-000E	ACPL-M61T-000E	1	SO-5	20	85	3750	4.14	3.83	3.62	3.42
630-ACPL-M75L-000E	ACPL-M75L-000E	1	SO-5	4	-	3750	2.93	2.41	2.14	1.95
630-ACSL-6210-00RE	ACSL-6210-00RE	2	SO-8	2.7	60	2500	2.99	2.59	2.31	2.10
630-ACSL-6400-00TE	ACSL-6400-00TE	4	SO-16	2.7	60	2500	5.97	5.18	4.62	4.20
630-CNY17-2-000E	CNY17-2-000E	1	DIP-6	0.3	250	5000	.30	.23	.20	.17
630-CNY17-3-000E	CNY17-3-000E	1	DIP-6	0.3	250	5000	.28	.23	.20	.17
630-CNY17-4-000E	CNY17-4-000E	1	DIP-6	0.3	250	5000	.30	.23	.20	.17
630-HCNR200-000E	HCNR200-000E	1	DIP-8	25	60	1414	2.70	2.46	2.19	1.99
630-HCNR200-300E	HCNR200-300E	1	SO-8	25	60	1414	2.74	2.49	2.23	2.02
630-HCNR201-000E	HCNR201-000E	1	DIP-8	25	60	1414	3.60	3.27	2.92	2.65
630-HCNR201-300E	HCNR201-300E	1	SO-8	25	60	1414	3.64	3.31	2.95	2.68
630-HCNW136-000E	HCNW136-000E	1	DIP-8	16	700	5000	1.71	1.48	1.32	1.20
630-HCNW137-000E	HCNW137-000E	1	DIP-8	5	700	5000	2.41	2.09	1.86	1.70
630-HCNW139-000E	HCNW139-000E	1	DIP-8	0.4	700	1414	2.29	1.98	1.77	1.61
630-HCNW139-300E	HCNW139-300E	1	SO-8	0.4	700	5000	2.34	2.02	1.80	1.64
630-HCNW2201-000E	HCNW2201-000E	1	DIP-8	1.6	600	5000	2.62	2.38	2.13	1.94
630-HCNW2211-000E	HCNW2211-000E	1	DIP-8	1.6	600	5000	2.85	2.59	2.31	2.10
630-HCNW2211-300E	HCNW2211-300E	1	SO-8	1.6	600	5000	2.89	2.63	2.34	2.13
630-HCNW2611-000E	HCNW2611-000E	1	DIP-8	1.6	600	5000	3.09	2.68	2.39	2.18
630-HCNW2611-300E	HCNW2611-300E	1	SO-8	1.6	600	5000	3.14	2.72	2.42	2.21
630-HCNW3120-000E	HCNW3120-000E	1	DIP-8	10	700	5000	3.31	2.87	2.56	2.33
630-HCNW4502-000E	HCNW4502-000E	1	DIP-8	16	700	5000	1.71	1.48	1.32	1.20
630-HCNW4503-000E	HCNW4503-000E	1	DIP-8	16	700	5000	2.28	1.98	1.77	1.61
630-HCNW4503-300E	HCNW4503-300E	1	SO-8	16	700	5000	2.45	2.02	1.80	1.64
630-HCNW4504-300E	HCNW4504-300E	1	DIP-8	12	100	5000	2.72	2.24	2.00	1.82
630-HCNW4506-300E	HCNW4506-300E	1	SO-8	10	145	3750	2.66	2.29	2.05	1.86
630-HCPL-0201-000E	HCPL-0201-000E	1	DIP-8	1.6	600	3750	2.40	2.18	1.95	1.77
630-HCPL-0201-500E	HCPL-0201-500E	1	SO-8	1.6	600	3750	2.40	2.10	1.98	1.68
630-HCPL-0211-000E	HCPL-0211-000E	1	DIP-8	1.6	600	3750	2.76	2.52	2.24	2.04
630-HCPL-0211-500E	HCPL-0211-500E	1	SO-8	1.6	600	3750	2.76	2.42	2.28	1.93
630-HCPL-0300-000E	HCPL-0300-000E	1	SO-8	0.5	600	3750	6.39	5.54	4.95	4.51
630-HCPL-0314-000E	HCPL-0314-000E	1	SO-8	8	400	3750	1.60	1.39	1.24	1.13
630-HCPL-0370-000E	HCPL-0370-000E	1	SO-8	50	275	3750	3.22	2.65	2.36	2.15
630-HCPL-0452-000E	HCPL-0452-000E	1	SO-8	16	600	3750	1.33	1.09	.97	.89
630-HCPL-0453-000E	HCPL-0453-000E	1	SO-8	16	600	3750	1.75	1.52	1.35	1.23
630-HCPL-0454-000E	HCPL-0454-000E	1	SO-8	16	600	3750	1.96	1.70	1.52	1.38
630-HCPL-0500-000E	HCPL-0500-000E	1	SO-8	16	600	3750	1.11	.96	.858	.78
630-HCPL-0501-000E	HCPL-0501-000E	1	SO-8	16	600	3750	1.24	1.07	.957	.87
630-HCPL-0501-500E	HCPL-0501-500E	1	SO-8	16	600	3750	1.28	1.11	.99	.90
630-HCPL-0530-000E	HCPL-0530-000E	2	SO-8	16	600	3750	2.88	2.50	2.23	2.03
630-HCPL-0531-000E	HCPL-0531-000E	2	SO-8	16	600	3750	2.99	2.59	2.31	2.10
630-HCPL-053L-000E	HCPL-053L-000E	2	SO-8	16	600	3750	3.24	2.81	2.51	2.28
630-HCPL-0600-000E	HCPL-0600-000E	1	SO-8	5	600	3750	1.58	1.30	1.16	1.05
630-HCPL-0600-500E	HCPL-0600-500E	1	SO-8	5	600	3750	1.54	1.33	1.19	1.08
630-HCPL-0601-000E	HCPL-0601-000E	1	SO-8	5	600	3750	1.58	1.30	1.16	1.05
630-HCPL-0601-500E	HCPL-0601-500E	1	SO-8	5	600	3750	1.54	1.33	1.19	1.08
630-HCPL-060L-000E	HCPL-060L-000E	1	SO-8	5	600	3750	1.71	1.48	1.32	1.20
630-HCPL-0611-000E	HCPL-0611-000E	1	SO-8	5	600	3750	1.92	1.67	1.49	1.35
630-HCPL-0611-500E	HCPL-0611-500E	1	SO-8	5	600	3750	1.84	1.61	1.52	1.29
630-HCPL-061A-000E	HCPL-061A-000E	1	SO-8	3	600	3750	2.20	1.91	1.70	1.55
630-HCPL-061N-000E	HCPL-061N-000E	1	SO-8	3	600	3750	2.35	2.04	1.82	1.65
630-HCPL-0630-000E	HCPL-0630-000E	2	SO-8	5	600	3750	3.88	3.37	3.00	2.73
630-HCPL-0630-500E	HCPL-0630-500E	2	SO-8	5	600	3750	3.68	3.22	3.04	2.58
630-HCPL-0631-000E	HCPL-0631-000E	2	SO-8	5	600	3750	3.88	3.37	3.00	2.73
630-HCPL-0631-500E	HCPL-0631-500E	2	SO-8	5	600	3750	3.92	3.40	3.04	2.76
630-HCPL-063A-000E	HCPL-063A-000E	2	SO-8	3	600	3750	5.01	4.35	3.88	3.53
630-HCPL-063L-000E	HCPL-063L-000E	2	SO-8	5	600	3750	4.26	3.70	3.30	3.00
630-HCPL-063N-000E	HCPL-063N-000E	2	SO-8	3	600	3750	6.61	5.74	5.12	4.65
630-HCPL-0661-000E	HCPL-0661-000E	2	SO-8	5	600	3750	6.39	5.55	4.95	4.50
630-HCPL-0700-000E	HCPL-0700-000E	1	SO-8	0.5	700	3750	1.27	1.09	.97	.89
630-HCPL-0701-000E	HCPL-0701-000E	1	SO-8	0.5	700	3750	1.42	1.22	1.09	.99