

## KRPA SERIES: OCTAL-TYPE ENCLOSED GENERAL PURPOSE RELAYS

**Specifications:**

- Enclosure: Clear polycarbonate cover
- Expected Mechanical life: 100,000 operations min.
- 3W
- Contact material: 5A - Silver; 10A - AgCdO



For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	P&B Part No.	Fig.	Coil Voltage	Contact Form	Contact Rating	Price Each			
						1	25	50	100
655-KRPA-11AG-12	KRPA-11AG-12	A1	12VAC	DPDT	10A	14.00	12.11	10.93	8.75
655-KRPA-11AG-24	KRPA-11AG-24	A1	24VAC	DPDT	10A	10.95	10.00	9.23	8.56
655-KRPA-11AG-120	KRPA-11AG-120	A1	120VAC	DPDT	10A	12.00	10.73	9.90	9.20
655-KRPA-11AG-240	KRPA-11AG-240	A1	240VAC	DPDT	10A	15.98	13.96	12.65	9.95
655-KRPA-11DG-12	KRPA-11DG-12	A1	12VDC	DPDT	10A	11.16	10.21	9.41	8.69
655-KRPA-11DG-24	KRPA-11DG-24	A1	24VDC	DPDT	10A	12.31	10.15	9.40	8.72
655-KRPA-11DG-48	KRPA-11DG-48	A1	48VDC	DPDT	10A	14.92	13.12	11.87	9.35
655-KRPA-11DG-110	KRPA-11DG-110	A1	110VDC	DPDT	10A	13.88	13.11	11.85	9.34
655-KRPA-11DN-12	KRPA-11DN-12	A1	12VDC	DPDT	10A	13.83	12.41	11.28	9.01
655-KRPA-11DN-24	KRPA-11DN-24	A1	24VDC	DPDT	10A	10.13	9.65	9.24	8.64
655-KRPA-11DN-110	KRPA-11DN-110	A1	110VDC	DPDT	10A	14.24	12.87	11.79	10.89
655-KRPA-11AN-12	KRPA-11AN-12	A1	12VAC	DPDT	10A	17.79	14.51	14.31	13.68
655-KRPA-11AN-24	KRPA-11AN-24	A1	24VAC	DPDT	10A	11.32	10.35	9.56	8.88
655-KRPA-11AN-120	KRPA-11AN-120	A1	120VAC	DPDT	10A	10.81	10.30	9.62	9.23
655-KRPA-11AN-240	KRPA-11AN-240	A1	240VAC	DPDT	10A	16.38	14.35	12.91	10.25
655-KRPA-11AY-12	KRPA-11AY-12	A1	12VAC	DPDT	5A	17.82	14.01	13.81	12.26
655-KRPA-11AY-24	KRPA-11AY-24	A1	24VAC	DPDT	5A	14.03	12.27	11.10	8.75
655-KRPA-11AY-120	KRPA-11AY-120	A1	120VAC	DPDT	5A	10.23	9.73	9.32	8.93
655-KRPA-11DY-12	KRPA-11DY-12	A1	12VDC	DPDT	5A	11.21	10.42	9.97	9.56
655-KRPA-11DY-24	KRPA-11DY-24	A1	24VDC	DPDT	5A	10.91	10.38	9.92	8.71
655-KRPA-14AG-12	KRPA-14AG-12	A2	12VAC	3PDT	10A	19.44	15.44	15.23	14.93
655-KRPA-14AG-24	KRPA-14AG-24	A2	24VAC	3PDT	10A	12.07	11.48	10.98	9.58
655-KRPA-14AG-120	KRPA-14AG-120	A2	120VAC	3PDT	10A	11.51	10.95	10.48	9.82
655-KRPA-14AG-240	KRPA-14AG-240	A2	240VAC	3PDT	10A	20.40	17.35	17.27	17.07
655-KRPA-14DG-12	KRPA-14DG-12	A2	12VDC	3PDT	10A	10.72	10.18	9.72	9.25
655-KRPA-14DG-24	KRPA-14DG-24	A2	24VDC	3PDT	10A	12.52	11.41	10.35	9.75
655-KRPA-14DG-48	KRPA-14DG-48	A2	48VDC	3PDT	10A	19.60	16.62	15.50	14.60
655-KRPA-14DG-110	KRPA-14DG-110	A2	110VDC	3PDT	10A	13.68	12.51	11.53	10.70
655-KRPA-14AN-24	KRPA-14AN-24	A2	24VAC	3PDT	10A	12.44	11.80	11.31	10.79
655-KRPA-14AN-120	KRPA-14AN-120	A2	120VAC	3PDT	10A	15.70	14.82	13.39	10.51
655-KRPA-14AN-240	KRPA-14AN-240	A2	240VAC	3PDT	10A	22.98	15.64	15.24	15.06
655-KRPA-14DN-24	KRPA-14DN-24	A2	24VDC	3PDT	10A	12.28	11.48	10.96	10.05
655-KRPA-14AY-24	KRPA-14AY-24	A2	24VAC	3PDT	5A	17.82	15.44	15.21	13.48
655-KRPA-14AY-120	KRPA-14AY-120	A2	120VAC	3PDT	5A	19.29	17.88	17.42	17.02
655-KRPA-14AY-240	KRPA-14AY-240	A2	240VAC	3PDT	5A	24.00	17.35	17.23	15.15
655-KRPA-14DY-24	KRPA-14DY-24	A2	24VDC	3PDT	5A	14.91	10.89	10.35	9.79

DIMENSIONS: mm

**A**

DPDT

**B**

DPDT

**C**

**D**

**1**

DPDT

**2**

3PDT

**4PDT**

**E**

**F**

**G**

**H**

## KHAU SERIES: MULTICONTACT GENERAL PURPOSE RELAYS

**Specifications:**

- Enclosure: Clear polycarbonate cover
- Expected life: 100,000 operations at rated load
- Socket mount, solder terminals
- Contact material: 1A - Bifurcated cross bar, Au over Ag; 3A - Ag; 5A-AgCdO



For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	P&B Part No.	Fig.	Coil Voltage	Contact Form	Contact Rating	Price Each			
						1	25	50	100
655-KHAU-17A11-24	KHAU-17A11-24	B	24VAC	4PDT	3A	5.63	5.18	4.79	4.57
655-KHAU-17A11-120	KHAU-17A11-120	B	120VAC	4PDT	3A	6.33	5.79	5.39	5.25
*655-KHAU-17A11N-120	KHAU-17A11N-120	B	120VAC	4PDT	3A	8.85	8.15	7.54	6.71
655-KHAU-17A12-120	KHAU-17A12-120	B	120VAC	4PDT	5A	6.10	5.15	4.79	4.56
655-KHAU-17D12-24	KHAU-17D12-24	B	24VDC	4PDT	5A	6.13	5.20	4.81	4.60
655-KHAU-17D11-12	KHAU-17D11-12	B	12VDC	4PDT	3A	6.13	5.20	4.81	4.60
655-KHAU-17D11-24	KHAU-17D11-24	B	24VDC	4PDT	3A	6.10	5.15	4.79	4.56
655-KHAU-17A16-24	KHAU-17A16-24	B	24VAC	4PDT	1A	28.52	24.96	23.76	19.56

\* neon indicator

## SOCKETS AND ACCESSORIES

For quantities of 200 and up, call for quote.

MOUSER STOCK NO.	P&B Part No.	Fig.	Description	Price Each			
				1	25	50	100
<b>KRPA Series</b>							
655-27E122	27E122	C	8-pin screw terminal socket, 10A, for KRPA11	4.65	4.27	3.89	3.60
655-27E123	27E123	D	11-pin screw terminal socket, 10A, for KRPA14	5.16	4.72	4.36	4.01
655-27E891	27E891	E	8-pin DIN rail snap mount socket, 10A, for KRPA11	5.38	4.90	4.49	3.91
655-27E892	27E892	F	11-pin DIN rail snap mount socket, 10A, for KRPA14	7.36	6.76	6.23	5.79
655-20C176	20C176	--	Hold down spring. Mounts to socket with socket screws	2.11	1.84	1.67	1.32
655-20C318	20C318	--	Hold down spring for use with 27E891, 27E892	.28	.24	.21	.18
655-24A110	24A110	--	Aluminum DIN rail track, 36"	10.28	9.42	8.68	8.01
655-24A071	24A071	--	Steel mounting clip with screw	2.10	1.84	1.67	1.32
655-24A072	24A072	--	Plastic twist mounting clip	.69	.65	.58	.50
655-40G432	40G432	--	Plastic insulator	1.59	1.46	1.30	1.04
<b>KHAU Series</b>							
655-27E006	27E006	G	Solder socket w/ grounding provision for KHAU, KHS	1.60	1.39	1.30	1.09
655-27E007	27E007	G	PCB terminals socket w/ grounding provision, for KHAU, KHS	1.28	1.18	1.07	1.01
655-27E023	27E023	G	PCB terminals socket w/out grounding provision, for KHAU, KHS	1.28	1.16	1.06	.89
655-27E166	27E166	H	Screw terminal socket w/ grounding provision for KHAU, KHS	11.90	10.70	9.75	7.80
655-27E894	27E894	H	Screw terminal, DIN rail snap-mount socket, for KHAU, KHS	7.90	7.20	6.69	6.17
655-24A110	24A110	--	Aluminum DIN rail track, 36"	10.28	9.42	8.68	8.01
655-20C217	20C217	--	Hold down spring for 27E006, 27E007, and 27E023	.28	.24	.21	.18
655-20C297	20C297	--	Hold down spring for 27E166 and 27E894	.28	.24	.21	.18