


KEYSTONE Hardware



HEX AND ROUND STANDOFFS



For quantities of 500 and up, call for quote.

Length "L" (in.)	Aluminum Clear Iridite				Brass Zinc Plate			
	Hex		Round		Hex		Round	
	MOUSER STOCK NO.	MOUSER STOCK NO.	1	100	MOUSER STOCK NO.	MOUSER STOCK NO.	1	100
2-56 Thread (.156 O.D.)								
.187	534-1797A	534-1801A	.74	.43	534-1798A	534-1802A	.88	.46
.250	534-1797B	534-1801B	.78	.47	534-1798B	534-1802B	.77	.44
.312	534-1797C	534-1801C	.82	.47	534-1798C	534-1802C	1.16	.66
.375	534-1797D	534-1801D	.85	.70	534-1798D	534-1802D	1.10	.63
4-40 Thread (.187 O.D.)								
.250	534-1891	534-2025	.34	.19	534-1450	534-1547	.50	.26
.375	534-1892	534-2026	.40	.23	534-1803	534-1864	.68	.34
.500	534-1893	534-2027	.35	.28	534-1656	534-1657	.50	.29
.625	534-1894	534-2028	.40	.29	534-1804	-----	.68	.39
.750	534-1895	534-2029	.44	.32	534-1656A	534-1657A	.64	.38
.875	534-1896	534-2030	.60	.35	534-1805	534-1866	.83	.48
1.000	534-1897	534-2031	.85	.46	534-1656B	534-1657B	.83	.50
4-40 Thread (.250 O.D.)								
.250	534-2201	534-3478	.33	.18	534-1450A	534-1547A	.45	.27
.375	534-2202	534-3479	.30	.21	534-1450B	534-1547B	.53	.29
.500	534-2203	534-3480	.37	.25	534-1450C	534-1547C	.55	.36
.625	534-1808	534-1839	.43	.22	534-1829	-----	.79	.42
.750	534-2204	534-3481	.46	.28	534-1450D	534-1547D	.81	.57
.875	534-1809	534-1846	.66	.37	534-1830	534-1876	.92	.52
1.000	534-2205	534-3482	.51	.41	534-1450E	534-1547E	1.10	.69
1.500	534-2206	534-3483	.82	.72	-----	-----	---	---
2.000	534-2207	534-3484	1.39	.80	534-1832	534-1878	1.40	1.26
6-32 Thread (.250 O.D.)								
.250	534-2208	534-3485	.28	.18	534-1451A	534-1548A	.38	.34
.375	534-2209	534-3486	.36	.19	534-1451B	534-1548B	.40	.28
.500	534-2210	534-3487	.33	.24	534-1451C	534-1548C	.52	.35


For quantities of 500 and up, call for quote.

Length "L" (in.)	Aluminum Clear Iridite				Brass Zinc Plate			
	Hex		Round		Hex		Round	
	MOUSER STOCK NO.	MOUSER STOCK NO.	1	100	MOUSER STOCK NO.	MOUSER STOCK NO.	1	100
6-32 Thread (.250 O.D.) (cont.)								
.625	534-1813	534-1847	.36	.27	534-1451D	534-1548D	.70	.50
.750	534-2211	534-3488	.46	.28	534-1451E	-----	.81	.57
.875	534-1816	534-1848	.48	.28	534-1833	534-1879	.74	.46
1.000	534-2212	534-3489	.71	.41	534-1635	534-1548F	.77	.51
1.250	534-1818	534-1853	.65	.56	534-1636	-----	.92	.86
1.500	534-2213	534-3490	.70	.65	534-1637	534-1882	1.06	.99
1.750	534-1819	534-1855	.89	.75	534-1638	-----	1.35	1.26
2.000	534-2214	534-3491	.84	.72	534-1639	534-1884	1.20	1.15
2.250	534-1820	534-1856	1.20	1.03	-----	534-1885	1.41	1.27
2.500	534-1825	534-1857	1.15	1.04	534-1643	-----	1.69	1.49
8-32 Thread (.250 O.D.)								
.250	534-2215	534-3492	.32	.17	534-1474A	534-1692A	.58	.32
.375	534-2216	534-3493	.40	.23	534-1474B	-----	.61	.28
.500	534-2217	534-3494	.42	.24	534-1474C	534-1692C	.59	.42
.625	534-1827	-----	.39	.30	-----	-----	---	---
.750	534-2218	534-3495	.60	.33	534-1474D	534-1692D	1.08	.53
.875	534-1828	-----	.78	.41	534-1836	-----	1.00	.55
1.000	534-2219	534-3496	.53	.36	534-1474E	534-1692E	1.11	.57
1.500	534-2220	534-3497	.86	.72	534-1837	-----	1.10	.98
2.000	534-2221	534-3498	.83	.74	534-1838	534-1899	1.25	1.18
8-32 Thread (.375 O.D.)								
.375	534-1926A	534-2315A	.96	.43	-----	-----	---	---
.500	534-1926B	534-2315B	1.08	.55	534-1452B	-----	1.22	.73
.625	534-1926C	534-2315C	1.09	.55	-----	-----	---	---
.750	534-1926D	534-2315D	1.22	.61	534-1452D	-----	1.41	1.20
1.000	534-1926E	534-2315E	1.42	.82	534-1452E	-----	1.95	1.20

Keystone

KEYSTONE HEX MALE/FEMALE THREADED STANDOFFS

DIMENSIONS: in.



† Int. thread - .130/.150 †† Int. thread - .250

For quantities of 500 and up, call for quote.

Length "L" (in.)	Stainless Steel				Brass Nickel Plate				Aluminum Clear Iridite			
	MOUSER STOCK NO.		Price Each		MOUSER STOCK NO.		Price Each		MOUSER STOCK NO.		Price Each	
	1	100	1	100	1	100	1	100	1	100		
4-40 Thread												
.250	† 534-8712	1.43	1.10	† 534-8713	.52	.30	† 534-8714	.37	.23			
.375	534-2087	1.66	1.15	534-7200	.58	.35	534-8400	.48	.30			
.500	534-2088	1.74	1.20	534-1944	.61	.52	534-8401	.68	.39			
.625	534-2089	2.96	1.25	534-1945	.74	.43	534-8402	.72	.41			
.750	534-2090	1.97	1.52	534-1946	.84	.48	534-8403	.76	.38			
.875	534-2091	2.18	1.89	534-7201	.79	.50	534-8404	.80	.44			
1.000	534-2092	1.63	1.38	534-1947	1.02	.56	534-8405	.86	.43			
1.125	534-2093	3.66	2.19	534-7202	1.10	.67	534-8406	1.04	.59			
1.250	534-2094	2.22	1.70	534-1948	1.57	.95	534-8407	.76	.53			
1.375	534-2095	3.44	2.36	534-1949	1.61	1.21	534-8408	1.23	.72			
1.500	534-2096	2.59	2.08	534-1950	1.57	1.16	534-8409	1.26	.73			
1.625	-----	---	---	534-7203	1.59	.90	534-8410	1.31	.77			
1.750	534-2098	2.67	1.85	-----	---	---	534-8411	1.32	.77			
2.000	534-2099	2.60	1.87	534-1951	1.62	1.16	534-8412	1.37	.79			
6-32 Thread												
.250	† 534-8715	1.13	.87	† 534-8716	.47	.28	† 534-8717	.34	.25			
.375	†† 534-2119	1.06	.75	†† 534-7210	.60	.33	†† 534-8413	.52	.30			
.500	534-2120	1.66	.82	534-1952	.53	.46	534-8414	.35	.27			
.625	534-2121	1.21	.86	534-1953	.81	.42	534-8415	.45	.37			
.750	534-2122	2.01	.99	534-1954	.87	.55	534-8416	.66	.37			
.875	534-2123	2.07	1.45	534-7211	.92	.55	534-8417	.70	.41			
1.000	534-2124	2.09	1.02	534-1644	1.02	.58	534-8418	.84	.62			
1.125	534-2125	1.63	1.32	534-7212	1.08	.65	534-8419	.76	.45			
1.250	534-2126	2.56	1.90	534-1955	1.27	.82	534-8420	.81	.47			
1.375	-----	---	---	534-1956	1.38	.87	534-8421	.92	.52			
1.500	534-2128	2.63	1.80	534-1645	1.40	.80	534-8422	1.15	.60			
1.625	534-2129	1.80	1.45	534-7214	1.59	1.13	534-8423	1.06	.62			
1.750	534-2130	2.69	1.31	534-7215	1.90	1.01	534-8424	.76	.67			
2.000	534-2131	1.57	1.36	534-1646	1.90	1.15	534-8425	1.14	.65			
8-32 Thread												
.375	†† 534-2149	3.01	1.74	†† 534-7220	.68	.42	†† 534-8426	.68	.39			
.500	534-2150	2.24	1.56	534-1957	.69	.41	534-8427	.68	.39			
.625	534-2151	2.28	1.54	534-1958	.96	.58	534-8428	.72	.36			
.750	534-2152	2.42	1.68	534-1959	1.00	.60	534-8429	.80	.40			
.875	534-2153	3.49	2.40	-----	---	---	534-8430	.90	.50			
1.000	534-2154	2.40	1.74	534-1960	1.15	.60	534-8431	.80	.52			
1.125	534-2155	3.02	2.51	534-7222	1.17	.97	534-8432	1.23	.71			
1.250	534-2156	3.59	3.29	534-1961	1.57	.97	534-8433	1.27	.71			
1.375	534-2157	3.94	2.87	-----	---	---	534-8434	1.37	.79			
1.500	534-2158	3.50	2.57	534-1963	1.67	1.02	534-8435	1.39	.80			
1.625	534-2159	5.48	3.15	534-7224	1.69	1.17	534-8436	1.37	.82			
1.750	534-2160	5.55	3.18	534-7225	1.60	1.15	534-8437	1.02	.82			
2.000	534-2161	3.74	2.72	534-1964	1.90	1.15	534-8438	1.03	.82			


KEYSTONE THREADED CERAMIC STANDOFFS

Features:

- Grade L5 Ceramic
- Ideal for very high temperature conditions
- Exceptional strength in compression and tension
- Withstands very high voltage without flashover



RoHS Compliant



For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Thread Size	Dimensions (in.)			Price Each		
		L	O.D.	D	1	100	500
534-7710	6-32	.250	.250	Thru	1.79	1.35	1.22
534-7711	6-32						