

AULT AC Adapters



PW170KB SERIES, 10-15W SINGLE OUTPUT

- 100-240VAC Universal Input
- Desktop and Wall Plug Style with Interchangeable Blades (Kit sold separately)
- Impact Resistant Polycarbonate Enclosure
- 2.5 x 5.5mm Output Connector
- Regulated Output with Low Ripple
- 3 year warranty
- Designed to Meet EISA Requirements
- No Load Power Consumption <50W



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Wallmount Models								
675-PW170KB0503B01	PW170KB0503B01	5V	2.00A	10.00W	18.31	16.91	15.68	
675-PW170KB0903B01	PW170KB0903B01	9V	1.50A	13.50W	18.31	16.91	15.68	
675-PW170KB1203B01	PW170KB1203B01	12V	1.20A	15.00W	18.31	16.91	15.68	
675-PW170KB2403B01	PW170KB2403B01	24V	0.63A	15.12W	18.31	16.91	15.68	
Desktop Models (AC Input Cord Not Included)								
675-PW170KB0503F01	PW170KB0503F01	5V	2.00A	10.00W	16.00	14.86	13.72	
675-PW170KB0903F01	PW170KB0903F01	9V	1.50A	13.50W	16.00	14.86	13.72	
675-PW170KB1203F01	PW170KB1203F01	12V	1.20A	15.00W	16.00	14.86	13.72	
675-PW170KB2403F01	PW170KB2403F01	24V	0.63A	15.12W	16.09	14.86	13.83	
AC Input Cord								
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black					4.81	4.38	---

AC Interchangeable Blade Kit

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Description	Price Each		
		1	10	25
831-KT1027K	Includes Europe, United Kingdom, Australian	4.63	4.28	4.13

PW172KB SERIES, 15-19W SINGLE OUTPUT

- 100-240VAC Universal Input
- Desktop and Wall Plug Style with Interchangeable Blades (Kit sold separately)
- Impact Resistant Polycarbonate Enclosure
- 2.5 x 5.5mm Output Connector
- Regulated Output with Low Ripple
- 3 year warranty
- Designed to Meet EISA Requirements
- No Load Power Consumption <50W



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Wallmount Models								
675-PW172KB0503B01	PW172KB0503B01	5V	3.00A	15W	20.57	19.02	18.00	
675-PW172KB0903B01	PW172KB0903B01	9V	2.00A	18W	20.57	19.02	17.65	
675-PW172KB1203B01	PW172KB1203B01	12V	1.50A	18W	20.57	19.02	17.65	
675-PW172KB2403B01	PW172KB2403B01	24V	0.75A	18W	20.57	19.02	17.65	
Desktop Models (AC Input Cord Not Included)								
675-PW172KB0503F01	PW172KB0503F01	5V	3.00A	15W	18.16	16.81	15.60	
675-PW172KB0903F01	PW172KB0903F01	9V	2.00A	18W	18.16	16.81	15.60	
675-PW172KB1203F01	PW172KB1203F01	12V	1.50A	18W	18.16	16.81	15.71	
675-PW172KB2403F01	PW172KB2403F01	24V	0.75A	18W	18.16	16.81	15.60	
AC Input Cord								
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black					4.81	4.38	---

PW173KB SERIES, 20-32W SINGLE OUTPUT

- 100-240VAC Universal Input
- Desktop and Wall Plug Style
- 2.5 x 5.5mm Output Connector
- Regulated Output with Low Ripple
- 3 year warranty
- Designed to Meet EISA Requirements
- No Load Power Consumption <50W



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Wallmount Models								
675-PW173KB0503B01	PW173KB0503B01	5V	4.00A	20.0W	30.36	27.90	25.97	
675-PW173KB0903B01	PW173KB0903B01	9V	3.00A	27.0W	28.76	25.56	23.96	
675-PW173KB1203B01	PW173KB1203B01	12V	2.50A	30.0W	28.76	25.56	23.96	
675-PW173KB2403B01	PW173KB2403B01	24V	1.33A	31.9W	28.76	25.56	23.96	
675-PW173KB4803B01	PW173KB4803B01	48V	0.67A	32.2W	30.36	27.90	25.97	
Desktop Models (AC Input Cord Not Included)								
675-PW173KB0503F01	PW173KB0503F01	5V	4.00A	20.0W	30.71	28.22	26.27	
675-PW173KB0903F01	PW173KB0903F01	9V	3.00A	27.0W	28.76	26.56	24.96	
675-PW173KB1203F01	PW173KB1203F01	12V	2.50A	30.0W	28.76	25.56	23.96	
675-PW173KB2403F01	PW173KB2403F01	24V	1.33A	31.9W	28.76	26.56	24.96	
675-PW173KB4803F01	PW173KB4803F01	48V	0.67A	32.2W	30.71	28.22	26.27	
AC Input Cord								
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black					4.81	4.38	---

PW153KB SERIES, 40W SINGLE OUTPUT

- 100-240VAC Universal Input
- 2.5 x 5.5mm Output Connector
- Regulated Output with Low Ripple
- Impact Resistant Polycarbonate Enclosure
- Designed to Meet EISA Requirements



RoHS Compliant

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Models (AC Input Cord Not Included)								
675-PW153KB1203F01	PW153KB1203F01	12V	3.4A	40.8W	33.06	30.99	28.92	
675-PW153KB2403F01	PW153KB2403F01	24V	1.7A	40.8W	33.06	30.99	28.92	
AC Input Cord								
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black					4.81	4.38	---

PW174KB SERIES, 60-65W SINGLE OUTPUT

- 100-240VAC Universal Input
- 2.5 x 5.5mm Output Connector
- Impact Resistant
- Regulated Output with Low Ripple
- 3 year warranty
- Designed to Meet EISA Requirements



RoHS Compliant

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Models (AC Input Cord Not Included)								
675-PW174KB1203F01	PW174KB1203F01	12V	5.0A	60.0W	44.54	41.75	38.96	
675-PW174KB2403F01	PW174KB2403F01	24V	2.7A	64.8W	44.54	41.75	38.96	
AC Input Cord								
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black					4.81	4.38	---

PW156 SERIES, 75W SINGLE OUTPUT

- 100-240VAC Universal Input
- 2.5 x 5.5mm Output Connector
- Low Life-Cycle Operation Cost
- Complies with EMI/RFI Regulations
- Impact Resistant, Non-vented Polycarbonate Enclosure
- ENERGY STAR Level IV Compliant



RoHS Compliant

* 12V model rated 70W with input voltages rated 100-119V, 75W with input voltages rated 120-240VAC.

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Models (AC Input Cord Not Included)								
* 675-PW156R1203N01	PW156RA1203N01	12V	6.30A	75W	74.48	71.58	67.10	
675-PW156R2403N01	PW156RA2403N01	24V	3.10A	75W	74.48	71.58	67.10	
AC Input Cord								
562-223021-01	8" AC input cord, 18AWG, Black					2.52	2.35	2.10

CENT1120 SERIES, 120W SINGLE OUTPUT

- 100-240VAC Universal Input
- IPX1 Compliant
- Complies with EMI/RFI Regulations
- Impact Resistant, Non-Vented Polycarbonate Enclosure
- 3 year warranty
- Meets ENERGY STAR Criteria level IV and EISA Requirements



RoHS Compliant

* 12V model rated 100W with input voltages rated 100-110VAC, 110W with input voltages rated 110VAC-240VAC

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Models (AC Input Cord Not Included)								
* 675-CENT11201251F01	CENT1120A1251F01	12V	9.17A	110W	99.48	88.40	85.45	
675-CENT11202451F01	CENT1120A2451F01	24V	5.00A	120W	129.10	121.70	117.59	
675-CENT1120A4803F01	CENT1120A4803F01	48V	2.50A	120W	95.79	88.40	85.45	
AC Input Cord								
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black					4.81	4.38	---