



## EC SERIES FILTERS

High Performance Compact RFI Power Line Filters with IEC Connectors

• 3 to 10 Amps; 120/250 Volts AC; 50/60Hz



For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Corcom Part No.	Fig.	Amps	Dimensions: in. (mm)					Price Each			
				A	B	C	D	E	1	10	25	50
592-3EC1	3EC1	A	3	2.62 (66.5)	1.19 (30.2)	0.81 (20.6)	1.575 (40.01)	1.98 (50.3)	17.60	16.40	16.10	15.73
592-6EC1	6EC1	A	6	2.62 (66.5)	1.19 (30.2)	0.81 (20.6)	1.575 (40.01)	1.98 (50.3)	17.60	16.34	16.30	15.45
592-10EC1	10EC1	A	10	2.62 (66.5)	1.19 (30.2)	0.81 (20.6)	1.575 (40.01)	1.98 (50.3)	17.72	16.25	15.00	13.93

## EMC SERIES FILTERS

Compact Dual Stage RFI Power Line Filters

• 6 to 30 Amps; 120/250 Volts AC; 50/60Hz



For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Corcom Part No.	Fig.	Amps	Dimensions: in. (mm)					Price Each			
				A	B	C	D	E	1	10	25	50
592-6EMC1	6EMC1	B	6	3.85 (97.8)	2.07 (52.6)	1.16 (29.5)	2.938 (74.6)	3.35 (85.1)	19.05	17.68	16.50	15.48
592-6EMC3	6EMC3	C	6	2.56 (65.0)	2.07 (52.6)	1.16 (29.5)	2.938 (74.6)	3.35 (85.1)	19.06	17.69	16.50	15.48
592-10EMC1	10EMC1	B	10	3.85 (97.8)	2.07 (52.6)	1.53 (38.91)	2.938 (74.6)	3.35 (85.1)	18.73	17.40	16.64	15.53
592-10EMC3	10EMC3	C	10	2.56 (65.0)	2.07 (52.6)	1.53 (38.9)	2.938 (74.6)	3.35 (85.1)	17.05	15.83	14.77	13.85
592-15EMC1	15EMC1	B	15	4.97 (126.2)	2.25 (57.2)	1.78 (45.2)	4.063 (103.2)	4.46 (113.3)	34.32	31.85	29.73	27.88
592-20EMC1	20EMC1	B	20	4.97 (126.2)	2.25 (57.2)	1.78 (45.2)	4.063 (103.2)	4.46 (113.3)	48.46	45.44	38.21	34.76
592-30EMC6	30EMC6	D	20	6.05 (153.7)	3.12 (79.12)	2.18 (55.4)	3.50 (88.9)	3.96 (100.6)	45.82	42.76	40.09	37.73

## RK SERIES FILTERS

Compact Single Stage Power Line Filters

• 3-20 Amps; 250 Volts AC; 50/60Hz



RoHS Compliant



For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Corcom Part No.	Fig.	Amps	Dimensions: in. (mm)					Price Each			
				A	B	C	D	E	1	10	25	50
592-3ERK1	3ERK1	E	3	3.35 (85.09)	1.81 (45.97)	1.16 (29.46)	2.375 (60.33)	2.78 (70.61)	30.86	21.60	19.62	18.04
592-6ERK1	6ERK1	E	6	3.35 (85.09)	3.35 (85.09)	1.82 (46.23)	1.28 (32.51)	2.375 (74.67)	34.16	23.91	21.72	19.97
592-20ERK1	20ERK1	E	20	3.85 (97.79)	2.07 (52.58)	1.78 (45.21)	2.94 (74.67)	3.35 (85.09)	53.24	44.07	37.23	33.88

## S SERIES FILTERS

Multipurpose Power Line RFI Filter for Emission Control

• 6 to 20 Amps; 120/250 Volts AC; 50/60Hz



For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Corcom Part No.	Fig.	Amps	Dimensions: in. (mm)					Price Each			
				A	B	C	D	E	1	10	25	50
592-6VS1	6VS1	F	6	3.86 (98.0)	2.08 (52.8)	1.53 (38.9)	2.938 (74.63)	3.34 (84.8)	22.23	20.39	18.83	17.47
592-10VS1	10VS1	F	10	3.86 (98.0)	2.08 (52.8)	1.53 (38.9)	2.938 (74.63)	3.34 (84.8)	26.18	24.00	22.15	20.56
592-20VS1	20VS1	G	20	5.23 (132.8)	3.38 (85.9)	1.53 (38.9)	3.75 (95.25)	4.20 (106.7)	60.52	56.20	53.51	48.99
592-60VS6	60VS6	G	60	7.2 (182.88)	3.08 (78.23)	2.28 (57.91)	5.63 (142.87)	6.28 (158.78)	79.50	73.83	72.29	71.18

## T SERIES FILTERS

High Performance RFI Power Line Filters for Switching Power Supplies

• 6 to 20 Amps; 120/250 Volts AC; 50/60Hz



RoHS Compliant



For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Corcom Part No.	Fig.	Amps	Dimensions: in. (mm)					Price Each			
				A	B	C	D	E	1	10	25	50
592-6ET1	6ET1	H	6	3.56 (90.4)	2.15 (54.6)	1.81 (46.0)	2.938 (74.63)	3.38 (85.9)	31.29	28.88	26.83	25.03
592-10ET1	10ET1	H	10	4.69 (119.1)	2.27 (57.7)	1.80 (45.7)	4.063 (103.2)	4.47 (113.5)	41.34	38.37	35.63	33.25
592-10VT1	10VT1	H	10	4.69 (119.1)	2.27 (57.7)	1.80 (45.7)	4.063 (103.2)	4.47 (113.5)	49.77	47.92	47.36	45.69

## V AND W SERIES

Multipurpose Power Line RFI Filters for Emission Control and High-Noise Industrial Environments

• 3 to 20 Amps; 120/250 Volts AC; 50/60Hz



For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	Corcom Part No.	Fig.	Amps	Dimensions: in. (mm)					Price Each			
				A	B	C	D	E	1	10	25	50
592-3VW1	3VW1	F	3	3.36 (85.3)	1.82 (46.2)	1.28 (32.5)	2.375 (60.33)	2.78 (70.6)	26.47	24.26	22.41	20.80
592-6VW1	6VW1	F	6	3.86 (98.0)	2.08 (52.8)	1.53 (38.9)	2.938 (74.63)	3.34 (84.8)	25.14	23.03	21.27	19.75
592-6VW1	6VW1	F	6	3.86 (98.0)	2.08 (52.8)	1.53 (38.9)	2.938 (74.63)	3.34 (84.8)	26.45	24.25	22.39	20.79
592-10VW1	10VW1	F	10	3.86 (98.0)	2.08 (52.8)	1.53 (38.9)	2.938 (74.63)	3.34 (84.8)	28.35	27.53	26.11	23.99
592-10VW1	10VW1	F	10	3.86 (98.0)	2.08 (52.8)	1.53 (38.9)	2.938 (74.63)	3.34 (84.8)	30.36	29.65	29.10	27.65
592-20VW1	20VW1	G	20	5.23 (132.8)	3.38 (85.9)	1.53 (38.9)	3.75 (95.25)	4.20 (106.7)	63.35	58.82	55.80	51.28
592-20VW1	20VW1	G	20	5.23 (132.8)	3.38 (85.9)	1.53 (38.9)	3.75 (95.25)	4.20 (106.7)	64.73	60.11	59.81	56.71