

# Consumer and Sealed Lead-Acid Battery Finder

## NON-RECHARGEABLE

\*Pack of 4 †Pack of 2

| Size    | Volt | mAh    | Chemistry     | MOUSER STOCK NO.    | Manufacturer         | Price Each  |
|---------|------|--------|---------------|---------------------|----------------------|-------------|
| AAAA    | 1.5  | 550    | Alkaline      | <b>525-E96</b>      | Energizer            | <b>1.24</b> |
| AAA     | 1.5  | 300    | Zinc Chloride | <b>639-HD-AAA</b>   | Golden Power         | .25         |
| AAA     | 1.5  | NR     | Alkaline      | <b>573-24A</b>      | GP                   | .40         |
| AAA     | 1.5  | 1,100  | Carbon Zinc   | <b>525-1212SW-4</b> | Eveready             | *2.07       |
| AAA     | 1.5  | 1,100  | Alkaline      | <b>613-PC2400</b>   | Duracell Procell     | .75         |
| AAA     | 1.5  | 1,150  | Alkaline      | <b>613-MN2400</b>   | Duracell             | 1.18        |
| AAA     | 1.5  | 1,250  | Alkaline      | <b>525-EN92</b>     | Energizer Industrial | .82         |
| AAA     | 1.5  | 1,250  | Alkaline      | <b>525-E92</b>      | Energizer            | 1.94        |
| AAA     | 1.5  | NR     | Alkaline      | <b>613-MX2400</b>   | Duracell M3 Ultra    | 1.52        |
| AAA     | 1.5  | 1,250  | Lithium       | <b>525-L92BP-2</b>  | Energizer            | †7.19       |
| AA      | 1.5  | 540    | Carbon Zinc   | <b>525-1215SW-4</b> | Eveready             | *2.07       |
| AA      | 1.5  | 570    | Zinc Chloride | <b>639-HD-AA</b>    | Golden Power         | .27         |
| AA      | 1.5  | NR     | Alkaline      | <b>573-15A</b>      | GP                   | .40         |
| AA      | 1.5  | 2,450  | Alkaline      | <b>613-PC1500</b>   | Duracell Procell     | .70         |
| AA      | 1.5  | 2,850  | Alkaline      | <b>525-EN91</b>     | Energizer Industrial | .82         |
| AA      | 1.5  | 2,850  | Alkaline      | <b>525-E91</b>      | Energizer            | 1.89        |
| AA      | 1.5  | 2,850  | Alkaline      | <b>613-MN1500</b>   | Duracell             | 2.68        |
| AA      | 1.5  | NR     | Alkaline      | <b>613-MX1500</b>   | Duracell M3 Ultra    | 1.52        |
| AA      | 1.5  | 2,900  | Lithium       | <b>525-L91BP-2</b>  | Energizer            | †7.19       |
| C       | 1.5  | 1,600  | Carbon Zinc   | <b>639-HD-C</b>     | Golden Power         | .58         |
| C       | 1.5  | 3,800  | Carbon Zinc   | <b>525-1235-4</b>   | Eveready             | *2.70       |
| C       | 1.5  | NR     | Alkaline      | <b>573-14A</b>      | GP                   | 1.17        |
| C       | 1.5  | 7,100  | Alkaline      | <b>613-PC1400</b>   | Duracell Procell     | 1.36        |
| C       | 1.5  | 7,800  | Alkaline      | <b>613-MN1400</b>   | Duracell             | 2.83        |
| C       | 1.5  | 8,350  | Alkaline      | <b>525-EN93</b>     | Energizer Industrial | 1.14        |
| C       | 1.5  | 8,350  | Alkaline      | <b>525-E93</b>      | Energizer            | 2.51        |
| D       | 1.5  | 3,300  | Carbon Zinc   | <b>639-HD-D</b>     | Golden Power         | .82         |
| D       | 1.5  | 8,000  | Carbon Zinc   | <b>525-1250-2</b>   | Eveready             | *1.67       |
| D       | 1.5  | 14,000 | Alkaline      | <b>613-PC1300</b>   | Duracell Procell     | 1.68        |
| D       | 1.5  | NR     | Alkaline      | <b>573-13A</b>      | GP                   | 1.54        |
| D       | 1.5  | 15,000 | Alkaline      | <b>613-MN1300</b>   | Duracell             | 2.27        |
| D       | 1.5  | 18,000 | Alkaline      | <b>525-EN95</b>     | Energizer Industrial | 1.28        |
| D       | 1.5  | 18,000 | Alkaline      | <b>525-E95</b>      | Energizer            | 2.51        |
| N       | 1.5  | NR     | Alkaline      | <b>573-910A</b>     | GP                   | .65         |
| N       | 1.5  | 1,000  | Alkaline      | <b>525-E90</b>      | Energizer            | 1.42        |
| 9V      | 9    | 209    | Carbon Zinc   | <b>639-GP-9V</b>    | Golden Power         | .86         |
| 9V      | 9    | 228    | Carbon Zinc   | <b>639-HD-9V</b>    | Golden Power         | 1.56        |
| 9V      | 9    | NR     | Alkaline      | <b>573-1604A</b>    | GP                   | 1.90        |
| 9V      | 9    | 565    | Alkaline      | <b>613-PC1604</b>   | Duracell Procell     | 2.33        |
| 9V      | 9    | 580    | Alkaline      | <b>613-MN1604</b>   | Duracell             | 3.38        |
| 9V      | 9    | 625    | Alkaline      | <b>525-EN22</b>     | Energizer Industrial | 2.19        |
| 9V      | 9    | 625    | Alkaline      | <b>525-522</b>      | Energizer            | 2.40        |
| 9V      | 9    | 1,200  | Lithium       | <b>5169-U9VL-FP</b> | Ultralife            | 6.53        |
| 9V      | 9    | 1,200  | Lithium       | <b>5169-U9VL-J</b>  | Ultralife            | 7.41        |
| Lantern | 6    | 12,000 | Carbon Zinc   | <b>525-1209</b>     | Eveready             | 3.79        |
| Lantern | 6    | 13,000 | Alkaline      | <b>613-MN908</b>    | Duracell             | 13.51       |
| ---     | 12   | 55     | Alkaline      | <b>573-23A</b>      | GP                   | .88         |
| ---     | 2    | 18     | Alkaline      | <b>573-25A</b>      | GP                   | .88         |
| ---     | 12   | 18     | Alkaline      | <b>573-27A</b>      | GP                   | .88         |

## RECHARGEABLE

\*Pack of 4 †Pack of 2

| Size | Volt | mAh   | Chemistry            | MOUSER STOCK NO.     | Manufacturer | Price Each |
|------|------|-------|----------------------|----------------------|--------------|------------|
| AAA  | 1.2  | 250   | Nickel-Cadmium       | <b>547-PS-AAA</b>    | Power Sonic  | 2.06       |
| AAA  | 1.2  | 250   | Nickel-Cadmium       | <b>639-N250AAA</b>   | Sanyo        | 3.42       |
| AAA  | 1.2  | 750   | Nickel Metal Hydride | <b>639-HR-4U</b>     | Sanyo        | 2.70       |
| AAA  | 1.2  | 750   | Nickel Metal Hydride | <b>525-NH12BP-4</b>  | Energizer    | *15.77     |
| AA   | 1.2  | 600   | Nickel-Cadmium       | <b>547-PS-AA</b>     | Power Sonic  | 2.08       |
| AA   | 1.2  | 600   | Nickel-Cadmium       | <b>573-60AAK</b>     | GP           | 2.40       |
| AA   | 1.2  | 700   | Nickel-Cadmium       | <b>639-N700AAC</b>   | Sanyo        | 2.94       |
| AA   | 1.2  | 900   | Nickel-Cadmium       | <b>639-KR900AAEC</b> | Sanyo        | 3.08       |
| AA   | 1.2  | 1,000 | Nickel-Cadmium       | <b>573-100AAK</b>    | GP           | 4.72       |
| AA   | 1.2  | 1,100 | Nickel-Cadmium       | <b>639-KR1100AAU</b> | Sanyo        | 3.61       |
| AA   | 1.2  | 1,600 | Nickel Metal Hydride | <b>573-GP160AA</b>   | GP           | 3.81       |
| AA   | 1.2  | 1,650 | Nickel Metal Hydride | <b>639-HR-3U</b>     | Sanyo        | 4.33       |
| AA   | 1.2  | 1,800 | Nickel Metal Hydride | <b>573-GP180AAHC</b> | GP           | 4.84       |
| AA   | 1.2  | 2,100 | Nickel Metal Hydride | <b>525-NH15BP-4</b>  | Energizer    | *15.77     |
| C    | 1.2  | 2,000 | Nickel-Cadmium       | <b>639-KR2000C</b>   | Sanyo        | *7.68      |
| C    | 1.2  | 2,200 | Nickel Metal Hydride | <b>525-NH35BP-2</b>  | Energizer    | †11.51     |
| D    | 1.2  | 2,200 | Nickel Metal Hydride | <b>525-NH50BP-2</b>  | Energizer    | †11.51     |
| D    | 1.2  | 4,000 | Nickel-Cadmium       | <b>547-PS-DL</b>     | Power Sonic  | †11.58     |
| D    | 1.2  | 4,400 | Nickel-Cadmium       | <b>639-KR4400D</b>   | Sanyo        | 13.09      |
| N    | 1.2  | 150   | Nickel-Cadmium       | <b>639-N150N</b>     | Sanyo        | 2.35       |
| 9V   | 7.2  | 150   | Nickel Metal Hydride | <b>525-NH22NBP</b>   | Energizer    | 11.51      |
| 9V   | 8.4  | 150   | Nickel Metal Hydride | <b>573-GP17R8H</b>   | GP           | 9.38       |
| 9V   | 8.4  | 150   | Nickel Metal Hydride | <b>672-05522</b>     | Varta        | 14.84      |



## SEALED LEAD-ACID (RECHARGEABLE)

\*\* Negative = .187" Faston, Positive = .250" Faston

| Volt | Nominal Capacity @ 20 Hr. Rate A.H. | Terminal Type | MOUSER STOCK NO.      | Manufacturer | Price Each |
|------|-------------------------------------|---------------|-----------------------|--------------|------------|
| 4    | 4.5                                 | .250" Faston  | <b>547-PS-445</b>     | Power Sonic  | 16.31      |
| 4    | 9.0                                 | .250" Faston  | <b>547-PS-490</b>     | Power Sonic  | 23.31      |
| 6    | 0.5                                 | Wire Leads    | <b>547-PS-605</b>     | Power Sonic  | 22.97      |
| 6    | 1.0                                 | .187" Faston  | <b>547-PS-610</b>     | Power Sonic  | 14.10      |
| 6    | 1.2                                 | .187" Faston  | <b>547-PS-612H</b>    | Power Sonic  | 9.63       |
| 6    | 1.3                                 | .187" Faston  | <b>632-GH613</b>      | CSB          | 6.64       |
| 6    | 1.3                                 | .187" Faston  | <b>658-LCR061R3P</b>  | Panasonic    | 15.87      |
| 6    | 3.3                                 | .187" Faston  | <b>632-GH633</b>      | CSB          | 10.44      |
| 6    | 3.4                                 | .187" Faston  | <b>547-PS-630</b>     | Power Sonic  | 19.09      |
| 6    | 3.4                                 | .187" Faston  | <b>658-LCR063R4PU</b> | Panasonic    | 26.45      |
| 6    | 4.5                                 | .187" Faston  | <b>632-GH645</b>      | CSB          | 7.58       |
| 6    | 4.5                                 | .187" Faston  | <b>632-GP645</b>      | CSB          | 11.66      |
| 6    | 4.5                                 | .187" Faston  | <b>547-PS-640</b>     | Power Sonic  | 10.26      |
| 6    | 4.5                                 | .187" Faston  | <b>658-LCR064R5P</b>  | Panasonic    | 15.84      |
| 6    | 6.5                                 | **            | <b>547-PS-665</b>     | Power Sonic  | 22.53      |
| 6    | 7.0                                 | .187" Faston  | <b>547-PS-670</b>     | Power Sonic  | 16.18      |
| 6    | 7.2                                 | .187" Faston  | <b>658-LCR067R2P</b>  | Panasonic    | 23.66      |
| 6    | 7.2                                 | .250" Faston  | <b>658-LCR067R2P1</b> | Panasonic    | 23.66      |
| 6    | 7.2                                 | .187" Faston  | <b>632-GP672</b>      | CSB          | 15.12      |
| 6    | 8.0                                 | .187" Faston  | <b>547-PS-682</b>     | Power Sonic  | 21.89      |
| 6    | 12.0                                | .187" Faston  | <b>547-PS-6100</b>    | Power Sonic  | 23.96      |
| 6    | 12.0                                | .187" Faston  | <b>632-GH6120</b>     | CSB          | 18.96      |
| 6    | 12.0                                | .187" Faston  | <b>632-GP6120</b>     | CSB          | 20.66      |
| 6    | 12.0                                | .187" Faston  | <b>658-LCR0612P</b>   | Panasonic    | 27.41      |
| 6    | 12.0                                | .250" Faston  | <b>658-LCR0612P1</b>  | Panasonic    | 27.41      |
| 6    | 12.0                                | .250" Faston  | <b>632-GP6120F2</b>   | CSB          | 20.66      |
| 6    | 12.0                                | **            | <b>547-PS-6120</b>    | Power Sonic  | 28.73      |
| 6    | 20.0                                | Nut and bolt  | <b>547-PS-6200</b>    | Power Sonic  | 64.72      |
| 6    | 36.0                                | .250" Faston  | <b>547-PS-6360</b>    | Power Sonic  | 79.35      |
| 12   | 0.8                                 | Mate-N-Lok    | <b>547-PS-1208</b>    | Power Sonic  | 24.67      |
| 12   | 1.2                                 | .187" Faston  | <b>547-PS-1212</b>    | Power Sonic  | 21.16      |
| 12   | 1.3                                 | .187" Faston  | <b>632-GH1213</b>     | CSB          | 10.72      |
| 12   | 1.3                                 | .187" Faston  | <b>658-LCR121R3PU</b> | Panasonic    | 32.56      |
| 12   | 2.5                                 | .187" Faston  | <b>547-PS-1220</b>    | Power Sonic  | 24.21      |
| 12   | 2.2                                 | .187" Faston  | <b>632-GH1222</b>     | CSB          | 13.36      |
| 12   | 2.2                                 | .187" Faston  | <b>632-GP1222</b>     | CSB          | 16.54      |
| 12   | 2.2                                 | .187" Faston  | <b>658-LCR122R2PU</b> | Panasonic    | 34.21      |
| 12   | 2.9                                 | .187" Faston  | <b>547-PS1229</b>     | Power Sonic  | 34.54      |
| 12   | 3.4                                 | .187" Faston  | <b>547-PS-1230</b>    | Power Sonic  | 27.77      |
| 12   | 3.4                                 | .187" Faston  | <b>632-GH1234</b>     | CSB          | 14.52      |
| 12   | 3.4                                 | .187" Faston  | <b>658-LCR123R4PU</b> | Panasonic    | 44.97      |
| 12   | 4.5                                 | .187" Faston  | <b>632-GP1245</b>     | CSB          | 18.82      |
| 12   | 5.0                                 | .187" Faston  | <b>547-PS1250F1</b>   | Power Sonic  | 21.62      |
| 12   | 5.0                                 | .250" Faston  | <b>547-PS1250F2</b>   | Power Sonic  | 21.62      |
| 12   | 7.0                                 | .187" Faston  | <b>632-GH1270</b>     | CSB          | 20.70      |
| 12   | 7.0                                 | .187" Faston  | <b>547-PS-1270</b>    | Power Sonic  | 27.56      |
| 12   | 7.2                                 | .187" Faston  | <b>632-GP1272</b>     | CSB          | 23.08      |
| 12   | 7.2                                 | .250" Faston  | <b>632-GP1272F2</b>   | CSB          | 22.02      |
| 12   | 7.2                                 | .187" Faston  | <b>658-LCR127R2P</b>  | Panasonic    | 39.26      |
| 12   | 7.2                                 | .250" Faston  | <b>658-LCR127R2P1</b> | Panasonic    | 39.26      |
| 12   | 8.0                                 | .187" Faston  | <b>547-PS-1282</b>    | Power Sonic  | 49.56      |
| 12   | 12.0                                | .250" Faston  | <b>547-PS-12100</b>   | Power Sonic  | 44.30      |
| 12   | 12.0                                | .250" Faston  | <b>632-GP12120F2</b>  | CSB          | 39.74      |
| 12   | 12.0                                | .250" Faston  | <b>547-PS-12120</b>   | Power Sonic  | 52.57      |
| 12   | 17.0                                | Nut and bolt  | <b>658-LCRD1217P</b>  | Panasonic    | 93.35      |
| 12   | 17.0                                | Nut and bolt  | <b>632-GP12170</b>    | CSB          | 57.56      |
| 12   | 17.0                                | Nut and bolt  | <b>632-EVX12170</b>   | CSB          | 60.30      |
| 12   | 17.5                                | Nut and bolt  | <b>547-PS-12180</b>   | Power Sonic  | 65.35      |
| 12   | 18.0                                | .250" Faston  | <b>547-PS-12180F</b>  | Power Sonic  | 79.31      |
| 12   | 26.0                                | Nut and bolt  | <b>632-EVX12260</b>   | CSB          | 85.84      |
| 12   | 26.0                                | .250" Faston  | <b>547-PS-12260</b>   | Power Sonic  | 100.23     |
| 12   | 26.0                                | Nut and bolt  | <b>632-GP12260</b>    | CSB          | 84.44      |
| 12   | 28.0                                | Nut and bolt  | <b>658-LCX1228P</b>   | Panasonic    | 143.30     |
| 12   | 28.0                                | Nut and bolt  | <b>547-PS12280</b>    | Power Sonic  | 125.01     |
| 12   | 33.0                                | Nut and bolt  | <b>658-LCLA1233P</b>  | Panasonic    | 139.86     |
| 12   | 34.0                                | Nut and bolt  | <b>632-EVX12340</b>   | CSB          | 96.58      |
| 12   | 35.0                                | Nut and bolt  | <b>547-PS-12350</b>   | Power Sonic  | 115.54     |
| 12   | 40.0                                | Nut and bolt  | <b>632-GP12400</b>    | CSB          | 126.96     |
| 12   | 75.0                                | Nut and bolt  | <b>547-PS-12750</b>   | Power Sonic  | 246.18     |
| 12   | 100.0                               | Nut and bolt  | <b>547-PS121000</b>   | Power Sonic  | 289.85     |

Please also see our offering of Battery Holders, Chargers, Computer, and Specialty Batteries