

POMONA Test Clips and Accessories



Pomona SMA PLUG 50 OHM CABLE

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.		Fig.	Description	Length (in.)	Price Each		
Mfr.	Mfr. Part No.				1	25	50
RG174/U							
565	4846-K-24	A	SMA male (plug) to SMA male (plug), 50Ω	24	44.44	42.32	40.20
565	4846-K-48	A	SMA male (plug) to SMA male (plug), 50Ω	48	44.44	42.32	40.20
565	4846-K-60	A	SMA male (plug) to SMA male (plug), 50Ω	60	44.44	42.32	40.20
RG316/U							
565	4846-BB-24	A	SMA male (plug) to SMA male (plug), 50Ω	24	49.47	47.11	44.75
565	4846-BB-48	A	SMA male (plug) to SMA male (plug), 50Ω	48	49.47	47.11	44.75
565	4846-BB-60	A	SMA male (plug) to SMA male (plug), 50Ω	60	49.47	47.11	44.75
RG142B/U							
565	4846X24	A	SMA male (plug) to SMA male (plug), 50Ω	24	65.53	62.41	59.29
565	4846X48	A	SMA male (plug) to SMA male (plug), 50Ω	48	65.53	62.41	59.29
565	4846-X-60	A	SMA male (plug) to SMA male (plug), 50Ω	60	65.53	62.41	59.29
565	72926-C-40	A	IEC Insulated BNC Male 50Ω Cable	40	12.74	12.13	11.52
565	5144-48-0	B	SMD Microtip Test Probe	48	13.67	13.02	12.37

Pomona BNC PLUG TO SMA PLUG 50OHM TEFLON INSULATED CABLE

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.		Fig.	Description	Length (in.)	Price Each		
Mfr.	Mfr. Part No.				1	25	50
RG316/U							
565	4935-BB-24	C	BNC male (plug) to SMA male (plug), 50Ω	24	45.72	43.54	41.36
565	4935-BB-48	C	BNC male (plug) to SMA male (plug), 50Ω	48	45.72	43.54	41.36
565	4935-BB-60	C	BNC male (plug) to SMA male (plug), 50Ω	60	45.72	43.54	41.36

Pomona MOLDED BREAKOUTS

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.		Fig.	Description	Length (in.)	Price Each			
Mfr.	Mfr. Part No.				1	25	50	
565	4969	D	BNC female to 20AWG leads	5.9	7.16	6.82	6.48	
565	2630	E	BNC female to mini alligator clips	5.0	10.69	10.19	9.68	
565	2631	E	BNC female to minigrabber clips	5.9	10.69	10.17	9.65	
565	3788	F	BNC female to Minigrabber test clips	5.5	10.59	10.09	9.59	
565	3789	F	BNC male to Minigrabber test clips	5.5	12.79	12.17	11.54	
565	3221	G	BNC female to stacking pin tip plugs	5.5	13.17	12.54	11.91	
565	3073	H	BNC female to multi-stacking banana plugs	5.4	10.46	9.97	9.47	
565	4970	I	BNC male to 20AWG leads	5.9	9.64	9.17	8.70	
565	5187-C-36	J	Minigrabber test clips to BNC male RG58C/U	36.0	18.15	17.27	16.38	

Pomona BNC TO BNC WITH MOLDED STRAIN RELIEF

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.		Fig.	Description	Length (in.)	Price Each		
Mfr.	Mfr. Part No.				1	25	50
RG58C/U							
565	2249-C-12	K	BNC male to BNC male, 50Ω	12	14.98	14.27	13.56
565	2249-C-24	K	BNC male to BNC male, 50Ω	24	14.98	14.27	13.56
565	2249-C-36	K	BNC male to BNC male, 50Ω	36	14.98	14.27	13.56
565	2249-C-48	K	BNC male to BNC male, 50Ω	48	18.84	17.94	17.04
565	2249-C-60	K	BNC male to BNC male, 50Ω	60	18.47	17.57	16.66
565	2249-C-72	K	BNC male to BNC male, 50Ω	72	18.47	17.57	16.66
565	2249-C-120	K	BNC male to BNC male, 50Ω	120	22.03	20.95	20.01
565	2249-C-180	K	BNC male to BNC male, 50Ω	180	26.65	25.35	24.05
RG223							
565	2249-Y-12	K	BNC male to BNC male, 50Ω	12	23.34	22.23	21.12
565	2249-Y-24	K	BNC male to BNC male, 50Ω	24	23.34	22.23	21.12
565	2249-Y-36	K	BNC male to BNC male, 50Ω	36	24.58	23.41	22.24
565	2249-Y-48	K	BNC male to BNC male, 50Ω	48	25.65	24.43	23.21
565	2249-Y-60	K	BNC male to BNC male, 50Ω	60	27.79	26.47	25.15
565	2249-Y-72	K	BNC male to BNC male, 50Ω	72	29.65	28.24	26.83
RG59B/U							
565	2249-E-12	K	BNC male to BNC male, 75Ω	12	16.05	15.29	14.53
565	2249-E-24	K	BNC male to BNC male, 75Ω	24	16.05	15.29	14.53
565	2249-E-36	K	BNC male to BNC male, 75Ω	36	14.96	14.19	13.52
565	2249-E-48	K	BNC male to BNC male, 75Ω	48	18.94	18.04	17.14
565	2249-E-60	K	BNC male to BNC male, 75Ω	60	18.94	18.04	17.14
565	2249-E-72	K	BNC male to BNC male, 75Ω	72	17.57	16.66	15.88
RG174/U							
565	2249-K-12	K	BNC male to BNC male, 50Ω	12	23.37	22.26	21.15
565	2249-K-24	K	BNC male to BNC male, 50Ω	24	22.69	21.61	20.53
565	2249-K-36	K	BNC male to BNC male, 50Ω	36	22.24	21.15	20.07
565	2249-K-48	K	BNC male to BNC male, 50Ω	48	24.58	23.41	22.24
565	2249-K-60	K	BNC male to BNC male, 50Ω	60	24.58	23.41	22.24
565	2249-K-72	K	BNC male to BNC male, 50Ω	72	26.02	24.78	23.54

