



KSW WIRE WRAPPING WIRE ROLLS FOR CUT/STRIP/WRAP APPLICATIONS

* Low strip force KYNAR insulated wire for use with CSW bits and sleeves.

Replace the blank in part number with: **B** for Blue, **W** for White, **R** for Red, **Y** for Yellow, **BLK** for Black.

MOUSER STOCK NO.	OK Industries Part No.	Fig.	AWG Size	Insulation Dia. (in.)	100' Spool		1000' Spool	
					1	5	1	5
801-KSW24	KSW24_-0100	A	24	.030	24.60	23.64	---	---
801-KSW26	KSW26_-0100	A	26	.027	22.58	21.70	---	---
801-KSW28	KSW28_-0100	A	28	.0235	22.58	21.70	---	---
801-KSW30	KSW30_-0100	A	30	.0195	22.58	21.70	---	---
801-KSW30_-1000	KSW30_1000	A	30	.0195	---	---	85.08	79.44

KYNAR INSULATED, SILVER PLATED COPPER CONDUCTOR

Replace the blank in part number with: **B** for Blue, **W** for White, **R** for Red, **Y** for Yellow.

MOUSER STOCK NO.	OK Industries Part No.	Fig.	AWG Size	Insulation Dia. (in.)	100' Spool		1000' Spool	
					1	5	1	5
801-R24	R24_-0100	A	24	.030	19.10	18.35	---	---
801-R26	R26_-0100	A	26	.027	13.95	13.40	---	---
801-R28	R28_-0100	A	28	.0235	12.09	11.63	---	---
801-R30	R30_-0100	A	30	.0195	10.80	10.38	---	---
801-R30_-1000	R30_-1000	A	30	.0195	---	---	56.86	53.08

PRE-CUT AND PRE-STRIPPED WIRE WRAPPING WIRE

- 50 pieces per package
- KYNAR insulated
- UIL listed
- Silver plated copper conductor

Replace the blank in part number with: **B** for Blue, **W** for White, **R** for Red, **Y** for Yellow.

MOUSER STOCK NO.	OK Industries Part No.	Fig.	Insulation Length	AWG Size	Price Each	
					1	5
801-30_-50-010	30_-50-010	B	1	30	7.66	7.36
801-30_-50-020	30_-50-020	B	2	30	7.66	7.36
801-30_-50-030	30_-50-030	B	3	30	8.47	8.14
801-30_-50-050	30_-50-050	B	5	30	8.47	8.14

WIRE DISPENSER-WD-30 SERIES

- 30AWG Kynar wire wrapping wire
- Built-in Stripper strips 1" of insulation
- Built-in Plunger cuts wire to desired length
- Refillable

MOUSER STOCK NO.	OK Industries Part No.	Fig.	Description	Price Each	
				1	5
801-WD-30-B	WD-30-B	C	Dispenser with 50' of Blue wire	18.68	17.44
801-WD-30-Y	WD-30-Y	C	Dispenser with 50' of Yellow wire	18.68	17.44
801-WD-30-W	WD-30-W	C	Dispenser with 50' of White wire	18.68	17.44
801-WD-30-R	WD-30-R	C	Dispenser with 50' of Red wire	18.68	17.44
801-WD-30-TRI	WD-30-TRI	C	Dispenser with 50' each Blue, White and Red wire	30.71	28.68

Replacement Rolls of Wire for WD-30 Series

MOUSER STOCK NO.	OK Industries Part No.	Description	1	5
801-R-30B-0050	R-30B-0050	30 AWG Blue 50' for WD-30-B	8.47	8.14
801-R-30Y-0050	R-30Y-0050	30 AWG Yellow 50' for WD-30-Y	8.47	8.14
801-R-30W-0050	R-30W-0050	30 AWG White 50' for WD-30-W	8.47	8.14
801-R-30R-0050	R-30R-0050	30 AWG Red 50' for WD-30-R	8.47	8.14
801-R30-TRI	R-30-TRI	30 AWG Red, White, Blue for WD-30-TRI	16.89	16.22

WIRE WRAPPING BITS AND SLEEVES

Fully compatible with any make or model wire wrapping tool.

Bits

MOUSER STOCK NO.	OK Industries Part No.	Fig.	AWG	Wrap	Price Each	MOUSER STOCK NO.	OK Industries Part No.	Fig.	Maximum Insulation Dia.	Minimum Term Diag.	Maximum Term Diag.	Terminal Hole Depth (in.)	Terminal Hole Dia. (in.)	Price Each
801-KB224	KB224	H	22-24	Reg.	47.98	801-P2224	P2224	I	---	.054	.073	.807	.075	20.81
*801-WB26SM	WB26SM	H	26	Mod.	50.81	801-P26LN	P26LN	I	.031	.023	.038	.750	.040	37.26
*801-WB3032M	WB3032M	H	30-32	Mod.	50.81	801-P3032	P3032	I	.027	.034	.038	.750	.040	37.26

* Recommended for .025" square terminals on .100" centers.

© Copyright 2009 Mouser Electronics

ADJUSTABLE PRECISION WIRE STRIPPERS

A calibrated wire stop can be adjusted for the desired insulation strip length. In a single motion, the operator squeezes and pulls the tool. This action engages four specially hardened blades to cleanly cut wire insulation while the pulling motion breaks the insulation/conductor bond.

- * Adjustable to six wire gauges:
 - ST-450 26 to 36 AWG
 - ST-500 20 to 30 AWG
 - ST-500ESD 20 to 30 AWG
 - ST-550 18 to 28 AWG
- * Calibrated Wire Stop adjustable to 2"(50.8mm)
- * Clean, precise strip of any insulation type
- * Lightweight-weighs 1oz.
- * Blade is hardened steel (RC58)
- * Dimensions 3.9"x1.6"x0.6" (90mm x 42mm x 14mm)

MOUSER STOCK NO.	OK Industries Part No.	Fig.	Description	Price Each	
				1	5
801-ST-450	ST-450	D	Wire Gauge 26-36 AWG	39.60	37.62
801-ST-500	ST-500	D	Wire Gauge 20-30 AWG	32.90	31.26
801-ST-500ESD	ST-500ESD	D	Wire Gauge 20-30 AWG	39.60	37.62
801-ST-550	ST-550	D	Wire Gauge 18-28 AWG	32.90	31.26

SOCKET-WRAP I.D.

Used to identify pin numbers on wire wrapping sockets. These unique items greatly simplify both initial wire wrapping and subsequent troubleshooting or repair.

MOUSER STOCK NO.	OK Industries Part No.	Fig.	Pins	Row Spacing	Qty./Pkg.	Price Each
801-ID-8-100	ID-8-100	E	8	.3"	100	29.10
801-ID-16-100	ID-16-100	E	16	.3"	100	29.10
801-ID-18-50	ID-18-50	E	18	.3"	50	28.13
801-ID-20-50	ID-20-50	E	20	.3"	50	29.10
801-ID-22-50	ID-22-50	E	22	.4"	50	28.13
801-ID-24-50	ID-24-50	E	24	.6"	50	28.13
801-ID-28-50	ID-28-50	E	28	.6"	50	29.10
801-ID-40-25	ID-40-25	E	40	.6"	25	28.08
801-ID-96-25	ID-96-25	E	96	.3"	25	28.08

HAND WRAPPING, STRIPPING AND UNWRAPPING TOOLS

Each WSU tool wraps, unwraps and even strips the appropriate wire diameter with a unique built-in stripper blade. Ideal for bench use or tool kit in all service and repair applications. In addition to versatility, convenience, and reliability, the WSU Series offers exceptional value.

MOUSER STOCK NO.	OK Industries Part No.	Fig.	AWG Size	Term. Hole Depth (in.)	Term. Hole Dia. (in.)	Outside Dia. (in.)	Square Post (in.)	Price Each
801-WSU-2224	WSU-2224	F	22-24	1.50	.075	.213	.045	45.72
801-WSU-24M	WSU-24M	F	24	1.50	.075	.213	.045	45.72
801-WSU-26M	WSU-26M	F	26	1.50	.075	.213	.045	45.72
801-WSU-30	WSU-30	F	30	1.50	.036	.125	.025	32.85
801-WSU-30M	WSU-30M	F	30	1.50	.036	.125	.025	31.85

MANUAL WIRE WRAPPING TOOLS

Accommodates wire sizes from 22 AWG through 32 AWG. Offered in aluminum, insulated aluminum, and lexan, an industrial grade plastic.

MOUSER STOCK NO.	OK Industries Part No.	Fig.	Description	Price Each
801-G200R3278	G200/R3278	G	Lexan	112.58
801-G100R3278	G100/R3278	G	Aluminum	148.95
801-G100R3278INS	G100/R3278INS	G	Insulated Aluminum	159.27
801-G100/R3278FL	G100/R3278FL	G	Insulated Aluminum with LED flashlight	163.93