

# TECHSPRAY Brushes, Wipes, and Swabs



RoHS Compliant This product is RoHS compliant.

## TECHSPRAY STATIC SENSITIVE BRUSHES

Use these brushes for your specific needs, whether you are cleaning sensitive optics or scrubbing heavy soils. The bristle cut is designed to offer optimum cleaning with minimum effort.

- ESD Safe stainless steel or natural horsehair
- Anodized aluminum handles



MOUSER STOCK NO.	Tech Spray Part No.	Fig.	Bristle Material	Bristle Width	Price Each	
					1	12
577-2040	2040-1	A	Horse Hair	1/8"	12.40	11.79
577-2042	2042-1	A	Horse Hair	3/8"	20.30	19.28
577-2043	2043-1	A	.003 Stainless Steel	3/8"	20.98	19.95

## TECHSPRAY GENERAL CLEANING BRUSHES

- Non-Static Bristles
- Easy-Grip Handles



MOUSER STOCK NO.	Tech Spray Part No.	Fig.	Handle Material	Bristle Material	Brush Face	Price Each	
						1	12
577-2020	2020-1	A	Wood	Horse hair	1/4" X 1 3/8"	3.20	3.03
577-2021	2021-1	A	Wood	Hog's hair	1/4" X 1 3/8"	4.57	4.35
577-2022	2022-1	A	Wood	Hog's hair	7/8" X 2 1/8"	9.32	8.86

## TECHSPRAY TECHNICAL CLEANING BRUSHES

Whether you are cleaning sensitive optics or scrubbing heavy soils, this bristle cut brush is designed to offer optimum cleaning with minimum effort. Handles are designed for a comfortable fit.



MOUSER STOCK NO.	Tech Spray Part No.	Fig.	Handle Material	Handle Length	Bristle Length	Price Each	
						1	12
577-2030	2030-1	B	Stainless Steel	3 1/2"	1/8"	8.23	7.82
577-2031	2031-1	C	Stainless Steel	4 1/2"	1/4"	8.67	8.24
577-2032	2032-1	D	Zinc Plated Steel	4 1/2"	1/2"	8.32	7.91
577-2033	2033-1	E	Zinc Plated Steel	4 1/2"	7/16"	6.30	5.98

## TECHSPRAY TECHCLEAN WIPES

### Features:

- 2350 Techclean Wiper - General-purpose cellulose/polyester wipe - high absorbency, and low linting.
- 2351/2352 Techclean Absorbwipe - Soft polyester wipe for sensitive surfaces.
- 2353/2354 Techclean Ultrawipe - Textured cellulose/polyester wipe for more aggressive cleaning.
- 2355 Techclean Purwipe - Very low lint, reusable polyester wipe.
- 2357 Techclean Twillwipe - Tough cotton twill wipe for abrasive surfaces.
- 2359 Techclean SMT Blue Wipe - Economical cellulose/polyester wipe for general maintenance.
- 2362 Anti-Static Wipe - ESD-safe wipe for static-controlled environments.



\* Not Folded

MOUSER STOCK NO.	Tech Spray Part No.	Fig.	Description	Size	Price Each		
					1	6	12
* 577-2350-100	2350-100	F	General Purpose, 100pk	9" X 9"	24.26	22.91	21.87
* 577-2351-100	2351-100	F	Absorbwipe, 100pk	4" X 4"	8.47	8.04	7.64
* 577-2352-100	2352-100	F	Absorbwipe, 100pk	9" X 9"	25.43	24.10	22.91
* 577-2355-100	2355-100	F	Purwipe, 100pk	9" X 9"	41.04	38.90	36.98
* 577-2357-100	2357-100	F	Twillwipe, 100pk	6" X 6"	24.80	23.50	22.34
* 577-2359-300	2359-300	F	Bluewipe, 300pk	9" X 9"	41.99	39.89	37.79
577-2362-150	2362-150	F	Anti-static wipe, 150pk	9" X 9"	107.37	102.39	97.41

## TECHSPRAY TECH SWABS



MOUSER STOCK NO.	Tech Spray Part No.	Fig.	Description	Size	Price Each		
					1	6	12
577-2300-100	2300-100	G	Double Tip Cotton, 100pk	3/16"	4.33	4.12	3.92
577-2300-1000	2300-1000	G	Double Tip Cotton, 1000pk	3/16"	33.21	31.57	29.93
577-2301-100	2301-100	H	Single Tip Cotton, 100pk	3/16"	3.96	3.77	3.60
577-2301-1000	2301-1000	H	Single Tip Cotton, 1000pk	3/16"	24.24	22.89	21.85
577-2302-50	2302-50	I	Broad Tip Foam, 50pk	7/16"	21.57	20.45	19.44
577-2302-1000	2302-1000	I	Broad Tip Foam, 1000pk	7/16"	253.65	239.57	228.62
577-2303-50	2303-50	J	Narrow Tip Foam, 50pk	1/4"	20.17	19.11	18.18
577-2303-1000	2303-1000	J	Narrow Tip Foam, 1000pk	1/4"	269.07	254.11	242.48
577-2306-50	2306-50	K	Super-Tip Foam, 50pk	1/2"	19.00	18.00	17.12
577-2306-1000	2306-1000	K	Super-Tip Foam, 1000pk	1/2"	272.39	257.26	245.49
577-2307-50	2307-50	L	Mini-Tip Foam, 50pk	3/16"	29.22	27.71	26.35
577-2307-1000	2307-1000	L	Mini-Tip Foam, 1000pk	3/16"	512.41	483.94	461.79
577-2313-30	2313-30	M	Double-Tip Pointed, 30pk	1/8"	6.50	6.16	5.85

