

VECTOR Extender Cards and Prototype Accessories



VECTORBORD® GENERAL PURPOSE EXTENDER CARDS

- Low insertion force
- Current Rating: 5 amps @ 10°F rise
- Gold-plated contacts
- Voltage Rating: 200 RMS or 300 VDC

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Extension Length (In.)	Description		Price Each	
				Contacts	Spacing	1	10
574-3690	3690	A	6.5	22 each side	.156"	40.43	37.80
574-3690-2	3690-2	B	11	36 each side	.100"	72.44	67.73
574-3690-6	3690-6	C	11	22 each side	.156"	54.16	50.65
574-3690-12	3690-12	D	7.5	50 each side	.125"	76.98	71.98
574-3690-16	3690-16	E	6.5	28 each side	.125"	48.04	44.91
Bus Extenders							
574-3690-22	3690-22	F	5.7	IBM PC, XT, 31 contacts each side	.100"	77.82	72.95
574-3690-26	3690-26	G	5.6	IBM AT-ISA, 18/31 contacts ea. side	.100"	76.98	71.98

VECTORBORD® METRIC EXTENDER CARDS

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Extension Length (In.)	Description	Price Each	
					1	10
574-VMEE-M	VMEE-M	H	12.2	VME J1, J2, 6U width	387.42	344.00
574-VMEE-J1	VMEE-J1	I	12.2	VME J1 only, 3U width	265.63	235.98
574-UEB220-3U	UEB220-3U	H	12.2	DIN uncommitted 3U	301.88	286.79
574-UEB220-6U	UEB220-6U	I	12.2	DIN uncommitted 6U	501.12	496.50

PROTOTYPE ACCESSORIES

Pins and Terminals For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Description	Package Quantity	Price Each
Press-In Terminals for .042" Holes Insertion Tool: 574-P133A					
574-T46-2-9/M	T46-2-9/M	J	A=.36", B=.42"	1000	95.85
574-T46-3-9/C	T46-3-9/C	J	A=.46", B=.60"	100	16.63
574-T46-3-9/M	T46-3-9/M	J	A=.46", B=.60"	1000	113.79
574-T46-4-9/C	T46-4-9/C	J	A=.04", B=.42"	100	10.45
574-T46-4-9/M	T46-4-9/M	J	A=.04", B=.42"	1000	104.45
Bifurcated Miniwrap Terminals for .042" Holes Insertion Tool: 574-A13 or 574-A13-1					
574-T44/C	T44/C	K	Max. .021" leads or 24 AWG wires	100	11.55
574-T44/M	T44/M	K	Max. .021" leads or 24 AWG wires	1000	66.50
574-T68/C	T68/C	L	Max. .032" leads or 20 AWG wires	100	10.71
574-T68/M	T68/M	L	Max. .032" leads or 20 AWG wires	1000	63.14
Trifurcated Klipwrap Terminals for .042" Holes Insertion Tool: 574-P156					
574-T49/C	T49/C	M	Wirewrap tail with 3-prong receptacle	100	16.09
574-T49/M	T49/M	M	Wirewrap tail with 3-prong receptacle	1000	141.98
Press-In Pins for .042" Holes Insertion Tool: 574-P133A					
574-K24A/M	K24A/M	N	A=.255", B=.375", gold plated	1000	110.69
574-K24C/M	K24C/M	N	A=.255", B=.375", tin plated	1000	66.40
574-K30C/M	K30C/M	O	A=.255", B=.305", tin plated	1000	59.75
574-K31C/M	K31C/M	O	A=.160", B=.195", tin plated	1000	46.50
Push-In Terminals for .042" Holes Insertion Tool: 574-P149 or 574-P149A					
574-T42-1/C	T42-1/C	P	Horizontal slot holds up to 7 wires	100	10.68
574-T42-1/M	T42-1/M	P	Horizontal slot holds up to 7 wires	1000	51.23
Push-In Terminals for .062" Holes Insertion Tool: 574-P91A					
574-T28/C	T28/C	Q	Vertical slot holds .025" leads/22 AWG wires	100	10.97
574-T28/M	T28/M	Q	Vertical slot holds .025" leads/22 AWG wires	1000	54.14
Wire-wrap Socket Pins for .042" Holes Insertion Tool: 574-P158					
574-R32/C	R32/C	R	Pressfit mounting, 4-finger contacts	100	38.38

Insertion Tools for Pins and Terminals

MOUSER STOCK NO.	Vector Part No.	For Use With	Price Each
574P133A	P133A	Press-In Terminals and Pins for .042" Holes	75.28
574-A13	A13	Bifurcated Miniwrap Terminals for .042" Holes	26.94
574-A13-1	A13-1	Bifurcated Miniwrap Terminals for .042" Holes	28.61
574-P149	P149	Push-In Terminals for .042" Holes	27.99
574-P149A	P149A	Push-In Terminals for .042" Holes	40.25
574-P91A	P91A	Push-In Terminals for .062" Holes	86.30

Tefzel Insulated Silver Plated Wire

This wire is designed to be used with wire wrap terminals. Spool diameter is 1".

• Two 50' Spools Per Package

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	AWG	Color	Price Per Package
574-W28-6A	W28-6A	28	Green	22.28
574-W28-6B	W28-6B	28	Red	22.28
574-W28-6D	W28-6D	28	Blue	22.38
574-W28-6E	W28-6E	28	White	23.37
574-W28-6F	W28-6F	28	Yellow	21.11
574-W28-6H	W28-6H	28	Black	22.28

Solder Eyelets and Bus Strips

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Description	Package Quantity	Price Per Package
574-T123/500	T123/500	S	Solder eyelets for .055" holes	500	33.18
574-T107/C	T107/C	T	.08" x 14" solder-coated bus strips	100	108.92

