


## DIAZED FUSES (BOTTLE FUSES)



Diazed Fuses	DIMENSIONS mm (in.)	
	Length (L)	Diameter (D)
A	50.0(1.97)	12.5(0.50)
B	50.0(1.97)	22.0(0.87)
C	50.0(1.97)	27.0(1.06)

g/LgG Slow Blow - Line Protection



For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-2D16SB		2	A	2.08
845-4D16SB		4	A	5.20
845-6D16SB		6	A	5.20
845-10D16SB		10	A	2.08
845-16D16SB		16	A	2.08
845-20D16SB		20	A	2.08
845-35D16SB		35	A	2.08
845-2D27SB		2	B	1.67
845-4D27SB		4	B	1.82
845-6D27SB		6	B	1.67
845-10D27SB		10	B	1.67
845-16D27SB		16	B	1.67
845-20D27SB		20	B	1.67
845-25D27SB		25	B	1.67
845-35D33SB		35	C	2.08
845-40D33SB		40	C	2.58
845-50D33SB		50	C	2.60
845-63D33SB		63	C	2.08

Fast Blow - Equipment Protection

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-2D16FB		2	A	2.08
845-4D16FB		4	A	2.08
845-6D16FB		6	A	2.08
845-10D16FB		10	A	2.08
845-16D16FB		16	A	2.08
845-20D16FB		20	A	2.08
845-25D16FB		25	A	2.08
845-2D27FB		2	B	2.47
845-4D27FB		4	B	1.82
845-6D27FB		6	B	1.67
845-10D27FB		10	B	1.67
845-16D27FB		16	B	1.67
845-20D27FB		20	B	1.67
845-25D27FB		25	B	1.67
845-35D33FB		35	C	2.08
845-50D33FB		50	C	2.08
845-63D33FB		63	C	2.08

gR Superfast Blow - Semiconductor Protection

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-4D16SC		4	A	5.41
845-6D16SC		6	A	5.41
845-10D16SC		10	A	5.41
845-16D16SC		16	A	5.41
845-20D16SC		20	A	5.41
845-25D16SC		25	A	5.41
845-30D16SC		30	A	7.57
845-4D27SC		4	B	5.41
845-6D27SC		6	B	5.19
845-10D27SC		10	B	5.19
845-16D27SC		16	B	5.19
845-20D27SC		20	B	5.19
845-25D27SC		25	B	5.19
845-30D27SC		30	B	5.31
845-35D33SC		35	C	6.49
845-50D33SC		50	C	6.71
845-63D33SC		63	C	5.54

## NEOZED FUSES



Neozed Fuses	DIMENSIONS mm (in.)	
	Length (L)	Diameter (D)
D	36.0(1.42)	11.0(0.43)
E	36.0(1.42)	15.3(0.60)
F	43.0(1.63)	22.5(0.84)

gL Slow Blow

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-2NZ01GL		2	D	2.16
845-4NZ01GL		4	D	2.16
845-6NZ01GL		6	D	2.16
845-10NZ01GL		10	D	2.16
845-16NZ01GL		16	D	2.16
845-20NZ02GL		20	E	2.16
845-25NZ02GL		25	E	2.79
845-35NZ02GL		35	E	2.77
845-50NZ02GL		50	E	3.03
845-63NZ02GL		63	E	3.03
845-80NZ03GL		80	F	6.06
845-100NZ03GL		100	F	6.06

## NH FUSES

NH Fuses	DIMENSIONS mm (in.)			
	Overall Length (L1)	Body Length (L2)	Depth (D)	Width (W)
G	78(3.10)	48(1.89)	36(1.42)	20(0.79)



g/LgG - 500V AC

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-2NH00GL		2	G	7.79
845-4NH00GL		4	G	7.49
845-6NH00GL		6	G	6.06
845-10NH00GL		10	G	6.06
845-16NH00GL		16	G	6.06
845-20NH00GL		20	G	6.06
845-32NH00GL		32	G	6.06
845-35NH00GL		35	G	6.06
845-40NH00GL		40	G	6.06
845-50NH00GL		50	G	6.06
845-63NH00GL		63	G	6.06
845-80NH00GL		80	G	6.06
845-100NH00GL		100	G	6.06
845-125NH00GL		125	G	6.92
845-160NH00GL		160	G	6.92

aM - 600V AC

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-2NH00AM-6		2	G	18.90
845-4NH00AM-6		4	G	19.47
845-6NH00AM-6		6	G	7.35
845-10NH00AM-6		10	G	6.87
845-16NH00AM-6		16	G	7.35
845-20NH00AM-6		20	G	7.35
845-32NH00AM-6		32	G	6.92
845-35NH00AM-6		35	G	7.35
845-40NH00AM-6		40	G	7.08
845-50NH00AM-6		50	G	7.35
845-63NH00AM-6		63	G	9.20
845-80NH00AM-6		80	G	7.35
845-100NH00AM-6		100	G	10.82
*845-125NH00AM-6		125	G	7.49
*845-160NH00AM-6		160	G	7.49

\* 500 VAC

gR/aR - Semiconductor Protection 690 VAC

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-16NH00GR-6		16	G	19.03
845-20NH00GR-6		20	G	17.30
845-32NH00GR-6		32	G	18.17
845-35NH00GR-6		35	G	18.17
845-40NH00GR-6		40	G	18.17
845-50NH00GR-6		50	G	18.17
845-63NH00GR-6		63	G	19.03
845-80NH00GR-6		80	G	19.03
845-100NH00GR-6		100	G	20.76
845-125NH00GR-6		125	G	20.76
845-160NH00AR-6		160	G	20.76

## CYLINDER FUSES

Cylinder Fuses	DIMENSIONS mm (in.)	
	Length (L)	Diameter (D)
H	32.0(1.25)	8.0(0.31)
I	38.0(1.49)	10.0(0.39)
J	51.0(2.00)	14.0(0.55)
K	58.0(2.28)	22.0(0.86)



gl. 380 VAC 8 x 32 mm (0.31 x 1.25")

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-2C8X32GI		2	H	1.73
845-4C8X32GI		4	H	1.73
845-6C8X32GI		6	H	1.73
845-10C8X32GI		10	H	1.73
845-16C8X32GI		16	H	1.73
845-20C8X32GI		20	H	1.73
845-25C8X32GI		25	H	1.73

## CYLINDER FUSES

Cylinder Fuses	DIMENSIONS mm (in.)	
	Length (L)	Diameter (D)
H	32.0(1.25)	8.0(0.31)
I	38.0(1.49)	10.0(0.39)
J	51.0(2.00)	14.0(0.55)
K	58.0(2.28)	22.0(0.86)

gl. 500 VAC 10 x 38 mm (0.39 x 1.49")

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-1C10X38GI		1	I	1.73
845-2C10X38GI		2	I	1.73
845-4C10X38GI		4	I	1.73
845-6C10X38GI		6	I	1.73
845-8C10X38GI		8	I	1.73
845-10C10X38GI		10	I	1.73
845-12C10X38GI		12	I	1.73
845-16C10X38GI		16	I	1.73
845-20C10X38GI		20	I	1.73
845-25C10X38GI		25	I	1.73
845-32C10X38GI		32	I	1.73

gl. 660 VAC 14 x 51 mm (0.55 x 2")

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-2C14X51GI		2	J	1.95
845-4C14X51GI		4	J	1.95
845-6C14X51GI		6	J	1.95
845-8C14X51GI		8	J	1.95
845-10C14X51GI		10	J	1.95
845-12C14X51GI		12	J	1.95
845-16C14X51GI		16	J	1.95
845-20C14X51GI		20	J	1.95
845-25C14X51GI		25	J	2.16
845-32C14X51GI		32	J	2.16
845-40C14X51GI		40	J	2.16
845-50C14X51GI		50	J	2.16

gl. 660 VAC 22 x 58 mm (0.86 x 2.28")

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Amps	Dim.	Price Each
Mfr.	Mfr. Part Number			
845-12C22X58GI		12	K	3.79
845-16C22X58GI		16	K	3.65
845-20C22X58GI		20	K	3.79
845-32C22X58GI		32	K	3.79
845-40C22X58GI		40	K	3.79
845-50C22X58GI		50	K	3.79
845-63C22X58GI		63	K	3.79
845-80C22X58GI		80	K	4.33
845-100C22X58GI		100	K	4.04
845-125C22X58GI		125	K	4.33

## Accessory Fuse Holders



For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Dimensions HxWxD mm	No. of Poles	Price Each
Mfr.	Mfr. Part Number			
8x32mm				
845-CB831-1		77x17.5x63.5	1	7.05
845-CB831-3		77x52.5x63.5	3	17.82
10x38mm				
845-CB1038-1		77x17.5x63.5	1	5.87
845-CB1038-3		77x52.5x63.5	3	21.88



14x51 mm For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Dimensions HxWxD mm	No. of Poles	Price Each
Mfr.	Mfr. Part Number			
845-CB1451-1		100x26x73	1	11.39
845-CB1451-3		100x78x73	3	26.91



22x58 mm For quantities of 25 and up, call for quote.

MOUSER STOCK NO.		Dimensions HxWxD mm	No. of Poles	Price Each
Mfr.	Mfr. Part Number			
845-CB2258-1		140x35x90	1	16.58
845-CB2258-3		140x105x90</		