




<p><b>One-Touch</b></p> <ul style="list-style-type: none"> <li>Will not corrode or contaminate liquid</li> <li>Cam-Lock Hinge</li> </ul> 	<p><b>Pure-Touch</b></p> <ul style="list-style-type: none"> <li>Patented Purity Protector</li> <li>Cam-Lock Hinge</li> </ul> 	<p><b>Take-Along</b></p> <ul style="list-style-type: none"> <li>Locking Pump</li> <li>Cam-Lock Hinge</li> </ul> 
--	--	---








Bottle / Pump Type	Chemical						
	Acetone	Gasoline	Isopropyl Alcohol	M.E.K.	Toluene	Turpentine	Water
HDPE/SS	E	E	E	E	G	G	E
Dissipative HDPE/SS	G	G	E	G	NR	NR	E
Glass/SS	E	E	E	E	E	E	E
Tin Coated Steel/SS	E	E	E	E	G	E	NR
HDPE/PP	E	NR	E	NR	NR	NR	E

E = Excellent  
G = Good  
NR = Not Recommended

The applications table at right is to be used as a guideline only. It is the user's responsibility to determine the suitability of a particular fluid dispensed from a Menda pump and bottle.

**Common Features:**

- Patented One Handed Operation
- Precision Machined Valves
- Perfect for ultra clean environments

<b>A</b> 	<b>B</b> 	<b>C</b> 	<b>D</b> 	<b>E</b> 	<b>F</b> 	<b>G</b> 
---	---	---	---	--	---	---

## MENDA BOTTLES WITH STAINLESS STEEL PUMP

### Natural HDPE

- High density polyethylene
- Square shape for stability
- Translucent white finish
- Wide opening

MOUSER STOCK NO.	Menda Part No.	Fig.	Description		Price Each		
			Pump Style	Bottle Size	1	10	25
809-35304	35304	A	One-Touch	2 oz.	14.52	13.79	13.10
809-35305	35305	A	One-Touch	4 oz.	14.77	14.03	13.33
809-35309	35309	A	One-Touch	6 oz.	15.23	14.47	13.75
809-35312	35312	A	One-Touch	8 oz.	15.48	14.71	13.97
809-35505	35505	A	Pure-Touch	4 oz.	17.51	16.63	15.80
809-35508	35508	A	Pure-Touch	6 oz.	17.89	16.99	16.15
809-35701	35701	A	Take-Along	2 oz.	22.14	21.03	19.98
809-35704	35704	A	Take-Along	8 oz.	22.55	21.42	20.35

### Yellow Dissipative ESD Protective

- No migratory additives
- Reduces the chance for contamination from the bottle
- Highly visible with ESD markings
- Flask style shape
- Available pump styles

MOUSER STOCK NO.	Menda Part No.	Fig.	Description	Bottle Size	1	10	25
809-35354	35354	B	One-Touch	6 oz.	16.85	16.00	15.21
809-35540	35540	B	Pure-Touch	6 oz.	20.44	19.42	18.45

### Blue Dissipative ESD Protective

- Low tribo-charging
- Provides stability and saves storage space

MOUSER STOCK NO.	Menda Part No.	Fig.	Description	Bottle Size	1	10	25
809-35337	35337	C	One-Touch	6 oz.	14.50	13.78	13.09
809-35531	35531	C	Pure-Touch	6 oz.	18.55	17.62	16.74

### Amber Glass

- Allows storage of fluids not compatible with plastic
- Translucent

MOUSER STOCK NO.	Menda Part No.	Fig.	Description		Price Each		
			Pump Style	Bottle Size	1	10	25
809-35315	35315	D	One-Touch	4 oz.	15.48	14.71	13.97
809-35112	35112	D	Pure-Touch	4 oz.	17.28	16.41	15.59

## MENDA HEPA HIGH PERFORMANCE VACUUMS

ESD Safe for cleaning debris from surface mount, pick and place, board routers/handlers and other equipment in your ESD protective areas.

- .12 micron HEPA filtration for lead, glass, pollen, soot, etc.
- ESD protected utensils included
- Great for field service applications
- Only 6.5lbs with all utensils
- Made in America
- ESD Protected
- RoHS Compliant



MOUSER STOCK NO.	Menda Part No.	Description	Price Each	
			1	5
809-35852	35852	120VAC HEPA Vacuum	285.00	270.75
809-35857	35857	120VAC HEPA Vacuum w/ Case & Extra Filter	388.46	369.05
809-35855	35855	Replacement Filter for HEPA Vacuum	46.95	44.60

## MENDA STEEL CAN WITH STAINLESS STEEL PUMP

- Steel construction
- Allows storage of fluid not compatible with plastic

MOUSER STOCK NO.	Menda Part No.	Fig.	Description		Price Each		
			Pump Style	Bottle Size	1	10	25
809-35335	35335	E	One-Touch	4 oz.	17.51	16.63	15.80

## MENDA HDPE WITH PLASTIC PUMP

- High density polyethylene
- Perfect for alcohol dispensing
- Reduces odors and maintains purity
- Available with alcohol imprint for demarcation

MOUSER STOCK NO.	Menda Part No.	Fig.	Description	Price Each		
				1	10	25
809-35601	35601	F	8 oz. Brown, with imprint	6.88	6.54	6.21
809-35602	35602	F	8 oz. Brown, no imprint	6.69	6.36	6.04
809-35603	35603	F	8 oz. Natural, no imprint	6.69	6.36	6.04

## MENDA GREEN DISSIPATIVE ESD PROTECTIVE WASH BOTTLE

Specifically for use in lead-free areas where RoHS compliant items are worked on.

- Angled non-drip spout delivers single drop or fine stream
- Provides controlled delivery of solvents, cleaners, water, and oils.
- No migratory additives - Reduces chance for contamination from the bottle.
- High visibility

MOUSER STOCK NO.	Menda Part No.	Fig.	Description	Price Each		
				1	10	25
809-35369	35369	G	8oz. Green Dissipative Wash Bottle	18.50	17.96	16.88

## MENDA OMEGA FIELD VACUUM

Ideal for cleaning tape and components from feeder trolleys on pick & place machines. Also used for cleaning automated insertion machines, copiers, computers, printers, lab equipment and x-ray machines.

- ESD protected vacuum with electronic line filter
- 25% better 0.3 micron filtration
- Attachments included
- UL Listed, UL/Canada Listed
- Portable, quick set up
- RoHS Compliant
- Made in America



MOUSER STOCK NO.	Menda Part No.	Description	Price Each	
			1	5
809-35849	35849	120VAC Field Vacuum	315.70	308.00
809-35853	35853	Replacement Filter for Field Vacuum	23.75	22.56

Tests your soldering tip to make sure it is grounded.

MOUSER STOCK NO.	Menda Part No.	Description	Price Each	
			1	5
809-35110	35110	Solder Tip Tester	205.53	195.23

## MENDA SOLDER TIP TESTER

- AC ground monitoring system
- LED pass/fail and audible alarm
- Ground and sensor cable harness
- Made in America
- Battery Power standard (2-AAA) or AC power optional

