

TOSHIBA Transistors

RoHS Compliant This product is RoHS compliant.

TOSHIBA
Leading Innovation >>>



RoHS Compliant
For quantities of 500 and up, call for quote.

Transistors

TOSHIBA
Leading Innovation >>>

TRANSISTORS

Toshiba

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Transistor Polarity	Voltage Output	Continuous Collector Current	Price Each			
						1	10	100	250
Bias Resistor Built-in Transistors (Cont.)									
757-RN1102FS(TPL3)	RN1102FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.064	.054	.05
757-RN1102MFV(TPL3)	RN1102MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1103FS(TPL3)	RN1103FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.064	.054	.05
757-RN1103MFV(TPL3)	RN1103MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.06	.051	.047
757-RN1104FS(TPL3)	RN1104FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.064	.054	.05
757-RN1104MFV(TPL3)	RN1104MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1105FS(TPL3)	RN1105FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.064	.054	.05
757-RN1105MFV(TPL3)	RN1105MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1106FS(TPL3)	RN1106FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.064	.054	.05
757-RN1106MFV(TPL3)	RN1106MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1107FS(TPL3)	RN1107FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.066	.056	.051
757-RN1107MFV(TPL3)	RN1107MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1108FS(TPL3)	RN1108FS(TPL3)	fSM-3	NPN	20V	50 mA	.09	.07	.06	.055
757-RN1108MFV(TPL3)	RN1108MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1109FS(TPL3)	RN1109FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.066	.056	.051
757-RN1109MFV(TPL3)	RN1109MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1110FS(TPL3)	RN1110FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.066	.056	.051
757-RN1110MFV(TPL3)	RN1110MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1111FS(TPL3)	RN1111FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.066	.056	.051
757-RN1111MFV(TPL3)	RN1111MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1112FS(TPL3)	RN1112FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.066	.056	.051
757-RN1112MFV(TPL3)	RN1112MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1113FS(TPL3)	RN1113FS(TPL3)	fSM-3	NPN	20V	50 mA	.08	.066	.056	.051
757-RN1113MFV(TPL3)	RN1113MFV(TPL3)	VESM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1114MFV(TPL3)	RN1114MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1115MFV(TPL3)	RN1115MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1116MFV(TPL3)	RN1116MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1117MFV(TPL3)	RN1117MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1118MFV(TPL3)	RN1118MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1119MFV(TPL3)	RN1119MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1130MFV(TPL3)	RN1130MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1131MFV(TPL3)	RN1131MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1132MFV(TPL3)	RN1132MFV(TPL3)	VESM-3	NPN	50V	100mA	.06	.05	.043	.039
757-RN1301(TE85L,F)	RN1301(TE85L,F)	USM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1302TE85LF	RN1302TE85LF	USM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1303(TE85L,F)	RN1303(TE85L,F)	USM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1305(TE85L,F)	RN1305(TE85L,F)	USM-3	NPN	50V	100 mA	.06	.05	.043	.039
757-RN1962FS(TPL3)	RN1962FS(TPL3)	fS-6	NPN	20V	50 mA	.11	.085	.073	.066
757-RN1963FS(TPL3)	RN1963FS(TPL3)	fS-6	NPN	20V	50 mA	.11	.084	.072	.066
757-RN1964FS(TPL3)	RN1964FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.085	.073	.066
757-RN1965FS(TPL3)	RN1965FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.085	.073	.066
757-RN1966FS(TPL3)	RN1966FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.084	.072	.066
757-RN1967FS(TPL3)	RN1967FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.085	.073	.066
757-RN1968FS(TPL3)	RN1968FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.085	.073	.066
757-RN1969FS(TPL3)	RN1969FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.085	.073	.066
757-RN1970FS(TPL3)	RN1970FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.084	.072	.066
757-RN1971FS(TPL3)	RN1971FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.085	.073	.066
757-RN1972FS(TPL3)	RN1972FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.085	.073	.066
757-RN1973FS(TPL3)	RN1973FS(TPL3)	fS-6	NPNx2	20V	50 mA	.11	.085	.073	.066
757-RN2101FS(TPL3)	RN2101FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.066	.056	.051
757-RN2101MFV(TPL3)	RN2101MFV(TPL3)	VESM-3	PNP	50V	100 mA	.08	.06	.051	.047
757-RN2102FS(TPL3)	RN2102FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.066	.056	.051
757-RN2102MFV(TPL3)	RN2102MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039
757-RN2103FS(TPL3)	RN2103FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.066	.056	.051
757-RN2103MFV(TPL3)	RN2103MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039
757-RN2104FS(TPL3)	RN2104FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.066	.056	.051
757-RN2104MFV(TPL3)	RN2104MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039
757-RN2105FS(TPL3)	RN2105FS(TPL3)	fSM-3	PNP	20V	50 mA	.09	.07	.06	.055
757-RN2105MFV(TPL3)	RN2105MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039
757-RN2106MFV(TPL3)	RN2106MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039
757-RN2107FS(TPL3)	RN2107FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.064	.054	.05
757-RN2107MFV(TPL3)	RN2107MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039
757-RN2108FS(TPL3)	RN2108FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.064	.054	.05
757-RN2108MFV(TPL3)	RN2108MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039
757-RN2109FS(TPL3)	RN2109FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.066	.056	.051
757-RN2109MFV(TPL3)	RN2109MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039
757-RN2110FS(TPL3)	RN2110FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.064	.054	.05
757-RN2110MFV(TPL3)	RN2110MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039