

COMCHIP Diodes and Rectifiers



SMD Diodes Specialist



This page of product is compliant.

For quantities of 250 and up, call for quote.

ZENER DIODES (CONT.)

MOUSER STOCK NO.		Package Type	Zener Voltage	Zener Current	Forward Voltage Drop	Max Reverse Leakage Current	Power Dissipation	Max Zener Impedence	Termination Style	Mounting Style	Price Each		
Mfr.	Mfr. Part No.										1	10	100
750	CZRE52C2V7	0503	2.7 V	5 mA	0.9 V	75 uA	150 mW	83 Ohms	Solder Pad	SMD/SMT	.43	.30	.20
750	CZRF52C2V7	1005	2.7 V	5 mA	0.9 V	75 uA	200 mW	83 Ohms	Solder Pad	SMD/SMT	.47	.34	.22
750	CZRUR52C2V7	0603	2.7 V	5 mA	0.9 V	75 uA	150 mW	83 Ohms	Solder Pad	SMD/SMT	.47	.34	.22
750	CZRE52C3	0503	3 V	5 mA	0.9 V	50 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.43	.30	.20
750	CZRF52C3	1005	3 V	5 mA	0.9 V	50 uA	200 mW	95 Ohms	Solder Pad	SMD/SMT	.47	.34	.22
750	CZRUR52C3	0603	3 V	5 mA	0.9 V	50 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.47	.34	.22
750	CZRE52C3V3	0503	3.3 V	5 mA	0.9 V	25 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.43	.30	.20
750	CZRF52C3V3	1005	3.3 V	5 mA	0.9 V	25 uA	200 mW	95 Ohms	Solder Pad	SMD/SMT	.47	.34	.22
750	CZRUR52C3V3	0603	3.3 V	5 mA	0.9 V	25 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.47	.34	.22
750	CZRE52C3V6	0503	3.6 V	5 mA	0.9 V	15 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C3V6	1005	3.6 V	5 mA	0.9 V	15 uA	200 mW	95 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C3V6	0603	3.6 V	5 mA	0.9 V	15 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C3V9	0503	3.9 V	5 mA	0.9 V	10 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C3V9	1005	3.9 V	5 mA	0.9 V	10 uA	200 mW	95 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C3V9	0603	3.9 V	5 mA	0.9 V	10 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C4V3	0503	4.3 V	5 mA	0.9 V	5 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C4V3	1005	4.3 V	5 mA	0.9 V	5 uA	200 mW	95 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C4V3	0603	4.3 V	5 mA	0.9 V	5 uA	150 mW	95 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C4V7	0503	4.7 V	5 mA	0.9 V	5 uA	150 mW	78 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C4V7	1005	4.7 V	5 mA	0.9 V	5 uA	200 mW	78 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C4V7	0603	4.7 V	5 mA	0.9 V	5 uA	150 mW	78 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C5V1	0503	5.1 V	5 mA	0.9 V	0.1 uA	150 mW	60 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C5V1	1005	5.1 V	5 mA	0.9 V	0.1 uA	200 mW	60 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C5V1	0603	5.1 V	5 mA	0.9 V	0.1 uA	150 mW	60 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C5V6	0503	5.6 V	5 mA	0.9 V	0.1 uA	150 mW	40 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C5V6	1005	5.6 V	5 mA	0.9 V	0.1 uA	200 mW	40 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C5V6	0603	5.6 V	5 mA	0.9 V	0.1 uA	150 mW	40 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C6V2	0503	6.2 V	5 mA	0.9 V	0.1 uA	150 mW	10 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C6V2	1005	6.2 V	5 mA	0.9 V	0.1 uA	200 mW	10 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C6V2	0603	6.2 V	5 mA	0.9 V	0.1 uA	150 mW	10 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C6V8	0503	6.8 V	5 mA	0.9 V	0.1 uA	150 mW	8 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C6V8	1005	6.8 V	5 mA	0.9 V	0.1 uA	200 mW	8 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C6V8	0603	6.8 V	5 mA	0.9 V	0.1 uA	150 mW	8 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C7V5	0503	7.5 V	5 mA	0.9 V	0.1 uA	150 mW	7 Ohms	Solder Pad	SMD/SMT	.45	.32	.21
750	CZRF52C7V5	1005	7.5 V	5 mA	0.9 V	0.1 uA	200 mW	7 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C7V5	0603	7.5 V	5 mA	0.9 V	0.1 uA	150 mW	7 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C8V2	0503	8.2 V	5 mA	0.9 V	0.1 uA	200 mW	7 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRF52C8V2	1005	8.2 V	5 mA	0.9 V	0.1 uA	200 mW	7 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C8V2	0603	8.2 V	5 mA	0.9 V	0.1 uA	150 mW	7 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRE52C9V1	0503	9.1 V	5 mA	0.9 V	0.1 uA	200 mW	10 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRF52C9V1	1005	9.1 V	5 mA	0.9 V	0.1 uA	200 mW	10 Ohms	Solder Pad	SMD/SMT	.49	.37	.27
750	CZRUR52C9V1	0603	9.1 V	5 mA	0.9 V	0.1 uA	150 mW	10 Ohms	Solder Pad	SMD/SMT	.49	.37	.27

CIRCUIT PROTECTION

TVS Diodes

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.		Package Type	Polarity	Clamping Voltage	Breakdown Voltage	Operating Voltage	Peak Surge Current	Peak Pulse Power Dissipation	Capacitance	Price Each		
Mfr.	Mfr. Part No.									1	10	100
750	CTAN1424V-G	SOIC-14	Bidirectional	43 V	26.7 V	24 V	5 A	600 mW	50 pF	.98	.84	.65

ESD Suppressors

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.		Package Type	Power Dissipation Pd	Breakdown Voltage	Capacitance	Forward Voltage	Termination Style	Clamping Voltage	Price Each		
Mfr.	Mfr. Part No.								1	10	100
750	CDA3S06-G	SOT-23-6	225 mW	7.2 V	5 pF	0.95 V	SMD/SMT	--	.71	.55	.47
750	CDA4S14-G	SOT-23-4	225 mW	7.2 V	5 pF	0.95 V	SMD/SMT	--	.71	.55	.47
750	CDA6N08-G	SOIC-8	400 mW	7.2 V	5 pF	0.95 V	SMD/SMT	--	2.81	2.47	2.10
750	CDA8S03-G	SOT-23	225 mW	7.2 V	5 pF	0.95 V	SMD/SMT	--	.77	.58	.45
750	CPDER24V	0503	150 mW	28 V	10 pF	--	SMD/SMT	25V	.62	.47	.34
750	CPDER5V0	0503	150 mW	70 V	15 pF	--	SMD/SMT	7 V	.62	.47	.34
750	CPDER5V0U	0503	150 mW	6 V	90 pF	0.8 V	SMD/SMT	9.8 V	.56	.42	.30
750	CPDERT5V0	0503	150 mW	7 V	15 pF	--	SMD/SMT	15 V	.62	.47	.34
750	CPDERT5V0U	0503	150 mW	7 V	15 pF	0.8 V	SMD/SMT	9.8 V	.62	.47	.34
750	CPDF12V0U	1005	200 mW	15.5 V	60 pF	0.8 V	SMD/SMT	19 V	.48	.36	.26
750	CPDF5V0U	1005	200 mW	6 V	90 pF	0.8 V	SMD/SMT	9.8 V	.42	.32	.23
750	CPDFR12V	1005	200 mW	17 V	12 pF	--	SMD/SMT	25 V	.48	.36	.26
750	CPDFR24V	1005	200 mW	28 V	10 pF	--	SMD/SMT	47 V	.48	.36	.26
750	CPDFR5V0	1005	200 mW	7 V	15 pF	--	SMD/SMT	15 V	.48	.36	.26
750	CPDH3-5V0U	SOT-523	225 mW	6.1 V	60 pF	1.2V	SMD/SMT	8 V	.62	.46	.36
750	CPDH3V3UP	SOD-523	150 mW	3.5 V	12 pF	3.3 V	SMD/SMT	5.5 V	.67	.50	.40
750	CPDH5-5V0U	SOT-553	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.67	.50	.40
750	CPDH6-5V0U	SOT-563	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.67	.50	.40
750	CPDQR12V0U	0402	125 mW	15.5 V	60 pF	0.8 V	SMD/SMT	19 V	.50	.38	.30
750	CPDQR5V0	0402	125 mW	7 V	15 pF	--	SMD/SMT	15 V	.50	.38	.30
750	CPDQR5V0U	0402	125 mW	6 V	90 pF	0.8 V	SMD/SMT	9.8 V	.50	.38	.30
750	CPDT-12V	SOT-23	225 mW	17 V	12 pF	--	SMD/SMT	25 V	.56	.42	.30
750	CPDT-24V	SOT-23	225 mW	28 V	10 pF	--	SMD/SMT	47 V	.56	.42	.30
750	CPDT5-5V0U	SOT-23-5	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.56	.42	.33
750	CPDT-5V0	SOT-23	225 mW	7 V	15 pF	--	SMD/SMT	15 V	.56	.42	.33
750	CPDT-5V0SR	SOT-23	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.56	.42	.30
750	CPDT-5V0U	SOT-23	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.56	.42	.33
750	CPDT6-5V0U	SOT-23-6	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.56	.42	.33
750	CPDT6-5V4U	SOT-23-6	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.67	.50	.40
750	CPDU12V0U	0603	150 mW	15.5 V	60 pF	0.8 V	SMD/SMT	19 V	.62	.47	.34
750	CPDU24V	0603	150 mW	28 V	10 pF	--	SMD/SMT	25 V	.48	.36	.26
750	CPDU5V0	0603	150 mW	7 V	15 pF	--	SMD/SMT	7 V	.48	.36	.26
750	CPDU5V0U	0603	150 mW	6 V	90 pF	0.8 V	SMD/SMT	9.8V	.42	.32	.23
750	CPDUR12V	0603	150 mW	17 V	12 pF	--	SMD/SMT	25 V	.62	.47	.34
750	CPDUR24V	0603	150 mW	28 V	10 pF	--	SMD/SMT	47 V	.48	.36	.26
750	CPDUR5V0	0603	150 mW	7 V	15 pF	--	SMD/SMT	15 V	.48	.36	.26
750	CPDV3-5V0U	SOT-323	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.56	.42	.33
750	CPDV5-5V0U	SOT-353	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.62	.46	.36
750	CPDV6-5V0U	SOT-363	225 mW	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	.62	.46	.36
750	CPDVR085V0U	SOT-383F	--	6.1 V	60 pF	1.2 V	SMD/SMT	8 V	1.12	.95	.81
750	CSRS045V0P	SOT-143	225 mW	6.2 V	1.2 pF	0.8 V	SMD/SMT	8.1 V	1.20	1.02	.87
750	CSRS065V0P	SOT-23-6	225 mW	6 V	1.3 pF	0.8 V	SMD/SMT	8.1 V	1.01	.86	.73
750	CSRV065V0P	SOT-363	225 mW	6 V	1.3 pF	0.8 V	SMD/SMT	8.1 V	1.00	.85	.73

Diodes & Rectifiers

Comchip

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER