



## COLLET KNOBS

These collet knobs are available in 15mm and 21mm diameters with 6mm and 6.4mm shaft sizes. The knobs are secured to the shafts by means of the proven collet tightening method. With its modular design, multiple accessories can plug into the knobs for a customized look.

- Knobs are available unmarked or with marker line (line on 15mm knob only)
- Various cap colors available (plain, marker line, or dot)
- Pointers and nut covers are available in multiple colors
- Collet nut size: 15mm knob: 6mm; 21mm knob: 9mm

## 15MM KNOBS AND ACCESSORIES

### Knobs

MOUSER STOCK NO.	Fig.	Body Color	Line Color	Dimension (mm)			Shaft Size (mm)	Price Each			
				A	B	C		1	10	100	500
450-CK1560	A	Black	--	14.7	13.0	16.2	6.0	2.56	2.33	1.97	1.82
450-CK1564	A	Black	--	14.7	13.0	16.2	6.4	2.56	2.33	1.97	1.82
450-CKL560	A	Black	White	14.7	13.0	16.2	6.0	2.56	2.33	1.97	1.82
450-CKL564	A	Black	White	14.7	13.0	16.2	6.4	2.56	2.33	1.97	1.82

### Color Coded Caps

- Fits knobs 450-CK1560, 450CK1564, 450-CKL560, 450-CKL564

MOUSER STOCK NO.	Fig.	Cap Color	Pointer Color	Price Each			
				1	10	100	500
450-C151	B	Red	--	.20	.18	.14	.13
450-C152	B	Yellow	--	.20	.18	.14	.13
450-C153	B	Blue	--	.20	.18	.14	.13
450-C154	B	Green	--	.20	.18	.14	.13
450-C155	B	Grey	--	.20	.18	.14	.13
450-C156	B	Black	--	.20	.18	.14	.13
450-C157	B	Orange	--	.20	.18	.14	.13
450-CL151	C	Red	White	.28	.26	.23	.21
450-CL152	C	Yellow	White	.28	.26	.23	.21
450-CL153	C	Blue	White	.28	.26	.23	.21
450-CL154	C	Green	White	.28	.26	.23	.21
450-CL155	C	Grey	Black	.28	.26	.23	.21
450-CL156	C	Black	White	.28	.26	.23	.21
450-CL159	C	Orange	White	.28	.26	.23	.21
450-CS151	D	Red	White	.28	.26	.23	.21
450-CS152	D	Yellow	White	.28	.26	.23	.21
450-CS153	D	Blue	White	.28	.26	.23	.21
450-CS154	D	Green	White	.28	.26	.23	.21
450-CS155	D	Grey	Black	.28	.26	.23	.21
450-CS156	D	Black	White	.28	.26	.23	.21
450-CS159	D	Orange	White	.28	.26	.23	.21

### Pointers

MOUSER STOCK NO.	Fig.	Pointer Color	Line Color	Price Each			
				1	10	100	500
450-P151	E	Red	--	.35	.32	.28	.26
450-P152	E	Yellow	--	.35	.32	.28	.26
450-P153	E	Blue	--	.35	.32	.28	.26
450-P154	E	Green	--	.35	.32	.28	.26
450-P155	E	Grey	--	.35	.32	.28	.26
450-P156	E	Black	--	.35	.32	.28	.26

### Nut Covers

MOUSER STOCK NO.	Fig.	Pointer Color	Line Color	Price Each			
				1	10	100	500
<b>15mm</b>							
450-NC151	F	Red	--	.35	.32	.28	.26
450-NC155	F	Grey	--	.35	.32	.28	.26
450-NC156	F	Black	--	.35	.32	.28	.26
450-NCL151	G	Red	White	.48	.44	.38	.36
450-NCL155	G	Grey	Black	.48	.44	.38	.36
450-NCL156	G	Black	White	.48	.44	.38	.36

## 21MM KNOBS AND ACCESSORIES

### Knobs

MOUSER STOCK NO.	Fig.	Body Color	Line Color	Dimension (mm)			Shaft Size (mm)	Price Each			
				A	B	C		1	10	100	500
450-CK2160	H	Black	--	21.3	19.6	17.1	6.0	2.88	2.71	2.29	2.11
450-CK2164	H	Black	--	21.3	19.6	17.1	6.4	2.88	2.71	2.29	2.11

### Color Coded Caps

- Fits knobs 450-CK2160, 450-CK2164

MOUSER STOCK NO.	Fig.	Cap Color	Pointer Color	Price Each			
				1	10	100	500
450-C211	B	Red	--	.28	.26	.23	.21
450-C212	B	Yellow	--	.28	.26	.23	.21
450-C213	B	Blue	--	.28	.26	.23	.21
450-C214	B	Green	--	.28	.26	.23	.21
450-C215	B	Grey	--	.28	.26	.23	.21
450-C216	B	Black	--	.28	.26	.23	.21
450-C219	B	Orange	--	.28	.26	.23	.21
450-CL211	C	Red	White	.35	.32	.28	.26
450-CL212	C	Yellow	White	.35	.32	.28	.26
450-CL213	C	Blue	White	.35	.32	.28	.26
450-CL214	C	Green	White	.35	.32	.28	.26
450-CL215	C	Grey	Black	.35	.32	.28	.26
450-CL216	C	Black	White	.35	.32	.28	.26
450-CL219	C	Orange	White	.35	.32	.28	.26
450-CS211	D	Red	White	.35	.32	.28	.26
450-CS212	D	Yellow	White	.35	.32	.28	.26
450-CS213	D	Blue	White	.35	.32	.28	.26
450-CS214	D	Green	White	.35	.32	.28	.26
450-CS215	D	Grey	Black	.35	.32	.28	.26
450-CS216	D	Black	White	.35	.32	.28	.26
450-CS219	D	Orange	White	.35	.32	.28	.26

### Pointers

MOUSER STOCK NO.	Fig.	Pointer Color	Line Color	Price Each			
				1	10	100	500
450-P211	I	Red	--	.45	.41	.36	.34
450-P212	I	Yellow	--	.45	.41	.36	.34
450-P213	I	Blue	--	.45	.41	.36	.34
450-P214	I	Green	--	.45	.41	.36	.34
450-P215	I	Grey	--	.45	.41	.36	.34
450-P216	I	Black	--	.45	.41	.36	.34