

TEXAS INSTRUMENTS Analog ICs



Products may be RoHS compliant.
Check mouser.com for RoHS status.

TEXAS INSTRUMENTS AUDIO ADC

For quantities 500 and up, call for quote.

MOUSER STOCK NO.	TI Part No.	Package	No. of ADCs	Res	SNR (Typ)	# Inputs/ # Outputs	Sampling Rate (Max) (kHz)	Analog Supply	Digital Audio Interface	Control Interface	Digital Supply (up to 5V)	Price Each			
												1	25	100	250
595-PCM4201PW	PCM4201PW	TSSOP-16	1	24	112	1/0	108	5	PCM/DSP	H/W	1.8 - 3.3	5.50	4.40	3.70	3.57
595-PCM1870RHFT	PCM1870RHFT	QFN-24	2	16	90	2/0	50	2.4 - 3.6	LJ, RJ, I2S, DSP	I2C, SPI	1.71 - 3.6	4.50	3.60	2.80	2.66
595-PCM1807PW	PCM1807PW	TSSOP-14	2	24	101	2/0	96	4.5 - 5.5	L, I2S	SPI	2.7 - 3.6	2.47	1.98	1.54	1.46
595-PCM1850APJT	PCM1850APJT	PCM1850APJT	2	24	101	6x2/2	96	4.5 - 5.5	L, R, I2S	SPI	2.7 - 3.6	8.83	7.95	7.04	6.75
595-PCM1851APJT	PCM1851APJT	TQFP-32	2	24	101	6x2/2	96	4.5 - 5.5	L, R, I2S	I2C	2.7 - 3.6	8.83	7.95	7.04	6.75
595-PCM1803ADB	PCM1803ADB	SSOP-20	2	24	103	2/0	96	4.5 - 5.5	L, R, I2S	H/W	2.7 - 3.6	2.67	2.14	1.66	1.57
595-PCM1802DB	PCM1802DB	SSOP-20	2	24	105	2/0	96	4.5 - 5.5	L, R, I2S	H/W	2.7 - 3.6	7.30	5.84	4.92	4.73
595-PCM1804DB	PCM1804DB	SSOP-28	2	24	112	2/0	192	4.75 - 5.25	L, R, I2S, DSP	H/W	3 - 3.6	8.70	6.96	5.86	5.64
595-PCM1808PW	PCM1808PW	TSSOP-14	2	24	99	2/0	96	4.5 - 5.5	L, I2S	H/W	2.7 - 3.6	2.47	1.98	1.54	1.46
595-PCM4202DB	PCM4202DB	SSOP-28	2	24	118	2/0	216	5	PCM, DSD	H/W	3.3	10.90	8.72	7.35	7.07
595-PCM4220PFB	PCM4220PFB	TQFP-48	2	24	123	2/0	216	3.8 - 4.2	L, I2S, TDM, DSD	H/W	3 - 3.6	18.27	16.41	14.55	14.00
595-PCM4222PFB	PCM4222PFB	TQFP-48	2	24	124	2/0	216	3.8 - 4.2	DSD, I2S, L, TDM	H/W	3 - 3.6	23.91	22.33	20.72	20.40
595-PCM4204PAPT	PCM4204PAPT	HTQFP-64	4	24	118	4/0	216	5	PCM/DSD	H/W	3.3	13.24	11.92	10.57	10.13

TEXAS INSTRUMENTS AUDIO CODEC

For quantities 500 and up, call for quote.

MOUSER STOCK NO.	TI Part No.	Package	# DACs/ # ADCs	Res	SNR DAC/ SNR ADC (Typ) (dB)	Sampling Rate (Max) (kHz)	Digital Audio Interface	Digital Supply (up to 5V)	IO Supply	Price Each			
										1	25	100	250
595-TLV320AIC1107PW	TLV320AIC1107PW	TSSOP-20	1/1	13	-	8	PCM	2.7 - 3.3	-	6.00	4.80	4.04	3.90
595-TLV320AIC1103PBS	TLV320AIC1103PBS	TQFP-32	1/1	15	-	8	PCM	2.7 - 3.3	-	6.20	4.96	4.18	4.03
595-TLV320AIC10CPFB	TLV320AIC10CPFB	TQFP-48	1/1	16	90/87	22.05	DSP	3 - 3.6	-	5.20	4.16	3.51	3.38
595-TLV320AIC10IPFB	TLV320AIC10IPFB	TQFP-48	1/1	16	90/87	22.05	DSP	3 - 3.6	-	5.13	4.56	3.84	3.70
595-TLV320AIC11IPFB	TLV320AIC11IPFB	TQFP-48	1/1	16	90/87	22.05	DSP	3 - 5.5	1.1 - 3.6	6.50	5.20	4.38	4.22
595-PCM3500E	PCM3500E	SSOP-24	1/1	16	92/88	26	DSP	2.7 - 3.6	-	7.20	5.76	4.84	4.66
595-TLV320AIC12KIDBT	TLV320AIC12KIDBTG4	TSSOP-30	1/1	16	92/84	26	DSP, SMART, TDM	1.65 - 1.95	1.1 - 3.6	4.03	3.24	2.52	2.38
595-TLV320AIC14KIDBT	TLV320AIC14KIDBT	TSSOP-30	1/1	16	92/84	26	DSP, SMART, TDM	1.65 - 1.95	1.1 - 3.6	3.38	2.70	2.10	1.99
595-PCM2912PJT	PCM2912PJT	TQFP-32	2/1	16	92/92	48	USB	3 - 3.6	5	8.91	7.92	6.68	6.43
595-TLV320AIC26IRHB	TLV320AIC26IRHB	QFN-32	2/1	24	97/92	53	L, R, I2S, DSP	1.525 - 1.95	1.1 - 3.6	6.60	5.28	4.45	4.29
595-TLV320AIC20KIPFB	TLV320AIC20KIPFB	TQFP-48	2/2	16	92/84	26	DSP, SMART, TDM	1.65 - 1.95	1.1 - 3.6	5.90	4.72	3.97	3.82
595-TLV320AIC24KIPFB	TLV320AIC24KIPFB	TQFP-48	2/2	16	92/84	26	DSP, SMART, TDM	1.65 - 1.95	1.1 - 3.6	5.40	4.32	3.63	3.50
595-PCM3794ARHBT	PCM3794ARHBT	QFN-32	2/2	16	93/90	50	DSP, I2S, L, R	1.71 - 3.6	1.71 - 3.6	9.40	7.52	6.34	6.11
595-PCM2900E	PCM2900E	SSOP-28	2/2	16	96/89	48	USB	4.35 - 5.25	-	8.56	7.71	6.83	6.55
595-PCM2902E	PCM2902E	SSOP-28	2/2	16	96/89	48	USB	4.35 - 5.25	-	9.90	7.92	6.67	6.43
595-PCM2906DB	PCM2906DB	SSOP-28	2/2	16	96/89	48	USB	4.35 - 5.25	-	9.35	8.41	7.46	7.15
595-PCM3000E	PCM3000E	SSOP-28	2/2	18	98/94	48	R, L, I2S, DSP	4.5 - 5.5	-	7.60	6.08	5.12	4.93
595-PCM3001E	PCM3001E	SSOP-28	2/2	18	98/94	48	R, L, I2S, DSP	4.5 - 5.5	-	7.60	6.08	5.12	4.93
595-PCM3003E	PCM3003E	SSOP-24	2/2	20	94/90	48	R, L	2.4 - 3.6	-	7.60	6.08	5.12	4.93
595-TLV320AIC23BIPW	TLV320AIC23BIPW	TSSOP-28	2/2	24	100/90	96	L, R, I2S, DSP	1.42 - 3.6	-	8.20	6.56	5.53	5.33
595-TLV320AIC23BPW	TLV320AIC23BPW	TSSOP-28	2/2	24	100/90	96	L, R, I2S, DSP	1.42 - 3.6	-	7.40	5.92	4.99	4.80
595-TLV320AIC23BRHD	TLV320AIC23BRHD	QFN-28	2/2	24	100/90	96	L, R, I2S, DSP	1.42 - 3.6	-	7.40	5.92	4.99	4.80
595-TLV320AIC31IRHBT	TLV320AIC31IRHBT	QFN-32	2/2	24	100/90	96	DSP, I2S, L, R	1.525 - 1.95	1.1 - 3.6	6.84	6.08	5.13	4.94
595-T320AIC3101IRHBT	TLV320AIC3101IRHBT	QFN-32	2/2	24	100/90	96	DSP, I2S, L, R	1.525 - 1.95	1.1 - 3.6	6.80	5.44	4.59	4.42
595-TLV320AIC3104IRHBT	TLV320AIC3104IRHBT	QFN-32	2/2	24	100/90	96	L, R, I2S, DSP	1.525 - 1.95	1.1 - 3.6	6.30	5.04	4.25	4.09
595-TLV320AIC3105IRHBT	TLV320AIC3105IRHBT	QFN-32	2/2	24	100/90	96	DSP, I2S, L, R	1.525 - 1.95	1.1 - 3.6	6.30	5.04	4.25	4.09
595-TLV320AIC32IRHBT	TLV320AIC32IRHBT	QFN-32	2/2	24	100/90	96	DSP, I2S, L, R	1.525 - 1.95	1.1 - 3.6	7.40	5.92	4.99	4.81
595-TLV320AIC33IGQE	TLV320AIC33IGQE	BGA MICROSTAR JR-80	2/2	24	100/90	96	DSP, I2S, L, R, TMD	1.525 - 1.95	1.1 - 3.6	8.10	6.48	5.45	5.25
595-TLV320AD77CDB	TLV320AD77CDB	SSOP-28	2/2	24	100/100	96	R, L, I2S, DSP	3 - 3.6	-	7.00	5.60	4.72	4.54
595-TLV320A3106IZQE	TLV320AIC3106IZQE	BGA MICROSTAR JR-80	2/2	24	102/92	96	DSP, I2S, L, R	1.525 - 1.95	1.1 - 3.6	7.30	5.84	4.92	4.74
595-PCM3010DB	PCM3010DB	SSOP-24	2/2	24	104/100	192	R, L, I2S	3 - 3.6	-	8.80	7.04	5.94	5.72
595-PCM3060PW	PCM3060PW	TSSOP-28	2/2	24	105/99	192	I2S, L, R	2.7 - 3.6	-	4.82	3.87	3.01	2.85
595-PCM3052ARTF	PCM3052ARTF	QFN-32	2/2	24	105/101	96	I2S	3 - 3.6	-	6.60	5.28	4.45	4.29
595-TLV320AIC34IZAS	TLV320AIC34IZAS	BGA-87	4/4	24	102/92	96	L, R, I2S, DSP	1.525 - 1.95	1.1 - 3.6	10.01	8.99	7.97	7.67

TEXAS INSTRUMENTS AUDIO DIGITAL-TO-ANALOG CONVERTERS (DACs)

For quantities 500 and up, call for quote.

MOUSER STOCK NO.	TI Part No.	Package	No. of DACs	Res	SNR (Typ) (dB)	Sampling Rate (Max) (kHz)	# Inputs/ # Outputs	Digital Audio Interface	Control Interface	Analog Supply	Price Each			
											1	25	100	250
595-PCM1702P-K	PCM1702P-K	PDIP-16	1	20	120	768	0/1	-	H/W	±4.75 - 5.25	24.61	22.97	21.33	20.92
595-PCM1704U	PCM1704U	SO-20	1	24	120	768	0/1	-	H/W	±4.75 - 5.25	37.64	35.13	32.62	31.99
595-PCM1774RGPT	PCM1774RGPT	QFN-20	2	16	93	50	0/2	LJ, RJ, I2S, DSP	I2C, SPI	2.4 - 3.6	3.35	2.97	2.31	2.19
595-PCM2704DB	PCM2704DB	SSOP-28	2	16	98	48	0/2	USB	HID	4.35 - 5.25	5.70	4.56	3.84	3.69
595-PCM2702E	PCM2702E	SSOP-28	2	16	105	48	0/2	USB	HID	4.5 - 5.5	13.59	12.24	10.85	10.39
595-PCM1754DBQG4	PCM1754DBQG4	SSOP-16	2	24	106	192	0/2	R, I2S	H/W	4.5 - 5.5	2.58	2.07	1.61	1.52
595-TLV320DAC32IRHBT	TLV320DAC32IRHBT	QFN-32	2	24	95	96	2/4	DSP, I2S, L, R, TDM	I2C	2.7-3.6	5.50	4.40	3.70	3.57
595-TLV320DAC23PW	TLV320DAC23PW	TSSOP-28	2	24	100	96	0/4	DSP, I2S, L, R	I2C, SPI	2.7-3.6	4.95	3.96	3.08	2.92
595-PCM1755DBQ	PCM1755DBQ	SSOP-16	2	24	106	192	0/2	L, R, I2S	SPI	4.5-5.5	2.58	2.07	1.61	1.52
595-PCM1791ADB	PCM1791ADB	SSOP-28	2	24	113	192	0/2	L, R, I2S, TDMCA, DSD	I2C, SPI	4.5-5.5	5.28	4.23	3.29	3.12
595-PCM1792ADB	PCM1792ADB	SSOP-28	2	24	127	192	0/2	L, R, I2C, TDMCA, DSD	SPI, I2C	4.75-5.25	16.58	14.92	13.23	12.68
595-PCM1793DB	PCM1793DB	SSOP-28	2	24	113	192	0/2	L, R, I2S	H/W	4.5-5.5	5.28	4.23	3.29	3.12
595-PCM1794ADB	PCM1794ADB	SSOP-28	2	24	127	192	0/2	L, R, I2S	H/W	4.75-5.25	18.27	16.41	14.55	14.00
595-PCM1796DB	PCM1796DB	SSOP-28	2	24	123	192	0/2	L, R, I2S, TDMCA, DSD	I2C, SPI	4.75-5.25	6.50	5.20	4.38	4.21
595-PCM4104PFBT	PCM4104PFBT	TQFP-48	4	24	118	192	0/2x2	I2S, TDM	H/W, SPI	5	8.67	8.17	7.24	6.94
595-PCM1602APT	PCM1602APT	LQFP-48	6	24	105	192	0/6	L, R, I2S	SPI	4.5 - 5.5	6.20	4.96	4.18	4.03
595-PCM1609APT	PCM1609APT	LQFP-48	8	24	105	192	0/8	L, R, I2S	SPI	4.5-5.5	7.10	5.68	4.79	4.61
595-PCM1680DBQ	PCM1680DBQ	SSOP-28	8	24	105	192	0/8	L, R, I2S	I2C, SPI	4.75-5.25	3.70	2.97	2.31	2.18
595-PCM1681PWP	PCM1681PWP	HTSSOP-28	8	24	105	200	0/8	L, R, I2S, TDM, DSD	SPI, I2C, HW	4.5-5.5	4.15	3.33	2.59	2.45

