

TEXAS INSTRUMENTS Analog ICs



Products may be RoHS compliant.
Check mouser.com for RoHS status.

TEXAS INSTRUMENTS LINE CIRCUITS

For quantities 500 and up, call for quote.

MOUSER STOCK NO.	TI Part No.	Package	Drivers Per Package	Receivers Per Package	Driver (RL) (Ohms)	Receiver (Vth) (mV)	Supply Voltage	Driver tpd (ns)	Receiver tpd (ns)	ICC (Max) (mA)	Price Each			
											1	25	100	250
595-SN75116N	SN75116N	PDIP-16	1	1	100	1000	5	-	30	60	3.78	3.34	2.60	2.47
595-SN75118N	SN75118N	PDIP-16	1	1	100	1000	5	-	30	60	4.39	3.88	3.01	2.86
595-SN75119P	SN75119P	PDIP-8	1	1	100	1000	5	-	30	60	4.39	3.88	3.01	2.86
595-SN65ALS1176D	SN65ALS1176D	SOIC-8	1	1	-	-	5	8	25	30	4.33	3.47	2.70	2.55
595-SN65HVD61D	SN65HVD61D	SOIC-14	1	1	-	-	5	-	-	65	8.75	7.87	6.98	6.69
595-SN75113N	SN75113N	PDIP-16	2	-	100	-	5	30	-	65	2.44	2.16	1.68	1.59
595-SN75114N	SN75114N	PDIP-16	2	-	100	-	5	30	-	50	2.32	2.05	1.59	1.51
595-SN75183N	SN75183N	PDIP-14	2	-	100	-	5	18	-	18	2.38	2.10	1.63	1.55
595-SN75110AD	SN75110AD	SOIC-14	2	-	-	-	5	15	-	35	.88	.66	.495	.365
595-SN75110AN	SN75110AN	PDIP-14	2	-	-	-	5	15	-	35	.72	.60	.45	.332
595-SN75112N	SN75112N	PDIP-14	2	-	-	-	5	15	-	40	.89	.82	.66	.495
595-SN751730D	SN751730D	SOIC-16	3	3	-	-	5	18.5	19.5	47, 80	4.45	3.56	2.77	2.62
595-SN75138N	SN75138N	PDIP-16	4	4	50	-	5	24	15	65	1.80	1.60	1.20	1.12
595-SN75ALS057N	SN75ALS057N	PDIP-20	4	4	-	-	5	-	-	40	5.24	4.19	3.26	3.09
595-AM26LV31CD	AM26LV31CD	SOIC-16	4	-	-	-	3.3	-	-	0.1	.99	.82	.66	.495
595-SN75160BDW	SN75160BDW	SOIC-20	8	8	-	-	5	20	22	110	2.20	1.76	1.32	1.23
595-SN75160BN	SN75160BN	PDIP-20	8	8	-	-	5	20	22	110	1.80	1.60	1.20	1.12
595-SN75161BDW	SN75161BDW	SOIC-20	8	8	-	-	5	20	35	110	2.20	1.76	1.32	1.23
595-SN75161BN	SN75161BN	PDIP-20	8	8	-	-	5	20	35	110	1.80	1.60	1.20	1.12
595-SN75162BDW	SN75162BDW	SOIC-24	8	8	-	-	5	20	35	110	4.27	3.78	2.94	2.79
595-SN75ALS160DW	SN75ALS160DW	SOIC-20	8	8	-	-	5	20	18	80	2.36	1.89	1.47	1.39
595-SN75ALS160N	SN75ALS160N	PDIP-20	8	8	-	-	5	20	18	80	2.37	1.90	1.42	1.33
595-SN75ALS162DW	SN75ALS162DW	SOIC-24	8	8	-	-	5	20	14	75	5.17	4.13	3.21	3.04
595-SN75107AN	SN75107AN	PDIP-14	-	2	-	25	-	-	-	-	1.35	1.20	.90	.84
595-SN75107BDR	SN75107BDR	SOIC-14	-	2	-	25	-	-	-	-	.80	.60	.45	.332
595-SN75107BN	SN75107BN	PDIP-14	-	2	-	25	-	-	-	-	.72	.60	.45	.332
595-SN75115D	SN75115D	SOIC-16	-	2	-	1000	5	-	75	50	2.36	1.89	1.47	1.39
595-SN75115N	SN75115N	PDIP-16	-	2	-	1000	5	-	75	50	2.14	1.90	1.42	1.33
595-SN75140P	SN75140P	PDIP-8	-	2	-	-	5	-	35	35	1.80	1.44	1.08	1.00
595-SN75182N	SN75182N	PDIP-14	-	2	-	1000	5	-	45	10.2	1.25	1.00	.75	.70
595-SN75207BN	SN75207BN	PDIP-14	-	2	-	25	5	-	35	30	2.81	2.25	1.75	1.66
595-SN75ALS197N	SN75ALS197N	PDIP-16	-	4	-	-	-	-	22	35	.60	.45	.33	.249
595-SN75ALS199D	SN75ALS199D	SOIC-16	-	4	-	-	-	-	22	35	1.38	1.15	.92	.69

TEXAS INSTRUMENTS PERIPHERAL DRIVERS & ACUATORS

For quantities 500 and up, call for quote.

MOUSER STOCK NO.	TI Part No.	Package	Output Voltage (Max)	Peak Switching Voltage (Max)	Output Current (mA)	Drivers Per Package	Input Compatibility	Delay Time (Typ) (ns)	Price Each			
									1	25	100	250
595-TPL9201N	TPL9201N	PDIP-20	16.5	-	150	8	CMOS	10, 80	1.27	1.02	.765	.714
595-TPL9201PWPR	TPL9201PWPR	HTSSOP-20	16.5	-	150	8	CMOS	10, 80	1.25	1.00	.75	.70
595-SN75372D	SN75372D	SOIC-8	24	24	500	2	TTL	20	2.47	1.98	1.48	1.38
595-SN75372P	SN75372P	PDIP-8	24	24	500	2	TTL	20	2.03	1.80	1.35	1.26
595-SN75374D	SN75374D	SOIC-16	24	24	500	4	TTL	20	2.71	2.17	1.69	1.60
595-SN75451BD	SN75451BD	SOIC-8	30	20	500	2	TTL	18	.60	.48	.363	.269
595-SN75451BP	SN75451BP	PDIP-8	30	20	500	2	TTL	18	.55	.44	.33	.244
595-SN75452BD	SN75452BD	SOIC-8	30	20	500	2	TTL	26	.88	.66	.495	.365
595-SN75452BP	SN75452BP	PDIP-8	30	20	500	2	TTL	26	.55	.44	.33	.244
595-SN75453BD	SN75453BD	SOIC-8	30	20	500	2	TTL	18	.88	.66	.495	.365
595-SN75453BP	SN75453BP	PDIP-8	30	20	500	2	TTL	18	.55	.44	.33	.244
595-SN75454BP	SN75454BP	PDIP-8	30	20	500	2	TTL	27	.72	.60	.45	.332
595-SN75462P	SN75462P	PDIP-8	35	30	500	2	TTL	45	1.03	.95	.76	.57
595-SN75463P	SN75463P	PDIP-8	35	30	500	2	TTL	30	1.22	1.08	.81	.756
595-L293DNE	L293DNE	PDIP-16	36	36	1200	4	TTL	800	2.48	2.19	1.70	1.62
595-L293NE	L293NE	PDIP-16	36	36	2000	4	TTL	800	2.48	2.19	1.70	1.62
595-SN754410NE	SN754410NE	PDIP-16	36	36	2000	4	CMOS, TTL	800	1.65	1.32	.99	.924
595-ULN2003AIDR	ULN2003AIDR	SOIC-16	50	0.02	500	7	CMOS, TTL	250	.64	.48	.36	.265
595-ULN2003AIN	ULN2003AIN	PDIP-16	50	0.02	500	7	CMOS, TTL	250	.57	.48	.36	.265
595-ULN2003AIPWR	ULN2003AIPWR	TSSOP-16	50	0.02	500	7	CMOS, TTL	250	.64	.48	.36	.265
595-ULN2003AD	ULN2003AD	SOIC-16	50	50	500	7	CMOS, TTL	250	.65	.54	.405	.298
595-ULN2003AN	ULN2003AN	PDIP-16	50	50	500	7	CMOS, TTL	250	.57	.48	.36	.265
595-ULN2004AD	ULN2004AD	SOIC-16	50	50	500	7	CMOS	250	.72	.54	.405	.298
595-ULN2004AN	ULN2004AN	PDIP-16	50	50	500	7	CMOS	250	.57	.48	.36	.265
595-ULN2803ADWR	ULN2803ADWR	SOIC-18	50	50	500	8	-	130	.67	.625	.50	.375
595-ULN2803AN	ULN2803AN	PDIP-18	50	50	500	8	-	130	1.22	1.12	.90	.675
595-DS3680D	DS3680D	SOIC-14	60	60	100	4	CMOS, TTL	1000	.93	.77	.62	.465
595-DS3680N	DS3680N	PDIP-14	60	60	100	4	CMOS, TTL	1000	.81	.75	.60	.45
595-SN75437ANE	SN75437ANE	PDIP-16	70	35	750	4	CMOS, TTL	1950	2.20	1.76	1.32	1.23
595-SN75471P	SN75471P	PDIP-8	70	55	500	2	TTL	30	.86	.72	.54	.398
595-SN75472P	SN75472P	PDIP-8	70	55	500	2	TTL	45	.66	.49	.371	.273
595-SN75468D	SN75468D	SOIC-16	100	50	500	7	CMOS, TTL	250	.84	.69	.56	.42
595-SN75468N	SN75468N	PDIP-16	100	50	500	7	CMOS, TTL	250	.62	.46	.346	.305
595-SN75469N	SN75469N	PDIP-16	100	50	500	7	CMOS	250	.72	.60	.45	.332
595-SN75477DR	SN75477DR	SOIC-8	100	55	500	2	CMOS, TTL	200	.80	.60	.45	.332
595-SN75477P	SN75477P	PDIP-8	100	55	500	2	CMOS, TTL	200	.66	.49	.371	.273

TEXAS INSTRUMENTS PCI BRIDGES

For quantities 500 and up, call for quote.

MOUSER STOCK NO.	TI Part No.	Package	Intel Compatible Part Number	Speed (MHz)	Expansion Interface (Bits)	Hot Swap	Supply Voltage	Price Each			
								1	25	100	250
595-PCI2050BIGHK	PCI2050BIGHK	BGA MICROSTAR-257	21150bc	66	32	Friendly	3.3, 5	15.67	14.63	13.58	13.37
595-PCI2050BIPDV	PCI2050BIPDV	LQFP-208	21150bc	66	32	Friendly	3.3, 5	15.67	14.63	13.58	13.37
595-PCI2050BPDV	PCI2050BPDV	LQFP-208	21150bc	66	32	Friendly	3.3, 5	15.83	14.25	12.63	12.11
595-PCI2050BZHK	PCI2050BZHK	BGA MICROSTAR-257	21150bc	66	32	Friendly	3.3, 5	15.83	14.25	12.63	12.11
595-PCI2060ZHK	PCI2060ZHK	BGA MICROSTAR-257	-	66	32	Friendly	3.3, 5	17.85	16.66	15.47	15.17

