


TOSHIBA Diodes

 This product is RoHS compliant.

TOSHIBA
Leading Innovation >>>

TOSHIBA
Leading Innovation >>>

ESD PROTECTION



RoHS Compliant

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Voltage Output	Current (mA)	Price Each			
					1	100	250	1000
757-DF3A5.6F(TE85L,F)	DF3A5.6F(TE85L,F)	S-MINI	5.6V	5mA	.13	.085	.078	.069
757-DF3A5.6LFUTE85LF	DF3A5.6LFU(TE85L,F)	USM	5.6V	5mA	.14	.094	.086	.076
757-DF3A6.2LFUTE85LF	DF3A6.2LFU(TE85L,F)	USM	6.2V	5mA	.14	.094	.086	.076
757-DF3A6.2CT(TPL3)	DF3A6.2CT(TPL3)	USM	6.2V	5mA	.15	.102	.093	.083
757-DF3A6.2F(TE85L,F)	DF3A6.2F(TE85L,F)	S-MINI	6.2V	5mA	.13	.085	.078	.069
757-DF3A6.8LFUTE85LF	DF3A6.8LFU(TE85L,F)	USM	6.8V	5mA	.14	.094	.086	.076
757-DF3A8.2CT(TPL3)	DF3A8.2CT(TPL3)	CST3	8.2V	5mA	.15	.102	.093	.083

TOSHIBA
Leading Innovation >>>

ZENER DIODES



RoHS Compliant

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Reverse Voltage	Power Dissipation	Price Each			
					1	100	250	1000
757-015AZ10-X(TH3,F,T)	015AZ10-X(TH3,F,T)	ESC-2	10V	150mW	.06	.043	.039	.035
757-015AZ11-X(TH3,F,T)	015AZ11-X(TH3,F,T)	ESC-2	11V	150mW	.06	.043	.039	.035
757-015AZ12-X(TH3,F,T)	015AZ12-X(TH3,F,T)	ESC-2	12V	150mW	.06	.043	.039	.035
757-015AZ2.0-X(TL3,F,T)	015AZ2.0-X(TL3,F,T)	ESC-2	2V	150mW	.06	.043	.039	.035
757-015AZ2.2-X(TH3,F,T)	015AZ2.2-X(TH3,F,T)	ESC-2	2.2V	150mW	.06	.043	.039	.035
757-015AZ2.4-X(TH3,F,T)	015AZ2.4-X(TH3,F,T)	ESC-2	2.4V	150mW	.06	.043	.039	.035
757-015AZ2.7-X(TH3,F,T)	015AZ2.7-X(TH3,F,T)	ESC-2	2.7V	150mW	.06	.043	.039	.035
757-015AZ20-X(TH3,F,T)	015AZ20-X(TH3,F,T)	ESC-2	20V	150mW	.06	.043	.039	.035
757-015AZ22-X(TH3,F,T)	015AZ22-X(TH3,F,T)	ESC-2	22V	150mW	.06	.043	.039	.035
757-015AZ24-X(TH3,F,T)	015AZ24-X(TH3,F,T)	ESC-2	24V	150mW	.06	.043	.039	.035
757-015AZ3.0-X(TH3,F,T)	015AZ3.0-X(TH3,F,T)	ESC-2	3V	150mW	.06	.043	.039	.035
757-015AZ3.3-X(TH3,F,T)	015AZ3.3-X(TH3,F,T)	ESC-2	3.3V	150mW	.06	.043	.039	.035
757-015AZ3.6-X(TH3,F,T)	015AZ3.6-X(TH3,F,T)	ESC-2	3.6V	150mW	.06	.043	.039	.035
757-015AZ3.9-X(TH3,F,T)	015AZ3.9-X(TH3,F,T)	ESC-2	3.9V	150mW	.06	.043	.039	.035
757-015AZ4.3-X(TH3,F,T)	015AZ4.3-X(TH3,F,T)	ESC-2	4.3V	150mW	.06	.043	.039	.035
757-015AZ4.7-X(TH3,F,T)	015AZ4.7-X(TH3,F,T)	ESC-2	4.7V	150mW	.06	.043	.039	.035
757-015AZ5.1-X(TH3,F,T)	015AZ5.1-X(TH3,F,T)	ESC-2	5.1V	150mW	.06	.043	.039	.035
757-015AZ5.6-X(TH3,F,T)	015AZ5.6-X(TH3,F,T)	ESC-2	5.6V	150mW	.06	.043	.039	.035
757-015AZ6.2-X(TH3,F,T)	015AZ6.2-X(TH3,F,T)	ESC-2	6.2V	150mW	.06	.043	.039	.035
757-015AZ6.8-X(TH3,F,T)	015AZ6.8-X(TH3,F,T)	ESC-2	6.8V	150mW	.06	.043	.039	.035
757-015AZ7.5-X(TH3,F,T)	015AZ7.5-X(TH3,F,T)	ESC-2	7.5V	150mW	.06	.043	.039	.035
757-015AZ8.2-X(TH3,F,T)	015AZ8.2-X(TH3,F,T)	ESC-2	8.2V	150mW	.06	.043	.039	.035
757-015AZ9.1-X(TH3,F,T)	015AZ9.1-X(TH3,F,T)	ESC-2	9.1V	150mW	.06	.043	.039	.035
757-02DZ100(TPH3,F)	02DZ100(TPH3,F)	USC-2	6.2V	200mW	.13	.091	.083	.078
757-02DZ10-X(TPH3,F)	02DZ10-X(TPH3,F)	USC-2	10V	150mW	.06	.043	.039	.035
757-02DZ11-X(TPH3,F)	02DZ11-X(TPH3,F)	USC-2	11V	150mW	.06	.043	.039	.035
757-02DZ12-X(TPH3,F)	02DZ12-X(TPH3,F)	USC-2	12V	150mW	.06	.043	.039	.035
757-02DZ13-X(TPH3,F)	02DZ13-X(TPH3,F)	USC-2	13V	150mW	.06	.043	.039	.035
757-02DZ15-X(TPH3,F)	02DZ15-X(TPH3,F)	USC-2	15V	150mW	.06	.043	.039	.035
757-02DZ16-X(TPH3,F)	02DZ16-X(TPH3,F)	USC-2	16V	150mW	.06	.043	.039	.035
757-02DZ18-X(TPH3,F)	02DZ18-X(TPH3,F)	USC-2	18V	150mW	.06	.043	.039	.035
757-02DZ20-X(TPH3,F)	02DZ20-X(TPH3,F)	USC-2	2V	150mW	.06	.043	.039	.035
757-02DZ2.2-X(TPH3,F)	02DZ2.2-X(TPH3,F)	USC-2	2.2V	150mW	.06	.043	.039	.035
757-02DZ2.4-X(TPH3,F)	02DZ2.4-X(TPH3,F)	USC-2	2.4V	150mW	.06	.043	.039	.035
757-02DZ2.7-X(TPH3,F)	02DZ2.7-X(TPH3,F)	USC-2	2.7V	150mW	.06	.043	.039	.035
757-02DZ20-X(TPH3,F)	02DZ20-X(TPH3,F)	USC-2	20V	150mW	.06	.043	.039	.035
757-02DZ22-X(TPH3,F)	02DZ22-X(TPH3,F)	USC-2	22V	150mW	.06	.043	.039	.035
757-02DZ24-X(TPH3,F)	02DZ24-X(TPH3,F)	USC-2	24V	150mW	.06	.043	.039	.035
757-02DZ3.0-X(TPH3,F)	02DZ3.0-X(TPH3,F)	USC-2	3V	150mW	.06	.043	.039	.035
757-02DZ3.3-X(TPH3,F)	02DZ3.3-X(TPH3,F)	USC-2	3.3V	150mW	.06	.043	.039	.035
757-02DZ3.6-X(TPH3,F)	02DZ3.6-X(TPH3,F)	USC-2	3.6V	150mW	.06	.043	.039	.035
757-02DZ3.9-X(TPH3,F)	02DZ3.9-X(TPH3,F)	USC-2	3.9V	150mW	.06	.043	.039	.035
757-02DZ4.3-X(TPH3,F)	02DZ4.3-X(TPH3,F)	USC-2	4.3V	150mW	.06	.043	.039	.035
757-02DZ4.7-X(TPH3,F)	02DZ4.7-X(TPH3,F)	USC-2	4.7V	150mW	.06	.043	.039	.035
757-02DZ5.1-X(TPH3,F)	02DZ5.1-X(TPH3,F)	USC-2	5.1V	150mW	.06	.043	.039	.035
757-02DZ5.6-X(TPH3,F)	02DZ5.6-X(TPH3,F)	USC-2	5.6V	150mW	.06	.043	.039	.035
757-02DZ6.2-X(TPH3,F)	02DZ6.2-X(TPH3,F)	USC-2	6.2V	150mW	.06	.043	.039	.035
757-02DZ6.8-X(TPH3,F)	02DZ6.8-X(TPH3,F)	USC-2	6.8V	150mW	.06	.043	.039	.035
757-02DZ7.5-X(TPH3,F)	02DZ7.5-X(TPH3,F)	USC-2	7.5V	150mW	.06	.043	.039	.035
757-02DZ8.2-X(TPH3,F)	02DZ8.2-X(TPH3,F)	USC-2	8.2V	150mW	.06	.043	.039	.035
757-02DZ9.1-X(TPH3,F)	02DZ9.1-X(TPH3,F)	USC-2	9.1V	150mW	.06	.043	.039	.035
757-CRZ10(TE85L,Q)	CRZ10(TE85L,Q)	S-FLAT-2	10V	0.7 W	.38	.26	.23	.21
757-CRZ15(TE85L,Q)	CRZ15(TE85L,Q)	S-FLAT-2	15V	0.7W	.38	.26	.23	.21
757-CRZ16(TE85L,Q)	CRZ16(TE85L,Q)	S-FLAT-2	16V	0.7 W	.33	.23	.20	.18
757-CRZ30(TE85L,Q)	CRZ30(TE85L,Q)	S-FLAT-2	30V	0.7 W	.38	.26	.23	.21

