

TOSHIBA MOSFETs

RoHS Compliant This product is RoHS compliant.

TOSHIBA
Leading Innovation >>>

TOSHIBA MOSFETS
Leading Innovation >>>



RoHS Compliant

For quantities of 2000 and up, call for quote.

MOSFETS

Toshiba

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Type	Voltage (V)	Average Current	Price Each			
						1	10	100	250
Power MOSFETs									
757-2SJ377(TE16L1,NQ)	2SJ377(TE16L1,NQ)	PW-MOLD	P-Channel	60	5A	.96	.77	.66	.58
757-2SJ412(SM,Q)	2SJ412(SM,Q)	TO-220FL/SM	P-Channel	100	16A	2.14	1.72	1.28	1.23
757-2SK2231(TE16R1,NQ)	2SK2231(TE16R1,NQ)	PW-MOLD	N-Channel	60	5A	.72	.58	.49	.43
757-2SK2232(F,T)	2SK2232(F,T)	TO-220NIS	N-Channel	60	25A	1.24	.99	.84	.739
757-2SK2312(F)	2SK2312(F)	TO-220NIS	N-Channel	60	45A	2.73	2.19	1.86	1.64
757-2SK2314(F)	2SK2314(F)	TO-220AB	N-Channel	100	27A	1.58	1.26	1.06	.95
757-2SK2376(Q)	2SK2376(Q)	TO-220	N-Channel	60	45A	3.05	2.44	2.07	1.83
757-2SK2542(F)	2SK2542(F)	TO-220AB	N-Channel	500	8A	2.00	1.60	1.35	1.20
757-2SK2545(Q,T)	2SK2545(Q,T)	TO-220	N-Channel	600	6A	1.55	1.24	.93	.868
757-2SK2614(Q)	2SK2614(Q)	S-7B5B	N-Channel	50	20A	1.14	.91	.78	.69
757-2SK2611(F,T)	2SK2611(F,T)	TO-3	N-Channel	900	9A	3.65	2.92	2.48	2.19
757-2SK2698(F,T)	2SK2698(F,T)	TO-3P(N)	N-Channel	500	15A	2.68	2.10	1.79	1.58
757-2SK2841(F)	2SK2841(F)	TO-220AB	N-Channel	400	10A	2.39	1.92	1.61	1.44
757-2SK2842(Q,T)	2SK2842(Q,T)	TO-220	N-Channel	500	12A	2.39	1.92	1.61	1.44
757-2SK2963(TE12L,F)	2SK2963(TE12L,F)	PW-MINI	N-Channel	100	1A	.65	.48	.408	.30
757-2SK2968(F,T)	2SK2968(F,T)	TO-3P(N)	N-Channel	900	10A	3.67	2.93	2.28	2.16
757-2SK3561(Q)	2SK3561(Q)	TO-220SIS	N-Channel	500	8A	1.53	1.22	.915	.854
757-2SK3562(Q)	2SK3562(Q)	TO-220SIS	N-Channel	600	6A	1.50	1.20	1.02	.90
757-2SK3563(Q)	2SK3563(Q)	TO-220SIS	N-Channel	500	5A	1.33	1.06	.912	.67
757-2SK3564(Q)	2SK3564(Q)	TO-220SIS	N-Channel	900	3A	1.47	1.17	.877	.819
757-2SK3565(Q)	2SK3565(Q)	TO-220SIS	N-Channel	900	5A	2.07	1.66	1.41	1.25
757-2SK3566(Q)	2SK3566(Q)	TO-220SIS	N-Channel	900	2.5A	1.21	.97	.82	.723
757-2SK3567(Q)	2SK3567(Q)	TO-220SIS	N-Channel	600	3.5A	1.44	1.14	.861	.803
757-2SK3568(Q)	2SK3568(Q)	TO-220SIS	N-Channel	500	12A	2.48	1.99	1.69	1.49
757-2SK3569(Q)	2SK3569(Q)	TO-220SIS	N-Channel	600	10A	2.24	1.80	1.53	1.35
757-2SK3667(Q)	2SK3667(Q)	TO-220SIS	N-Channel	600	7.5A	1.81	1.45	1.23	1.09
757-2SK3742(Q)	2SK3742(Q)	TO-220SIS	N-Channel	900	5A	2.28	1.82	1.36	1.27
757-2SK3757(Q)	2SK3757(Q)	TO-220	NChannel	450	2A	.76	.61	.52	.46
757-2SK3767(Q,M)	2SK3767(Q)	TO-220SIS	N-Channel	600	2A	.76	.61	.52	.459
757-2SK3797(Q,M)	2SK3797(Q,M)	TO-220	N-Channel	600	13A	3.38	2.71	2.06	2.03
Small-Signal MOSFETs									
757-SSM3J108TU(TE85L)	SSM3J108TU(TE85L)	UFM-3	P-Channel	-20	- 1.8 A	.27	.218	.189	.17
757-SSM3J109TU(TE85L)	SSM3J109TU(TE85L)	UFM-3	P-Channel	-20	- 2 A	.29	.23	.20	.18
757-SSM3J110TU(TE85L)	SSM3J110TU(TE85L)	UFM-3	P-Channel	-12	- 2.3 A	.29	.23	.20	.18
757-SSM3J111TU(TE85L)	SSM3J111TU(TE85L)	UFM-3	P-Channel	-20	- 1 A	.27	.222	.193	.173
757-SSM3J112TU(TE85L)	SSM3J112TU(TE85L)	UFM-3	P-Channel	-30	- 1.1 A	.27	.222	.193	.173
757-SSM3J113TU(TE85L)	SSM3J113TU(TE85L)	UFM-3	P-Channel	-20	- 1.7 A	.29	.23	.20	.18
757-SSM3J115TU(TE85L)	SSM3J115TU(TE85L)	UFM-3	P-Channel	-20	- 2.2 A	.29	.23	.20	.18
757-SSM3J117TU(TE85L)	SSM3J117TU(TE85L)	UFM-3	P-Channel	-30	- 2 A	.27	.222	.193	.173
757-SSM3J118TU(TE85L)	SSM3J118TU(TE85L)	UFM-3	P-Channel	-30	- 1.4 A	.29	.23	.20	.18
757-SSM3J120TU(TE85L)	SSM3J120TU(TE85L)	UFM-3	P-Channel	-20	- 4 A	.29	.23	.20	.18
757-SSM3K101TU(TE85L)	SSM3K101TU(TE85L)	UFM-3	N-Channel	20	2.2 A	.29	.23	.20	.18
757-SSM3K102TU(TE85L)	SSM3K102TU(TE85L)	UFM-3	N-Channel	20	2.6 A	.29	.23	.20	.18
757-SSM3K104TU(TE85L)	SSM3K104TU(TE85L)	UFM-3	N-Channel	20	3 A	.29	.23	.20	.18
757-SSM3K105TU(TE85L)	SSM3K105TU(TE85L)	UFM-3	N-Channel	30	2.1 A	.29	.23	.20	.18
757-SSM3K106TU(TE85L)	SSM3K106TU(TE85L)	UFM-3	N-Channel	20	1.2 A	.26	.208	.18	.162
757-SSM3K107TU(TE85L)	SSM3K107TU(TE85L)	UFM-3	N-Channel	20	1.5 A	.29	.23	.20	.18
757-SSM3K116TU(TE85L)	SSM3K116TU(TE85L)	UFM-3	N-Channel	30	2.2 A	.29	.23	.20	.18
757-SSM3K119TU(TE85L)	SSM3K119TU(TE85L)	UFM-3	N-Channel	30	2.5 A	.29	.23	.20	.18
757-SSM3K121TU(TE85L)	SSM3K121TU(TE85L)	UFM-3	N-Channel	20	3.2 A	.29	.23	.20	.18
757-SSM3K124TU(TE85L)	SSM3K124TU(TE85L)	UFM-3	N-Channel	30	2.4 A	.29	.23	.20	.18
757-SSM3K7002FT5LFT	SSM3K7002FT5LFT	S-mini-3	P-Channel	30	2.2A	.08	.06	.051	.047
757-SSM6J06FUTE85L,F	SSM6J06FU(TE85L,F)	US6	P-Channel	-20	- 0.65 A	.38	.30	.26	.23
757-SSM6J07FUTE85L,F	SSM6J07FU(TE85L,F)	US-6	P-Channel	-30	- 0.8 A	.28	.23	.19	.17
757-SSM6J08FUTE85L,F	SSM6J08FU(TE85L,F)	US-6	P-Channel	-20	- 1.3 A	.40	.32	.27	.24
757-SSM6J206FETE85L,F	SSM6J206FE(TE85L,F)	ES-6	P-Channel	-20	- 2 A	.33	.262	.231	.201
757-SSM6J207FETE85L,F	SSM6J207FE(TE85L,F)	ES-6	P-Channel	-30	- 1.4 A	.33	.262	.231	.201
757-SSM6J21TUTE85L,F	SSM6J21TU(TE85L,F)	UF-6	P-Channel	-12	- 3 A	.29	.23	.20	.18
757-SSM6J25FETE85L,F	SSM6J25FE(TE85L,F)	ES-6	P-Channel	-20	0.5 A	.28	.22	.19	.17
757-SSM6J26FETE85L,F	SSM6J26FE(TE85L,F)	ES-6	P-Channel	-20	- 0.5 A	.28	.22	.19	.17
757-SSM6J50TUTE85L,F	SSM6J50TU(TE85L,F)	UF-6	P-Channel	-20	- 2.5 A	.33	.26	.23	.20
757-SSM6J51TUTE85L,F	SSM6J51TU(TE85L,F)	UF-6	P-Channel	-12	- 4 A	.34	.27	.23	.21
757-SSM6K07FUTE85L,F	SSM6K07FU(TE85L,F)	US-6	N-Channel	30	1.5 A	.28	.23	.19	.17
757-SSM6K08FUTE85L,F	SSM6K08FU(TE85L,F)	US-6	N-Channel	20	1.6 A	.23	.184	.157	.143
757-SSM6K18TUTE85L,F	SSM6K18TU(TE85L,F)	UF-6	N-Channel	20	4 A	.41	.33	.28	.25
757-SSM6K202FETE85L,F	SSM6K202FE(TE85L,F)	ES-6	N-Channel	30	2.3 A	.39	.314	.268	.237
757-SSM6K22FETE85L,F	SSM6K22FE(TE85L,F)	ES-6	N-Channel	20	1.4 A	.52	.41	.35	.31
757-SSM6K24FETE85L,F	SSM6K24FE(TE85L,F)	ES-6	N-Channel	30	0.5 A	.52	.41	.35	.31
757-SSM6K25FETE85L,F	SSM6K25FE(TE85L,F)	ES-6	N-Channel	20	0.5 A	.28	.22	.19	.17
757-SSM6K32TUTE85L,F	SSM6K32TU(TE85L,F)	UF-6	N-Channel	60	2 A	.52	.41	.35	.31
757-SSM6K34TUTE85L,F	SSM6K34TU(TE85L,F)	UF-6	N-Channel	30	3 A	.52	.41	.35	.31

