

COOPER/BUSSMANN Versa-Pac SMT Inductors and Transformers



Features:

- Six winding, surface mount devices that offer more than 500 inductor or transformer configurations
- High power density and low profile
- Low radiated noise and tightly coupled windings
- Power range from 1 Watt - 70 Watts
- Frequency range to over 1MHz
- 500 VAC Isolation
- Ferrite core material

Applications:

- Inductors: buck, boost, coupled, choke, filter, resonant, noise filtering, differential, forward, common mode
- Transformers: flyback, feed forward, push-pull, multipleoutput, inverter, step-up, step-down, gate driver, base/river, wide band, pulse, control, impedance, isolation, bridging, ringer, converter, auto

NOTE: Base - The value for a single winding.
There are 6 windings in each device.

Environmental Data:

- Storage temperature range: -55°C to 125°C
- Operating ambient temperature range: -40°C to +85°C
- Solder reflow temperature: +260°C max. for 10 seconds max.

Packaging:

- Supplied in tape and reel packaging. 600 (VP01), 300 (VP02), and 200 (VP03) per reel
- Supplied in bulk packaging (VP04 and VP05)

RoHS Compliant This product is RoHS compliant.

VP1 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	10	50	100
704-VP1-0059-R	VP1-0059-R	A	3.8	±20%	1.37	0.85	0.145	21.8	2.48	0.096	60.7	7.82	5.21	4.74	4.31
704-VP1-0076-R	VP1-0076-R	A	4.9	±20%	1.06	0.85	0.145	21.8	1.92	0.096	60.7	7.82	5.21	4.74	4.31
704-VP1-0102-R	VP1-0102-R	A	6.5	±20%	0.80	0.85	0.145	21.8	1.45	0.096	60.7	7.82	5.21	4.74	4.31
704-VP1-0190-R	VP1-0190-R	A	12.2	±20%	0.43	0.85	0.145	21.8	0.77	0.096	60.7	7.82	5.21	4.74	4.31
704-VP1-1400-R	VP1-1400-R	A	89.6	±30%	0.06	0.85	0.145	21.8	0.11	0.096	60.7	7.82	5.21	4.74	4.31

For quantities of 600 and up, call for quote.

VPH1 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	10	50	100
704-VPH1-0059-R	VPH1-0059-R	A	8.5	±20%	0.92	0.55	0.344	32.9	2.48	0.212	60.7	7.82	5.21	4.74	4.31
704-VPH1-0076-R	VPH1-0076-R	A	10.9	±20%	0.72	0.55	0.344	32.9	1.92	0.212	60.7	7.82	5.21	4.74	4.31
704-VPH1-0102-R	VPH1-0102-R	A	14.7	±20%	0.53	0.55	0.344	32.9	1.45	0.212	60.7	7.82	5.21	4.74	4.31
704-VPH1-0190-R	VPH1-0190-R	A	27.4	±20%	0.29	0.55	0.344	32.9	0.77	0.212	60.7	7.82	5.21	4.74	4.31
704-VPH1-1400-R	VPH1-1400-R	A	201.6	±30%	0.04	0.55	0.344	32.9	0.11	0.212	60.7	7.82	5.21	4.74	4.31

For quantities of 600 and up, call for quote.

VP2 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	25	50	100
704-VP2-0066-R	VP2-0066-R	B	3.2	±20%	2.50	1.26	0.090	33.7	7.01	0.083	44.0	9.23	6.15	5.59	5.08
704-VP2-0083-R	VP2-0083-R	B	4.1	±20%	1.95	1.26	0.090	33.7	5.47	0.083	44.0	9.23	6.15	5.59	5.08
704-VP2-0116-R	VP2-0116-R	B	5.7	±20%	1.41	1.26	0.090	33.7	3.94	0.083	44.0	9.23	6.15	5.59	5.08
704-VP2-0216-R	VP2-0216-R	B	10.6	±20%	0.76	1.26	0.090	33.7	2.11	0.083	44.0	9.23	6.15	5.59	5.08
704-VP2-1600-R	VP2-1600-R	B	78.4	±30%	0.10	1.26	0.090	33.7	0.29	0.083	44.0	9.23	6.15	5.59	5.08

For quantities of 300 and up, call for quote.

VPH2 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	10	25	50
704-VPH2-0066-R	VPH2-0066-R	B	6.6	±20%	1.74	0.95	0.159	48.3	7.01	0.165	44.0	9.23	6.15	5.59	5.08
704-VPH2-0083-R	VPH2-0083-R	B	8.3	±20%	1.39	0.95	0.159	48.3	5.47	0.165	44.0	9.23	6.15	5.59	5.08
704-VPH2-0116-R	VPH2-0116-R	B	11.6	±20%	0.99	0.95	0.159	48.3	3.94	0.165	44.0	9.23	6.15	5.59	5.08
704-VPH2-0216-R	VPH2-0216-R	B	21.6	±20%	0.53	0.95	0.159	48.3	2.11	0.165	44.0	9.23	6.15	5.59	5.08
704-VPH2-1600-R	VPH2-1600-R	B	160	±30%	0.07	0.95	0.159	48.3	0.29	0.165	44.0	9.23	6.15	5.59	5.08

For quantities of 300 and up, call for quote.

VP3 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	10	25	100
704-VP3-0047-R	VP3-0047-R	C	3.8	±20%	1.73	1.47	0.061	27.7	4.00	0.058	43.4	9.83	6.55	5.95	5.41
704-VP3-0055-R	VP3-0055-R	C	4.5	±20%	1.46	1.47	0.061	27.7	3.38	0.058	43.4	9.83	6.55	5.95	5.41
704-VP3-0084-R	VP3-0084-R	C	6.8	±20%	0.97	1.47	0.061	27.7	2.23	0.058	43.4	9.83	6.55	5.95	5.41
704-VP3-0138-R	VP3-0138-R	C	11.2	±20%	0.59	1.47	0.061	27.7	1.36	0.058	43.4	9.83	6.55	5.95	5.41
704-VP3-0780-R	VP3-0780-R	C	63.2	±30%	0.10	1.47	0.061	27.7	0.24	0.058	43.4	9.83	6.55	5.95	5.41

For quantities of 200 and up, call for quote.

VPH3 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	10	25	50
704-VPH3-0047-R	VPH3-0047-R	C	7.94	±20%	1.19	0.97	0.14	39.8	4.00	0.125	43.4	9.83	6.55	5.95	5.41
704-VPH3-0055-R	VPH3-0055-R	C	9.3	±20%	1.02	0.97	0.14	39.8	3.38	0.125	43.4	9.83	6.55	5.95	5.41
704-VPH3-0084-R	VPH3-0084-R	C	14.2	±20%	0.67	0.97	0.14	39.8	2.23	0.125	43.4	9.83	6.55	5.95	5.41
704-VPH3-0138-R	VPH3-0138-R	C	23.3	±20%	0.41	0.97	0.14	39.8	1.36	0.125	43.4	9.83	6.55	5.95	5.41
704-VPH3-0780-R	VPH3-0780-R	C	132	±30%	0.07	0.97	0.14	39.8	0.24	0.125	43.4	9.83	6.55	5.95	5.41

For quantities of 200 and up, call for quote.

VP4 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	6	12	24
704-VP4-0047-R	VP4-0047-R	D	3.8	±20%	2.81	1.70	0.057	44.7	10.52	0.075	39.4	13.25	8.83	8.03	7.30
704-VP4-0060-R	VP4-0060-R	D	4.9	±20%	2.18	1.70	0.057	44.7	8.16	0.075	39.4	13.25	8.83	8.03	7.30
704-VP4-0075-R	VP4-0075-R	D	6.1	±20%	1.75	1.70	0.057	44.7	6.55	0.075	39.4	13.25	8.83	8.03	7.30
704-VP4-0140-R	VP4-0140-R	D	11.3	±20%	0.95	1.70	0.057	44.7	3.54	0.075	39.4	13.25	8.83	8.03	7.30
704-VP4-0860-R	VP4-0860-R	D	87	±30%	0.15	1.70	0.057	44.7	0.57	0.075	39.4	13.25	8.83	8.03	7.30

For quantities of 36 and up, call for quote.

VPH4 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	10	100	1000
704-VPH4-0047-R	VPH4-0047-R	D	7.94	±20%	1.94	1.41	0.0828	64.6	10.52	0.156	39.4	17.70	11.80	10.73	9.75
704-VPH4-0060-R	VPH4-0060-R	D	10.1	±20%	1.52	1.41	0.0828	64.6	8.16	0.156	39.4	17.70	11.80	10.73	9.75
704-VPH4-0075-R	VPH4-0075-R	D	12.7	±20%	1.21	1.41	0.0828	64.6	6.55	0.156	39.4	17.70	11.80	10.73	9.75
704-VPH4-0140-R	VPH4-0140-R	D	23.7	±20%	0.65	1.41	0.0828	64.6	3.54	0.156	39.4	17.70	11.80	10.73	9.75
704-VPH4-0860-R	VPH4-0860-R	D	159.65	±30%	0.11	1.41	0.0828	64.6	0.57	0.156	39.4	17.70	11.80	10.73	9.75

For quantities of 36 and up, call for quote.

VP5 SERIES

MOUSER STOCK NO.	Coiltronics Part No.	Fig.	Value (Base) (µH)	Tol.	Isat (Base) (A)	Irms (Base) (A)	DCR (Base) (A)	Volt (µSec) (Base)(µVs)	Epeak (Base) (µJ)	Leakage Inductance (Base)(µH)	Thermal Resistance (°C/Watt)	Price Each			
												1	15	25	35
704-VP5-0053-R	VP5-0053-R	E	3.4	±20%	4.59	2.08	0.047	65.6	25.10	0.105	30.3	14.90	9.93	9.03	8.21
704-VP5-0067-R	VP5-0067-R	E	4.3	±20%	3.63	2.08	0.047	65.6	19.83	0.105	30.3	14.90	9.93	9.03	8.21
704-VP5-0083-R	VP5-0083-R	E	5.3	±20%	2.95	2.08	0.047	65.6	16.07	0.105	30.3	14.90	9.93	9.03	8.21
704-VP5-0155-R	VP5-0155-R	E	9.9	±20%	1.60	2.08	0.047	65.6	8.83	0.105	30.3	14.90	9.93	9.03	8.21
704-VP5-1200-R	VP5-1200-R	E	76.8	±30%	0.20	2.08	0.047	65.6	1.11	0.105	30.3	14.90	9.93	9.03	8.21

For quantities of 50 and up, call for quote.

VPH5 SERIES

MOUSER STOCK NO.	Coiltronics Part
------------------	------------------