

Product Index

A

AC Adapters	1116, 1965, 2016, 2024, 2040-2054
Adapters	
Bluetooth	58, 1249
D-Sub	1221, 1279, 1282, 1291
I/O	1105, 1212, 1221, 1249
Modular	1212, 1242, 2124
Phono (RCA)	1101, 1103, 1156
RF	1103, 1155, 1162, 1164, 1166, 1168, 1170-1171, 1176, 1178-1182, 1184-1185, 1188, 1191, 1193-1195, 1197-1198
SMT	2168
Socket	230, 1168, 1499-1500
XLR	1152, 1156
Alarms	618, 1085, 1827-1829, 2087, 2177
Alligator Clips	2119
Alerters	(See Semiconductors)
Amplifiers	(See Semiconductors)
Analog ICs	(See Semiconductors)
Antennas	5, 8, 10, 14, 18-20, 26-28, 30, 47, 49, 951, 1024-1027, 1225
Arrays	
Capacitor	632, 774, 811, 815
Resistor	627-634
Attenuators	1190, 1198, 1698
Audible Signal Devices	
Alarms	1827-1829
Benders	1830
Buzzers	1819-1822, 1827-1829
Earphones	1823
Electret Condenser Microphone	1822-1823, 1832
Elements	1823, 1830
Hardware	1828
Indicators	1829, 1831
Piezo	1828-1830
Ringers	1821, 1828
Sirens	1829, 1834
Sonalerts	1827-1829
Speakers	1817, 1824-1826, 1828, 1833-1834
Transducers	1817, 1824, 1828, 1830, 1834
Automotive	
12VDC Jacks and Plugs	1102
Capacitors	776, 802-803, 825
Connectors	128, 1102, 1317, 1420, 1490, 1505
LED	(See Illumination)
Relays	1731-1735, 1785-1786

B

Basic Stamp	51-52
Batteries	
1/2AA	2072-2073, 2077
1/3AA	2068
2/3A	2068, 2074, 2077
2/3AA	2068, 2072-2073
4/5A	2068
AAAA	2067
A	2068, 2074, 2077
AA	2067-2069, 2073, 2076-2077
AAA	2067-2069, 2076
C	2067-2069, 2073-2074
D	2067-2069, 2073
F	2067-2068
N	2067-2068
SC	2068-2069
9V	2067-2068, 2072, 2077
Alkaline	2067, 2076
Battery Packs	2068-2069, 2072-2073
Button Cell	2072, 2076
Calculator	2076
Camera	2076
Carbon Zinc	2067, 2076
Chargers	2068, 2070, 2077
Coin Cell	2072, 2074-2076
Computer	2076
Electronic	2076, 2099
Hearing Aid	2076
Lantern	2067
Lead Acid	2067, 2070-2071
Lithium	441, 2067, 2072-2077
Manganese Dioxide	2076
Memory Backup	2072-2073
Nickel-Cadmium	2067-2069
Nickel-Metal Hydride	2067-2069, 2072
Photo	2076
Pure Lead	2071
Rechargeable	2067-2072, 2074, 2077
Scooter	2067, 2070-2071
Silver-Oxide	2076
UPS	2020, 2030, 2060, 2067, 2070-2071
Watch	2076
Wheelchair	2067, 2070-2071
Zinc Chloride	2067

Battery Accessories

Analyzer	2071, 2096
Chargers	402, 428, 2020, 2068, 2070, 2077
Clips	2082, 2084, 2119
Holders	1915, 1927, 2075, 2079-2084
Indicator Labels	2084
Modular Contacts	2078
Snaps	1513, 2082-2083
Spring Contacts	2078, 2082, 2084, 2118
Binding Post	1140-1141, 1147, 1156, 1198, 1514, 2121
Blowers	1896, 1936, 1943, 1945
Bluetooth	7, 23, 29, 49, 52, 58, 369, 926, 1026, 1249
Boxes	(See Enclosures)
Braid	2149, 2153, 2165
Breadboards	239, 2165-2172
Buzzers	1819-1822, 1827-1829

C

Cabinets	1893-1899
Cable	(See Wire and Cable)
Cable Assemblies	(See Wire and Cable)
Cable Ties	1033-1037, 1040-1043
Capacitors	
Aluminum Electrolytic	
5mm	764
7mm	749, 755, 765
Axial	750, 756-757, 759-760, 762-763, 766
Bi-Polar	726, 755, 763
Computer Grade	741
Double Layer	742, 744, 747
Flatpack	736
General Purpose 85°C	723-724, 726-727, 732, 734, 736-738, 740-741, 749, 751, 755-756, 758-761, 764-766
High Capacitance	727, 731, 734-737, 740-742, 744, 755-756, 761
High Frequency	742, 763
High Reliability	750, 753-754
High Ripple	725, 735-736, 741, 750, 753, 763
High Temperature	723-725, 727-730, 733, 735, 738-740, 742, 749-750, 752-754, 758-759, 762, 765
High Voltage	734-741, 751-752, 756, 759-762, 766
Kit	766
Low ESR	723, 728, 730-731, 736, 750, 763
Low Impedance	723-725, 749, 753-754
Low Leakage	741, 759, 764
Memory Backup	742, 744, 747
Mounting Hardware	737
Non-Polar	763, 765
Organic	728, 731
Polymer	728-731
Radial	730-731, 742, 744, 749, 751-755, 758, 761-766
Screw Terminal	736-737, 741
Snap Mount	732-735, 738-740
Supercapacitors	742, 744, 747
Surface Mount	723-731, 742, 744, 747
Ultracapacitors	745-746
Ceramic	
Arrays	774, 811, 815
Automotive	776, 802-803, 825
Axial	826, 828, 897
Broadband Blocks	786
Chip	767-814, 816-824
Conformal Coated	825-826, 828-831
Coupling	833, 836
Disc	833-834, 836-839
EMI Suppression	774-775
Fail-Safe	768-769
Floating-Electrode	768-769
Flexible Termination	767-773
Flexicap	770-772
Flexitem	767, 769-771
General Purpose	790-799, 804-806, 816-819
Half-Turn	896
High Capacitance	772, 774-775, 782, 788, 798-804, 807, 816-817, 825, 827-839
High Q	778, 786, 797-799
High Temperature	772-773, 775, 778-780, 782-785, 788-799, 804-809, 814, 824-825, 827-833, 835
High Voltage	767, 772-773, 779-781, 785, 789, 807-808, 812-814, 820-821, 827-831, 833-834, 836-839
Interdigitated	775
Kits	771, 782, 785-786, 788-789
Low ESL / Low ESR	775, 780, 797-799, 810-811
Molded	776, 827-828, 833
Multilayer	767-770, 772, 774-785, 787-809, 816-827, 830-831, 833, 835, 897
Multi-Turn Trimmer	894-897
Open-Mode	769, 771-773
Radial	825-839, 897
RF Microwave	778-779, 786
Surface Mount	767-824
Tin/Lead Termination	781, 787
Tip and Ring	777, 789, 807, 812
Trimmer	894-897
Feedthru (Arrays & Capacitors)	774-775, 960-962
Film	
Axial	844, 852-854, 860-861
Chip	841
DC Link	847-848
Dipped	843, 859
Film/Foil	854, 857-858
Kits	861
Metalized	
Box	850, 853, 860
Paper	851
Polycarbonate	854
Polyester	840-846, 850-855, 860
Polyphenylene	851
Polypropylene	842, 844-845, 850-855, 858, 861
Non-Inductive	860
Orange Drop	855
Polyester	840-846, 850-857, 859-860
Polypropylene	842, 844-845, 847-858, 861
Polystyrene	861
Radial	840-843, 845-847, 850-853, 855-861
Snubbers	845-846, 849, 858
Suppression	846, 850-852
Surface Mount	840-841
Switching	847-848
High Reliability	750, 753-754
Mica	862-864
Mounting Hardware	737
RC Networks	632
Silicon Chip	865
Supercapacitors	742-748
Surface Mount	723-731, 742, 744, 747, 767-824, 840-841, 862-863, 865-885, 892, 894, 896, 949, 962, 1505
Tantalum	
Axial	889, 891-893
Dipped	886-888, 890
Fail-Safe Fused	880
Hermetically Sealed	889, 891
High Temperature	868, 870-871, 873-874, 876, 880, 893
Low ESR	866-868, 872-875, 878-884, 889, 892
Low Profile	875, 881-882
Niobium Oxide	866
Polymer	870, 873-874
Radial	886-888, 890
Surface Mount	866-885, 892
Wet	892-893
Trimmer	894-897
Card Readers	332, 343, 1342-1343, 1349-1350, 1354, 1363
Cases	937, 956, 1899, 1903-1906, 1908, 1911-1913, 1919, 1927, 1931, 2094-2096, 2100-2101, 2103
CCFLs	129
Chassis	1894, 1896, 1899, 1905, 1911
Chemicals	
Adhesives	1053, 2150, 2152
Anti-Static Coating	2152
Bottles	2145, 2164
Circuit Board Repair Pens	2150, 2153
Cleaners	2145, 2149-2150, 2152-2153, 2158-2159, 2163-2164
Conformal Coating	2152, 2164
Dispensers	1033, 2145, 2150, 2160, 2164
Dusting Gas	2150, 2163
Flux	2147-2150, 2163
Freezers	2150
Heat Sink Compound	1952, 1955, 2152, 2164
Leadcheck Tester	2150
Lubricant	1033, 2143, 2150, 2153, 2164-2165
Pumps	2164
Threadlocker	2165
Transistor Grease	2152
Wipes	2150, 2152-2153, 2163
Chip Coolers	1936
Chokes/Coils	(See Inductors)
Circuit Board Indicators	(See Illumination)
Circuit Breakers	
Hydraulic/Magnetic	1810-1811, 1814
Push-to-Reset	1813-1814, 1816
Seals	1694
Thermal	1129, 1811-1816
Thermo Magnetic	1807-1808, 1812

Circuit Protection

Circuit Breakers	1810-1816
DIN Rail	591, 1557, 1810, 1812, 1816, 2031, 2062
Filters	463, 558, 565-566, 2031, 2061
Fuse Blocks	614-617, 625-626, 1557
Fuse Clips	614-617, 626
Fuse Holders	609, 614-617, 625-626, 1557
Fuses	597, 602-613, 618-624, 1557
Gas Discharge Tubes	584, 591-594, 601
Metal Oxide Varistors	586-590
ESD Devices	463, 478, 558, 562, 564-566, 570, 573, 575-576, 583, 607
Resettable Fuses	597, 602-607, 618
Surface Mount	562, 569, 571-574, 577-579, 585, 593, 598-600, 602-603, 605-611, 618-619, 624
Surge Protectors	561-571, 573-574, 577-580, 591-594, 601, 606, 2031, 2060-2062, 2064-2065
Thermal Cutoffs	601
Thermistors	595-601
Thyristors	558, 572, 606
Varistors	583-590, 600
Voltage Suppressors	463, 473-474, 561-562, 566-574, 577-580, 591-594
Cleaners	2149-2150, 2152-2153, 2158-2159, 2162-2164
Clips	
Alligator	2119
Battery	2082, 2084, 2119
Fahnestock	1515
Heat Sink	1952
Test	2116, 2119-2124
Coils	(See Inductors)
Compiler Software	221, 241
Computers, Single Board	60-64
Connectors	
0.25mm	1491
0.30mm	164, 1132, 1135, 1445, 1491
0.40mm	1466
0.50mm	1219-1220, 1235, 1431, 1439-1440, 1445-1446, 1448, 1467, 1492, 1494
0.80mm	1215, 1220, 1233, 1417, 1426, 1446-1447, 1491
1.00mm / .039"	1235, 1358, 1396, 1426, 1431, 1440, 1447, 1466-1469, 1471, 1491, 1493, 1544
1.25mm / .049"	1388, 1441, 1447-1448, 1450, 1470-1471
1.27mm / .050"	1060, 1062-1063, 1219, 1234, 1253-1254, 1256, 1282, 1383, 1394-1396, 1402, 1426, 1436, 1450, 1473-1474, 2117
1.50mm	