



BELDEN COAXIAL CABLES

MIL-C-17G QPL Cable

- 94% Silver Coated Copper Braid
- Tinted Brown FEP Jacket



Recommend Heat Shrink **FT221**

RoHS Compliant

Belden Part No.	Fig.	AWG (Stranded)	Nominal O.D. (in.)	100' Spools		500' Spools		1000' Spools	
				MOUSER STOCK NO.	Price Per 100' Spool	MOUSER STOCK NO.	Price Per 500' Spool	MOUSER STOCK NO.	Price Per 1000' Spool
83264	A	30 (7 x 38)	.100	566-83264-100	151.50	566-83264-500	591.16	566-83264-1000	1154.95

Mini Hi-Res Component Video Cable

- Available Colors: 00 is Clear, 10 is Black

* Uses Belden Connector (see below) 566-1B25A and 566-1R25A



Recommend Heat Shrink **FT400**

RoHS Compliant

Belden Part No.	Fig.	Component Descriptions	AWG (Stand)	Shielding	500' Spools		1000' Spools	
					MOUSER STOCK NO.	Price Per 500' Spool	MOUSER STOCK NO.	Price Per 1000' Spool
*1281S3	B	75Ω Coax 3C	25 (Solid)	100% Duobond® Foil	566-1281S3-500-00	483.49	566-1281S3-1000-00	914.13
*1281S5	B	75Ω Coax 5C	25 (Solid)	100% Duobond® Foil	566-1281S5-500-00	727.98	566-1281S5-1000-00	1376.39
*1281S6	B	75Ω Coax 6C	25 (Solid)	100% Duobond® Foil	566-1281S6-500-00	903.64	566-1281S6-1000-00	1731.06
*1282S3	B	75Ω Coax 3C Plenum	25 (Solid)	100% Duobond® Foil	566-1282S3-500-00	554.30	566-1282S3-1000-00	1048.03
*1282S4	B	75Ω Coax 4C Plenum	25 (Solid)	100% Duobond® Foil	566-1282S4-500-00	734.94	566-1282S4-1000-00	1408.32
*1282S5	B	75Ω Coax 5C Plenum	25 (Solid)	100% Duobond® Foil	566-1282S5-500-00	888.21	566-1282S5-1000-00	1679.31
*1282S6	B	7Ω Coax 6C Plenum	25 (Solid)	100% Duobond® Foil	566-1282S6-500-00	1051.06	566-1282S6-1000-00	2014.19
1283S3	B	75Ω Coax 3C	20 (Solid)	95% Duofoil® + TC Foil	566-1283S3-500-00	2535.19	566-1283S3-1000-00	4858.20
1283S5	B	75Ω Coax 5C	20 (Solid)	95% Duofoil® + TC Foil	566-1283S5-500-00	3996.08	-----	-----
1283S6	B	75Ω Coax 6C	20 (Solid)	95% Duofoil® + TC Foil	566-1283S6-500-00	4685.81	566-1283S6-1000-00	8979.43

BELDEN BANANA PEEL® PROJECTOR CABLES

- Inter-room Audio/Video Composites: 6 Mini Hi-res Coaxes
- + 2 Shielded Twisted Pairs Riser- and Plenum-rated
- Insulation for 5788AV: Gas-injected foam Polyethylene (coax) and PVC (pairs)
- 6788AV: Low smoke foam Fluoropolymer (coax) and LS-PVC (pairs)
- Uses Belden Connector (See Below) 566-1B25A and 566-1R25A



Recommend Heat Shrink **FT400**

Belden Part No.	Fig.	NEC Type	No. of Pairs	AWG Stranded	Nominal O.D. (in.)	Nom Imp.	% Type Shield	500' Box		1000' Spools	
								MOUSER STOCK NO.	Price Per 500' Spool	MOUSER STOCK NO.	Price Per 1000' Spool
5788AV	C	CMR	6-Coax 2-Pair	25 (solid) 22 (7x30)	.442	75	95	566-5788AV-250-09	445.68	-----	-----

BELDEN 75 OHM BNC CONNECTOR (MADE FOR MINI HI-RES COAXIAL CABLE)



RoHS Compliant

- Current Rating: 5 amps
- Max. Working Voltage: 300V
- Body Material: Brass
- Body Plating: Nickel
- Cable Attachment Method: Compression Style

MOUSER STOCK NO.	Belden Part No.	Fig.	Price Each	
			1	5
566-1B25A	1B25A	D	3.95	3.51

BELDEN COAX CABLE STRIPPER TOOL



RoHS Compliant

This Prep tool is suitable for RG-6, RG-59 and Mini RG-59 cable.

MOUSER STOCK NO.	Belden Part No.	Fig.	Price Each	
			1	2
566-HCST	HCST	F	49.11	47.87

BELDEN RCA CONNECTOR (MADE FOR MINI HI-RES COAXIAL CABLE)



RoHS Compliant

- Current Rating: 2 amps
- Max. Working Voltage: 300V
- Body Material: Brass
- Body Plating: Nickel
- Cable Attachment Method: Compression Style

MOUSER STOCK NO.	Belden Part No.	Fig.	Price Each	
			1	5
566-1R25A	1R25A	E	2.59	2.41

BELDEN COMPRESSION TOOL (WORKS WITH BNC AND RCA PRODUCTS)



RoHS Compliant

This Compression tool is suitable for connectors 1B25A and 1R25A

MOUSER STOCK NO.	Belden Part No.	Fig.	Price Each	
			1	2
566-HCCT	HCCT	G	84.54	81.98