

# CRYSTEK CORPORATION RF Cable Assemblies



RoHS Compliant This page of product is compliant.

## RG174: 50Ω COAXIAL CABLE ASSEMBLIES

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Crystek Part No.	Fig.	Cable Type	Length: in.	Price Each	
					1	5
<b>BNC (Male) to Alligator Clip</b>						
549-CCBNCCL-MC-30	CCBNCCL-MC-30	A	RG 174	30		
<b>SMA Straight (Male) to BNC Straight (Male)</b>						
549-BNS-MM-RG174-18	CCBNS-MM-RG174-18	A	RG 174	18		
549-CCBNS-MMRG174-36	CCBNS-MM-RG174-36	A	RG 174	36		
<b>SMA Straight (Male) to SMA Straight (Male)</b>						
549-SMA-MM-RG174-6	CCSMA-MM-RG174-6	A	RG 174	6		
549-SMA-MM-RG174-12	CCSMA-MM-RG174-12	A	RG 174	12		
549-SMA-MM-RG174-24	CCSMA-MM-RG174-24	A	RG 174	24		
549-SMA-MM-RG174-36	CCSMA-MM-RG174-36	A	RG 174	36		
549-SMA-MM-RG174-48	CCSMA-MM-RG174-48	A	RG 174	48		
<b>SMA Straight (Male) to SMA Right Angle (Male)</b>						
549-SMA1-MM-RG174-6	CCSMA1-MM-RG174-6	A	RG 174	6		
549-SMA1-MM-RG174-12	CCSMA1-MM-RG174-12	A	RG 174	12		
549-SMA1-MM-RG174-24	CCSMA1-MM-RG174-24	A	RG 174	24		
549-SMA1-MM-RG174-36	CCSMA1-MM-RG174-36	A	RG 174	36		
<b>SMA Right Angle (Male) to SMA Right Angle (Male)</b>						
549-SMA2-MM-RG174-6	CCSMA2-MM-RG174-6	A	RG 174	6		
549-SMA2-MM-RG174-12	CCSMA2-MM-RG174-12	A	RG 174	12		
549-SMA2-MM-RG174-24	CCSMA2-MM-RG174-24	A	RG 174	24		
549-SMA2-MM-RG174-36	CCSMA2-MM-RG174-36	A	RG 174	36		
<b>SMA Straight (Male) to Alligator Clip</b>						
549-CCSMACL-MC-24	CCSMACL-MC-24	A	RG 174	24		

## 50Ω 18GHZ COAXIAL CABLE W/STAINLESS STEEL CONNECTORS

LL142: Low Loss

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Crystek Part No.	Fig.	Cable Type	Length: in.	Price Each	
					1	5
<b>SMA Straight (Male) to SMA Straight (Male)</b>						
549-SMA-MMLL142-12	CCSMA-MM-LL142-12	B	LL 142	12		
549-SMA-MMLL142-24	CCSMA-MM-LL142-24	B	LL 142	24		
549-SMA-MMLL142-36	CCSMA-MM-LL142-36	B	LL 142	36		
549-SMA-MMLL142-48	CCSMA-MM-LL142-48	B	LL 142	48		

SS402: Precision

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Crystek Part No.	Fig.	Cable Type	Length: in.	Price Each	
					1	5
<b>SMA Straight (Male) to SMA Straight (Male)</b>						
549-SMA-MMSS402-12	CCSMA-MM-SS402-12	C	SS 402	12		
549-SMA-MMSS402-24	CCSMA-MM-SS402-24	C	SS 402	24		
549-SMA-MMSS402-36	CCSMA-MM-SS402-36	C	SS 402	36		
549-SMA-MMSS402-60	CCSMA-MM-SS402-60	C	SS 402	60		
549-SMA-MMSS402-120	CCSMA-MM-SS402-120	C	SS 402	120		

## RG316DS: 50Ω DOUBLE SHIELDED COAXIAL CABLE ASSEMBLIES

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Crystek Part No.	Fig.	Cable Type	Length: in.	Price Each	
					1	5
<b>SMA Straight (Male) to BNC Straight (Male)</b>						
549-BNS-MM-RG316DS6	CCBNS-MM-RG316DS-6	D	RG 316DS	6		
549-BNS-MM-RG316DS12	CCBNS-MM-RG316DS-12	D	RG 316DS	12		
549-BNS-MM-RG316DS24	CCBNS-MM-RG316DS-24	D	RG 316DS	24		
549-BNS-MM-RG316DS36	CCBNS-MM-RG316DS-36	D	RG 316DS	36		
<b>SMA Straight (Male) to SMA Straight (Male)</b>						
549-SMA-MMRG316DS6	CCSMA-MM-RG316DS-6	D	RG 316DS	6		
549-SMA-MMRG316DS-12	CCSMA-MM-RG316DS-12	D	RG 316DS	12		
549-SMA-MMRG316DS-24	CCSMA-MM-RG316DS-24	D	RG 316DS	24		
549-SMA-MMRG316DS-36	CCSMA-MM-RG316DS-36	D	RG 316DS	36		
549-SMA-MMRG316DS-48	CCSMA-MM-RG316DS-48	D	RG 316DS	48		
<b>SMA Straight (Male) To SMA Right Angle (Male)</b>						
549-SMA1-MMRG316DS6	CCSMA1-MM-RG316DS-6	D	RG 316DS	6		
549-SMA1-MMRG316DS12	CCSMA1-MM-RG316DS-12	D	RG 316DS	12		
549-SMA1-MMRG316DS24	CCSMA1-MM-RG316DS-24	D	RG 316DS	24		
549-SMA1-MMRG316DS36	CCSMA1-MM-RG316DS-36	D	RG 316DS	36		
<b>SMA Right Angle (Male) to SMA Right Angle (Male)</b>						
549-SMA2-MMRG316DS6	CCSMA2-MM-RG316DS-6	D	RG 316DS	6		
549-SMA2-MMRG316DS12	CCSMA2-MM-RG316DS-12	D	RG 316DS	12		
549-SMA2-MMRG316DS24	CCSMA2-MM-RG316DS-24	D	RG 316DS	24		
549-SMA2-MMRG316DS36	CCSMA2-MM-RG316DS-36	D	RG 316DS	36		



NEW AT MOUSER

Cable Assemblies

Crystek Corporation

NEW AT MOUSER