

KSA & KSL SERIES SEALED TACTILE SWITCH

Features:

- Designed for automatic or manual insertion
- Cambered terminals to ensure self retention
- Top or side actuated

Applications:

- Automotive
- Industrial
- Telecommunication networks

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Operating Force	Height (mm)	Price Each			
					1	25	100	250
611-KSA0M211-LFT	KSA0M211 LFT	A	130g	4.7	.51	.44	.39	.36
611-KSA0M411-LFT	KSA0M411 LFT	A	300g	4.7	.47	.40	.35	.31
611-KSL0M412-LFT	KSL0M412 LFT	B	300g	9.9	.67	.61	.52	.46
611-KSL0V411-LFT	KSL0V411 LFT	B	300g	9.9	.82	.75	.68	.59

KSC SERIES SEALED TACTILE SWITCH FOR SMT

Features:

- Positive tactile feeling
- Range of 6 actuation forces
- J or G terminations
- IP 67

Applications:

- Automotive
- Cellular phones
- Industrial electronics
- Network infrastructure and IT

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Operating Force	Height (mm)	Price Each			
					1	25	100	250
611-KSC221G-LFS	KSC221G LFS	C	160g	3.5	.43	.37	.33	.29
611-KSC221J-LFS	KSC221J LFS	C	160g	3.5	.41	.35	.32	.28
611-KSC241G-LFS	KSC241G LFS	C	300g	3.5	.43	.37	.34	.30
611-KSC241J-LFS	KSC241J LFS	C	300g	3.5	.43	.39	.34	.30
611-KSC341J-LFS	KSC341J LFS	D	300g	3.5	.41	.35	.32	.28
611-KSC351J-LFS	KSC351J LFS	D	550g	3.5	.47	.40	.35	.31
611-KSC421G70SH-LFS	KSC421G70SH LFS	E	160g	5.2	.47	.40	.35	.31
611-KSC441J70SH-LFS	KSC441J70SH LFS	E	300g	5.2	.47	.40	.35	.31
611-KSC641G-LFS	KSC641G LFS	F	300g	7.7	.56	.51	.45	.39
611-KSC641J-LFS	KSC641J LFS	F	300g	7.7	.56	.51	.45	.39

KT SERIES RIGHT ANGLE SEALED TACTILE SWITCH FOR SMT

Features:

- Positive tactile feeling
- Range of 6 actuation forces
- J or G terminations
- IP 57

Applications:

- Automotive
- Cellular phones
- Industrial electronics
- Network infrastructure and IT

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Operating Force	Terminal	Price Each			
					1	25	100	250
611-KT11B2JM34-LFS	KT11B2JM34 LFS	G	300g	SMT Gullwing	1.95	1.79	1.65	1.52
611-KT11P2JM34-LFS	KT11P2JM34 LFS	G	300g	SMT Gullwing	2.52	2.42	2.24	2.12
611-KT11P2SM34-LFS	KT11P2SM34 LFS	G	300g	SMT Gullwing	2.08	1.90	1.74	1.63
611-KT11P4JM34-LFS	KT11P4JM34 LFS	G	300g	SMT Gullwing	1.83	1.68	1.55	1.46

PTS125/525/635/645 TACTILE SWITCHES

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Operating Force	Height (mm)	Price Each			
					1	25	100	250
12mm, Operating Temperature: -40°C to 60°C								
611-PTS125SM43-LFS	PTS125SM43 LFS	H	160g	4.3	.36	.33	.262	.23
611-PTS125SM85-LFS	PTS125SM85 LFS	H	160g	8.5	.41	.379	.30	.252
Microminiature SMT, 5.25mm x 5.25mm, Operating Temperature: -40°C to 60°C								
611-PTS525SM10-LFS	PTS525SM10SMT LFS	I	160g	1.5	.56	.44	.355	.324
3.5mm, Operating Temperature: -40°C to 60°C								
611-PTS635VL39-LFS	PTS635VL39 LFS	J	130g	3.85	.26	.24	.22	.21
6x6 mm, Operating Temperature: -20°C to 60°C								
611-PTS645SL70LFS	PTS645SL70 LFS	K	130g	3.6	.15	.14	.13	.12
611-PTS645VL31LFS	PTS645VL31 LFS	K	130g	3.6	.18	.16	.15	.14

KMR2/KSR/KSS TACTILE SWITCHES

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Operating Force	Height (mm)	Price Each			
					1	25	100	250
Microminiature SMT Top Actuated, Operating Temperature -40°C to 125°C								
611-KMR211G-LFS	KMR211G LFS	L	120g	1.9	.47	.40	.374	.327
611-KMR221G-LFS	KMR221G LFS	L	200g	1.9	.41	.35	.32	.28
Subminiature SMT, IP 50 Sealed, Operating Temperature -40°C to 125°C								
611-KSR221G-LFS	KSR221G LFS	M	200g	2.5	.47	.40	.35	.31
Subminiature SMT Side Actuated, IP 50 Sealed, Operating Temperature -40°C to 125°C								
611-KSS221GLFS	KSS231GLFS	N	200g	1.7	.40	.31	.25	.23
611-KSS231G-LFS	KSS231G LFS	N	250g	1.7	.41	.35	.32	.28
611-KSS331G-LFS	KSS331G LFS	N	250g	1.7	.47	.40	.35	.31

