

BIVAR Mounts and PCB Hardware



RoHS Compliant This product is RoHS compliant.

BIVAR PERM-O-PADS™

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Diameter	Pin Spacing	Overall Height	Price Each			
					1	10	100	500
TO-18 and T1 - 3/4 (5mm) LED Mounts								
749-100-095	100-095	.200	.10	.095	.30	.22	.168	.135
749-104-020	104-020	.200	.10	.020	.30	.22	.168	.135
749-105-021	105-021	.250	.10	.020	.30	.22	.168	.135
749-108-021	108-021	.225	.10	.020	.30	.22	.168	.135
749-109-045	109-045	.200	.10	.050	.30	.22	.168	.135
749-110-030	110-030	.200	.10	.030	.30	.22	.168	.135
749-111-080	111-080	.200	.10	.080	.30	.22	.168	.135
749-112-040	112-040	.225	.10	.040	.30	.22	.168	.135
749-116-060	116-060	.200	.10	.060	.30	.22	.168	.135
749-117-080	117-080	.255	.10	.080	.30	.22	.168	.135
749-118-055	118-055	.245	.10	.040	.30	.22	.168	.135
749-121-032	121-032	.187	.10	.032	.30	.22	.168	.135
TO-18 and T1 - 3/32 (5mm) LED Mounts								
749-102-090	102-090	.245	.10	.090	.30	.22	.168	.135
749-102-160	102-160	.245	.10	.150	.30	.22	.168	.135
749-102-200	102-200	.245	.10	.200	.30	.22	.168	.135
749-113-125	113-125	.250	.10	.125	.30	.22	.168	.135
749-115-100	115-100	.200	.10	.095	.30	.22	.168	.135
749-119-096	119-096	.190	.10	.096	.30	.22	.168	.135
TO-5 Pad								
749-501-075	501-075	.345	.20	.075	.30	.22	.168	.135
749-503-075	503-075	.340	.20	.075	.30	.22	.168	.135
749-506-038	506-038	.345	.20	.038	.30	.22	.168	.135
749-508-075	508-075	.280	.20	.075	.30	.22	.168	.135
749-511-038	511-038	.345	.20	.040	.30	.22	.168	.135
749-513-075	513-075	.345	.20	.075	.30	.22	.168	.135
749-515-020	515-020	.345	.20	.020	.30	.22	.168	.135
749-518-038	518-038	.345	.20	.038	.30	.22	.168	.135
749-520-021	520-021	.345	.20	.020	.30	.22	.168	.135
749-525-038	525-038	.345	.20	.040	.30	.22	.168	.135
TO-5 Mount								
749-514-050	514-050	.365	.20	.050	.30	.22	.168	.135
749-514-070	514-070	.365	.20	.070	.30	.22	.168	.135
749-514-100	514-100	.365	.20	.100	.30	.22	.168	.135
749-514-120	514-120	.365	.20	.120	.30	.22	.168	.135
TO-5 and Integrated Circuit Mounts								
749-505-120	505-120	.350	.20	.120	.30	.22	.168	.135
749-510-110	510-110	.280	.20	.110	.30	.22	.168	.135
749-517-095	517-095	.340	.20	.090	.30	.22	.168	.135
749-521-094	521-094	.375	.20	.094	.30	.22	.168	.135
749-528-117	528-117	.350	.20	.117	.30	.22	.168	.135
749-600-080	600-080	.360	-	.080	.30	.22	.168	.135
749-605-085	605-085	.375	-	.080	.30	.22	.168	.135
749-606-075	606-075	.365	.31	.075	.30	.22	.168	.135
8 Lead Integrated Circuit Mount								
749-610-075	610-075	.375	-	.075	.30	.22	.168	.135
749-615-075	615-075	.375	-	.075	.30	.22	.168	.135
749-711-085	711-085	.375	-	.060	.47	.35	.26	.21
10 Lead Integrated Circuit Mount								
749-611-075	611-075	.375	-	.075	.30	.22	.168	.135

BIVAR CRYSTAL INSULATORS AND MOUNTS

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	L x W (mm)	Pin Spacing	Overall Height	Price Each			
					1	10	100	500
HC-49/U Molded Mounts								
749-470-025	470-025	.495 x .245	.200	.060	.38	.29	.22	.17
749-470-035	470-035	.495 x .245	.200	.070	.38	.29	.22	.17
749-470-045	470-045	.495 x .245	.200	.080	.38	.29	.22	.17
HC-80/U Mylar Mounts								
749-CI-148-028	CI-148-028	.325 x .145	.148	.005	.08	.06	.045	.036
749-CI-148-028-3SR	CI-148-028-3SR	.325 x .145	.148	.005	.08	.06	.045	.036
749-CI-148-028-SR	CI-148-028-SR	.325 x .145	.148	.005	.08	.06	.045	.036
HC-80/U, HC-43/U, HC-49/U Mylar Mounts								
749-CI-192-028	CI-192-028	.465 x .219	.192	.005	.08	.06	.045	.036
749-CI-192-028-3SR	CI-192-028-3 SR	.465 x .219	.192	.005	.08	.06	.045	.036
749-CI-192-028-SR	CI-192-028-SR	.465 x .219	.192	.005	.08	.06	.043	.034
749-CI-192-050	CI-192-050	.465 x .219	.192	.005	.08	.06	.045	.036

BIVAR CARD-O-PULLS™ PCB HANDLES

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Color	Tapered Length	Handle Length	Price Each			
					1	10	100	500
749-CP-2-WE	CP-2-WE	White	Handle	1.13	.74	.69	.60	.54
749-CP-3-WE	CP-3 WE	White	Handle	1.1	.82	.61	.46	.37
749-CP-26-WE	CP-26-WE	White	Ejector	1.13	.73	.55	.41	.33
749-CP-36-WE	CP-36-WE	White	Ejector	1.1	.73	.55	.41	.33
749-CP-46-WE	CP-46-WE	White	Ejector	1.5	.74	.69	.60	.54
749-CP-66-WE	CP-66-WE	White	Ejector	1.25	.73	.55	.41	.33
749-CP-86-WE	CP-86-WE	White	Ejector	0.98	.73	.55	.41	.33
749-LP-06-WE	LP-06 WE	White	Ejector	1.12	.74	.69	.60	.54
749-LP-36-WE	LP-36 WE	White	Ejector	1.13	.74	.69	.60	.54

BIVAR PCB CARD GUIDES

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Length	Snap-in Spacing	Center Snap-in Spacing	Price Each			
					1	10	100	500
ECON-O-GIDE™								
749-E-200	E-200	2	1	-	.92	.69	.52	.46
749-E-250	E-250	2.5	1.5	-	.92	.69	.52	.46
749-E-300	E-300	3	1.5	-	.92	.69	.52	.46
749-E-350	E-350	3.5	1.5	-	.92	.69	.52	.46
749-E-400	E-400	4	3	-	.64	.60	.53	.52
749-E-450	E-450	4.5	3	-	.64	.60	.53	.52
749-E-500	E-500	5	3	-	.64	.60	.53	.52
749-E-600	E-600	6	5	-	.70	.66	.57	.56
749-E-650	E-650	6.5	5	-	.70	.66	.57	.56
749-E-700	E-700	7	6	-	.94	.88	.77	.76
749-E-800	E-800	8	6	-	.94	.88	.77	.76
749-E-1000	E-1000	10	9	4.51	1.50	1.41	1.22	1.22
749-E-1200	E-1200	12	10.5	5.27	1.66	1.56	1.36	1.35
749-E-1300	E-1300	13	10.5	5.27	1.85	1.74	1.51	1.50
NARR-O-GIDE™								
749-N-250-2	N-250-2	2.5	2	-	.58	.44	.33	.29
749-N-300-2	N-300-2	3	2.5	-	.58	.44	.33	.29
749-N-350-2	N-350-2	3.5	3	-	.58	.44	.33	.29
749-N-400-2	N-400-2	4	3.5	-	.62	.47	.35	.31
749-N-450-2	N-450-2	4.5	4	-	.62	.47	.35	.31
749-N-500-2	N-500-2	5	4.5	-	.62	.47	.35	.31
749-N-550-2	N-550-2	5.5	5	-	.68	.51	.38	.34
749-N-600-2	N-600-2	6	5.5	-	.68	.51	.38	.34
749-N-700-3	N-700-3	7	6.5	-	.75	.56	.42	.37
749-N-850-3	N-850-3	8.5	8	4	.79	.59	.44	.39
GRIP-O-GIDE™								
749-DC-250	DC-250	2.5	1.5	-	.69	.65	.56	.56
749-DC-450	DC-450	4.5	3.5	-	.73	.68	.59	.59
749-DC-450-102	DC-450-102	4.5	3.5	-	.73	.68	.59	.53
749-DC-600	DC-600	6	5	-	.80	.75	.66	.65
749-DC-600-102	DC-600-102	6	5	-	.80	.75	.66	.59
749-DC-600-130	DC-600-130	6	5	-	.80	.75	.66	.59
749-DC-800	DC-800	8	7	3.5	.94	.88	.77	.76
749-DC-800-102	DC-800-102	8	7	3.5	.94	.88	.77	.69

BIVAR COMP-O-GIDE™

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Length	Snap-in Spacing	Center Snap-in Spacing	Price Each			
					1	10	100	500
Standard Snap-in Card Guides - SDC Series								
749-SDC-250	SDC-250	2.5	1.5	0.175	.87	.65	.49	.43
749-SDC-300	SDC-300	3	2	0.175	.87	.65	.49	.43
749-SDC-400	SDC-400	4	3	0.175	.92	.69	.52	.46
749-SDC-450	SDC-450	4.5	3.5	0.175	.92	.69	.52	.46
749-SDC-600	SDC-600	6	5	0.175	.96	.72	.54	.48
749-SDC-650	SDC-650	6.5	5.5	0.175	.96	.72	.54	.48
Standard Snap-in Card Guides - SFS Series								
749-SFS-450	SFS-450	4.5	3	0.125	.62	.58	.50	.50
749-SFS-500	SFS-500	5	4	0.125	.62	.58	.50	.50
749-SFS-600	SFS-600	6	5	0.125	.64	.60	.53	.52
749-SFS-800	SFS-800	8	7	0.125	.70	.66	.57	.56

BIVAR VERT-O-GIDE™ VERTICAL PCB GUIDE

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Length	Snap-in Spacing	Center Snap-in Spacing	Price Each			
					1	10	100	500
749-VG2-2	VG2-2	2	1.5	0.076	1.80	1.69	1.47	1.46
749-VG2-25	VG2-25	2.5	1.5	0.076	1.80	1.69	1.47	1.46