

# AVAGO Optocouplers



This product is RoHS compliant.



## AVAGO OPTOCOUPLEDERS

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Avago Part No.	Number of Channels	Package	Forward on Current (mA)	Total Power Dissipation (mW)	Isolation Voltage (VRMS)	Price Each			
							1	25	100	500
630-4N25-000E	4N25-000E	-	DIP-6	80	250	2500	.32	.20	.18	.15
630-4N25-W00E	4N25-W00E	-	DIP-6	80	250	2500	.33	.22	.20	.17
630-4N35-000E	4N35-000E	-	DIP-6	60	350	3550	.32	.20	.18	.15
630-4N46-000E	4N46-000E	-	DIP-6	20	100	3750	2.67	1.94	1.79	1.65
630-6N135-000E	6N135-000E	1	DIP-8	8	100	3750	1.46	.99	.90	.77
630-6N136-000E	6N136-000E	1	DIP-8	8	100	3750	1.46	.99	.90	.77
630-6N136-300E	6N136-300E	1	SO-8	8	100	3750	1.53	1.03	.94	.80
630-6N137-000E	6N137-000E	1	DIP-8	15	85	3750	1.63	1.10	1.00	.85
630-6N138-000E	6N138-000E	1	DIP-8	20	135	3750	1.46	.99	.90	.77
630-6N139-000E	6N139-000E	1	DIP-8	20	135	3750	1.46	.99	.90	.77
630-6N140A	6N140A	4	DIP-16	40	200	-	71.62	53.72	50.13	48.34
630-ACPL-071L-000E	ACPL-071L-000E	1	SO-8	9	-	3750	3.44	2.50	2.31	2.13
630-ACPL-072L-000E	ACPL-072L-000E	1	SO-8	10	150	3750	4.40	3.20	2.96	2.72
630-ACPL-074L-060E	ACPL-074L-060E	2	SO-8	9	-	3750	6.38	4.64	4.29	3.94
630-ACPL-312T-000E	ACPL-312T-000E	1	DIP-8	7	400	3750	5.80	4.22	3.90	3.59
630-ACPL-782T-000E	ACPL-782T-000E	1	DIP-8	16	600	3750	13.48	10.78	9.80	7.84
630-ACPL-C780-000E	ACPL-C780-000E	1	Stretched SO-8	11	600	5000	8.87	6.48	5.90	5.18
630-ACPL-C784-000E	ACPL-C784-000E	1	Stretched SO-8	11	600	5000	6.54	4.78	4.35	3.83
630-ACPL-C78A-000E	ACPL-C78A-000E	1	Stretched SO-8	11	600	5000	12.50	9.13	8.31	7.31
630-ACPL-W70L-000E	ACPL-W70L-000E	1	Stretched SO-6	10	600	5000	3.58	2.60	2.41	2.21
630-ACPL-K73L-000E	ACPL-K73L-000E	2	Stretched SO-8	10	600	5000	6.60	4.80	4.44	4.08
630-ACPL-M46T-000E	ACPL-M46T-000E	1	SO-5	10	130	3750	5.64	4.10	3.79	3.49
630-ACPL-M61T-000E	ACPL-M61T-000E	1	SO-5	20	85	3750	5.64	4.10	3.79	3.49
630-ACPL-M75L-000E	ACPL-M75L-000E	1	SO-5	4	-	3750	3.58	2.60	2.41	2.21
630-ACSL-6210-00RE	ACSL-6210-00RE	2	SO-8	2.7	60	2500	3.85	2.80	2.59	2.38
630-ACSL-6400-00TE	ACSL-6400-00TE	4	SO-16	2.7	60	2500	7.70	5.60	5.18	4.76
630-CNY17-2-000E	CNY17-2-000E	1	DIP-6	0.3	250	5000	.32	.20	.18	.15
630-CNY17-3-000E	CNY17-3-000E	1	DIP-6	0.3	250	5000	.32	.20	.18	.15
630-CNY17-4-000E	CNY17-4-000E	1	DIP-6	0.3	250	5000	.32	.20	.18	.15
630-HCNR200-000E	HCNR200-000E	1	DIP-8	25	60	1414	4.66	3.87	3.19	2.52
630-HCNR200-300E	HCNR200-300E	1	SO-8	25	60	1414	4.73	3.74	3.24	2.56
630-HCNR201-000E	HCNR201-000E	1	DIP-8	25	60	1414	6.20	5.12	4.24	3.36
630-HCNR201-300E	HCNR201-300E	1	SO-8	25	60	1414	6.27	5.12	4.29	3.40
630-HCNRW136-000E	HCNRW136-000E	1	DIP-8	16	700	5000	2.20	1.60	1.48	1.36
630-HCNRW137-000E	HCNRW137-000E	1	DIP-8	5	700	5000	3.11	2.26	2.09	1.92
630-HCNRW139-000E	HCNRW139-000E	1	DIP-8	0.4	700	1414	2.94	2.14	1.98	1.82
630-HCNRW139-300E	HCNRW139-300E	1	SO-8	0.4	700	5000	3.00	2.18	2.02	1.85
630-HCNRW2201-000E	HCNRW2201-000E	1	DIP-8	1.6	600	5000	3.55	2.58	2.39	2.19
630-HCNRW2211-000E	HCNRW2211-000E	1	DIP-8	1.6	600	5000	3.85	2.80	2.59	2.38
630-HCNRW2211-300E	HCNRW2211-300E	1	SO-8	1.6	600	5000	3.91	2.84	2.63	2.41
630-HCNRW2611-000E	HCNRW2611-000E	1	DIP-8	1.6	600	5000	3.99	2.90	2.68	2.47
630-HCNRW2611-300E	HCNRW2611-300E	1	SO-8	1.6	600	5000	4.04	2.94	2.72	2.50
630-HCNRW3120-000E	HCNRW3120-000E	1	DIP-8	10	700	5000	4.26	3.10	2.87	2.64
630-HCNRW4502-000E	HCNRW4502-000E	1	DIP-8	16	700	5000	2.20	1.60	1.48	1.36
630-HCNRW4503-000E	HCNRW4503-000E	1	DIP-8	16	700	5000	2.94	2.14	1.98	1.82
630-HCNRW4503-300E	HCNRW4503-300E	1	SO-8	16	700	5000	3.00	2.18	2.02	1.85
630-HCNRW4504-300E	HCNRW4504-300E	1	DIP-8	12	100	5000	3.33	2.42	2.24	2.06
630-HCNRW4506-300E	HCNRW4506-300E	1	SO-8	10	145	3750	3.41	2.48	2.29	2.11
630-HCPL-0201-000E	HCPL-0201-000E	1	DIP-8	1.6	600	3750	3.25	2.36	2.18	2.01
630-HCPL-0201-500E	HCPL-0201-500E	1	SO-8	1.6	600	3750	3.30	3.00	2.40	2.04
630-HCPL-0211-000E	HCPL-0211-000E	1	DIP-8	1.6	600	3750	3.74	2.72	2.52	2.31
630-HCPL-0211-500E	HCPL-0211-500E	1	SO-8	1.6	600	3750	3.80	3.45	2.76	2.35
630-HCPL-0300-000E	HCPL-0300-000E	1	SO-8	0.5	600	3750	8.25	6.00	5.55	5.10
630-HCPL-0314-000E	HCPL-0314-000E	1	SO-8	8	400	3750	2.06	1.50	1.39	1.28
630-HCPL-0370-000E	HCPL-0370-000E	1	SO-8	50	275	3750	3.93	2.86	2.65	2.43
630-HCPL-0452-000E	HCPL-0452-000E	1	SO-8	16	600	3750	1.92	1.30	1.18	1.00
630-HCPL-0453-000E	HCPL-0453-000E	1	SO-8	16	600	3750	2.26	1.64	1.52	1.39
630-HCPL-0454-000E	HCPL-0454-000E	1	SO-8	16	600	3750	2.53	1.84	1.70	1.56
630-HCPL-0500-000E	HCPL-0500-000E	1	SO-8	16	600	3750	1.69	1.14	1.04	.88
630-HCPL-0501-000E	HCPL-0501-000E	1	SO-8	16	600	3750	1.89	1.28	1.16	.99
630-HCPL-0501-500E	HCPL-0501-500E	1	SO-8	16	600	3750	1.80	1.62	1.32	1.02
630-HCPL-0530-000E	HCPL-0530-000E	2	SO-8	16	600	3750	3.71	2.70	2.50	2.30
630-HCPL-0531-000E	HCPL-0531-000E	2	SO-8	16	600	3750	3.85	2.80	2.59	2.38
630-HCPL-053L-000E	HCPL-053L-000E	2	SO-8	16	600	3750	4.18	3.04	2.81	2.58
630-HCPL-0600-000E	HCPL-0600-000E	1	SO-8	5	600	3750	1.93	1.40	1.30	1.19
630-HCPL-0600-500E	HCPL-0600-500E	1	SO-8	5	600	3750	1.98	1.80	1.44	1.22
630-HCPL-0601-000E	HCPL-0601-000E	1	SO-8	5	600	3750	1.93	1.40	1.30	1.19
630-HCPL-0601-500E	HCPL-0601-500E	1	SO-8	5	600	3750	1.98	1.80	1.44	1.22
630-HCPL-060L-000E	HCPL-060L-000E	1	SO-8	5	600	3750	2.20	1.60	1.48	1.36
630-HCPL-0611-000E	HCPL-0611-000E	1	SO-8	5	600	3750	2.48	1.80	1.67	1.53
630-HCPL-0611-500E	HCPL-0611-500E	1	SO-8	5	600	3750	2.53	2.30	1.84	1.56
630-HCPL-061A-000E	HCPL-061A-000E	1	SO-8	3	600	3750	2.83	2.06	1.91	1.75
630-HCPL-061N-000E	HCPL-061N-000E	1	SO-8	3	600	3750	3.03	2.20	2.04	1.87
630-HCPL-0630-000E	HCPL-0630-000E	2	SO-8	5	600	3750	5.01	3.64	3.37	3.09
630-HCPL-0630-500E	HCPL-0630-500E	2	SO-8	5	600	3750	5.06	4.60	3.68	3.13
630-HCPL-0631-000E	HCPL-0631-000E	2	SO-8	5	600	3750	5.01	3.64	3.37	3.09
630-HCPL-0631-500E	HCPL-0631-500E	2	SO-8	5	600	3750	5.06	4.60	3.68	3.13
630-HCPL-063A-000E	HCPL-063A-000E	2	SO-8	3	600	3750	6.46	4.70	4.35	4.00
630-HCPL-063L-000E	HCPL-063L-000E	2	SO-8	3	600	3750	5.50	4.00	3.70	3.40
630-HCPL-063N-000E	HCPL-063N-000E	2	SO-8	3	600	3750	8.53	6.20	5.74	5.27
630-HCPL-0661-000E	HCPL-0661-000E	2	SO-8	5	600	3750	8.25	6.00	5.55	5.10
630-HCPL-0700-000E	HCPL-0700-000E	1	SO-8	0.5	700	3750	1.92	1.30	1.18	1.00
630-HCPL-0701-000E	HCPL-0701-000E	1	SO-8	0.5	700	3750	1.98	1.45	1.32	1.12