

# NXP SEMICONDUCTOR Standard Logic



STANDARD LOGIC

RoHS Compliant This product is RoHS compliant.



For quantities of 250 and up, call for quote.

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	NXP Part No.	Package Type	Description	Price Each		
				1	25	100
<b>4000 Family</b>						
771-HEF4001BPN	HEF4001BP,652	DIP-14	Qd 2-In NOR	.35	.26	.17
771-HEF4001BT652	HEF4001BT,652	SO-14	Qd 2-In NOR	.31	.29	.211
771-HEF4002BT652	HEF4002BT,652	SO-14	DI 4-In NOR	.55	.44	.33
771-HEF4011BPN	HEF4011BP,652	DIP-14	Qd 2-In NAND	.42	.333	.266
771-HEF4011BTD	HEF4011BT,652	SO-14	Qd 2-In NAND	.22	.19	.15
771-HEF4013BPN	HEF4013BP,652	DIP-14	Dual D F/F	.30	.24	.16
771-HEF4013BT652	HEF4013BT,652	SO-14	Dual D F/F	.38	.299	.209
771-HEF4014BT652	HEF4014BT,652	SO-16	8B Stat Sh Reg	.35	.322	.304
771-HEF4015BPN	HEF4015BP,652	DIP-16	DI 4B Sh Reg	.35	.29	.18
771-HEF4016BPN	HEF4016BP,652	DIP-14	Qd Bilat Sw	.54	.40	.30
771-HEF4017BTD	HEF4017BT,652	SO-16	5St Johnson Cnt	.36	.27	.20
771-HEF4020BT652	HEF4020BT,652	SO-16	14St Bin Rip Cnt	.45	.366	.275
771-HEF4021BPN	HEF4021BP,652	DIP-16	8B Stat Sh Reg	.44	.33	.23
771-HEF4021BT652	HEF4021BT,652	SO-16	8B Stat Sh Reg	.58	.466	.35
771-HEF4023BTD	HEF4023BT,652	SO-14	Trp 3-In NAND	.32	.24	.16
771-HEF4027BPN	HEF4027BP,652	DIP-16	Dual JK F/F	.31	.26	.18
771-HEF4027BT652	HEF4027BT,652	SO-16	Dual JK F/F	.40	.352	.279
771-HEF4028BT652	HEF4028BT,652	SO-16	Dec BCD-Dec	.17	.166	.155
771-HEF4030BT652	HEF4030BT,652	SO-14	Qd Excl-OR	.42	.377	.283
771-HEF4040BT652	HEF4040BT,652	SO-16	12St Bin Rip Cnt	.20	.188	.166
771-HEF4044BTD	HEF4044BT,652	SO-16	Qd R/S Ltch 3St	.31	.28	.20
771-HEF4046BPN	HEF4046BP,652	DIP-16	Ph Lock Loop	.36	.27	.20
771-HEF4046BT652	HEF4046BT,652	SO-16	Ph Lock Loop	.26	.24	.23
771-HEF4047BPN	HEF4047BP,652	DIP-14	Mono/Astbl Multiv	.35	.27	.20
771-HEF4047BT652	HEF4047BT,652	SO-14	Mono/Astbl Multiv	.50	.445	.343
771-HEF4049BPN	HEF4049BP,652	DIP-16	Buff Hex Inv	.37	.28	.20
771-HEF4049BT652	HEF4049BT,652	SO-16	Buff Hex Inv	.42	.377	.287
771-HEF4050BT652	HEF4050BT,652	SO-16	Buff Hex NonInv	.40	.352	.279
771-HEF4051BPN	HEF4051BP,652	DIP-16	8-Ch Mux/Demux	.36	.288	.20
771-HEF4051BT652	HEF4051BT,652	SO-16	8-Ch Mux/Demux	.20	.177	.166
771-HEF4051BTT-T	HEF4051BTT,118	TSSOP-16	8-Ch Mux/Demux	.60	.45	.33
771-HEF4052BPN	HEF4052BP,652	DIP-16	DI 4-Ch Mux/Dmux	.42	.31	.22
771-HEF4052BT652	HEF4052BT,652	SO-16	DI 4-Ch Mux/Dmux	.16	.155	.15
771-HEF4053BPN	HEF4053BP,652	DIP-16	Trp 2-Ch Mux/Dmux	.42	.31	.22
771-HEF4053BT652	HEF4053BT,652	SO-16	Trp 2-Ch Mux/Dmux	.16	.155	.15
771-HEF4059BTD	HEF4059BT,652	SO-24	Cnt Prog Div-By-N	2.36	1.89	1.47
771-HEF4060BT652	HEF4060BT,652	SO-16	14St Bin Cnt/Div	.58	.466	.35
771-HEF4066BPN	HEF4066BP,652	DIP-14	Qd Bilat Sw	.41	.33	.25
771-HEF4066BT652	HEF4066BT,652	SO-14	Qd Bilat Sw	.34	.30	.27
771-HEF4067BTD	HEF4067BT,652	DIP-24	16-Ch Mux/Dmux	1.38	1.15	1.05
771-HEF4068BTD	HEF4068BT,652	SO-14	8-In NAND Gt	.25	.23	.19
771-HEF4069UBP652	HEF4069UBP,652	DIP-14	Hex Inverter	.16	.155	.144
771-HEF4069UBT652	HEF4069UBT,652	SO-14	Hex Inv Unbuff	.36	.317	.232
771-HEF4071BT652	HEF4071BT,652	SO-14	Quad 2-In OR	.38	.30	.208
771-HEF4072BT652	HEF4072BT,652	SO-14	Dual 4-In OR	.25	.23	.19
771-HEF4077BPN	HEF4077BP,652	DIP-14	Qd Excl NOR	.49	.42	.315
771-HEF4081BPN	HEF4081BP,652	DIP-14	Qd 2-In AND	.26	.18	.14
771-HEF4081BT652	HEF4081BT,652	SO-14	Qd 2-In AND	.37	.34	.24
771-HEF4093BPN	HEF4093BP,652	DIP-14	Qd 2-In NAND Sch	.38	.288	.188
771-HEF4093BTD-T	HEF4093BT,653	SO-14	Qd 2-In NAND Sch	.41	.33	.22
771-HEF4094BT652	HEF4094BT,652	SO-16	8-St Bus Reg	.50	.396	.297
771-HEF40106BPN	HEF40106BP,652	DIP-14	Hex Sch Trig	.38	.288	.188
771-HEF40106BTD-T	HEF40106BT,653	SO-14	Hex Sch Trig	.26	.17	.14
771-HEF40244BT652	HEF40244BT,652	SO-20	Oct Buff/Drv	1.07	.98	.75
771-HEF40373BPN	HEF40373BP,652	DIP-20	Oct Trans Ltch	1.25	.98	.81
771-HEF40373BT652	HEF40373BT,652	SO-20	Oct Trans Ltch	1.35	1.08	.81
771-HEF4511BPN	HEF4511BP,652	DIP-16	BCD 7-Segmnt	.42	.34	.24
771-HEF4511BT652	HEF4511BT,652	SO-16	BCD 7-Segmnt	.45	.396	.31
771-HEF4516BT652	HEF4516BT,652	SO-16	Bin Up/Dwn Cnt	.53	.50	.387
771-HEF4520BPN	HEF4520BP,652	DIP-16	DI Cntr Bin	.37	.28	.20
771-HEF4520BT652	HEF4520BT,652	SO-16	DI Cntr Bin	.41	.40	.343
771-HEF4521BT652	HEF4521BT,652	SO-16	Freq Div 24St	.69	.58	.44
771-HEF4528BT652	HEF4528BT,652	SO-16	DI Mono Multiv	.54	.40	.31
771-HEF4538BPN	HEF4538BP,652	DIP-16	DI Mono Multiv	.56	.42	.31
771-HEF4538BTD	HEF4538BT,652	SO-16	DI Mono Multiv	.40	.30	.19
771-HEF4541BPN	HEF4541BP,652	DIP-14	Prog Timer	.26	.18	.16
771-HEF4543BPN	HEF4543BP,652	DIP-16	BCD 7-Segmnt	.35	.29	.18
771-HEF4555BT652	HEF4555BT,652	SO-16	DI 1-4 Dcod/Dmux	.41	.366	.298
771-HEF4794BPN	HEF4794BP,112	DIP-16	8St Sh/Str Reg	1.31	1.09	.87
771-HEF4794BT112	HEF4794BT,112	SO-16	8St Sh/Str Reg	1.31	1.09	.87
771-HEF4894BPN	HEF4894BP,112	DIP-20	12St Shft Reg	1.80	1.65	1.24
771-HEF4894BT112	HEF4894BT,112	SO-20	12St Shft Reg	1.80	1.65	1.24
<b>74F Family</b>						
771-N74F00D-T	N74F00D,623	SO-14	Qd 2-In NAND	.34	.228	.162
771-N74F04D-T	N74F04D,623	SO-14	Hex Inverter	.29	.21	.14
771-NF06N602	N74F06N,602	DIP-14	Hex Buff/Drv	.86	.81	.80
771-NF07D602	N74F07D,602	SO-14	Hex Buff/Drv	.86	.81	.80
771-N74F07N	N74F07N,602	DIP-14	Hex Buff/Drv	.86	.81	.80
771-NF08D602	N74F08D,602	SO-14	Qd 2-In AND	.43	.33	.241
771-NF14D602	N74F14D,602	SO-14	Hex Inv Sch Trig	.48	.40	.283
771-NF32D602	N74F32D,602	SO-14	Qd 2-In OR	.17	.145	.123
771-NF38D602	N74F38D,602	SO-14	2-In NAND Buff	.16	.15	.138
771-NFD602	N74F74D,602	SO-14	Dual D F/F	.47	.38	.261

MOUSER STOCK NO.	NXP Part No.	Package Type	Description	Price Each		
				1	25	100
<b>74F Family (Cont.)</b>						
771-NF125D602	N74F125D,602	SO-14	Qd Buff 3St	.46	.32	.283
771-N74F125N	N74F125N,602	DIP-14	Qd Buff 3St	.39	.30	.22
771-N74F125N	N74F125N,602	DIP-14	Qd Buff 3St	.39	.30	.22
771-N74F244D	N74F244D,602	SO-20	Buff Oct 3St	.39	.29	.22
771-NF245D602	N74F245D,602	SO-20	Oct Bus Trans	.26	.23	.20
771-NF367D602	N74F367D,602	SO-16	Hex Buff/Drv	1.17	1.05	.88
771-NF3037D512	N74F3037D,512	SO-16	Qd 2-In NAND Drv	1.16	1.04	.868
771-N74F3037N	N74F3037N,602	DIP-16	Qd 2-In NAND Drv	1.95	1.69	1.33
<b>CAN Family</b>						
771-CBT3244APW-T	CBT3244APW,118	TSSOP-20	Oct Bus Sw	.35	.318	.241
771-IP4776CZ38-T/3	IP4776CZ38,118	TSSOP-38	HDMI Intrfc	2.32	1.86	1.43
771-PCA82C250T-D-T	PCA82C250T/N4,118	SO-8	Hi-Sp CAN Trans	1.37	1.08	.813
771-PCA82C251T-D-T	PCA82C251T/N3,118	SO-8	CAN Transcvr	1.49	1.19	.891
771-TJA1020T/N112	TJA1020T/N1,112	SO-8	LIN Transcvr	1.30	1.08	.86
771-TJA1040T-D-T	TJA1040T/N1,518	SO-8	Hi-Sp CAN Trans	1.32	1.05	.79
771-TJA1054AT-D-T	TJA1054AT,518	SO-14	CAN Transcvr	2.05	1.63	1.22
771-TJA1054T/N1512	TJA1054T/N1,512	SO-14	CAN Transcvr	2.05	1.63	1.22
<b>HC Family</b>						
771-HC00D652	74HC00D,652	SO-14	Qd 2-In NAND	.23	.20	.18
771-74HC00D-T	74HC00D,653	SOT-108	AND/NAND/OR/NOR	.18	.15	.13
771-74HC00DB	74HC00DB,112	SOT-337	AND/NAND/OR/NOR	.23	.20	.19
771-74HC00N	74HC00N,652	SOT-27	AND/NAND/OR/NOR	.25	.18	.15
771-74HC00PW-T	74HC00PW,118	SOT-402	AND/NAND/OR/NOR	.12	.11	.102
771-74HC02D	74HC02D,652	SOT-108	AND/NAND/OR/NOR	.17	.14	.132
771-74HC02N	74HC02N,652	SOT-27	AND/NAND/OR/NOR	.25	.18	.15
771-74HC03N	74HC03N,652	SOT-27	AND/NAND/OR/NOR	.13	.12	.113
771-74HC03PW	74HC03PW,112	SOT-402	AND/NAND/OR/NOR	.12	.11	.102
771-HC04D652	74HC04D,652	SO-14	Hex Inv LSTTL	.22	.20	.192
771-74HC04D-T	74HC04D,653	SOT-108	Inverters	.17	.14	.132
771-74HC04N	74HC04N,652	SOT-27	Inverters	.25	.18	.15
771-74HC04D-T	74HC04D,653	SO-14	Hex Inv Unbuff	.17	.14	.124
771-HC08D652	74HC08D,652	SO-14	Qd 2-In AND	.20	.17	.162
771-74HC08D-T	74HC08D,653	SOT-108	AND/NAND/OR/NOR	.18	.16	.141
771-74HC08DB-T	74HC08DB,118	SOT-337	AND/NAND/OR/NOR	.21	.20	.19
771-74HC08N	74HC08N,652	SOT-27	AND/NAND/OR/NOR	.25	.18	.15
771-74HC11D-T	74HC11D,653	SOT-108	AND/NAND/OR/NOR	.17	.15	.13
771-74HC14DB	74HC14DB,112	SOT-337	Inverters	.32	.29	.24
771-74HC20N	74HC20N,652	SOT-27	AND/NAND/OR/NOR	.25	.18	.15
771-74HC21D	74HC21D,652	SOT-108	AND/NAND/OR/NOR	.11	.10	.092
771-74HC27D-T	74HC27D,653	SOT-108	AND/NAND/OR/NOR	.17	.14	.132
771-74HC30D-T	74HC30D,653	SOT-108	AND/NAND/OR/NOR	.18	.174	.169
771-74HC30N	74HC30N,652	SOT-27	AND/NAND/OR/NOR	.25	.18	.15
771-HC32D652	74HC32D,652	SO-14	Quad J-K M/S	.23	.21	.192
771-74HC32D-T	74HC32D,653	SOT-108	AND/NAND/OR/NOR	.18	.174	.169
771-74HC32N	74HC32N,652	SOT-27	AND/NAND/OR/NOR	.25	.19	.17
771-74HC32PW-T	74HC32PW,118	SOT-402	AND/NAND/OR/NOR	.12	.11	.102
771-74HC42N	74HC42N,652	DIP-16	Dec BCD-Dec	.59	.44	.33
771-74HC73D-T	74HC73D,653	SO-14	Dual J-K M/S	.19	.16	.14
771-74HC73N	74HC73N,652	DIP-14	Dual J-K F/F	.37	.28	.20
771-74HC74BQ-G	74HC74BQ,115	DH/QFN-14	Qd 2-In NAND	.77	.58	.43
771-74HC74D-T	74HC74D,653	SO-14	Dual D F/F	.17	.14	.132
771-74HC74N	74HC74N,652					