

NXP SEMICONDUCTOR Standard Logic



Standard Logic

NXP Semiconductor

STANDARD LOGIC

This product is RoHS compliant.



For quantities of 250 and up, call for quote.

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	NXP Part No.	Package Type	Description	Price Each			MOUSER STOCK NO.	NXP Part No.	Package Type	Description	Price Each		
				1	25	100					1	25	100
HC Family (Cont.)						HC Family (Cont.)							
771-74HC163D	74HC163D,652	SOT-109	Counter ICs	.17	.15	.135	771-74HC4066N	74HC4066N,652	DIP-14	Qd Bilat Sw	.31	.28	.20
771-74HC164D-T	74HC164D,653	SOT-108	Cntr Sh Reg	.36	.25	.18	771-74HC4066PW112	74HC4066PW,112	TSSOP-14	Qd Bilat Sw	.36	.29	.27
771-74HC164N	74HC164N,652	SOT-27	Cntr Sh Reg	.19	.17	.142	771-74HC4066PW,118	74HC4066PW,118	SOT-402	Switch ICs	.30	.27	.20
771-74HC164PW-T	74HC164PW,118	SOT-402	Cntr Sh Reg	.18	.16	.136	771-74HC4067BQ-T	74HC4067BQ,118	SOT-815	Enc/Dec Mux/DeMux	1.96	1.85	1.75
771-HC165D652	74HC165D,652	SO-16	8B Shift Reg	.16	.15	.14	771-74HC4067D	74HC4067D,652	SO-24	16-Ch Mux/Demux	.35	.33	.30
771-74HC165D-T	74HC165D,653	SOT-109	Cntr Sh Reg	.25	.19	.17	771-HC4067PW112	74HC4067PW,112	TSSOP-24	16-Ch Mux/Demux	2.25	1.80	1.35
771-74HC165N	74HC165N,652	SOT-38	Cntr Sh Reg	.40	.30	.21	771-74HC4075N	74HC4075N,652	SOT-27	AND/NAND/OR/NOR	.25	.211	.20
771-74HC165PW-T	74HC165PW,118	SOT-403	Cntr Sh Reg	.27	.24	.168	771-74HC4094D	74HC4094D,652	SO-16	8St BUS Reg	.26	.18	.16
771-74HC166D-T	74HC166D,653	SOT-109	Cntr Sh Reg	.26	.18	.16	771-74HC4094D-T	74HC4094D,653	SOT-109	Cnt Shift Reg	.37	.28	.196
771-74HC173N	74HC173N,652	SOT-38	Flip Flops	.45	.34	.25	771-74HC4094N	74HC4094N,652	DIP-16	8St Bus Reg	.52	.38	.28
771-74HC174D-T	74HC174D,653	SOT-109	Flip Flops	.26	.18	.16	771-HC4316D652	74HC4316D,652	SO-16	Qd Bilat Sw	.55	.46	.34
771-74HC175D-T	74HC175D,653	SOT-109	Flip Flops	.41	.36	.32	771-74HC4514D-T	74HC4514D,653	SO-24	4-16 Dec/Mux w/Ltch	1.44	1.16	.861
771-74HC193N	74HC193N,652	SOT-38	Counter ICs	.37	.34	.29	771-74HC4520D-T	74HC4520DB,118	SSOP-16	DI 4B Bin Rip Cnt	.57	.54	.53
771-74HC194N	74HC194N,652	SOT-38	Cntr Sh Reg	.42	.37	.334	771-HC4520PW112	74HC4520PW,112	TSSOP-16	DI 4B Bin Rip Cnt	.84	.70	.56
771-74HC221D	74HC221D,652	SOT-109	Mono Multiv	.47	.35	.26	771-74HC4538D-T	74HC4538D,653	SO-16	DI Mono Retrig	.23	.21	.20
771-74HC221D-T	74HC221D,653	SOT-109	Mono Multiv	.48	.47	.375	771-74HC4538N	74HC4538N,652	DIP-16	DI Mono Retrig	.45	.33	.249
771-74HC237N	74HC237N,652	SOT-38	Enc/Dec Mux/DeMux	.52	.38	.28	771-74HC5555D-T	74HC5555D,118	SO-16	Prog Delay Timer	.95	.89	.87
771-74HC238D-T	74HC238D,653	SOT-109	Enc/Dec Mux/DeMux	.51	.41	.311	771-HC6323AD112	74HC6323AD,112	SO-8	Prog Rip Cnt	.56	.53	.51
771-74HC238N	74HC238N,652	SOT-38	Enc/Dec Mux/DeMux	.52	.38	.28	771-74HC7014D-T	74HC7014D,118	SO-14	Hex Non-Inv Schm	.79	.75	.73
771-74HC241N	74HC241N,652	SOT-146	Buff/Ln Drvr	.45	.34	.25	771-74HC7014N	74HC7014N,112	DIP-14	Hex Non-Inv Schm	.79	.75	.73
771-74HC244D	74HC244D,652	SOT-163	Buff/Ln Drvr	.32	.24	.168	771-HC7266DB112	74HC7266DB,112	SSOP-14	Qd 2-In Excl-NOR	.48	.44	.37
771-74HC244D-T	74HC244D,653	SOT-163	Buff/Ln Drvr	.32	.24	.168	771-HC03N112	74HC7403N,112	DIP-16	4Bx64W FIFO Reg	2.36	1.89	1.54
771-74HC244N	74HC244N,652	SOT-146	Buff/Ln Drvr	.33	.30	.231	771-74HC7540D-T	74HC7540D,118	SO-20	Oct Buff/Drvr	.89	.82	.69
771-74HC245D	74HC245D,653	SOT-163	Bus Transcvr	.27	.24	.168	771-HC7540DB112	74HC7540DB,112	SSOP-20	Oct Buff/Drvr	.89	.82	.69
771-74HC245D-T	74HC245D,653	SOT-163	Bus Transcvr	.31	.24	.17	771-74HC7541D-T	74HC7541D,118	SO-20	Buff/Ln Drvr	.89	.82	.69
771-74HC245PW	74HC245PW,112	SOT-360	Bus Transcvr	.31	.26	.18	771-74HC7541DB	74HC7541DB,112	SOT-339	Buff/Ln Drvr	.89	.82	.69
771-74HC259N	74HC259N,652	SOT-38	Latches	.44	.33	.20	771-74HC7541DB-T	74HC7541DB,118	SSOP-20	Oct Buff/Drvr	.89	.82	.69
771-74HC273D-T	74HC273D,653	SOT-163	Flip Flops	.25	.21	.16	771-74HC7541N	74HC7541N,112	DIP-20	Oct Buff/Drvr	.89	.82	.69
771-74HC273N	74HC273N,652	SOT-146	Flip Flops	.37	.28	.20	771-74HC1G00GW-G	74HC1G00GW,125	SOT-353	AND/NAND/OR/NOR	.11	.10	.074
771-74HC367N	74HC367N,652	SOT-38	Buff/Ln Drvr	.38	.35	.296	771-74HC1G02GV	74HC1G02GV,125	SOT-753	AND/NAND/OR/NOR	.06	.055	.051
771-HC373D652	74HC373D,652	SO-20	Oct D Latch	.16	.15	.138	771-74HC1G02GW-G	74HC1G02GW,125	SOT-353	AND/NAND/OR/NOR	.13	.10	.074
771-74HC373D-T	74HC373D,653	SOT-163	Latches	.25	.21	.16	771-74HC1G04GV	74HC1G04GV,125	SOT-753	Inverters	.06	.055	.051
771-74HC373N	74HC373N,652	SOT-146	Latches	.37	.28	.20	771-74HC1G04GW-G	74HC1G04GW,125	SOT-353	Inverters	.13	.111	.082
771-74HC374D-T	74HC374D,653	SOT-163	Flip Flops	.30	.24	.16	771-74HC1G08GV	74HC1G08GV,125	SOT-753	AND/NAND/OR/NOR	.06	.055	.051
771-74HC390D-T	74HC390D,653	SOT-109	Counter ICs	.36	.27	.20	771-74HC1G14GW-G	74HC1G14GW,125	SOT-353	Inverters	.13	.111	.082
771-74HC390N	74HC390N,652	SOT-38	Counter ICs	.53	.40	.29	771-74HC1G32GV	74HC1G32GV,125	SOT-753	AND/NAND/OR/NOR	.06	.055	.051
771-74HC393D-T	74HC393D,653	SOT-108	Counter ICs	.27	.24	.15	771-74HC1G66GW-G	74HC1G66GW,125	SOT-353	Switch ICs	.17	.12	.09
771-74HC423D-T	74HC423D,653	SO-16	DI Retrg Mono Multi	.20	.198	.192	771-74HC1G86GV	74HC1G86GV,125	SOT-753	AND/NAND/OR/NOR	.07	.061	.056
771-74HC423N	74HC423N,652	DIP-16	DI Retrg Mono Multi	.63	.47	.34	771-74HC2G17GW-G	74HC2G17GW,125	SOT-363	Buff/Ln Drvr	.15	.141	.117
771-HC540D652	74HC540D,652	SO-20	Oct Buff/Drvr	.55	.42	.311	HCT Family						
771-74HC540D-T	74HC540D,653	SOT-163	Buff/Ln Drvr	.55	.41	.311	771-74HCT00D-T	74HCT00D,653	SO-14	Qd 2-In NAND	.17	.14	.132
771-74HC540N	74HC540N,652	DIP-20	Oct Buff/Ln Drv	.53	.40	.29	771-74HCT00N	74HCT00N,652	DIP-14	Qd 2-In NAND	.27	.24	.15
771-74HC541D-T	74HC541D,653	SO-20	Oct Buff/Drvr	.24	.19	.16	771-74HCT02D-T	74HCT02D,653	SO-14	Qd 2-In NOR	.40	.33	.295
771-74HC563N	74HC563N,652	DIP-20	Oct D Ltch Inv	.69	.51	.38	771-74HCT02N	74HCT02N,652	DIP-14	Qd 2-In NOR	.27	.24	.15
771-74HC573D	74HC573D,652	SO-20	Oct D Ltch Inv	.30	.24	.174	771-HCT04BQ115	74HCT04BQ,115	DHVQFN-14	Hex Inverter	.40	.37	.31
771-74HC573D-T	74HC573D,653	SOT-163	Latches	.41	.36	.32	771-74HCT04D-T	74HCT04D,653	SO-14	Hex Inverter	.17	.14	.124
771-74HC573DB	74HC573DB,112	SSOP-20	Oct D Trans Ltch	.76	.51	.35	771-74HCT04N	74HCT04N,652	DIP-14	Hex Inverter	.24	.19	.16
771-74HC573N	74HC573N,652	DIP-20	Octal D Ltch Inv	.36	.27	.20	771-HCT08BQ115	74HCT08BQ,115	DHVQFN-14	Qd 2-In AND	.40	.37	.31
771-74HC573PW-T	74HC573PW,118	TSSOP-20	Octal D Ltch Inv	.31	.26	.18	771-74HCT08D-T	74HCT08D,653	SO-14	Qd 2-In AND	.20	.16	.146
771-HC5D652	74HC574D,652	SO-20	Octal D F/F	.38	.332	.249	771-74HCT08N	74HCT08N,652	DIP-14	Qd 2-In AND	.25	.19	.17
771-74HC574D-T	74HC574D,653	SO-20	Octal D F/F	.25	.21	.16	771-HCT14D652	74HCT14D,652	SO-14	Hex Inv Schm	.25	.23	.212
771-74HC574DB-T	74HC574DB,118	SSOP-20	Octal D F/F	.40	.37	.31	771-74HCT14D-T	74HCT14D,653	SO-14	Hex Inv Schm	.17	.14	.124
771-HC5N652	74HC574N,652	DIP-20	Octal D F/F	.49	.36	.279	771-74HCT14N	74HCT14N,652	DIP-14	Hex Inv Schm	.24	.19	.16
771-74HC574PW-T	74HC574PW,118	SOT-360	Flip Flops	.17	.15	.135	771-HCT32D652	74HCT32D,652	SO-14	Quad 2-In OR	.34	.32	.186
771-74HC58N	74HC58N,652	DIP-14	Dual AND/OR	.51	.39	.29	771-74HCT32N	74HCT32N,652	DIP-14	Quad 2-In OR	.24	.19	.16
771-HC594D112	74HC594D,112	SO-16	8B Shift Reg	.58	.42	.319	771-HCTBQ115	74HCT74BQ,115	DHVQFN-14	Dual D F/F	.77	.58	.43
771-74HC594D-T	74HC594D,118	SO-16	8B Shift Reg	1.77	1.32	.99	771-74HCT74D-T	74HCT74D,653	SO-14	Dual D F/F	.29	.21	.14
771-74HC595BQ-G	74HC595BQ,115	DHVQFN-16	8B Shift Reg	.86	.72	.58	771-74HCT74N	74HCT74N,652	DIP-14	Dual D F/F	.24	.19	.16
771-74HC595D	74HC595D,112	SO-16	8B Shift Reg	.37	.25	.19	771-74HCT85N	74HCT85N,652	DIP-16	4B Mag Comp	.35	.32	.29
771-74HC595D-T	74HC595D,118	SOT-109	Cnt Shift Reg	.33	.32	.31	771-74HCT86D-T	74HCT86D,653	SO-14	Qd 2-In Excl OR	.17	.15	.13
771-HC595DB112	74HC595DB,112	SSOP-16	8B Shift Reg	.55	.50	.42	771-74HCT86N	74HCT86N,652	DIP-14	Qd 2-In Excl OR	.44	.33	.23
771-74HC595N	74HC595N,112	DIP-16	8B Shift Reg	.37	.28	.20	771-HCT112D652	74HCT112D,652	SO-16	DI J-K F/F	.34	.31	.26
771-74HC595PW-T	74HC595PW,118	TSSOP-16	8B Shift Reg	.25	.18	.15	771-74HCT123D-T	74HCT123D,653	SO-16	DI Mono Multiv	.25	.21	.16
771-74HC597D-T	74HC597D,653	SO-16	8B Shift Reg	.41	.39	.297	771-74HCT123N	74HCT123N,652	DIP-16	DI Mono Multiv	.42	.31	.237
771-74HC597DB-T	74HC597DB,118	SSOP-16	8B Shift Reg	.54	.51	.50	771-74HCT123PW	74HCT123PW,112	TSSOP-16	DI Mono Multiv	.70	.53	.39
771-74HC597N	74HC597N,652	DIP-16	8B Shift Reg	.35	.32	.29	771-74HCT125D-T	74HCT125D,653	SO-14	Qd Buff/Drvr	.31	.21	.16
771-74HC640DB-T	74HC640DB,118	SSOP-20	Oct Bus Trans	.57	.54	.48	771-74HCT132D-T	74HCT132D,653	SO-14	Qd 2-In NAND	.24	.232	.225
771-74HC688D-T	74HC688D,653	SO-20	8B Mag Comp	.56	.42	.355	771-74HCT132N	74HCT132N,652	DIP-14	Qd 2-In NAND	.37	.27	.19
771-74HC688N	74HC688N,652	DIP-20	8B Mag Comp	.69	.51	.38	771-74HCT138D-T	74HCT138D,653	SO-16	3-8 Ln Dec/Demux	.23	.18	.16
771-74HC4050D-T	74HC4050D,653	SO-16	Hex Hi-Lo Lvl Sh	.41	.36	.32							