

# NXP SEMICONDUCTOR Standard Logic



STANDARD LOGIC

This product is RoHS compliant.



For quantities of 250 and up, call for quote.

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	NXP Part No.	Package Type	Description	Price Each		
				1	25	100
<b>HCT Family (Cont.)</b>						
771-74HCT221D	74HCT221D,112	SO-16	DI Mono Multv	.39	.36	.329
771-74HCT238D-T	74HCT238D,653	SO-16	3-to-8 Dec/Demux	.36	.33	.30
771-HCT238DB112	74HCT238DB,112	SSOP-16	3-to-8 Dec/Demux	.53	.47	.461
771-74HCT238PW-T	74HCT238PW,118	TSSOP-16	3-to-8 Dec/Demux	.40	.38	.37
771-74HCT240N	74HCT240N,652	DIP-20	Oct Buff/Drvr	.37	.28	.20
771-HCT244D652	74HCT244D,652	SO-20	Oct Buff/Drvr	.50	.393	.279
771-74HCT244D-T	74HCT244D,653	SO-20	Oct Buff/Drvr	.27	.24	.15
771-74HCT244N	74HCT244N,652	DIP-20	Oct Buff/Drvr	.29	.22	.21
771-74HCT245D-T	74HCT245D,653	SO-20	Oct Transcvr	.27	.24	.15
771-74HCT245N	74HCT245N,652	DIP-20	Oct Transcvr	.37	.28	.20
771-74HCT245PW	74HCT245PW,112	TSSOP-20	Oct Transcvr	.31	.26	.18
771-74HCT259D-T	74HCT259D,653	SO-16	8B Address Latch	.43	.32	.22
771-74HCT259N	74HCT259N,652	DIP-16	8B Address Latch	.35	.29	.18
771-HCT273D652	74HCT273D,652	SO-20	Oct D F/F w/Rest	.36	.332	.249
771-74HCT273N	74HCT273N,652	DIP-20	Oct D F/F w/Rest	.21	.17	.161
771-HCT280D652	74HCT280D,652	SO-14	9B Par Gen/Chkr	.92	.69	.52
771-74HCT365D-T	74HCT365D,653	SO-16	Hex Buff w/Com En	.38	.35	.33
771-HCT365DB112	74HCT365DB,112	SSOP-16	Hex Buff w/Com En	.42	.38	.32
771-HCT366D652	74HCT366D,652	SO-16	Hex Buff/Drvr	.48	.43	.42
771-74HCT367D-T	74HCT367D,653	SO-16	Hex Buff/Drvr	.49	.45	.41
771-74HCT367N	74HCT367N,652	DIP-16	Hex Buff/Drvr	.33	.31	.29
771-HCT373D653	74HCT373D,653	SO-20	Octal D Latch	.16	.15	.138
771-74HCT373N	74HCT373N,652	DIP-20	Octal D Latch	.30	.27	.20
771-HCT3D652	74HCT374D,652	SO-20	Octal D F/F	.33	.31	.241
771-74HCT374N	74HCT374N,652	DIP-20	Octal D F/F	.40	.30	.22
771-HCT377PW112	74HCT377PW,112	TSSOP-20	Octal D F/F	.40	.37	.31
771-74HCT393D-T	74HCT393D,653	SO-14	DI Bin Rip Ctr	.33	.32	.295
771-HCT393DB112	74HCT393DB,112	SSOP-14	DI Bin Rip Ctr	.40	.34	.31
771-74HCT540D	74HCT540D,652	SO-20	Oct Buff/Drvr Inv	.40	.30	.22
771-74HCT541D	74HCT541D,652	SO-20	Oct Buff/Ln Drvr	.27	.24	.15
771-74HCT541N	74HCT541N,652	DIP-20	Oct Buff/Ln Drvr	.44	.33	.20
771-74HCT573D	74HCT573D,652	SO-20	Octal D Latch	.24	.19	.16
771-74HCT573N	74HCT573N,652	DIP-20	Octal D Latch	.30	.27	.20
771-74HCT574D-T	74HCT574D,653	SO-20	Octal D F/F	.41	.36	.32
771-74HCT574DB-T	74HCT574DB,118	SSOP-20	Octal D F/F	.40	.37	.31
771-74HCT574N	74HCT574N,652	DIP-20	Octal D F/F	.40	.30	.22
771-74HCT594D-T	74HCT594D,118	SO-16	Sh Reg w/Out Reg	.85	.76	.70
771-74HCT595BQ-G	74HCT595BQ,115	DHVFQFN-16	Sh Reg w/Out Reg	.86	.72	.58
771-74HCT595D-T	74HCT595D,118	SO-16	Sh Reg w/Out Reg	.40	.39	.37
771-74HCT595N	74HCT595N,112	DIP-16	Sh Reg w/Out Reg	.63	.58	.49
771-74HCT595PW-T	74HCT595PW,118	TSSOP-16	Sh Reg w/Out Reg	.75	.47	.44
771-74HCT640N	74HCT640N,652	DIP-20	Oct Bus Xcvr Inv	.75	.59	.451
771-74HCT688D-T	74HCT688D,653	SO-20	8B Mag Comp	.45	.34	.25
771-74HCT688N	74HCT688N,652	DIP-20	8B Mag Comp	.62	.50	.37
771-74HCT4016N	74HCT4016N,112	DIP-14	Qd Billat Sw	.46	.37	.35
771-74HCT4040D-T	74HCT4040D,653	SO-16	12St Bin Cnt	.48	.41	.33
771-74HCT4040N	74HCT4040N,652	DIP-16	12St Bin Cnt	.50	.37	.27
771-74HCT4046AD-T	74HCT4046AD,118	SO-16	Ph-Lock Loop	1.20	.88	.66
771-HCT4046ADB112	74HCT4046ADB,112	SSOP-16	Ph-Lock Loop	1.50	1.20	.90
771-74HCT4051D-T	74HCT4051D,118	SO-16	8-Ch Mux/Demux	.35	.34	.32
771-74HCT4052D-T	74HCT4052D,118	SO-16	DI 4-Ch Mux/Demux	.37	.33	.31
771-74HCT4052DB-T	74HCT4052DB,118	SSOP-16	DI 4-Ch Mux/Demux	.48	.43	.39
771-74HCT4053D-T	74HCT4053D,118	SO-16	Trp 2Ch Mux/Demux	.27	.24	.15
771-74HCT4059N	74HCT4059N,112	DIP-24	Cnt Prog Div-By-N	1.99	1.95	1.51
771-74HCT4066D	74HCT4066D,118	SO-14	Qd Billat Sw	.21	.19	.17
771-HCT4066PW112	74HCT4066PW,112	TSSOP-14	Qd Billat Sw	.45	.41	.34
771-HCT4067DB112	74HCT4067DB,112	SSOP-24	16-Ch Mux/Demux	2.25	1.80	1.42
771-74HCT4067N	74HCT4067N,112	DIP-24	16-Ch Mux/Demux	2.25	1.80	1.42
771-74HCT4067PW-T	74HCT4067PW,118	TSSOP-24	16-Ch Mux/Demux	1.72	1.63	1.59
771-HCT4075D652	74HCT4075D,652	SO-14	Trp 3-In OR	.29	.27	.25
771-74HCT4094D-T	74HCT4094D,118	SO-16	Sh/Str Bus Reg	.42	.33	.275
771-74HCT4316PW-T	74HCT4316PW,118	TSSOP-16	Qd Billat Sw	.48	.39	.37
771-HCT4511D652	74HCT4511D,652	SO-16	BCD-7Sg Ltc/Dc/Drvr	.53	.47	.461
771-74HCT4514D-T	74HCT4514D,653	SO-24	4-16 Dec/Mux w/Ltch	1.22	1.13	.915
771-HCT4538D112	74HCT4538D,112	SO-16	DI Mono Multivb	.56	.41	.309
771-74HCT5555D-T	74HCT5555D,118	SO-16	Prog Delay Timer	1.60	1.32	.99
771-HCT7273D112	74HCT7273D,112	SO-20	Octal D FF	.87	.73	.58
771-HCT7541D112	74HCT7541D,112	SO-20	Oct Buff/Drvr	1.29	1.10	.91
771-74HCT9046AD-T	74HCT9046AD,118	SO-16	PLL Bnd Gap Cont	2.12	1.69	1.27
771-74HCT9046AN	74HCT9046AN,112	DIP-16	PLL Bnd Gap Cont	2.12	1.69	1.27
771-HCT9046APW112	74HCT9046APW,112	TSSOP-16	PLL Bnd Gap Cont	2.12	1.69	1.27

<b>Interface</b>						
771-SSTVF16859BS118	SSTVF16859BS,118	HVQFN-56	13B Reg Buff	1.16	1.04	.87
771-TDA8020HL2BD-T	TDA8020HL/C2,118	LQFP-32	Smart Crd Intrfc	2.01	1.63	1.39
771-TDA8020HLC1118	TDA8020HL/C1,118	LQFP-32	Smart Crd Intrfc	3.43	2.74	2.13

<b>Logic Translation</b>						
771-GTL2009PW112	GTL2009PW,112	TSSOP-16	3B FSB Freq Cmplr	.80	.60	.45
771-GTL2014PW112	GTL2014PW,112	TSSOP-14	4B LVTTL-GTL Trns	1.06	.85	.641
771-GTL2034PW112	GTL2034PW,112	TSSOP-14	4B GTL-GTL Buffer	1.35	1.13	.90

<b>LV Family</b>						
771-74LV14D-T	74LV14D,118	SO-14	Hex Inv Schmt	.23	.18	.16
771-74LV153D-T	74LV153D,118	SO-16	Dual 4-In Mux	.38	.33	.32
771-74LV251PW	74LV251PW,112	TSSOP-16	8-Input Mux	.92	.77	.61
771-LV259D112	74LV259D,112	SO-16	8B Add BL Ltch	.67	.62	.56

MOUSER STOCK NO.	NXP Part No.	Package Type	Description	Price Each		
				1	25	100
<b>LV Family (Cont.)</b>						
771-LV259PW112	74LV259PW,112	TSSOP-16	8B Add BL Ltch	.81	.68	.57
771-LV377D112	74LV377D,112	SO-20	Octal D F/F	.81	.68	.57
771-LV377DB112	74LV377DB,112	SSOP-20	Octal D F/F	.92	.77	.61
771-74LV393D-T	74LV393D,118	SO-14	DI 4B Bin Rip Cnt	.80	.47	.42
771-LV4020PW112	74LV4020PW,112	TSSOP-16	14St Bin Rip Cnt	.74	.68	.57
771-74LV4060D-T	74LV4060D,118	SO-16	14St Bin Rip Cnt	.65	.62	.60
771-74LV4060PW	74LV4060PW,112	TSSOP-16	14St Bin Rip Cnt	1.13	.94	.75
771-74LV4094D-T	74LV4094D,118	SO-16	8St Sh/Str Bus Reg	.65	.62	.60
771-LV4094DB112	74LV4094DB,112	SSOP-16	8St Sh/Str Bus Reg	1.10	.91	.73
771-74LV4094PW-T	74LV4094PW,118	TSSOP-16	8St Sh/Str Bus Reg	.72	.68	.65

<b>LV Family</b>						
771-74LVC00AD-T	74LVC00AD,118	SO-14	Qd 2-In NAND	.21	.19	.16
771-74LVC00APW-T	74LVC00APW,118	TSSOP-14	Qd 2-In NAND	.17	.15	.13
771-74LVC02APW-T	74LVC02APW,118	TSSOP-14	Qd 2-In NOR	.35	.24	.162
771-74LVC04AD-T	74LVC04AD,118	SO-14	3.3V Hex Inv	.18	.15	.137
771-74LVC04APW-T	74LVC04APW,118	TSSOP-14	Hex Inverter	.17	.15	.124
771-LVCU04AD118	74LVCU04AD,118	SO-14	Hex Inverter	.11	.099	.088
771-74LVC06AD-T	74LVC06AD,118	SO-14	Hex Inv Buff/Drvr	.25	.23	.16
771-74LVC07AD-T	74LVC07AD,118	SO-14	Hex Buff/Drvr	.25	.23	.16
771-74LVC07APW-T	74LVC07APW,118	TSSOP-14	Hex Buff/Drvr	.33	.23	.15
771-74LVC08AD-T	74LVC08AD,118	SO-14	Qd 2-In AND	.17	.14	.132
771-74LVC08APW-T	74LVC08APW,118	TSSOP-14	Qd 2-In AND	.17	.15	.13
771-74LVC14AD-T	74LVC14AD,118	SO-14	Hex Buff/Drvr	.21	.19	.166
771-74LVC14ADB-T	74LVC14ADB,118	SSOP-14	Hex Inv Sch Trg	.15	.13	.117
771-74LVC14APW-T	74LVC14APW,118	TSSOP-14	Hex Inv Sch Trg	.33	.23	.15
771-74LVC27D-T	74LVC27D,118	SO-14	Trp 3-In NOR	.25	.23	.19
771-LVC27PW112	74LVC27PW,112	TSSOP-14	Trp 3-In NOR	.25	.23	.19
771-74LVC32ABQ-G	74LVC32ABQ,115	DHVFQFN-14	Quad 2-In OR	.40	.37	.313
771-74LVC32AD-T	74LVC32AD,118	SO-14	Quad 2-In OR	.30	.21	.14
771-74LVC32APW-T	74LVC32APW,118	TSSOP-14	Quad 2-In OR	.35	.24	.162
771-74LVC74AD-T	74LVC74AD,118	SO-14	Dual D F/F	.28	.19	.14
771-74LVC74APW	74LVC74APW,112	TSSOP-14	Dual D F/F	.28	.19	.14
771-LVC125ABQ115	74LVC125ABQ,115	DHVFQFN-14	Qd Buff/Ln Drvr	.90	.67	.50
771-74LVC125AD-T	74LVC125AD,118	SO-14	Qd Buff/Ln Drvr	.31	.22	.15
771-74LVC125ADB-T	74LVC125ADB,118	SSOP-14	Qd Buff/Ln Drvr	.32	.22	.16
771-74LVC125APW-T	74LVC125APW,118	TSSOP-14	Qd Buff/Ln Drvr	.28	.19	.14
771-74LVC138AD-T	74LVC138AD,118	SO-16	3to8 Ln Dec/Demux	.32	.25	.19
771-LVC139BQ115	74LVC139BQ,115	DHVFQFN-16	DI 2-4 Dec/Demux	.90	.67	.50
771-LVC157ABQ115	74LVC157ABQ,115	DHVFQFN-16	Qd 2-In Multiplex	.90	.67	.50
771-74LVC163PW-T	74LVC163PW,118	TSSOP-16	4B Sync Bin Cntr	.26	.257	.249
771-74LVC244AD-T	74LVC244AD,118	SO-20	Oct Buff/Ln Drv	.25	.21	.163
771-74LVC244ADB	74LVC244ADB,112	SSOP-20	Oct Buff/Ln Drv	.30	.24	.164
771-74LVC244APW-T	74LVC244APW,118	TSSOP-20	Oct Buff/Ln Drv	.40	.27	.20
771-74LVC245AD-T	74LVC245AD,118	SO-20	Oct Bus Trans	.30	.24	.164
771-74LVC245ADB-T	74LVC245ADB,118	SSOP-20	Oct Bus Trans	.30	.24	.164
771-74LVC245AP						