

LOW DROPOUT VOLTAGE REGULATORS

- Ranging upward from a low output voltage of 1.5V
- Low current consumption with CMOS process, reduced from 1.5mA

- On/off function on UPC30 series
- High precision output voltage ($\pm 1\%$)

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	NEC Part No.	Package	Vin. (V) Max.	Io (A)	Vo (V)	Dropout (V) Max.	Price Each		
							1	25	100
Bipolar Analog									
879-UPC2933BHFZ	UPC2933BHF-AZ	TO-220	16	1.0	3.3	0.6 at IO=0.5A	.78	.72	.65
879-UPC2933BT1D-AT	UPC2933BT1D-AT-E1	TO-252	16	1.0	3.3	0.6 at IO=0.5A	.74	.68	.62
879-UPC2905BT1D-E1	UPC2905BT1D-E1-AT	SC-74A	16	1	5	0.6 at IO=0.5A	.70	.64	.59
879-UPC2918BT1D-E1	UPC2918BT1D-E1-AT	TO-220	16	1	1.8	0.6 at IO=0.5A	.70	.64	.59
879-UPC2905BHFZ	UPC2905BHF-AZ	TO-220	16	1	5	0.6 at IO=0.5A	.78	.72	.65
Standard									
879-UPD120N15T1BZ	UPD120N15T1B-AZ	SOT-89	6	0.3	1.5	0.9 at IO=0.15A	.51	.47	.42
879-UPD120N18T1B-E1	UPD120N18T1B-E1-AZ	TO-126	6	0.3	1.8	0.9 at IO=0.15A	.51	.46	.42
879-UPD120N18TA-E1-A	UPD120N18TA-E1-A	TO-126	6	0.3	1.8	0.65 at IO=0.15A	.53	.48	.44

LOW VOLTAGE POWER MOSFETS

- Super low ON-resistance
- Applications ranging from automotive electronics to PC power supplies

- A wide variety of package types for various mounting requirements
- High reliability

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	NEC Part No.	Package	Configuration	Polarity	Vdss (V)	Id (DC) (A)	Price Each		
							1	25	100
879-2SK3105-T1B	2SK3105-T1B-A	SC-75	Single	N	30	2.5	.47	.43	.39
879-NP110N055PUG-E1Z	NP110N055PUG-E1-AZ	MP-25ZP	Single	N	55	110	2.36	2.16	1.96
879-2SK1580-T1	2SK1580-T1-A	SC-70	Single	N	16	1	.15	.129	.118
879-2SK1586-T1Z	2SK1586-T1-AZ	SC-62	Single	N	30	1	.57	.53	.48
879-2SK1824-T1	2SK1824-T1-A	SC-75	Single	N	30	0.1	.18	.166	.154
879-2SK1958-T1	2SK1958-T1-A	SC-70	Single	N	16	0.1	.12	.118	.108
879-2SK2857-T1Z	2SK2857-T1-AZ	SC-62	Single	N	60	4	.63	.58	.52
879-2SK2858-T1	2SK2858-T1-A	SC-70	Single	N	30	0.1	.14	.129	.118
879-2SK3105-T1B	2SK3105-T1B-A	SC-75	Single	N	30	2.5	.47	.43	.39
879-NP22N055SLE-E1	NP22N055SLE-E1-AZ	TO-253	Single	N	55	22	.93	.86	.78
879-2SK3503-T1	2SK3503-T1-A	SC-75	Single	N	16	0.1	.12	.11	.10
879-UPA2707TP-E1Z	UPA2707TP-E1-AZ	HSOP-8	Single	N	30	42	1.70	1.55	1.41
879-NP40N055KLEE1-AZ	NP40N055KLE-E1-AZ	TO-263ZK	Single	N	55	± 40	1.53	1.41	1.27
879-NP48N055KHEE1-AZ	NP48N055KHE-E1-AZ	TO-263ZK	Single	N	55	± 48	1.64	1.51	1.36
879-NP52N06SLG-E1-AZ	NP52N06SLG-E1-AZ	TO-252ZK	Single	N	60	± 52	1.31	1.21	1.09
879-NP55N03SUG-E1-AZ	NP55N03SUG-E1-AZ	TO-252ZK	Single	N	30	± 55	2.17	1.99	1.81
879-NP55N04SUG-E1-AZ	NP55N04SUG-E1-AZ	TO-252ZK	Single	N	40	± 55	1.56	1.43	1.30
879-NP82N04PDG-E1-AZ	NP82N04PDG-E1-AZ	TO-263ZP	Single	N	40	± 82	2.99	2.74	2.49
879-NP82N06PDG-E1-AZ	NP82N06PDG-E1-AZ	TO-263ZP	Single	N	60	± 82	3.42	3.13	2.85
879-2SJ202-T1	2SJ202-T1-A	SC-70	Single	P	-16	-0.1	.14	.12	.11
879-2SJ243-T1	2SJ243-T1-A	SC-75	Single	P	-30	-0.1	.17	.16	.138
879-2SJ647-T1	2SJ647-T1-A	SC-70	Single	P	-20	-0.4	.21	.192	.181
879-2SJ648-T1	2SJ648-T1-A	SC-75	Single	P	-20	-0.4	.20	.18	.17
879-UPA650TT-E1	UPA650TT-E1-A	WSOF-6	Single	P	-12	-5	.41	.385	.353
879-UPA1816GR-9JG-E1	UPA1816GR-9JG-E1-A	TSSOP-8	Single	P	-12	-9	.83	.761	.697
879-NP100P06PDGE1-AZ	NP100P06PDG-E1-AZ	TO-263ZP	Single	P	-60	± 100	5.57	5.10	4.63
879-NP36P04KDG-E1-AZ	NP36P04KDG-E1-AZ	TO-263ZK	Single	P	-40	± 108	2.24	2.05	1.87
879-NP36P06KDG-E1-AZ	NP36P06KDG-E1-AZ	TO-263ZK	Single	P	-60	± 36	2.48	2.27	2.07
879-NP50P04KDG-E1-AZ	NP50P04KDG-E1-AZ	TO-263ZK	Single	P	-40	± 50	3.20	2.94	2.66
879-NP50P06KDG-E1-AZ	NP50P06KDG-E1-AZ	TO-263ZK	Single	P	-60	± 50	3.19	2.93	2.67
879-NP83P04PDG-E1-AZ	NP83P04PDG-E1-AZ	TO-263ZP	Single	P	-40	± 83	4.83	4.42	4.03
879-NP83P06PDG-E1-AZ	NP83P06PDG-E1-AZ	TO-263ZP	Single	P	-60	± 83	5.10	4.67	4.25
879-NP100P04PDGE1-AZ	NP100P04PDG-E1-AZ	TO-263ZP	Single	P	-40	± 100	5.26	4.82	4.21
879-UPA1970TE-T1	UPA1970TE-T1-A	SC-95	Dual	N	20	2.2	.46	.421	.387
879-UPA2755GR-E1	UPA2755GR-E1-A	SOP-8	Dual	N	30	8	.75	.695	.63
879-UPA672T-T1	UPA672T-T1-A	SC-88	Dual	N	50	0.1	.23	.214	.192
879-UPA677TB-T1	UPA677TB-T1-A	SC-88	Dual	N	20	0.35	.26	.23	.21
879-UPA1856GR-9JG-E1	UPA1856GR-9JG-E1-A	TSSOP-8	Dual	P	-20	-4.5	.99	.91	.83
879-UPA1890GR-9JG-E1	UPA1890GR-9JG-E1-A	TSSOP-8	Complementary	N/P	30	6	.83	.764	.70

ESD PROTECTION DIODES

- Ensured compliance with international ESD standard (IEC61000-4-2 Level 4)
- Low capacitance, suitable for high-speed signal lines

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	NEC Part No.	Package	Configuration	Ct (pF)	IR (uA)	ESD (min.) kV	Price Each		
							1	25	100
879-NSAD500F	NSAD500F-A	SC-59	Dual	3.5	0.1	8	.15	.14	.12
879-NSAD500H	NSAD500H-A	SC-88A	Quad	3.5	0.1	8	.35	.32	.29

USB DEVICES

- USB2.0 specification
- Supports connection to existing USB1.x devices
- 40 times faster than USB 1.x.

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	NEC Part No.	Package	Transfer Rate (USB 2.0)	Vdd (typ.)	Price Each		
					1	25	100
879-UPD720101GJ-UEN	UPD720101GJ-UEN-A	144 Pin LQFP	480Mbps	3.3 - 5.0	16.50	15.13	13.75
879-UPD720101F1-EA8	UPD720101F1-EA8-A	144 Pin FPBGA	480Mbps	3.3 - 5.0	13.71	12.57	11.43
879-UPD720112GK-9EU	UPD720112GK-9EU-A	4 port HUB	480Mbps	2.5 - 3.3	10.50	9.63	8.75
879-UPD720113GK-9EU	UPD720113GK-9EU-A	7 port HUB	480Mbps	2.5 - 3.3	16.20	14.85	13.50
879-UPD720114GA-9EU	UPD720114GA-9EU-A	4 port HUB	480Mbps	3.3	9.00	8.25	7.50