

AVAGO LED Displays



TECHNOLOGIES

For quantities of 1000 and up, call for quote.

AVAGO SMART LED DISPLAYS

MOUSER STOCK NO.	Avago Part No.	Character Count	Color	Interface	Character Height	Intensity (µcd)(Typ.)	Supply Current (mA)(Typ.)	Price Each			
								1	25	100	500
630-HDSP-0762	HDSP-0762	1	Red	-	7.4mm	140	78	46.55	29.79	27.93	25.14
630-HDSP-0772	HDSP-0772	1	Red	-	7.4mm	620	120	46.55	29.79	27.93	25.14
630-HDSP-0962	HDSP-0962	1	Green	-	7.4mm	1100	120	40.35	25.82	24.21	21.79
630-HDLO-2416	HDLO-2416	4	Red	Parallel	5.1mm	3.5	110	22.23	14.22	13.34	12.00
630-HDLS-2416	HDLS-2416	4	Red	Parallel	5.1mm	12.7	125	24.70	15.81	14.82	13.34
630-HCMS-2902	HCMS-2902	4	Red	Serial	3.7mm	64	132	26.65	17.06	15.99	14.39
630-HCMS-2912	HCMS-2912	4	Red	Serial	3.7mm	64	264	40.08	25.65	24.05	21.64
630-HCMS-2962	HCMS-2962	4	Red	Serial	4.6mm	64	132	27.43	17.55	16.46	14.81
630-HDSP-0760	HDSP-0760	4	Red	-	7.4mm	140	78	44.65	28.58	26.79	24.11
630-HCMS-2915	HCMS-2915	4	Red	Serial	3.7mm	230	290	44.75	28.64	26.85	24.17
630-HCMS-2965	HCMS-2965	4	Red	Serial	4.6mm	230	145	30.25	19.36	18.15	16.34
630-HDLY-2416	HDLY-2416	4	Yellow	Parallel	5.1mm	3.7	110	22.23	14.22	13.34	12.00
630-HCMS-2961	HCMS-2961	4	Yellow	Serial	4.6mm	64	132	27.43	17.55	16.46	14.81
630-HDLG-2416	HDLG-2416	4	Green	Parallel	5.1mm	5.6	110	22.23	14.22	13.34	12.00
630-HCMS-2903	HCMS-2903	4	Green	Serial	3.7mm	114	132	26.65	17.06	15.99	14.39
630-HCMS-2913	HCMS-2913	4	Green	Serial	3.7mm	114	264	40.08	25.65	24.05	21.64
630-HCMS-2963	HCMS-2963	4	Green	Serial	4.6mm	114	132	27.43	17.55	16.46	14.81
630-HDSP-2112	HDSP-2112	8	Red	Parallel	4.8mm	7.5	300	44.10	28.22	26.46	23.81
630-HDSP-2502	HDSP-2502	8	Red	Parallel	7mm	7.5	300	53.50	34.24	32.10	28.89
630-HDSP-2532	HDSP-2532	8	Red	Parallel	4.6mm	7.5	300	41.75	26.72	25.05	22.55
630-HDSP-2534	HDSP-2534	8	Red	Parallel	4.6mm	7.5	300	46.25	29.60	27.75	24.98
630-HCMS-2972	HCMS-2972	8	Red	Serial	4.6mm	64	264	41.75	26.72	25.05	22.55
630-HCMS-2975	HCMS-2975	8	Red	Serial	4.6mm	230	290	46.25	29.60	27.75	24.98
630-HDSP-2111	HDSP-2111	8	Yellow	Parallel	4.8mm	7.5	300	44.10	28.22	26.46	23.81
630-HDSP-2531	HDSP-2531	8	Yellow	Parallel	4.6mm	7.5	300	41.75	26.72	25.05	22.55
630-HCMS-2971	HCMS-2971	8	Yellow	Serial	4.6mm	64	264	41.75	26.72	25.05	22.55
630-HDSP-2113	HDSP-2113	8	Green	Parallel	4.8mm	7.5	300	44.10	28.22	26.46	23.81
630-HDSP-2133	HDSP-2133	8	Green	Parallel	4.8mm	7.5	300	160.70	140.62	135.59	131.58
630-HDSP-2503	HDSP-2503	8	Green	Parallel	7mm	7.5	300	53.50	34.24	32.10	28.89
630-HDSP-2533	HDSP-2533	8	Green	Parallel	4.6mm	7.5	300	41.75	26.72	25.05	22.55
630-HCMS-2973	HCMS-2973	8	Green	Serial	4.6mm	114	264	41.75	26.72	25.05	22.55
630-HCMS-2923	HCMS-2923	16	Green	Serial	3.7mm	114	528	89.05	56.99	53.43	48.09

AVAGO LED DISPLAYS

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Avago Part No.	Character Count	Color	Character Height	Pin Configuration	Intensity (µcd)(Typ.)	Supply Voltage	Price Each			
								1	25	100	500
630-HDSP-7511	HDSP-7511	1	Red	7.6mm	Common Anode	270	1.6	3.47	2.27	2.02	1.83
630-HDSP-7513	HDSP-7513	1	Red	7.6mm	Common Cathode	270	1.6	3.47	2.27	2.02	1.83
630-HDSP-A101	HDSP-A101	1	Red	7.6mm	Common Anode	600	1.6	3.63	2.38	2.11	1.91
630-HDSP-A103	HDSP-A103	1	Red	7.6mm	Common Cathode	600	1.6	3.63	2.38	2.11	1.91
630-5082-7610	5082-7610	1	Red	7.6mm	Common Anode	800	2.1	3.36	2.20	1.95	1.77
630-5082-7611	5082-7611	1	Red	7.6mm	Common Anode	800	2.1	3.36	2.20	1.95	1.77
630-5082-7613	5082-7613	1	Red	7.6mm	Common Cathode	800	2.1	3.36	2.20	1.95	1.77
630-5082-7616	5082-7616	1	Red	7.6mm	Overflow	800	-2.1	3.36	2.20	1.95	1.77
630-HDSP-7501	HDSP-7501	1	Red	7.6mm	Common Anode	980	2	3.03	1.98	1.76	1.60
630-HDSP-7501-CD000	HDSP-7501-CD000	1	Red	7.6mm	Common Anode	980	2	3.38	2.21	1.97	1.78
630-HDSP-7503	HDSP-7503	1	Red	7.6mm	Common Cathode	980	2	3.03	1.98	1.76	1.60
630-HDSP-7503-CD000	HDSP-7503-CD000	1	Red	7.6mm	Common Cathode	980	2	3.38	2.21	1.97	1.78
630-HDSP-A903	HDSP-A903	1	Green	7.6mm	Common Cathode	475	1.9	3.47	2.27	2.02	1.83
630-HDSP-3601	HDSP-3601	1	Green	7.6mm	Common Anode	2700	2.1	3.36	2.20	1.95	1.77
630-HDSP-3603	HDSP-3603	1	Green	7.6mm	Common Cathode	2700	2.1	3.36	2.20	1.95	1.77
630-HDSP-7801	HDSP-7801	1	Green	7.6mm	Common Anode	3000	2.1	3.03	1.98	1.76	1.60
630-HDSP-7803	HDSP-7803	1	Green	7.6mm	Common Cathode	3000	2.1	3.03	1.98	1.76	1.60
630-HDSP-F101	HDSP-F101	1	Red	10mm	Common Anode	650	1.6	3.63	2.38	2.11	1.91
630-HDSP-F103	HDSP-F103	1	Red	10mm	Common Cathode	650	1.6	3.63	2.38	2.11	1.91
630-HDSP-F201	HDSP-F201	1	Red	10mm	Common Anode	1200	2	3.03	1.98	1.76	1.60
630-HDSP-F203	HDSP-F203	1	Red	10mm	Common Cathode	1200	2	3.03	1.98	1.76	1.60
630-HDSP-F501	HDSP-F501	1	Green	10mm	Common Anode	3500	2.1	3.03	1.98	1.76	1.60
630-HDSP-F503	HDSP-F503	1	Green	10mm	Common Cathode	3500	2.1	3.03	1.98	1.76	1.60
630-HDSP-E101	HDSP-E101	1	Red	10.9mm	Common Anode	650	1.6	4.02	2.63	2.34	2.12
630-HDSP-E103	HDSP-E103	1	Red	10.9mm	Common Cathode	650	1.6	4.02	2.63	2.34	2.12
630-5082-7650	5082-7650	1	Red	10.9mm	Common Anode	1115	2.1	3.36	2.20	1.95	1.77
630-5082-7651	5082-7651	1	Red	10.9mm	Common Anode	1115	2.1	3.36	2.20	1.95	1.77
630-5082-7653	5082-7653	1	Red	10.9mm	Common Cathode	1115	2.1	3.36	2.20	1.95	1.77
630-5082-7656	5082-7656	1	Red	10.9mm	Overflow	1115	2.1	3.36	2.20	1.95	1.77
630-HDSP-4601	HDSP-4601	1	Green	10.9mm	Common Anode	4000	2.1	3.36	2.20	1.95	1.77
630-HDSP-4603	HDSP-4603	1	Green	10.9mm	Common Cathode	4000	2.1	3.36	2.20	1.95	1.77
630-HDSP-4603-IJ000	HDSP-4603-IJ000	1	Green	10.9mm	Common Cathode	4000	2.1	3.71	2.43	2.16	1.96
630-HDSP-5701	HDSP-5701	1	Yellow	14.2mm	Common Anode	1800	-2.1	2.75	1.80	1.60	1.45
630-HDSP-H151	HDSP-H151	1	Red	14.2mm	Common Anode	16	1.8	3.44	2.25	2.00	1.81
630-HDSP-H153	HDSP-H153	1	Red	14.2mm	Common Cathode	16	1.8	3.44	2.25	2.00	1.81
630-HDSP-5551	HDSP-5551	1	Red	14.2mm	Common Anode	370	2	3.16	2.07	1.84	1.67
630-HDSP-5553	HDSP-5553	1	Red	14.2mm	Common Cathode	370	2	3.16	2.07	1.84	1.67
630-HDSP-H101	HDSP-H101	1	Red	14.2mm	Common Anode	700	1.6	3.30	2.16	1.92	1.74
630-HDSP-H103	HDSP-H103	1	Red	14.2mm	Common Cathode	700	1.6	3.30	2.16	1.92	1.74
630-HDSP-5501	HDSP-5501	1	Red	14.2mm	Common Anode	2800	2.1	2.75	1.80	1.60	1.45
630-HDSP-5501-GH000	HDSP-5501-GH000	1	Red	14.2mm	Common Anode	2800	2.1	3.11	2.03	1.81	1.64
630-HDSP-5521	HDSP-5521	1	Red	14.2mm	Common Anode	2800	2.1	4.13	2.70	2.40	2.18
630-HDSP-5523	HDSP-5523	1	Red	14.2mm	Common Cathode	2800	2.1	4.13	2.70	2.40	2.18
630-HDSP-5503	HDSP-5503	1	Red	14.2mm	Common Cathode	2801	2.1	2.75	1.80	1.60	1.45
630-HDSP-5621	HDSP-5621	1	Green	14.2mm	Common Anode	2500	2.1	4.13	2.70	2.40	2.18
630-HDSP-5623	HDSP-5623	1	Green	14.2mm	Common Cathode	2500	2.1	4.13	2.70	2.40	2.18
630-HDSP-5601	HDSP-5601	1	Green	14.2mm	Common Anode	2800	2.1	2.75	1.80	1.60	1.45
630-HDSP-5603	HDSP-5603	1	Green	14.2mm	Common Cathode	2800	2.1	2.75	1.80	1.60	1.45
630-HDSP-3901	HDSP-3901	1	Red	20mm	Common Anode	7000	2.6	4.79	3.13	2.78	2.52
630-HDSP-3903	HDSP-3903	1	Red	20mm	Common Cathode	7000	2.6	4.79	3.13	2.78	2.52
630-HDSP-8601	HDSP-8601	1	Green	20mm	Common Anode	15000	2.1	4.79	3.13	2.78	2.52
630-HDSP-8603	HDSP-8603	1	Green	20mm	Common Cathode	15000	2.1	4.79	3.13	2.78	2.52
630-HDSP-521E	HDSP-521E	2	Red	14.2mm	Common Anode	2800	2.1	1.21	.79	.70	.64
630-HDSP-523E	HDSP-523E	2	Red	14.2mm	Common Cathode	2800	2.1	1.21	.79	.70	.64
630-HDSP-521G	HDSP-521G	2	Green	14.2mm	Common Anode	2500	2.1	1.21	.79	.70	.64
630-HDSP-523G	HDSP-523G	2	Green	14.2mm	Common Cathode	2500	2.1	1.21	.79	.70	.64