

Product Index

A

Adapters	
AC	1109, 1965, 2017, 2025, 2040-2054
Bluetooth	7, 57, 1245
D-Sub	1216, 1275, 1278, 1287
GPIO to USB	2114
I/O	1098, 1207, 1216, 1245
Modular	1207, 1238, 2123
Phono (RCA)	1094, 1096, 1151
RF	1096, 1150, 1157, 1159, 1161, 1163, 1165-1166, 1171, 1173-1177, 1179-1180, 1183, 1188-1190, 1192-1193
SMT	2168
Socket	231, 1163, 1495-1496
XLRL	1147, 1151
Alarms	614, 1077, 1822-1824, 2086, 2177
Alligator Clips	2102, 2118-2119, 2123
Alternistors	(See Semiconductors)
Amplifiers	(See Semiconductors)
Analog ICs	(See Semiconductors)
Antennas	5, 8, 10, 18-20, 26-28, 30, 40, 46, 48, 945, 1016-1019, 1220
Arrays	
Capacitor	628, 771, 808, 812
Resistor	623-630
Attenuators	1185, 1193, 1695
Audible Signal Devices	
Alarms	1822-1824
Benders	1825
Buzzers	1814-1817, 1822-1824
Earpieces	1818
Electret Condenser Microphone	1817-1818, 1827
Elements	1818, 1825
Hardware	1823
Indicators	1824, 1826
Piezo	1823-1825
Ringers	1816, 1823
Sirens	1824, 1829
Sonalerts	1822-1824
Speakers	1812, 1819-1821, 1823, 1828-1829
Transducers	1812, 1819, 1823, 1825, 1829
Automotive	
12VDC Jacks and Plugs	1095
Capacitors	773, 799-800, 821
Connectors	129, 1095, 1313, 1417-1418, 1486, 1501
LED	(See Illumination)
Relays	1728-1730, 1781-1782

B

Basic Stamp	50-51
Batteries	
1/2AA	2071-2072, 2076
1/3AA	2067
2/3AA	2067, 2073, 2076
2/3AA	2067, 2071-2072
4/5A	2067
AAAA	2066
A	2067, 2073, 2076
AA	2066-2068, 2072, 2075-2076
AAA	2066-2068, 2075
C	2066-2068, 2072-2073
D	2066-2068, 2072
F	2067
N	2066-2067
SC	2067-2068
9V	2066-2067, 2071, 2076
Alkaline	2066, 2075
Battery Packs	2067-2068, 2071-2072, 2076
Button Cell	2071, 2075
Calculator	2075
Camera	2075
Carbon Zinc	2066, 2075
Chargers	2067, 2069
Coin Cell	2071, 2073-2075
Computer	2075
Electronic	2075, 2098
Hearing Aid	2075
Lantern	2066
Lead Acid	2066, 2069-2070
Lithium	437, 2066, 2071-2076
Manganese Dioxide	2075
Memory Backup	2071-2072, 2076
Nickel-Cadmium	2066-2068
Nickel-Metal Hydride	2066-2068, 2071
Photo	2075
Pure Lead	2070
Rechargeable	2066-2071, 2073, 2076
Scooter	2066, 2069-2070
Silver-Oxide	2075
UPS	2021, 2031, 2060, 2066, 2069-2070
Watch	2075
Wheelchair	2066, 2069-2070
Zinc Chloride	2066

Battery Accessories

Analyzer	2070
Chargers	400, 424, 2021, 2067, 2069, 2076
Clips	2081, 2083
Holders	1920, 1932, 2074, 2078-2083
Indicator Labels	2083
Modular Contacts	2077
Snaps	1513, 2081-2082
Spring Contacts	2077, 2081, 2083, 2117
Binding Post	1135-1136, 1142, 1151, 1193, 1154, 2120
Blowers	1896, 1944
Bluetooth	7, 14, 23, 29, 48, 51, 57, 367-368, 921, 1018, 1245
Boxes	(See Enclosures)
Braid	2149, 2153, 2165
Breadboards	240, 2165-2172
Buzzers	1814-1817, 1822-1824

C

Cabinets	1893-1899, 1901
Cable	(See Wire and Cable)
Cable Assemblies	(See Wire and Cable)
Cable Ties	1025-1029, 1032-1035
Capacitors	
Aluminum Electrolytic	
5mm	761
7mm	746, 752, 762
Axial	747, 753-754, 756-757, 759-760, 763
BestCap™	739
Bi-Polar	722, 747, 752, 760
Computer Grade	738
Double Layer	739, 741, 744-745
Flatpack	732
General Purpose 85°C	719-720, 722-723, 728, 730, 732-734, 736-738, 746, 748, 752-753, 755-758, 761-763
High Capacitance	723, 727, 730-733, 737-739, 741, 752-753, 758
High Frequency	739
High Reliability	747, 750-751
High Ripple	721, 731-732, 736, 738, 747, 750, 760
High Temperature	719-721, 723-726, 729, 731, 734-735, 737, 739, 746-747, 749-751, 755-756, 759, 762
High Voltage	730-735, 737-738, 748-749, 753, 756-759, 763
Kit	743, 763
Low ESR	719, 724, 726-727, 732, 741, 747, 760
Low Impedance	719-721, 746, 750-751
Low Leakage	738, 756, 761
Memory Backup	739, 741, 744
Miniature	727, 754-757, 761
Mounting Hardware	733
Non-Polar	760, 762
Organic	724, 727
Polymer	724-727
Radial	726-727, 739, 741, 745-746, 748-752, 755, 758-763
Screw Terminal	732-733, 736, 738, 745
Snap Mount	728-731, 734-735, 737, 745
Supercapacitors	739, 741, 744
Surface Mount	719-727, 739, 741, 744
Ultracapacitors	742-743
Ceramic	
Arrays	771, 808, 812
Automotive	773, 799-800, 821
Axial	822
Broadband Blocks	783
Chip	764-811, 813-820
Conformal Coated	821-822, 824-827
Coupling	829, 832
Disc	829-830, 832-835
EMI Suppression	771-772
Fail-Safe	765-766
Feedthru	771-772
Floating-Electrode	765-766
Flexible Termination	764-770
Flexicap	767-769
Flexitem	764, 766-768
General Purpose	787-796, 801-803, 813-816
Half-Turn	891
High Capacitance	769, 771-772, 779, 785, 795-801, 804, 813-814, 821, 823-835
High Q	775, 783, 794-796
High Temperature	769-770, 772, 775-777, 779-782, 785-796, 801-806, 811, 820-821, 823-829, 831-832
High Voltage	764, 769-770, 776-778, 782, 786, 789, 804-805, 809-811, 817, 823-830, 832-835
Interdigitated	772
Kits	768, 779, 782-783, 785-786
Low ESL / Low ESR	772, 777, 794-796, 807-808
Molded	773, 823-824, 829
Multilayer	764-767, 769, 771-782, 784-806, 813-823, 826-827, 829, 831, 892
Multi-Turn Trimmer	889-892
Open-Mode	766, 768-770
Radial	821-835, 892
RF Microwave	775-776, 783
Surface Mount	764-820
Tin/Lead Termination	778, 784
Tip and Ring	774, 786, 804, 809
Trimmer	889-892
Feedthru (Arrays & Capacitors)	771-772, 954-956
Film	
Axial	840, 848-850, 856-857
Chip	837
DC Link	843-844
Dipped	839, 855
Film/Foil	850, 853-854
Kits	857
Metallized	
Box	846, 849, 856
Paper	847
Polycarbonate	850
Polyester	836-842, 846-851, 853, 856
Polyphenylene	847
Polypropylene	838, 840-841, 857
Non-Inductive	846-854, 857
Orange Drop	851
Polyester	836-842, 846-853, 855-856
Polypropylene	838, 840-841, 843-854, 857
Polystyrene	857
Radial	836-839, 841-843, 846-847, 849, 851-857
Snubbers	841-842, 845, 854
Suppression	842, 846-848
Surface Mount	836-837
Switching	843-844
High Reliability	747, 750-751
Mica	858-860
Mounting Hardware	733
RC Networks	628
Supercapacitors	739-745
Surface Mount	719-727, 739, 741, 744, 764-820, 836-837, 858-859, 861-880, 887, 889, 891, 943, 956, 1501
Tantalum	
Axial	884, 886-888
Dipped	881-883, 885
Fail-Safe Fused	875
Hermetically Sealed	884, 886
High Temperature	863, 865-866, 868-869, 871, 875, 888
Kits	868, 871, 874
Low ESR	861-863, 867-870
Low Profile	873-879, 884, 887
Niobium Oxide	870, 876-877
Polymer	861
Radial	865, 868-869
Radial	881-883, 885
Surface Mount	861-880, 887
Wet	887-888
Trimmer	889-892
Card Readers	331, 342, 1339-1340, 1346-1347, 1351, 1360
Cases	931, 950, 1899, 1904-1906, 1913-1917, 1924, 1932, 1936, 2093-2095, 2099-2100, 2102
CCFLs	130
Chassis	1894, 1896, 1899, 1913, 1915
Chemicals	
Adhesives	2152
Anti-Static Coating	2152
Bottles	2145, 2164
Circuit Board Repair Pens	2150, 2153
Cleaners	2149-2150, 2152-2153, 2158-2159, 2163-2164
Conformal Coating	2152, 2164
Dispensers	2145, 2150, 2160, 2164
Dusting Gas	2150, 2163
Epoxies	2153, 2164
Flux	2147-2148, 2163
Freezers	2150, 2163
Heat Sink Compound	1950, 1956, 2152, 2164
Leadcheck Tester	2150
Lubricant	1025, 2143, 2150, 2153, 2164-2165
Pumps	2164
Silicones	2164
Threadlocker	2165
Transistor Grease	2152
Wipes	2150-2153, 2163
Chokes/Coils	(See Inductors)
Circuit Board Indicators	(See Illumination)
Circuit Breakers	
Hydraulic/Magnetic	1805-1806, 1809
Push-to-Reset	1808-1809, 1811
Seals	1691
Thermal	1123, 1806-1811
Thermo Magnetic	1802-1803, 1807
Circuit Protection	
Circuit Breakers	1805-1811
DIN Rail	587, 1557, 1805, 1807, 1811, 2032, 2061
Filters	462, 552, 557-558, 567, 2032
Fuse Blocks	610-613, 621-622, 1557
Fuse Clips	610-613, 622
Fuse Holders	605, 610-613, 621-622, 1557
Fuses	593, 598-609, 614-620, 1557, 1808
Gas Discharge Tubes	580, 587-590, 597
Metal Oxide Varistors	582-586
ESD Devices	447, 462, 552, 556-558, 562, 565, 567-568, 576, 579, 603
Resettable Fuses	593, 598-603, 614
Surface Mount	561, 563-566, 569-571, 576, 578, 581, 589, 594-596, 598-599, 601-607, 614-615, 620
Surge Protectors	555-563, 565-566, 569-572, 575-578, 587-590, 597, 602, 2032, 2060-2061, 2063
Thermal Cutoffs	597
Thermistors	591-597
Thyristors	552, 564, 602
Varistors	575-586, 596
Voltage Suppressors	462, 471, 555, 558-566, 569-572, 575-578, 587-590, 2061
Cleaners	2149-2150, 2152-2153, 2158-2159, 2162-2164
Clips	
Alligator	2102, 2118-2119, 2123
Battery	2083
Fahnestock	1515
Heat Sink	1950
Test	2115, 2118-2124
Coils	(See Inductors)
Compiler Software	222, 242
Computers, Single Board	59-63
Connectors	
0.25mm	1385, 1439, 1446-1447, 1466-1467, 1487, 1503, 1530
0.30mm	166, 1126, 1129, 1443, 1447, 1487
0.40mm	1444, 1462
0.50mm	1214-1215, 1231, 1429, 1437-1438, 1443-1444, 1463, 1488, 1490
0.80mm	1210, 1215, 1229, 1414, 1424, 1445, 1487
1.00mm / .039"	1231, 1355, 1393, 1424, 1429, 1438, 1446, 1449
1.25mm / .049"	1385, 1439, 1446-1447, 1466-1467, 1503
1.27mm / .050"	1052, 1054-1055, 1214, 1230, 1249-1250, 1252, 1278, 1380, 1391-1393, 1399, 1424, 1434, 1469-1470, 1503
1.50mm / .059"	1231, 1385, 1462, 1468
2.00mm / .079"	1129, 1210, 1338, 1344-1345, 1348, 1353, 1359, 1381-1383, 1386, 1393, 1427, 1430-1433, 1435-1436, 1440-1442, 1449, 1467, 1471-1477, 1482-1483, 1503, 1538
2.13mm / .084"	1451
2.36mm / .093"	1413, 1452
2.50mm / .098"	1126, 1129, 1138, 1140, 1143, 1363, 1418, 1447, 1478, 1541-1542
2.54mm / .100"	1311, 1338, 1375-1380, 1383, 1389-1391, 1393-1402, 1419-1422, 1425-1426, 1428, 1445-1459, 1494, 1496, 1503-1506, 1536, 1538, 2117
3.00mm / .118"	1410, 1479-1481, 1527-1528, 1533, 1538
3.50mm / .137"	1138, 1140, 1143-1145, 1153, 1527-1528, 1530, 1533, 1536, 1540-1544
3.81mm / .150"	1418, 1