

JOHNSON Tip Plugs and Jacks, Test Jacks

RoHS Compliant This product is RoHS compliant.

TIP PLUGS

Insulated Solderless Type

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Johnson Components Part No.	Fig.	Amp	Max Wire	Color	Price Each					
						1	10	25	100	500	1000
530-105-0302-1	105-0302-001	A	10	16AWG	Red	.79	.69	.64	.54	.51	.45
530-105-0303-1	105-0303-001	A	10	16AWG	Black	.79	.69	.64	.54	.51	.45
530-105-0301-1	105-0301-001	A	10	16AWG	White	.79	.69	.64	.54	.51	.47
530-105-0304-1	105-0304-001	A	10	16AWG	Green	.79	.69	.64	.54	.51	.45
530-105-0310-1	105-0310-001	A	10	16AWG	Blue	.79	.69	.64	.54	.51	.45

Insulated Small Handle Type

For quantities of 5000 and up, call for quote.

530-105-0771-001	105-0771-001	B	10	16AWG	White	1.03	.93	.86	.79	.70	.65
530-105-0772-1	105-0772-001	B	10	16AWG	Red	.87	.77	.69	.62	.59	.53
530-105-0773-1	105-0773-001	B	10	16AWG	Black	.87	.77	.69	.62	.59	.545

TIP JACKS

Insulated Metal Clad Standard Type

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Johnson Components Part No.	Fig.	Amp	Panel Thickness	Color	Price Each					
						1	10	25	100	500	1000
530-105-0251-1	105-0251-001	C	10	Up to .281"	White	1.19	1.14	1.06	.98	.91	.86
530-105-0252-1	105-0252-001	C	10	Up to .281"	Red	1.05	.89	.79	.71	.66	.58
530-105-0253-1	105-0253-001	C	10	Up to .281"	Black	1.05	.89	.79	.71	.66	.58
530-105-0201-200	105-0201-200	C	10	Up to .281"	White	3.06	2.80	2.58	2.39	2.22	2.08
530-105-0202-200	105-0202-200	C	10	Up to .281"	Red	2.51	2.34	2.14	1.98	1.84	1.84
530-105-0203-200	105-0203-200	C	10	Up to .281"	Black	2.40	2.11	1.91	1.75	1.61	1.61
530-105-0204-200	105-0204-200	C	10	Up to .281"	Green	3.06	2.80	2.58	2.39	2.22	2.08

Insulated Standard

For quantities of 5000 and up, call for quote.

530-105-0802-1	105-0802-001	D	10	Up to .437"	Red	.69	.60	.53	.46	.42	.37
530-105-0803-1	105-0803-001	D	10	Up to .437"	Black	.69	.60	.53	.46	.42	.37
530-105-0801-1	105-0801-001	D	10	Up to .437"	White	.68	.60	.55	.47	.43	.41
530-105-0804-1	105-0804-001	D	10	Up to .437"	Green	.69	.60	.53	.46	.42	.37
530-105-0807-1	105-0807-001	D	10	Up to .437"	Yellow	.69	.60	.53	.46	.42	.37
530-105-0810-1	105-0810-001	D	10	Up to .437"	Blue	.66	.60	.54	.46	.42	.37

Insulated Standard Rib-Loc®

For quantities of 5000 and up, call for quote.

530-105-1042-1	105-1042-001	E	5	Up to .375"	Red	1.10	.97	.89	.78	.70	.65
530-105-1043-1	105-1043-001	E	5	Up to .375"	Black	1.10	.97	.89	.78	.70	.63
530-105-1041-1	105-1041-001	E	5	Up to .375"	White	1.10	.97	.89	.78	.70	.63
530-105-1044-1	105-1044-001	E	5	Up to .375"	Green	1.10	.97	.89	.78	.70	.66
530-105-1047-1	105-1047-001	E	5	Up to .375"	Yellow	1.10	.97	.89	.78	.70	.66
530-105-1050-1	105-1050-001	E	5	Up to .375"	Blue	1.52	1.35	1.08	.95	.92	.90

Insulated Deluxe

For quantities of 5000 and up, call for quote.

530-105-0602-1	105-0602-001	F	10	Up to .437"	Red	1.13	1.01	.91	.80	.74	.65
530-105-0603-1	105-0603-001	F	10	Up to .437"	Black	1.13	1.01	.91	.80	.74	.65
530-105-0601-1	105-0601-001	F	10	Up to .437"	White	1.13	1.01	.91	.80	.74	.65
530-105-0604-1	105-0604-001	F	10	Up to .437"	Green	1.13	1.01	.91	.80	.74	.68
530-105-0607-1	105-0607-001	F	10	Up to .437"	Yellow	.98	.89	.84	.79	.74	.68
530-105-0610-1	105-0610-001	F	10	Up to .437"	Blue	1.13	1.01	.91	.80	.74	.68

TEST JACKS

Horizontal Insulated Standard

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Johnson Components Part No.	Fig.	Amp	Pin Spacing	Color	Price Each					
						1	10	25	100	500	1000
530-105-0751-1	105-0751-001	G	5	.400"	White	.42	.36	.30	.26	.24	.22
530-105-0752-1	105-0752-001	G	5	.400"	Red	.42	.36	.30	.26	.24	.22
530-10507531	105-0753-001	G	5	.400"	Black	.42	.36	.30	.26	.24	.22
530-105-0754-1	105-0754-001	G	5	.400"	Green	.34	.30	.28	.27	.24	.22
530-105-0757-1	105-0757-001	G	5	.400"	Yellow	.34	.30	.28	.27	.23	.22
530-105-0756-1	105-0756-001	G	5	.400"	Orange	.42	.36	.30	.26	.24	.22
530-105-0758-1	105-0758-001	G	5	.400"	Brown	.42	.36	.30	.26	.24	.23
530-105-0760-1	105-0760-001	G	5	.400"	Blue	.34	.30	.28	.27	.24	.23
530-105-0762-1	105-0762-001	G	5	.400"	Violet	.42	.36	.30	.26	.24	.23
530-105-0763-1	105-0763-001	G	5	.400"	Gray	.38	.36	.35	.33	.323	.323

Horizontal Insulated Miniature

For quantities of 5000 and up, call for quote.

530-105-1101-1	105-1101-001	H	5	.200"	White	.42	.36	.30	.26	.24	.23
530-105-1102-1	105-1102-001	H	5	.200"	Red	.42	.36	.30	.26	.24	.23
530-105-1103-1	105-1103-001	H	5	.200"	Black	.42	.36	.30	.26	.24	.23
530-105-1104-1	105-1104-001	H	5	.200"	Green	.42	.36	.30	.26	.24	.23
530-105-1107-1	105-1107-001	H	5	.200"	Yellow	.42	.36	.30	.26	.24	.23
530-105-1110-1	105-1110-001	H	5	.200"	Blue	.42	.36	.30	.26	.24	.23

Vertical Insulated - Machined Contact

For quantities of 5000 and up, call for quote.

530-105-0851-1	105-0851-001	I	5	---	White	.61	.55	.49	.43	.38	.34
530-105-0852-1	105-0852-001	I	5	---	Red	.61	.55	.49	.43	.38	.34
530-105-0853-1	105-0853-001	I	5	---	Black	.61	.55	.49	.43	.38	.34

Vertical Insulated - Formed Contact

For quantities of 5000 and up, call for quote.

530-105-2201-1	105-2201-201	J	5	---	White	.56	.49	.47	.37	.35	.33
530-105-2202-1	105-2202-201	J	5	---	Red	.56	.49	.47	.37	.33	.31
530-105-2203-1	105-2203-201	J	5	---	Black	.56	.49	.47	.37	.33	.30

