

# JOHNSON Tip Plugs and Jacks, Test Jacks Johnson®

RoHS Compliant This product is RoHS compliant.

## TIP PLUGS

### Insulated Solderless Type

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Johnson Components Part No.	Fig.	Amp	Max Wire	Color	Price Each					
						1	10	25	100	500	1000
530-105-0302-1	105-0302-001	A	10	16AWG	Red	.82	.72	.671	.566	.535	.472
530-105-0303-1	105-0303-001	A	10	16AWG	Black	.92	.80	.746	.629	.594	.524
530-105-0301-1	105-0301-001	A	10	16AWG	White	.92	.80	.746	.629	.594	.548
530-105-0304-1	105-0304-001	A	10	16AWG	Green	.92	.80	.746	.629	.594	.524
530-105-0310-1	105-0310-001	A	10	16AWG	Blue	.92	.80	.746	.629	.594	.524

### Insulated Small Handle Type

For quantities of 5000 and up, call for quote.

530-105-0772-1	105-0772-001	B	10	16AWG	Red	.94	.83	.749	.673	.64	.575
530-105-0773-1	105-0773-001	B	10	16AWG	Black	1.03	.91	.818	.735	.70	.646

## TIP JACKS

### Insulated Metal Clad Standard Type

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Johnson Components Part No.	Fig.	Amp	Panel Thickness	Color	Price Each					
						1	10	25	100	500	1000
530-105-0251-1	105-0251-001	C	10	Up to .281"	White	1.52	1.46	1.35	1.25	1.16	1.10
530-105-0252-1	105-0252-001	C	10	Up to .281"	Red	1.55	1.31	1.16	1.04	.975	.856
530-105-0253-1	105-0253-001	C	10	Up to .281"	Black	1.55	1.31	1.16	1.04	.975	.856
530-105-0201-200	105-0201-200	C	10	Up to .281"	White	4.71	4.31	3.97	3.68	3.41	3.20
530-105-0202-200	105-0202-200	C	10	Up to .281"	Red	4.87	4.54	4.16	3.84	3.57	3.57
530-105-0203-200	105-0203-200	C	10	Up to .281"	Black	4.66	4.10	3.71	3.40	3.12	3.12
530-105-0204-200	105-0204-200	C	10	Up to .281"	Green	4.71	4.31	3.97	3.68	3.41	3.20

### Insulated Standard

For quantities of 5000 and up, call for quote.

530-105-0802-1	105-0802-001	D	10	Up to .437"	Red	.72	.63	.557	.484	.442	.389
530-105-0803-1	105-0803-001	D	10	Up to .437"	Black	.72	.63	.557	.484	.442	.389
530-105-0801-1	105-0801-001	D	10	Up to .437"	White	.76	.67	.617	.527	.482	.46
530-105-0804-1	105-0804-001	D	10	Up to .437"	Green	.77	.67	.595	.516	.471	.415
530-105-0807-1	105-0807-001	D	10	Up to .437"	Yellow	.78	.685	.605	.525	.479	.422
530-105-0810-1	105-0810-001	D	10	Up to .437"	Blue	.74	.67	.606	.516	.471	.415

### Insulated Standard Rib-Loc®

For quantities of 5000 and up, call for quote.

530-105-1042-1	105-1042-001	E	5	Up to .375"	Red	1.19	1.05	.956	.838	.752	.699
530-105-1043-1	105-1043-001	E	5	Up to .375"	Black	1.19	1.05	.956	.838	.752	.677
530-105-1041-1	105-1041-001	E	5	Up to .375"	White	1.19	1.05	.956	.838	.752	.677
530-105-1044-1	105-1044-001	E	5	Up to .375"	Green	1.10	.97	.89	.78	.70	.66
530-105-1047-1	105-1047-001	E	5	Up to .375"	Yellow	1.19	1.05	.956	.838	.752	.709
530-105-1050-1	105-1050-001	E	5	Up to .375"	Blue	1.52	1.35	1.08	.95	.92	.92

### Insulated Deluxe

For quantities of 5000 and up, call for quote.

530-105-0602-1	105-0602-001	F	10	Up to .437"	Red	1.30	1.16	1.05	.923	.853	.75
530-105-0603-1	105-0603-001	F	10	Up to .437"	Black	1.30	1.16	1.05	.923	.853	.75
530-105-0601-1	105-0601-001	F	10	Up to .437"	White	1.30	1.16	1.05	.923	.853	.75
530-105-0604-1	105-0604-001	F	10	Up to .437"	Green	1.30	1.16	1.05	.923	.853	.784
530-105-0607-1	105-0607-001	F	10	Up to .437"	Yellow	1.13	1.02	.969	.911	.853	.784
530-105-0610-1	105-0610-001	F	10	Up to .437"	Blue	1.30	1.16	1.05	.923	.853	.784

## TEST JACKS

### Horizontal Insulated Standard

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Johnson Components Part No.	Fig.	Amp	Pin Spacing	Color	Price Each					
						1	10	25	100	500	1000
530-105-0751-1	105-0751-001	G	5	.400"	White	.67	.57	.479	.415	.383	.351
530-105-0752-1	105-0752-001	G	5	.400"	Red	.67	.57	.479	.415	.383	.351
530-10507531	105-0753-001	G	5	.400"	Black	.67	.57	.479	.415	.383	.351
530-105-0754-1	105-0754-001	G	5	.400"	Green	.60	.53	.497	.479	.426	.39
530-105-0757-1	105-0757-001	G	5	.400"	Yellow	.85	.77	.71	.65	.61	.52
530-105-0756-1	105-0756-001	G	5	.400"	Orange	1.05	.905	.754	.653	.603	.553
530-105-0758-1	105-0758-001	G	5	.400"	Brown	.85	.77	.71	.65	.61	.57
530-105-0760-1	105-0760-001	G	5	.400"	Blue	.85	.77	.71	.65	.61	.589
530-105-0762-1	105-0762-001	G	5	.400"	Violet	1.05	.905	.754	.653	.603	.578
530-105-0763-1	105-0763-001	G	5	.400"	Gray	.61	.579	.563	.531	.519	.519

### Horizontal Insulated Miniature

For quantities of 5000 and up, call for quote.

530-105-1101-1	105-1101-001	H	5	.200"	White	.58	.50	.42	.364	.336	.322
530-105-1102-1	105-1102-001	H	5	.200"	Red	.58	.50	.42	.364	.336	.322
530-105-1103-1	105-1103-001	H	5	.200"	Black	.58	.50	.42	.364	.336	.322
530-105-1104-1	105-1104-001	H	5	.200"	Green	.58	.50	.42	.364	.336	.322
530-105-1107-1	105-1107-001	H	5	.200"	Yellow	.58	.50	.42	.364	.336	.322
530-105-1110-1	105-1110-001	H	5	.200"	Blue	.58	.50	.42	.364	.336	.322

### Vertical Insulated - Machined Contact

For quantities of 5000 and up, call for quote.

530-105-0851-1	105-0851-001	I	5	---	White	1.54	1.39	1.24	1.09	.964	.863
530-105-0852-1	105-0852-001	I	5	---	Red	1.30	1.18	1.09	1.00	.927	.80
530-105-0853-1	105-0853-001	I	5	---	Black	1.17	1.09	.997	.925	.867	.867

### Vertical Insulated - Formed Contact

For quantities of 5000 and up, call for quote.

530-105-2201-1	105-2201-201	J	5	---	White	.61	.53	.516	.406	.384	.362
530-105-2202-1	105-2202-201	J	5	---	Red	.61	.53	.516	.406	.362	.34
530-105-2203-1	105-2203-201	J	5	---	Black	.56	.49	.47	.37	.33	.30

