

AULT AC Adapters



This product is RoHS compliant.



AC INTERCHANGEABLE BLADE KIT

- For use with medical & commercial wall plug interchangeable
- For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Description	Price Each		
		1	10	25
831-KT1027K	Includes Europe, United Kingdom, Australian	4.63	4.28	4.13

CENB1010 SERIES, 10-12W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 12W
- No load Power Consumption <0.3W
- Limited Power Source



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Wall-Plug Models							
675-CENB1010A0503B01	CENB1010A0503B01	5V	2.00A	10.0W	15.23	14.88	14.53
675-CENB1010A0903B01	CENB1010A0903B01	9V	1.10A	10.0W	15.23	14.88	14.53
675-CENB1010A1203B01	CENB1010A1203B01	12V	1.00A	12.0W	15.23	14.88	14.53
675-CENB1010A2403B01	CENB1010A2403B01	24V	0.50A	12.0W	15.23	14.88	14.53
Desktop Modules (AC input cord not included)							
675-CENB1010A0503F01	CENB1010A0503F01	5V	2.00A	10.0W	14.80	14.46	14.12
675-CENB1010A0903F01	CENB1010A0903F01	9V	1.10A	10.0W	14.80	14.46	14.12
675-CENB1010A1203F01	CENB1010A1203F01	12V	1.00A	12.0W	14.80	14.46	14.12
675-CENB1010A2403F01	CENB1010A2403F01	24V	0.50A	12.0W	14.80	14.46	14.12

AC Input Cord		Description			Price Each		
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black	6.69	6.09	-			

CENB1020 SERIES, 15-20W SINGLE OUTPUT

- 100-240 VAC Universal Input Range
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 20W
- Modified and Custom Designs Available
- Regulated Output with Low Ripple
- No load Power Consumption <0.3W
- Limited Power Source



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Wall-Plug Models							
675-CENB1020A0503B01	CENB1020A0503B01	5V	3.00A	15.0W	17.22	16.82	16.42
675-CENB1020A0903B01	CENB1020A0903B01	9V	2.00A	18.0W	17.22	16.82	16.42
675-CENB1020A1203B01	CENB1020A1203B01	12V	1.50A	18.0W	17.22	16.82	16.42
675-CENB1020A2403B01	CENB1020A2403B01	24V	0.75A	18.0W	17.22	16.82	16.42
675-CENB1020A4803B01	CENB1020A4803B01	48V	0.40A	19.20W	17.22	16.82	16.42
Desktop Modules (AC input cord not included)							
675-CENB1020A0503F01	CENB1020A0503F01	5V	3.00A	15.0W	15.22	14.87	14.52
675-CENB1020A0903F01	CENB1020A0903F01	9V	2.00A	18.0W	15.22	14.87	14.52
675-CENB1020A1203F01	CENB1020A1203F01	12V	1.50A	18.0W	15.22	14.87	14.52
675-CENB1020A2403F01	CENB1020A2403F01	24V	0.75A	18.0W	15.22	14.87	14.52
675-CENB1020A4803F01	CENB1020A4803F01	48V	0.40A	19.20W	15.22	14.87	14.52

AC Input Cord		Description			Price Each		
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black	6.69	6.09	-			

CENB1030 SERIES, 20-32W SINGLE OUTPUT

- 100-240 VAC Universal Input
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 32W
- Regulated Output with Low Ripple
- No load Power Consumption <0.3W
- Limited Power Source



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Wall-Plug Models (AC Plug N. America/Japan)							
675-CENB1030A0503B01	CENB1030A0503B01	5V	4.00A	20.0W	20.20	19.74	19.27
675-CENB1030A0903B01	CENB1030A0903B01	9V	3.00A	27.0W	20.20	19.74	19.27
675-CENB1030A1203B01	CENB1030A1203B01	12V	2.50A	30.0W	20.20	19.74	19.27
675-CENB1030A2403B01	CENB1030A2403B01	24V	1.33A	31.9W	20.20	19.74	19.27
675-CENB1030A4803B01	CENB1030A4803B01	48V	0.67A	32.1W	20.20	19.74	19.27
Desktop Modules (AC input cord not included)							
675-CENB1030A0503F01	CENB1030A0503F01	5V	4.00A	20.0W	20.20	19.74	19.27
675-CENB1030A0903F01	CENB1030A0903F01	9V	3.00A	27.0W	20.20	19.74	19.27
675-CENB1030A1203F01	CENB1030A1203F01	12V	2.50A	30.0W	20.20	19.74	19.27
675-CENB1030A2403F01	CENB1030A2403F01	24V	1.33A	31.9W	20.20	19.74	19.27
675-CENB1030A4803F01	CENB1030A4803F01	48V	0.67A	32.1W	20.20	19.74	19.27

AC Input Cord		Description			Price Each		
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black	6.69	6.09	-			

CENB1040 SERIES, 25-40W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 40W
- No load Power Consumption <0.3W
- Limited Power Source
- Impact-Resistance Polycarbonate Enclosure
- Regulated Output with Low Ripple



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Desktop Modules (AC input cord not included)							
675-CENB1040A0503F01	CENB1040A0503F01	5V	5.00A	25.0W	22.36	21.84	21.33
675-CENB1040A0903F01	CENB1040A0903F01	9V	4.00A	36.0W	22.36	21.84	21.33
675-CENB1040A1203F01	CENB1040A1203F01	12V	3.40A	40.8W	22.36	21.84	21.33
675-CENB1040A2403F01	CENB1040A2403F01	24V	1.70A	40.8W	22.36	21.84	21.33
675-CENB1040A4803F01	CENB1040A4803F01	48V	0.83A	39.8W	22.36	21.84	21.33

AC Input Cord		Description			Price Each		
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black	6.69	6.09	-			

CENB1050 SERIES, 30-53W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- Desktop and Wall Plug Styles
- 5V to 48V Single Output Models, up to 53W
- No load Power Consumption <0.3W
- Limited Power Source



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Desktop Modules (AC input cord not included)							
675-CENB1050A0503F01	CENB1050A0503F01	5V	6A	30W	26.39	25.78	25.17
675-CENB1050A0903F01	CENB1050A0903F01	9V	5A	45W	26.39	25.78	25.17
675-CENB1050A1203F01	CENB1050A1203F01	12V	4.2A	50.4W	26.39	25.78	25.17
675-CENB1050A2403F01	CENB1050A2403F01	24V	2.1A	50.4W	26.39	25.78	25.17
675-CENB1050A4803F01	CENB1050A4803F01	48V	1.1A	52.8W	26.39	25.78	25.17
AC Input Cord							
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black	6.69	6.09	-			

CENB1060 SERIES, 35-64W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 64W
- No load Power Consumption <0.5W
- Modified and Custom Designs Available
- 2.5 Barrel Type Connector



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Desktop Modules (AC input cord not included)							
* 675-CENB1060A0551F01	CENB1060A0551F01	5V	7A	35W	29.25	28.57	27.90
675-CENB1060A0903F01	CENB1060A0903F01	9V	6A	54W	29.25	28.57	27.90
675-CENB1060A1203F01	CENB1060A1203F01	12V	5A	60W	29.25	28.57	27.90
675-CENB1060A2403F01	CENB1060A2403F01	24V	2.7A	64.8W	29.25	28.57	27.90
675-CENB1060A4803F01	CENB1060A4803F01	48V	1.3A	62.4W	29.25	28.57	27.90
AC Input Cord							
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black	6.69	6.09	-			

CENB1080 & CENB1090 SERIES, 78-90W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 12V to 48V Single Output Models, up to 90W
- No load Power Consumption <0.5W
- Limited Power Source
- Modified and Custom Designs Available
- 2.5 Barrel Type Connector



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Desktop Modules (AC input cord not included)							
* 675-CENB1080A1251F01	CENB1080A1251F01	12V	6.5A	78W	50.21	49.05	47.89
675-CENB1080A2403F01	CENB1080A2403F01	24V	3.25A	78W	50.21	49.05	47.89
675-CENB1080A4803F01	CENB1080A4803F01	48V	1.65A	79.2W	50.21	49.05	47.89
* 675-CENB1090A1251F01	CENB1090A1251F01	12V	7A	84W	61.18	59.77	58.36
675-CENB1090A2403F01	CENB1090A2403F01	24V	3.75A	90W	61.18	59.77	58.36
675-CENB1090A4803F01	CENB1090A4803F01	48V	1.9A	90W	61.18	59.77	58.36
AC Input Cord							
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black	6.69	6.09	-			

CENB1100 SERIES, 90-101W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- Desktop Styles
- 12V to 48V Single Output Models, up to 120W
- No load Power Consumption <0.5W
- IPX Compliant
- 2.5 Barrel Type Connector



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Desktop Modules (AC input cord not included)							
* 675-CENB1100A1251F01	CENB1100A1251F01	12V	7.50A	90.0W	66.67	65.13	63.59
675-CENB1100A2403F01	CENB1100A2403F01	24V	4.20A	101.0W	66.67	65.13	63.59
675-CENB1100A4803F01	CENB1100A4803F01	48V	2.10A	101.0W	66.67	65.13	63.59
AC Input Cord							
173-63101-E	7' 6" AC input cord, 3-wire input, 18AWG, Black	6.69	6.09	-			

CENB1120 SERIES, 120W SINGLE OUTPUT

- 100-240VAC Universal Input
- IPX1 Compliant
- Complies with EMI/RFI Regulations
- Impact Resistant, Non-Vented Polycarbonate Enclosure
- 3 year warranty
- Meets ENERGY STAR Criteria level IV and EISA Requirements
- 2.5 Barrel Type Connector

