

# VECTOR Extender Cards and Prototype Accessories



## VECTORBORD® GENERAL PURPOSE EXTENDER CARDS

- Low insertion force
- Gold-plated contacts
- Current Rating: 5 amps @ 10°F rise
- Voltage Rating: 200 RMS or 300 VDC

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Extension Length (In.)	Description		Price Each	
				Contacts	Spacing	1	10
574-3690	3690	A	6.5	22 each side	.156"	40.43	37.80
574-3690-16	3690-16	B	6.5	28 each side	.125"	48.04	44.91
<b>Bus Extenders</b>							
574-3690-22	3690-22	C	5.7	IBM PC, XT, 31 contacts each side	.100"	77.82	72.95
574-3690-26	3690-26	D	5.6	IBM AT-ISA, 18/31 contacts ea. side	.100"	76.98	71.98

## PROTOTYPE ACCESSORIES

### Pins and Terminals

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Description	Package Quantity	Price Each
<b>Press-In Terminals for .042" Holes</b>					
Insertion Tool: 574-P133A					
574-T46-2-9/M	T46-2-9/M	E	A=.36", B=.42"	1000	95.85
574-T46-3-9/C	T46-3-9/C	E	A=.46", B=.60"	100	16.63
574-T46-3-9/M	T46-3-9/M	E	A=.46", B=.60"	1000	113.79
574-T46-4-9/C	T46-4-9/C	E	A=.04", B=.42"	100	10.45
574-T46-4-9/M	T46-4-9/M	E	A=.04", B=.42"	1000	104.45
<b>Bifurcated Miniwrap Terminals for .042" Holes</b>					
Insertion Tool: 574-A13 or 574-A13-1					
574-T44/C	T44/C	F	Max. .021" leads or 24 AWG wires	100	11.55
574-T44/M	T44/M	F	Max. .021" leads or 24 AWG wires	1000	66.50
574-T68/C	T68/C	G	Max. .032" leads or 20 AWG wires	100	10.71
574-T68/M	T68/M	G	Max. .032" leads or 20 AWG wires	1000	63.14
<b>Trifurcated Klipwrap Terminals for .042" Holes</b>					
Insertion Tool: 574-P156					
574-T49/C	T49/C	H	Wirewrap tail with 3-prong receptacle	100	16.09
<b>Press-In Pins for .042" Holes</b>					
Insertion Tool: 574-P133A					
574-K24A/M	K24A/M	I	A=.255", B=.375", gold plated	1000	110.69
574-K24C/M	K24C/M	I	A=.255", B=.375", tin plated	1000	69.65
574-K30C/M	K30C/M	J	A=.255", B=.305", tin plated	1000	59.75
574-K31C/M	K31C/M	J	A=.160", B=.195", tin plated	1000	46.50
<b>Push-In Terminals for .042" Holes</b>					
Insertion Tool: 574-P149 or 574-P149A					
574-T42-1/C	T42-1/C	K	Horizontal slot holds up to 7 wires	100	11.19
574-T42-1/M	T42-1/M	K	Horizontal slot holds up to 7 wires	1000	53.74
<b>Push-In Terminals for .062" Holes</b>					
Insertion Tool: 574-P91A					
574-T28/C	T28/C	L	Vert. slot holds .025" leads/22 AWG wires	100	10.97
574-T28/M	T28/M	L	Vert. slot holds .025" leads/22 AWG wires	1000	71.42
<b>Wire-wrap Socket Pins for .042" Holes</b>					
Insertion Tool: 574-P158					
574-R32/C	R32/C	M	Pressfit mounting, 4-finger contacts	100	38.38

### Insertion Tools for Pins and Terminals

MOUSER STOCK NO.	Vector Part No.	For Use With	Price Each
574P133A	P133A	Press-In Terminals and Pins for .042" Holes	75.28
574-A13	A13	Bifurcated Miniwrap Terminals for .042" Holes	26.94
574-P149	P149	Push-In Terminals for .042" Holes	27.99
574-P149A	P149A	Push-In Terminals for .042" Holes	40.25

### Tefzel Insulated Silver Plated Wire

This wire is designed to be used with wire wrap terminals. Spool diameter is 1".

- Two 50' Spools Per Package

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	AWG	Color	Price Per Package
574-W28-6A	W28-6A	28	Green	22.28
574-W28-6B	W28-6B	28	Red	24.74
574-W28-6D	W28-6D	28	Blue	22.38
574-W28-6E	W28-6E	28	White	23.37
574-W28-6F	W28-6F	28	Yellow	21.11
574-W28-6H	W28-6H	28	Black	22.28

### Solder Eyelets and Bus Strips

For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Description	Package Quantity	Price Per Package
574-T123/500	T123/500	N	Solder eyelets for .055" holes	500	33.18
574-T107/C	T107/C	O	.08" x 14" solder-coated bus strips	100	108.92

