

BIVAR LED Mounts and Light Pipes



Bivar LED Indication

RoHS Compliant This product is RoHS compliant.

BIVAR RIGHT ANGLE LIGHT PIPES



BIVAR LED MOUNTING HARDWARE CONT.

Single Station

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Color	LED Size	Mounting Style	Price Each			
					1	10	100	500
749-RLP1-200-500	RLP1-200-500	White	2.8mm	SMD	.84	.77	.67	.63
749-RLP1-200-650	RLP1-200-650	White	2.8mm	SMD	.85	.78	.67	.64
749-RLP1-200-800	RLP1-200-800	White	2.8mm	SMD	.86	.79	.68	.65
749-RLP1-400-500	RLP1-400-500	White	2.8mm	SMD	.84	.779	.669	.639
749-RLP1-400-650	RLP1-400-650	White	2.8mm	SMD	.85	.789	.679	.639
749-RLP1-400-800	RLP1-400-800	White	2.8mm	SMD	.87	.801	.69	.65
749-RLP1-600-500	RLP1-600-500	White	2.8mm	SMD	.84	.77	.67	.63
749-RLP1-600-650	RLP1-600-650	White	2.8mm	SMD	.85	.78	.67	.64
749-RLP1-600-800	RLP1-600-800	White	2.8mm	SMD	.86	.79	.68	.65

Black Nylon

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Dia.	Pin Spacing	Overall Height	Price Each			
					1	10	100	500
749-LTM-120	LTM-120	0.2	0.1	0.12	.22	.17	.12	.097
749-LTM-150	LTM-150	0.2	0.1	0.15	.22	.17	.11	.081
749-LTM-200	LTM-200	0.2	0.1	0.2	.22	.17	.11	.081
749-LTM-250	LTM-250	0.2	0.1	0.25	.23	.17	.13	.10
749-LTM-300	LTM-300	0.2	0.1	0.3	.23	.17	.13	.10
749-LTM-350	LTM-350	0.2	0.1	0.35	.23	.17	.13	.10
749-LTM-400	LTM-400	0.2	0.1	0.4	.24	.18	.12	.089
749-LTM-450	LTM-450	0.2	0.1	0.45	.24	.18	.12	.089
749-LTM-500	LTM-500	0.2	0.1	0.5	.26	.20	.14	.115

Double Station

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Color	LED Size	Mounting Style	Price Each			
					1	10	100	500
749-RLP2-200-500	RLP2-200-500	White	2.8mm	SMD	1.05	.96	.83	.78
749-RLP2-200-650	RLP2-200-650	White	2.8mm	SMD	1.06	.97	.83	.79
749-RLP2-200-800	RLP2-200-800	White	2.8mm	SMD	1.06	.98	.84	.80
749-RLP2-400-500	RLP2-400-500	White	2.8mm	SMD	1.06	.97	.84	.79
749-RLP2-400-650	RLP2-400-650	White	2.8mm	SMD	1.06	.978	.839	.799
749-RLP2-400-800	RLP2-400-800	White	2.8mm	SMD	1.07	.989	.849	.809
749-RLP2-600-500	RLP2-600-500	White	2.8mm	SMD	1.05	.96	.83	.78
749-RLP2-600-650	RLP2-600-650	White	2.8mm	SMD	1.06	.97	.83	.79
749-RLP2-600-800	RLP2-600-800	White	2.8mm	SMD	1.06	.98	.84	.80

BIVAR LED PANEL CLIPS

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Color	Size	Desc.	Price Each			
					1	10	100	500
749-C-103-SR	C-103-SR	Black	T1	1 Piece	.36	.27	.20	.16
749-CR-104	CR-104	Black	T1	2 Piece	.26	.20	.144	.115
749-C-105-SR	C-105-SR	Black	T1-3/4	1 Piece	.21	.158	.117	.094
749-CR-174	CR-174	Black	T1-3/4	2 Piece	.26	.20	.144	.115
749-CR-174L	CR-174L	Black	T1-3/4	2 Piece	.30	.23	.166	.133
749-CR-175	CR-175	Black	T1-3/4	2 Piece	.26	.20	.144	.115
749-CR-300	CR-300	Black	RWXD	2 Piece	.38	.32	.30	.28

Triple Station

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Color	LED Size	Mounting Style	Price Each			
					1	10	100	500
749-RLP3-200-500	RLP3-200-500	White	2.8mm	SMD	1.18	1.08	.93	.88
749-RLP3-200-650	RLP3-200-650	White	2.8mm	SMD	1.18	1.08	.93	.88
749-RLP3-200-800	RLP3-200-800	White	2.8mm	SMD	1.22	1.12	.96	.91
749-RLP3-400-500	RLP3-400-500	White	2.8mm	SMD	1.18	1.08	.939	.889
749-RLP3-400-650	RLP3-400-650	White	2.8mm	SMD	1.21	1.11	.96	.91
749-RLP3-400-800	RLP3-400-800	White	2.8mm	SMD	1.22	1.12	.969	.919
749-RLP3-600-500	RLP3-600-500	White	2.8mm	SMD	1.18	1.08	.939	.889
749-RLP3-600-650	RLP3-600-650	White	2.8mm	SMD	1.21	1.11	.96	.91
749-RLP3-600-800	RLP3-600-800	White	2.8mm	SMD	1.22	1.12	.969	.919

BIVAR RIGID LIGHT ROPES

Flat Face

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Dia.	Color	Height	Price Each			
					1	10	100	500
749-PLP1-125-F	PLP1-125-F	0.118	Clear	0.125	.73	.41	.29	.25
749-PLP1-250-F	PLP1-250-F	0.118	Clear	0.25	.73	.41	.29	.25
749-PLP1-350-F	PLP1-350-F	0.118	Clear	0.35	.42	.37	.241	.205
749-PLP1-500-F	PLP1-500-F	0.118	Clear	0.5	.73	.41	.29	.25
749-PLP1-750-F	PLP1-750-F	0.118	Clear	0.75	.42	.37	.241	.205

Flat Face - Vertical

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Dia.	Color	Height	Price Each			
					1	10	100	500
749-VLP-250-F	VLP-250-F	0.118	Clear	0.25	.26	.20	.14	.115
749-VLP-350-F	VLP-350-F	0.118	Clear	0.35	.28	.21	.16	.124
749-VLP-550-F	VLP-550-F	0.118	Clear	0.55	.30	.23	.17	.133

Quad Station

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Color	LED Size	Mounting Style	Price Each			
					1	10	100	500
749-RLP4-200-500	RLP4-200-500	White	2.8mm	SMD	1.37	1.26	1.08	1.02
749-RLP4-200-650	RLP4-200-650	White	2.8mm	SMD	1.37	1.26	1.08	1.02
749-RLP4-200-800	RLP4-200-800	White	2.8mm	SMD	1.41	1.30	1.11	1.06
749-RLP4-400-500	RLP4-400-500	White	2.8mm	SMD	1.37	1.26	1.08	1.02
749-RLP4-400-650	RLP4-400-650	White	2.8mm	SMD	1.40	1.29	1.11	1.05
749-RLP4-400-800	RLP4-400-800	White	2.8mm	SMD	1.41	1.30	1.11	1.06
749-RLP4-600-500	RLP4-600-500	White	2.8mm	SMD	1.37	1.26	1.08	1.02
749-RLP4-600-650	RLP4-600-650	White	2.8mm	SMD	1.40	1.29	1.11	1.05
749-RLP4-600-800	RLP4-600-800	White	2.8mm	SMD	1.40	1.29	1.11	1.05

Low Profile

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Dia.	Color	Height	Price Each			
					1	10	100	500
749-PLP2-125	PLP2-125	0.112	Clear	0.125	.73	.41	.29	.25
749-PLP2-250	PLP2-250	0.112	Clear	0.25	.73	.41	.29	.25
749-PLP2-350	PLP2-350	0.112	Clear	0.35	.73	.41	.29	.25
749-PLP2-375	PLP2-375	0.112	Clear	0.375	.73	.41	.29	.25
749-PLP2-500	PLP2-500	0.112	Clear	0.5	.73	.41	.29	.25
749-PLP2-625	PLP2-625	0.112	Clear	0.625	.73	.41	.29	.25
749-PLP2-750	PLP2-750	0.112	Clear	0.75	.73	.41	.29	.25
749-PLP5-2-250	PLP5-2-250	0.152	Clear	0.25	.73	.41	.29	.25
749-PLP5-2-500	PLP5-2-500	0.152	Clear	0.5	.73	.41	.29	.25
749-PLP5-2-625	PLP5-2-625	0.152	Clear	0.625	.73	.41	.29	.25
749-PLP5-2-750	PLP5-2-750	0.152	Clear	0.75	.73	.63	.41	.35

BIVAR LED MOUNTING HARDWARE

Natural Nylon - Round

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Dia.	Pin Spacing	Overall Height	Price Each			
					1	10	100	500
749-450-050	450-050	0.25	0.1	0.05	.30	.22	.168	.135
749-450-060	450-060	0.25	0.1	0.06	.30	.22	.168	.135
749-450-120	450-120	0.25	0.1	0.12	.30	.22	.168	.135
749-450-200	450-200	0.25	0.1	0.2	.30	.22	.168	.135
749-455-250	455-250	0.25	0.1	0.25	.30	.22	.168	.135
749-455-300	455-300	0.25	0.1	0.3	.30	.22	.168	.135
749-455-350	455-350	0.25	0.1	0.35	.30	.22	.168	.135
749-456-500	456-500	0.25	0.1	0.5	.30	.22	.168	.135

Round Face

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Dia.	Color	Height	Price Each			
					1	10	100	500
749-PLP1-125	PLP1-125	0.118	Clear	0.125	.73	.63	.41	.35
749-PLP1-250	PLP1-250	0.118	Clear	0.25	.42	.37	.241	.205
749-PLP1-375	PLP1-375	0.118	Clear	0.375	.42	.37	.241	.205
749-PLP1-500	PLP1-500	0.118	Clear	0.5	.42	.37	.241	.205
749-PLP1-625	PLP1-625	0.118	Clear	0.625	.73	.63	.41	.35
749-PLP1-750	PLP1-750	0.118	Clear	0.75	.73	.63	.41	.35

Round Face - Vertical

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Dia.	Color	Height	Price Each			
					1	10	100	500
749-VLP-250-R	VLP-250-R	0.118	Clear	0.25	.26	.20	.14	.115
749-VLP-300-R	VLP-300-R	0.118	Clear	0.3	.26	.20	.14	.115
749-VLP-350-R	VLP-350-R	0.118	Clear	0.35	.28	.21	.16	.124
749-VLP-450-R	VLP-450-R	0.118	Clear	0.45	.28	.21	.16	.124

Natural Nylon - Square

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Bivar Part No.	Dia.	Pin Spacing	Overall Height	Price Each			
					1	10	100	500
749-460-060	460-060	0.18 sq	0.1	0.06	.30	.22	.168	.135
749-460-100	460-100	0.18 sq	0.1	0.1	.30	.22	.168	.135
749-460-110	460-110	0.18 sq	0.1	0.11	.30	.22	.168	.135
749-460-120	460-120	0.18 sq	0.1	0.12	.30	.22	.168	.135
749-460-200	460-200	0.18 sq	0.1	0.2	.30	.22	.168	.135
749-461-380	461-380	0.18 sq	0.1	0.38	.30	.22	.168	.135
749-465-250	465-250	0.18 sq						