

RoHS Compliant Prototype Kits

RoHS Compliant

PROTOTYPING KIT HARDWARE

MOUSER STOCK NO.	Type	Pieces in Each Kit	Description	Price Each
Keystone Prototyping Hardware Kits				
534-1721	Staking Tool Kit	6	2 1/4 staking tools, 2 bottom anvils, 1 tool holder, 1 instruction	44.24
534-4732	TO-3 Transistor Mnt.	4	2 #6-20 screws, 1 mica insulator, 1 Stock No. 534-4602 transistor socket	2.12
534-4734	TO-3 Transistor Mnt.	8	2 #6-20 screws, 1 mica insulator, 4 nylon bushings, 1 Stock No. 534-4606 transistor socket	2.33
534-4616	Transistor Mount	1	Nylon power transistor mount only for TO-3	.20
534-4725	TO-3 Transistor Mount	12	1 ea.: mica insulator, solder terminal; 2 ea.: #6-32 screws, shoulder washers, metal washers	1.20
534-4729	Transistor Mount	5	For DO-4, TO-59, TO-60, TO-62 - 1 ea each: mica insulator, shoulder washer, solder terminal, lockwasher, #10-32 nut+D97	1.20
534-4730	Transistor Mount	5	For DO-5, TO-48, TO-61 - 1 ea.: mica insulator, shoulder washer, solder terminal, lockwasher, 1/4-28 nut	1.38
534-4724	TO-220 Transistor Mnt.	5	1 ea each: #4-40 screw, mica insulator, shoulder washer, lockwasher, #4-40 nut	1.20
Eagle Plastic Devices Prototyping Hardware Kits				
561-M1991	Transistor Hardware, Nylon	180	20 ea each: capacitor mounts - 561-F001, 561-F002, 561-F003 assortment of 14 styles of standard and heavy duty power transistor mounts for TO-3 and TO-66	32.16
561-M1992	Spacers/Standoffs, Nylon	290	30 ea each: hex spacers - tapped 440, 632, 832 diameter, 1/4" to 1" long; 35 ea each: round spacers - tapped 440, 632, 832, 1032, 1/4-20, 1/4", 5/16", 3/8", 1/2" diameter, 1/4" to 1" long; 45 ea each: hex male/female standoffs - threaded 440, 632, 832 diameter, 1/4" to 1" long; 80 ea each: hex spacers - plain 1/4" to 1" long; 100 ea each: round spacers - plain 3/16", 1/4", 3/8", 1/2" diameters, 1/8" to 1" long	50.46
561-M1993	Shoulder Washers, Nylon	320	10 ea each: 5/16 screw insulators; 25 ea each: #6, #8, #10, 1/4 screw insulators; 30 ea each: #2, #4 screw insulators; 150 ea each: shoulder washers .093 to 1/4" ID .125 to .500 OD	32.16
561-M1994	PCB Posts, Nylon	735	40 ea each: 561-A0750; 50 ea each: 561-A0625; 60 ea each: 561-A0500; 65 ea each: 561-A1000; 70 ea each: 561-A0437; 80 ea each: 561-A0375; 95 ea each: 561-A0312; 100 ea each: 561-A0125, 561-A0250	52.96
561-M1995	Cable Clips, Nylon	140	Adhesive backed clips - 4 ea each: 1/2" single, 1/2" double; 6 ea each: 3/8" single, 3/8" double; 10 ea each: 1/4" single, 1/4" double; 12 ea each: 1/8" single, 1/8" double Heavy duty clips - 6 ea each: 1/2"; 12 ea each: 1/8", 3/16", 1/4", 5/16", 3/8", 7/16"	32.16
561-M1996	Cable Clamps, Nylon	300	3 ea each: 1 1/4" x 1/2", 1 1/2" x 1/2"; 5 ea each: 1" x 1/2"; 10 ea each: 1/2" x 1/2", 9/16" x 1/2", 5/8" x 1/2", 3/4" x 1/2"; 15 ea each: 5/16" x 1/2", 3/8" x 1/2", 7/16" x 1/2"; 20 ea each: 5/16" x 3/8", 3/8" x 3/8", 7/16" x 3/8", 1/2" x 3/8"; 25 ea each: 3/16" x 1/2", 1/4" x 1/2", 1/4" x 3/8"; 40 ea each: 1/8" x 1/8"	52.96
561-M1997	Flat Washers, Nylon	510	20 ea each: 1/2"; 40 ea each: 3/8"; 50 ea each: #2; 60 ea each: #4, #6, #8, #10, 1/4"; 100 ea each: 9/16" to 3/4"	30.64
561-M1998	Screws and Nuts, Nylon	755	100 ea each: 440 x 1/4" to 1" long assorted headstyles 623 x 1/4" to 5/8" long assorted headstyles 832 x 1/4" to 3/4" long assorted headstyles 1032 x 1/4" to 1/2" long assorted headstyles 440, 632, 832, 1032, 1/4-20 socket set screws 440, 632, 832, 1032, 1/4-20 hex nuts; 30 ea each: 1/4-20 x 1/4" to 3/4" long round and fillister head; 125 ea each: #4, #6, #8, #10, 1/4 flat washer	50.46
561-M1999	Strain Relief	108	2 ea each: 561-MP7W2, 561-30-1; 4 ea each: 561-MP6N4; 6 ea each: 561-MP6P34; 8 ea each: 561-MP14L1, MP15L1; 10 ea each: 561-MP4K4, 561-MP4N4, 561-MP5P4; 12 ea each: 561-MP6W1; 16 ea each: 561-MP3P4; 20 ea each: 561-MP2M4	33.07

BOURNS HIGH Q INDUCTOR KITS

MOUSER STOCK NO.	Pieces in Each Kit	Description	Price Each
652-CW160808-LAB1	540	30 ea each: 4.7, 6.8, 8.2, 10, 12, 15, 18, 22, 27, 33, 39, 47, 56, 68, 82, 100, 150, 220	163.96
652-CW201212-LAB1	450	25 ea each: 12, 15, 22, 33, 47, 100, 150, 220, 330, 470, 1000, 1500, 2200, 3300, 4700	163.96
652-CW252016-LAB1	300	20 ea each: 2.2, 3.3, 4.7, 6.8, 8.2, 10, 15, 22, 33, 47, 68, 100, 150, 220, 330, 470, 680, 91	99.23

KINGBRIGHT LED KITS

MOUSER STOCK NO.	Description	Quantity	Values Contained in Kit	Price Each		
				1	3	5
370-KBTBLINK	Blinking T-1 (3mm) and T-1-3/4 (5mm) LED Lamps	25 Pieces each of 6 Values	565nm - 700nm	104.95	99.95	94.95
370-KBTBLWH	Blue and White LED Lamps in assorted sizes	10 Pieces each of 16 Values	Blue and White	288.95	279.95	272.95
370-KBTDUALCLR	Dual Color LED Lamps in assorted sizes	10 Pieces each of 11 Values	Dual Color, Varies	39.95	37.95	35.95
370-KBTRECTAN	Rectangular LED Lamps	10 Pieces each of 9 Values	565nm - 700nm	14.95	13.95	12.95
370-KBTSBT1347113	Super Bright T-1-3/4 (5mm) LED Lamps	10 Pieces each of 26 Values	565nm - 660nm	91.95	85.95	79.95
370-KBTSBT17104	Super Bright T-1 (3mm) LED Lamps	10 Pieces each of 23 Values	565nm - 660nm	75.95	69.95	63.95
370-KBTSPRFLUX	Super Flux LED Lamps	25 Pieces each of 6 Values	Fluctuating	96.95	92.95	88.95
370-KBTSTD48VL	Standard T-1 (3mm) and T-1-3/4 (5mm) LED Lamps	10 Pieces each of 48 Values	555nm - 700nm	64.95	61.95	57.95
370-KBTSTDT1T134	Standard T-1 (3mm) and T-1-3/4 (5mm) LED Lamps	10 Pieces each of 34 Values	555nm - 700nm	37.95	35.95	33.95
370-KBTT1341571	Standard T-1-3/4 (5mm) LED Lamps	10 Pieces each of 18 Values	Varies	18.95	17.95	16.95
370-KBTT1WP1704	Standard T-1 (3mm) LED Lamps	10 Pieces Each of 15 Values	555nm - 700nm	19.95	18.95	17.95
370-KBTXBRITE	X-Brite T-1 (3mm) and T-1-3/4 (5mm) LED Lamps	10 Pieces each of 12 Values	Varies	189.95	184.95	179.95

KYCON CONNECTOR KITS

MOUSER STOCK NO.	Description	Quantity	Styles Included	Price Each		
				1	3	5
370-KYCDCCON	DC Power Connectors in various styles	3 Pieces each of 11 Items in 4 Styles	Standard, Mini, and Snap & Lock	29.95	28.95	27.95
370-KYCSJTACK	Stereo Jacks in various styles	27 Pieces of 10 Items	PCB Mount, Surface Mount, and Stacked	35.95	34.95	33.95
370-KYCMODJACK	Modular Jacks in various sizes	2 Pieces each of 12 items	Right Angle, Low Profile, and with LEDs	35.95	34.95	33.95