


Circuit Diagram



PCB Hole Layout

**Dimensions (In.)**  
(except where noted)

**Specifications:**

- Type: 1/4" mono phone w/switch
- Contact resistance: 30mΩ max.
- Insulation resistance: 100MΩ min. @ 250VAC
- Dielectric strength: 250VAC for 1 minute
- Insertion & extraction force: .3Kg~2Kg
- Operating temperature: -10°~+70°C
- Life: 10,000 cycles