




Circuit Diagram



PCB Hole Layout

Dimensions (In.) (except where noted)

Specifications:

- Type: 1/4" stereo phone w/switch
- Contact resistance: 30m Ω max.
- Insulation resistance: 100M Ω min. @ 250VAC
- Dielectric strength: 250VAC for 1 minute
- Insertion & extraction force: .3Kg~2Kg
- Operating temperature: -10°~+70°C
- Life: 10,000 cycles