




Dimensions (In.)

Specifications:

- Pin size (A): $\varnothing 2\text{mm}$ (163-4302), $\varnothing 2.35$ (163-4303)
- Contact resistance: $30\text{m}\Omega$ max.
- Insulation resistance: $100\text{M}\Omega$ min. @ 250VDC
- Breakdown voltage: 250VAC for 1 minute
- Rated current: 0.5A @ 12/24V
- Body: ABS
- Pin: nickel plated brass
- Contact spring: silver plated copper/zinc/aluminum alloy
- Terminals: silver plated brass
- Insulator: Phenol 94HB
- Nut: Polymid 12.5mm P=1