
**Dimensions (In.)****Specifications:**

- Type: 5 pin square DIN
- Rating: 12VDC 1A max., 100VAC 1A
- Insulation resistance: 50M Ω min. @ 250VDC
- Dielectric strength: 250VAC for 1 minute
- Contact: silver plated brass
- Metal sleeve: nickel plated brass
- Insulator & outer hood: UL94UV-2 nylon